

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927552

Luminaire Tested: DFN2DIP-HX4F0-040D120US840-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927552
REPORT IS A COMBINATION OF REPORTS P900963 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D120US840-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15995.2 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 129.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927552

CATALOG NUMBER: DFN2DIP-HX4F0-040D120US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927552

CATALOG NUMBER: DFN2DIP-HX4F0-040D120US840-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	51	51	51	33	33	33
1	92	88	84	81	82	79	75	73	61	59	57	44	43	42	29	29	28
2	84	77	71	66	74	69	64	59	53	50	47	39	37	35	26	25	24
3	76	67	60	55	68	60	54	50	47	43	39	34	32	30	23	21	20
4	70	60	52	46	62	53	47	42	42	37	33	31	28	25	20	19	17
5	64	53	45	39	57	47	41	36	37	32	29	27	24	22	18	16	15
6	59	47	40	34	52	42	36	31	33	28	25	25	21	19	17	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	38	31	26	45	35	28	24	27	23	19	20	17	15	14	12	10
9	47	35	28	23	41	31	25	21	25	20	17	19	15	13	13	11	9
10	43	32	25	20	39	29	23	19	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1169	1169	1169
5°	1171	1152	1160
10°	1161	1137	1145
15°	1144	1118	1120
20°	1121	1093	1095
25°	1098	1062	1066
30°	1070	1033	1029
35°	1043	999	990
40°	1009	964	953
45°	976	930	915
50°	939	894	871
55°	901	852	831
60°	858	802	784
65°	811	751	730
70°	751	688	671
75°	668	614	617
80°	569	518	513
85°	413	353	341

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2101 cd/sqm

TEST NUMBER: P927552

CATALOG NUMBER: DFN2DIP-HX4F0-040D120US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	147.9	0.9
10°-20°	416.2	2.6
20°-30°	611.7	3.8
30°-40°	710.4	4.4
40°-50°	709.5	4.4
50°-60°	618.7	3.9
60°-70°	457.3	2.9
70°-80°	258.8	1.6
80°-90°	75.5	0.5
90°-100°	134.8	0.8
100°-110°	502.7	3.1
110°-120°	1333.2	8.3
120°-130°	2211.3	13.8
130°-140°	2348.9	14.7
140°-150°	2183.0	13.6
150°-160°	1755.1	11.0
160°-170°	1130.9	7.1
170°-180°	389.2	2.4
0°-30°	1175.8	7.4
0°-40°	1886.2	11.8
0°-60°	3214.4	20.1
0°-90°	4006.0	25.0
90°-120°	1970.8	12.3
90°-150°	8714.0	54.5
90°-180°	11989.0	75.0
0°-180°	15995.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1572	1572	1572	1572	1572	
5°	1572	1566	1549	1561	1558	149
15°	1496	1487	1467	1474	1466	421
25°	1354	1342	1316	1319	1316	623
35°	1168	1153	1129	1120	1112	730
45°	951	940	917	901	895	734
55°	720	710	692	674	667	643
65°	485	476	461	447	440	480
75°	254	251	243	234	237	271
85°	62	60	59	54	53	69
90°	3	35	59	74	80	15
95°	192	94	115	130	127	228
105°	900	988	181	213	225	961
115°	1701	1752	1826	456	243	1675
125°	2406	2444	2501	2521	2530	2146
135°	2977	3024	3051	3081	3075	2300
145°	3454	3450	3501	3521	3506	2160
155°	3802	3776	3812	3829	3806	1752
165°	4007	3989	3998	4019	3998	1132
175°	4098	4078	4084	4104	4075	390
180°	4090	4090	4090	4090	4090	

TEST NUMBER: P927552

CATALOG NUMBER: DFN2DIP-HX4F0-040D120US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1571.7	1571.7	1571.7	1571.7	1571.7
2.5°	1580.8	1573.3	1556.6	1571.7	1568.8
5°	1571.7	1565.7	1549.0	1561.0	1558.2
7.5°	1561.0	1552.1	1535.4	1547.6	1544.6
10°	1544.6	1534.0	1515.9	1527.9	1523.4
12.5°	1521.8	1512.8	1494.7	1502.3	1499.1
15°	1496.1	1487.1	1467.4	1473.5	1466.0
17.5°	1464.4	1455.4	1435.7	1443.2	1435.7
20°	1429.6	1420.6	1399.5	1403.9	1398.1
22.5°	1394.9	1381.3	1361.6	1361.6	1358.6
25°	1354.0	1342.0	1316.4	1319.3	1316.4
27.5°	1308.7	1298.1	1278.6	1274.1	1266.6
30°	1263.5	1251.3	1228.7	1224.2	1218.1
32.5°	1215.1	1206.1	1181.9	1172.8	1166.6
35°	1168.2	1153.2	1129.0	1119.9	1112.3
37.5°	1115.3	1101.7	1077.5	1067.0	1059.4
40°	1061.0	1048.8	1024.5	1011.1	1005.1
42.5°	1008.1	995.9	971.8	956.6	947.6
45°	950.6	940.1	917.3	900.8	894.7
47.5°	894.7	884.1	859.9	843.3	834.3
50°	835.7	828.1	807.0	785.8	778.3
52.5°	778.3	767.8	748.2	731.5	720.9
55°	719.5	710.3	692.2	674.0	666.6
57.5°	660.4	652.9	633.1	615.1	609.0
60°	601.4	595.5	574.4	557.7	553.2
62.5°	544.1	533.5	518.4	503.3	497.2
65°	485.2	476.0	461.0	447.3	439.9
67.5°	424.7	417.0	403.6	393.0	387.0
70°	368.8	362.7	349.1	338.5	332.5
72.5°	311.4	305.3	297.8	287.2	282.6
75°	253.9	250.9	243.3	234.3	237.3
77.5°	202.5	196.4	193.4	188.8	184.4
80°	151.2	149.6	146.5	142.1	139.0
82.5°	102.8	102.8	101.4	95.2	95.2
85°	61.9	60.5	59.0	54.3	52.9
87.5°	27.3	24.2	21.2	16.7	15.0
90°	2.8	35.4	59.1	74.1	79.8
92.5°	74.1	62.2	71.0	76.9	79.8
95°	192.2	94.5	115.2	130.4	127.2
97.5°	346.2	103.7	150.8	159.9	162.7
100°	523.9	118.4	168.6	192.2	198.2
102.5°	719.0	713.3	174.6	207.0	216.1
105°	899.5	988.5	180.7	213.0	224.9
107.5°	1109.7	1183.5	186.6	218.9	230.8
110°	1311.0	1372.9	517.9	222.1	233.7

TEST NUMBER: P927552

CATALOG NUMBER: DFN2DIP-HX4F0-040D120US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1500.5	1553.5	1503.3	227.7	236.8
115°	1701.4	1751.7	1825.8	455.7	242.9
117.5°	1876.1	1935.2	1985.8	1562.3	787.1
120°	2071.5	2115.7	2169.2	2204.7	1805.1
122.5°	2237.0	2284.5	2343.8	2361.4	2364.5
125°	2405.6	2444.3	2500.6	2521.3	2530.1
127.5°	2559.5	2601.0	2645.7	2675.2	2678.0
130°	2704.6	2752.1	2784.4	2817.1	2814.3
132.5°	2852.6	2891.3	2923.6	2950.3	2947.5
135°	2977.0	3024.5	3050.8	3080.7	3074.7
137.5°	3107.1	3142.5	3172.4	3201.9	3193.1
140°	3234.3	3258.1	3290.4	3317.2	3302.4
142.5°	3341.0	3361.8	3400.1	3423.6	3408.9
145°	3453.5	3450.4	3500.6	3521.4	3506.5
147.5°	3550.9	3542.1	3592.4	3607.1	3595.5
150°	3645.7	3625.0	3672.4	3690.0	3675.3
152.5°	3725.5	3701.9	3746.3	3764.1	3743.4
155°	3802.4	3776.0	3811.6	3829.2	3805.6
157.5°	3864.6	3841.1	3867.8	3888.5	3864.6
160°	3918.0	3900.2	3918.0	3935.6	3914.9
162.5°	3965.2	3947.6	3962.4	3983.1	3956.4
165°	4006.6	3989.0	3997.8	4018.6	3997.8
167.5°	4039.3	4021.3	4030.5	4051.2	4024.6
170°	4066.0	4048.1	4054.0	4074.7	4048.1
172.5°	4083.5	4066.0	4072.0	4092.7	4066.0
175°	4098.3	4077.6	4083.5	4104.3	4074.7
177.5°	4104.3	4083.5	4086.8	4107.5	4080.8
180°	4089.6	4089.6	4089.6	4089.6	4089.6

TEST NUMBER: P927552

CATALOG NUMBER: DFN2DIP-HX4F0-040D120US840-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.87	5.55	6.02	6.68	8.27	4.44	5.11	5.59	6.25	7.84
	3H	6.52	7.12	7.67	8.27	9.87	6.05	6.65	7.20	7.79	9.40
	4H	7.10	7.67	8.26	8.81	10.42	6.62	7.20	7.79	8.34	9.95
	6H	7.49	8.02	8.66	9.16	10.78	7.01	7.54	8.18	8.69	10.31
	8H	7.59	8.09	8.76	9.25	10.86	7.11	7.62	8.29	8.78	10.39
	12H	7.63	8.11	8.81	9.26	10.90	7.15	7.63	8.33	8.78	10.41
4H	2H	5.31	5.88	6.48	7.03	8.64	4.97	5.54	6.14	6.68	8.29
	3H	7.16	7.64	8.34	8.81	10.43	6.77	7.25	7.94	8.42	10.04
	4H	7.87	8.31	9.04	9.47	11.10	7.46	7.90	8.64	9.06	10.70
	6H	8.37	8.75	9.55	9.93	11.56	7.96	8.34	9.14	9.52	11.15
	8H	8.52	8.87	9.70	10.04	11.69	8.11	8.46	9.29	9.63	11.28
	12H	8.58	8.90	9.78	10.08	11.73	8.16	8.48	9.36	9.66	11.31
8H	4H	8.05	8.40	9.23	9.57	11.22	7.69	8.04	8.87	9.21	10.86
	6H	8.67	8.97	9.87	10.18	11.82	8.31	8.60	9.51	9.82	11.46
	8H	8.89	9.15	10.10	10.34	12.00	8.53	8.78	9.73	9.97	11.63
	12H	9.02	9.24	10.23	10.43	12.12	8.63	8.86	9.84	10.04	11.74
12H	4H	8.03	8.35	9.22	9.53	11.18	7.67	7.99	8.87	9.18	10.83
	6H	8.70	8.96	9.91	10.15	11.81	8.35	8.60	9.56	9.80	11.46
	8H	8.94	9.16	10.15	10.35	12.04	8.58	8.80	9.79	9.99	11.68

END OF REPORT