

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913547

Luminaire Tested: DFN2DIP-HX3F0-070D080US927-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913547
REPORT IS A COMBINATION OF REPORTS P899280 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D080US927-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10322.1 lumens
Efficiency: N/A
Efficacy: 79.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 130.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913547

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US927-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913547

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US927-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2655	2655	2655
5°	2658	2611	2628
10°	2630	2558	2541
15°	2593	2471	2407
20°	2544	2353	2244
25°	2493	2221	2086
30°	2426	2086	1887
35°	2360	1940	1712
40°	2293	1790	1511
45°	2216	1623	1329
50°	2135	1456	1152
55°	2051	1276	981
60°	1953	1089	806
65°	1841	899	724
70°	1705	722	653
75°	1533	633	591
80°	1285	525	508
85°	878	342	373

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2216 cd/sqm

TEST NUMBER: P913547

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US927-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	214.8	2.1
10°-20°	589.7	5.7
20°-30°	827.9	8.0
30°-40°	902.4	8.7
40°-50°	829.4	8.0
50°-60°	651.4	6.3
60°-70°	424.0	4.1
70°-80°	218.2	2.1
80°-90°	61.4	0.6
90°-100°	124.0	1.2
100°-110°	394.1	3.8
110°-120°	674.4	6.5
120°-130°	886.9	8.6
130°-140°	995.5	9.6
140°-150°	976.2	9.5
150°-160°	818.9	7.9
160°-170°	543.1	5.3
170°-180°	189.8	1.8
0°-30°	1632.3	15.8
0°-40°	2534.7	24.6
0°-60°	4015.5	38.9
0°-90°	4719.1	45.7
90°-120°	1192.5	11.6
90°-150°	4051.1	39.2
90°-180°	5603.0	54.3
0°-180°	10322.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2292	2292	2292	2292	2292	
5°	2292	2282	2254	2273	2267	217
15°	2180	2157	2086	2047	2026	614
25°	1979	1912	1775	1690	1659	910
35°	1705	1599	1417	1286	1240	1067
45°	1394	1255	1037	890	840	1076
55°	1060	898	674	550	510	947
65°	716	548	361	290	284	709
75°	382	236	166	151	149	404
85°	89	46	39	39	39	102
90°	2	22	59	56	57	10
95°	88	105	108	108	105	98
105°	364	369	372	375	375	384
115°	677	686	683	682	677	669
125°	984	999	995	989	987	880
135°	1273	1292	1296	1294	1289	984
145°	1546	1558	1567	1569	1563	966
155°	1767	1772	1778	1786	1781	813
165°	1923	1921	1921	1933	1924	542
175°	2001	1996	1992	2004	1994	190
180°	2004	2004	2004	2004	2004	

TEST NUMBER: P913547

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US927-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2291.9	2291.9	2291.9	2291.9	2291.9
2.5°	2302.2	2291.9	2269.0	2289.9	2285.7
5°	2291.9	2281.5	2254.5	2273.2	2267.0
7.5°	2273.2	2260.8	2231.8	2239.9	2229.6
10°	2248.3	2233.8	2192.4	2186.0	2173.7
12.5°	2217.2	2198.5	2142.5	2130.1	2107.2
15°	2179.8	2157.0	2086.5	2047.2	2026.5
17.5°	2136.3	2103.1	2015.9	1970.3	1937.1
20°	2086.5	2044.9	1941.3	1889.6	1843.8
22.5°	2032.7	1984.9	1864.5	1794.1	1763.1
25°	1978.7	1912.2	1775.4	1690.4	1659.2
27.5°	1914.5	1843.8	1692.4	1595.0	1547.2
30°	1846.0	1767.0	1601.1	1495.5	1439.4
32.5°	1779.6	1684.1	1514.2	1389.6	1337.7
35°	1704.9	1599.1	1416.7	1286.0	1240.2
37.5°	1632.4	1518.1	1325.4	1182.1	1130.4
40°	1555.5	1431.2	1229.9	1082.7	1028.7
42.5°	1476.8	1344.1	1134.6	981.0	929.3
45°	1393.8	1254.7	1037.1	889.7	839.9
47.5°	1315.0	1167.8	943.8	796.4	750.8
50°	1227.9	1080.7	852.5	709.2	665.9
52.5°	1142.7	987.1	765.3	628.4	589.1
55°	1059.8	898.0	674.0	549.7	510.3
57.5°	974.9	808.9	593.3	477.1	443.9
60°	887.7	721.8	508.1	402.5	369.2
62.5°	802.7	636.8	435.5	336.0	319.5
65°	715.6	547.5	360.9	290.5	284.1
67.5°	632.6	464.5	290.5	255.0	248.9
70°	545.5	383.7	240.5	219.8	211.4
72.5°	462.6	309.0	201.1	184.7	180.5
75°	381.6	236.3	165.9	151.4	149.4
77.5°	300.8	167.9	130.7	122.3	118.2
80°	226.0	120.3	99.5	91.3	91.3
82.5°	157.6	81.0	68.4	64.2	64.2
85°	89.1	45.6	39.4	39.4	39.4
87.5°	33.2	16.5	16.5	14.5	14.5
90°	1.8	21.8	59.3	55.6	57.4
92.5°	37.5	50.8	52.6	54.3	54.3
95°	88.2	105.1	108.1	108.1	105.1
97.5°	146.9	162.6	169.2	169.2	169.2
100°	214.5	228.4	233.2	233.2	231.4
102.5°	285.8	296.1	302.7	304.5	302.7
105°	363.8	368.6	372.2	375.3	375.3
107.5°	441.1	448.4	448.4	449.6	441.1
110°	516.0	525.7	525.7	525.7	520.9

TEST NUMBER: P913547

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US927-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	597.0	607.3	605.5	600.6	597.0
115°	676.8	686.4	683.4	681.6	676.8
117.5°	755.9	769.2	760.7	755.9	751.1
120°	835.7	849.0	835.7	835.7	830.2
122.5°	908.2	925.1	916.6	911.8	908.2
125°	984.3	999.4	994.6	989.1	987.4
127.5°	1058.7	1077.4	1070.7	1063.5	1058.7
130°	1128.1	1149.9	1146.8	1143.3	1136.6
132.5°	1206.1	1223.0	1224.2	1215.8	1210.9
135°	1273.1	1291.9	1295.5	1293.7	1288.9
137.5°	1348.1	1363.2	1366.2	1365.0	1357.7
140°	1414.0	1429.0	1437.5	1437.5	1430.8
142.5°	1481.6	1496.7	1501.6	1503.4	1496.7
145°	1545.7	1557.7	1567.4	1569.2	1562.6
147.5°	1603.1	1618.2	1625.4	1628.5	1621.8
150°	1662.3	1672.5	1679.2	1684.7	1679.2
152.5°	1714.8	1725.1	1733.6	1740.3	1733.6
155°	1767.4	1772.3	1777.7	1786.1	1780.7
157.5°	1812.7	1816.4	1819.4	1831.4	1823.0
160°	1853.2	1856.9	1858.7	1868.9	1861.7
162.5°	1890.7	1890.7	1892.5	1904.0	1895.5
165°	1922.7	1920.9	1920.9	1933.0	1924.5
167.5°	1951.7	1946.3	1946.3	1958.4	1949.9
170°	1973.5	1968.6	1966.8	1978.9	1968.6
172.5°	1988.6	1983.8	1982.0	1994.0	1983.8
175°	2000.7	1995.8	1992.2	2004.3	1994.0
177.5°	2007.3	2002.5	1998.8	2009.1	1998.8
180°	2004.3	2004.3	2004.3	2004.3	2004.3

TEST NUMBER: P913547

CATALOG NUMBER: DFN2DIP-HX3F0-070D080US927-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.08	10.88	11.08	11.88	13.22	6.06	6.85	7.06	7.86	9.19
	3H	11.75	12.46	12.76	13.47	14.83	7.24	7.95	8.25	8.97	10.32
	4H	12.35	13.02	13.37	14.04	15.40	7.68	8.36	8.71	9.38	10.74
	6H	12.76	13.38	13.80	14.41	15.78	8.00	8.62	9.03	9.64	11.02
	8H	12.88	13.47	13.92	14.51	15.88	8.09	8.68	9.13	9.72	11.09
	12H	12.94	13.50	13.98	14.53	15.93	8.13	8.69	9.17	9.72	11.11
4H	2H	10.09	10.77	11.12	11.79	13.15	6.64	7.32	7.67	8.34	9.70
	3H	11.91	12.47	12.95	13.52	14.89	7.99	8.55	9.02	9.59	10.97
	4H	12.60	13.11	13.64	14.15	15.54	8.53	9.04	9.57	10.08	11.48
	6H	13.10	13.54	14.16	14.60	16.00	8.94	9.38	9.99	10.44	11.84
	8H	13.27	13.68	14.33	14.74	16.14	9.07	9.48	10.12	10.53	11.94
	12H	13.36	13.73	14.43	14.80	16.21	9.13	9.50	10.20	10.57	11.98
8H	4H	12.56	12.97	13.61	14.02	15.43	8.80	9.21	9.86	10.27	11.67
	6H	13.12	13.45	14.19	14.55	15.96	9.31	9.65	10.39	10.75	12.15
	8H	13.33	13.62	14.41	14.70	16.13	9.50	9.80	10.58	10.88	12.30
	12H	13.46	13.72	14.55	14.80	16.26	9.61	9.87	10.70	10.95	12.42
12H	4H	12.51	12.88	13.58	13.95	15.36	8.80	9.17	9.88	10.24	11.66
	6H	13.09	13.39	14.18	14.47	15.89	9.36	9.66	10.44	10.74	12.16
	8H	13.30	13.57	14.39	14.64	16.11	9.56	9.82	10.65	10.90	12.37