

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927586

Luminaire Tested: DFN2DIP-HX4F0-050D110US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927586
REPORT IS A COMBINATION OF REPORTS P900948 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D110US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15288.3 lumens
Efficiency: N/A
Efficacy: 116.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 130.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927586

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927586

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	44	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	29	27	26
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	48	63	55	49	44	43	39	35	33	30	28	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	26	24	21	19	17
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	24	24	21	19	17	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1552	1552	1552
5°	1554	1527	1537
10°	1539	1497	1487
15°	1518	1448	1410
20°	1490	1380	1315
25°	1461	1304	1223
30°	1423	1225	1107
35°	1385	1141	1005
40°	1347	1054	888
45°	1303	957	782
50°	1257	860	679
55°	1209	755	579
60°	1153	646	477
65°	1089	535	429
70°	1012	432	389
75°	915	381	353
80°	774	320	307
85°	541	214	231

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1925 cd/sqm

TEST NUMBER: P927586

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	1.3
10°-20°	536.9	3.5
20°-30°	753.8	4.9
30°-40°	821.7	5.4
40°-50°	755.2	4.9
50°-60°	593.1	3.9
60°-70°	386.0	2.5
70°-80°	198.7	1.3
80°-90°	57.3	0.4
90°-100°	123.6	0.8
100°-110°	460.8	3.0
110°-120°	1222.1	8.0
120°-130°	2027.0	13.3
130°-140°	2153.1	14.1
140°-150°	2001.1	13.1
150°-160°	1608.8	10.5
160°-170°	1036.7	6.8
170°-180°	356.8	2.3
0°-30°	1486.2	9.7
0°-40°	2307.9	15.1
0°-60°	3656.2	23.9
0°-90°	4298.3	28.1
90°-120°	1806.5	11.8
90°-150°	7987.8	52.2
90°-180°	10990.0	71.9
0°-180°	15288.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2077	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1616	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1142	944	810	765	980
55°	965	818	614	500	465	862
65°	652	498	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	3	32	54	68	73	14
95°	176	87	106	120	117	209
105°	825	906	166	195	206	881
115°	1560	1606	1674	418	223	1535
125°	2205	2241	2292	2311	2319	1967
135°	2729	2772	2796	2824	2818	2108
145°	3166	3163	3209	3228	3214	1980
155°	3486	3461	3494	3510	3488	1606
165°	3673	3657	3665	3684	3665	1038
175°	3757	3738	3743	3762	3735	358
180°	3749	3749	3749	3749	3749	

TEST NUMBER: P927586

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2086.8	2086.8	2086.8	2086.8	2086.8
2.5°	2096.1	2086.8	2065.9	2084.9	2081.1
5°	2086.8	2077.4	2052.7	2069.7	2064.1
7.5°	2069.7	2058.5	2032.0	2039.5	2030.0
10°	2047.1	2033.8	1996.2	1990.4	1979.1
12.5°	2018.8	2001.8	1950.7	1939.5	1918.6
15°	1984.8	1964.0	1899.8	1864.0	1845.1
17.5°	1945.1	1914.9	1835.5	1794.0	1763.7
20°	1899.8	1862.0	1767.6	1720.5	1678.8
22.5°	1850.8	1807.2	1697.7	1633.6	1605.3
25°	1801.6	1741.1	1616.5	1539.1	1510.7
27.5°	1743.1	1678.8	1541.0	1452.2	1408.8
30°	1680.8	1608.9	1457.8	1361.6	1310.5
32.5°	1620.3	1533.4	1378.7	1265.3	1218.0
35°	1552.4	1456.0	1289.9	1170.9	1129.3
37.5°	1486.2	1382.3	1206.8	1076.3	1029.3
40°	1416.3	1303.1	1119.8	985.8	936.7
42.5°	1344.6	1223.8	1033.0	893.2	846.1
45°	1269.1	1142.5	944.3	810.1	764.7
47.5°	1197.3	1063.3	859.3	725.1	683.6
50°	1118.1	983.9	776.2	645.8	606.3
52.5°	1040.5	898.8	696.9	572.3	536.4
55°	965.0	817.6	613.7	500.5	464.6
57.5°	887.6	736.5	540.1	434.4	404.1
60°	808.2	657.2	462.6	366.5	336.2
62.5°	730.9	579.8	396.5	306.0	290.9
65°	651.5	498.5	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.7	349.4	219.0	200.1	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.5
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.8	35.8	35.8
87.5°	30.3	15.0	15.0	13.2	13.2
90°	2.6	32.5	54.1	68.0	73.1
92.5°	68.0	57.1	65.0	70.6	73.1
95°	176.2	86.6	105.6	119.5	116.6
97.5°	317.3	95.0	138.1	146.5	149.1
100°	480.3	108.6	154.6	176.2	181.7
102.5°	659.0	653.8	160.1	189.7	198.1
105°	824.6	906.1	165.6	195.2	206.2
107.5°	1017.3	1084.8	171.1	200.6	211.7
110°	1201.8	1258.5	474.8	203.6	214.2

TEST NUMBER: P927586

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1375.4	1424.0	1378.0	208.7	217.1
115°	1559.6	1605.7	1673.7	417.8	222.6
117.5°	1719.8	1773.9	1820.3	1432.1	721.5
120°	1898.8	1939.4	1988.4	2020.9	1654.7
122.5°	2050.6	2094.0	2148.5	2164.6	2167.5
125°	2205.2	2240.6	2292.1	2311.1	2319.2
127.5°	2346.3	2384.2	2425.1	2452.2	2454.8
130°	2479.3	2522.8	2552.4	2582.4	2579.8
132.5°	2614.9	2650.3	2680.0	2704.4	2701.9
135°	2729.0	2772.4	2796.5	2824.0	2818.5
137.5°	2848.1	2880.7	2908.0	2935.1	2927.0
140°	2964.8	2986.6	3016.3	3040.7	3027.2
142.5°	3062.6	3081.6	3116.7	3138.4	3124.8
145°	3165.7	3162.8	3208.8	3227.9	3214.4
147.5°	3255.0	3246.9	3293.0	3306.5	3295.9
150°	3341.9	3322.9	3366.4	3382.5	3369.0
152.5°	3415.0	3393.4	3434.0	3450.5	3431.5
155°	3485.6	3461.4	3493.9	3510.1	3488.5
157.5°	3542.6	3521.0	3545.5	3564.5	3542.6
160°	3591.6	3575.1	3591.6	3607.6	3588.6
162.5°	3634.7	3618.6	3632.1	3651.1	3626.7
165°	3672.7	3656.6	3664.7	3683.6	3664.7
167.5°	3702.6	3686.3	3694.7	3713.6	3689.2
170°	3727.2	3710.7	3716.2	3735.3	3710.7
172.5°	3743.2	3727.2	3732.6	3751.6	3727.2
175°	3756.8	3737.8	3743.2	3762.3	3735.3
177.5°	3762.3	3743.2	3746.2	3765.1	3740.7
180°	3748.8	3748.8	3748.8	3748.8	3748.8

TEST NUMBER: P927586

CATALOG NUMBER: DFN2DIP-HX4F0-050D110US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.18	6.86	7.31	7.97	9.53	2.15	2.83	3.28	3.95	5.50
	3H	7.84	8.45	8.98	9.58	11.15	3.33	3.94	4.47	5.06	6.63
	4H	8.45	9.02	9.59	10.15	11.72	3.77	4.35	4.92	5.48	7.05
	6H	8.86	9.39	10.01	10.52	12.11	4.09	4.62	5.24	5.75	7.33
	8H	8.98	9.49	10.14	10.63	12.21	4.17	4.68	5.33	5.82	7.40
	12H	9.04	9.52	10.20	10.66	12.26	4.21	4.69	5.37	5.83	7.43
4H	2H	6.18	6.75	7.33	7.88	9.45	2.73	3.30	3.88	4.43	6.01
	3H	7.99	8.47	9.15	9.63	11.21	4.07	4.54	5.22	5.70	7.29
	4H	8.68	9.12	9.84	10.26	11.87	4.61	5.05	5.77	6.19	7.80
	6H	9.19	9.56	10.35	10.73	12.33	5.02	5.40	6.19	6.56	8.16
	8H	9.36	9.71	10.53	10.87	12.48	5.15	5.50	6.31	6.66	8.27
	12H	9.45	9.77	10.63	10.94	12.55	5.21	5.53	6.39	6.69	8.31
8H	4H	8.64	8.99	9.80	10.14	11.76	4.88	5.23	6.04	6.39	8.00
	6H	9.20	9.49	10.38	10.69	12.30	5.39	5.68	6.58	6.88	8.49
	8H	9.42	9.67	10.61	10.84	12.48	5.58	5.84	6.78	7.01	8.64
	12H	9.55	9.77	10.74	10.94	12.61	5.70	5.92	6.89	7.09	8.76
12H	4H	8.58	8.90	9.76	10.07	11.69	4.88	5.20	6.06	6.36	7.98
	6H	9.17	9.43	10.36	10.60	12.23	5.44	5.69	6.63	6.87	8.50
	8H	9.39	9.61	10.58	10.78	12.45	5.65	5.87	6.84	7.04	8.71

END OF REPORT