

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916171

Luminaire Tested: DFN2DIP-HX3F0-030D060US930-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P916171  
REPORT IS A COMBINATION OF REPORTS P900763 AND P897645  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-030D060US930-FLONL  
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7264.3 lumens  
Efficiency: N/A  
Efficacy: 105.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 69  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.983  
Total Harmonic Distortion (THDi): 0.073  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P916171  
CATALOG NUMBER: DFN2DIP-HX3F0-030D060US930-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P916171  
 CATALOG NUMBER: DFN2DIP-HX3F0-030D060US930-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33				33
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34	28				28
2	86	78	72	67	77	71	66	62	57	53	50	44	41	39	32	30	29	24				24
3	78	69	62	56	70	62	56	51	50	46	42	39	36	33	28	26	25	20				20
4	71	61	53	47	64	55	49	43	44	40	36	34	31	28	25	23	21	17				17
5	65	54	46	40	59	49	42	37	40	35	31	31	27	25	23	20	18	15				15
6	60	48	41	35	54	44	37	32	36	31	27	28	24	21	20	18	16	13				13
7	56	44	36	30	50	40	33	28	32	27	23	25	22	19	19	16	14	12				12
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	15	13	10				10
9	48	36	29	24	43	33	26	22	27	22	19	21	18	15	16	13	12	9				9
10	45	33	26	21	40	30	24	20	25	20	17	19	16	14	15	12	11	9				9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1102	1102	1102
5°	1104	1086	1094
10°	1094	1071	1078
15°	1078	1053	1055
20°	1055	1027	1030
25°	1033	997	1002
30°	1006	969	967
35°	979	936	929
40°	947	903	894
45°	915	870	857
50°	880	834	815
55°	843	794	776
60°	801	746	731
65°	756	696	679
70°	698	635	622
75°	618	562	568
80°	521	468	468
85°	369	310	303

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1058 cd/sqm



TEST NUMBER: P916171

CATALOG NUMBER: DFN2DIP-HX3F0-030D060US930-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	89.6	1.2
10°-20°	252.0	3.5
20°-30°	370.4	5.1
30°-40°	430.2	5.9
40°-50°	429.7	5.9
50°-60°	374.6	5.2
60°-70°	277.0	3.8
70°-80°	156.7	2.2
80°-90°	44.2	0.6
90°-100°	54.4	0.7
100°-110°	202.9	2.8
110°-120°	538.2	7.4
120°-130°	892.7	12.3
130°-140°	948.2	13.1
140°-150°	881.3	12.1
150°-160°	708.5	9.8
160°-170°	456.5	6.3
170°-180°	157.1	2.2
0°-30°	712.0	9.8
0°-40°	1142.2	15.7
0°-60°	1946.5	26.8
0°-90°	2424.4	33.4
90°-120°	795.6	11.0
90°-150°	3517.8	48.4
90°-180°	4840.0	66.6
0°-180°	7264.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	952	952	952	952	952	
5°	952	948	938	945	944	90
15°	906	901	889	892	888	255
25°	820	813	797	799	797	377
35°	707	698	684	678	674	442
45°	576	569	556	545	542	444
55°	436	430	419	408	404	390
65°	294	288	279	271	266	290
75°	154	152	147	142	144	164
85°	38	37	36	33	32	42
90°	1	14	24	30	32	7
95°	78	38	47	53	51	92
105°	363	399	73	86	91	388
115°	687	707	737	184	98	676
125°	971	987	1009	1018	1021	866
135°	1202	1221	1232	1244	1241	928
145°	1394	1393	1413	1422	1416	872
155°	1535	1524	1539	1546	1536	707
165°	1618	1610	1614	1622	1614	457
175°	1654	1646	1648	1657	1645	157
180°	1651	1651	1651	1651	1651	



TEST NUMBER: P916171

CATALOG NUMBER: DFN2DIP-HX3F0-030D060US930-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	951.7	951.7	951.7	951.7	951.7
2.5°	957.2	952.7	942.6	951.7	950.0
5°	951.7	948.1	938.0	945.3	943.5
7.5°	945.3	939.9	929.8	937.2	935.3
10°	935.3	928.9	917.9	925.2	922.5
12.5°	921.5	916.1	905.1	909.6	907.8
15°	906.0	900.6	888.6	892.3	887.7
17.5°	886.7	881.3	869.4	873.9	869.4
20°	865.7	860.2	847.4	850.1	846.5
22.5°	844.7	836.5	824.5	824.5	822.6
25°	819.9	812.7	797.1	798.9	797.1
27.5°	792.5	786.0	774.2	771.5	767.0
30°	765.1	757.7	744.0	741.3	737.6
32.5°	735.8	730.3	715.7	710.1	706.5
35°	707.4	698.3	683.6	678.1	673.5
37.5°	675.4	667.2	652.5	646.0	641.5
40°	642.5	635.1	620.4	612.3	608.6
42.5°	610.4	603.1	588.5	579.3	573.8
45°	575.7	569.2	555.5	545.4	541.8
47.5°	541.8	535.4	520.7	510.6	505.2
50°	506.1	501.5	488.7	475.9	471.3
52.5°	471.3	464.9	453.1	443.0	436.5
55°	435.7	430.2	419.1	408.2	403.7
57.5°	399.9	395.3	383.4	372.4	368.8
60°	364.2	360.6	347.8	337.7	335.0
62.5°	329.5	323.0	313.9	304.8	301.1
65°	293.8	288.3	279.2	270.9	266.4
67.5°	257.2	252.6	244.3	238.0	234.3
70°	223.3	219.6	211.4	205.0	201.4
72.5°	188.6	184.8	180.3	173.9	171.2
75°	153.7	152.0	147.3	141.9	143.7
77.5°	122.6	119.0	117.1	114.4	111.7
80°	91.6	90.6	88.7	86.0	84.2
82.5°	62.2	62.2	61.4	57.6	57.6
85°	37.5	36.6	35.7	32.9	32.0
87.5°	16.5	14.7	12.8	10.1	9.1
90°	1.1	14.3	23.8	29.9	32.2
92.5°	29.9	25.1	28.6	31.1	32.2
95°	77.6	38.2	46.6	52.7	51.4
97.5°	139.7	41.8	60.8	64.6	65.7
100°	211.5	47.8	68.1	77.6	80.0
102.5°	290.2	288.0	70.5	83.6	87.2
105°	363.1	399.0	72.9	85.9	90.8
107.5°	448.0	477.8	75.3	88.4	93.2
110°	529.3	554.2	209.1	89.7	94.3



TEST NUMBER: P916171

CATALOG NUMBER: DFN2DIP-HX3F0-030D060US930-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	605.7	627.1	606.8	91.9	95.6
115°	686.9	707.2	737.1	184.0	98.0
117.5°	757.3	781.2	801.6	630.7	317.7
120°	836.3	854.1	875.7	890.0	728.7
122.5°	903.0	922.2	946.2	953.2	954.6
125°	971.2	986.8	1009.4	1017.8	1021.3
127.5°	1033.3	1050.0	1068.0	1079.9	1081.1
130°	1091.8	1111.0	1124.1	1137.3	1136.1
132.5°	1151.6	1167.2	1180.2	1191.0	1189.8
135°	1201.8	1221.0	1231.6	1243.7	1241.2
137.5°	1254.3	1268.6	1280.7	1292.6	1289.1
140°	1305.6	1315.3	1328.4	1339.1	1333.2
142.5°	1348.7	1357.1	1372.6	1382.1	1376.1
145°	1394.2	1392.9	1413.2	1421.6	1415.6
147.5°	1433.5	1429.9	1450.2	1456.1	1451.5
150°	1471.8	1463.4	1482.5	1489.6	1483.7
152.5°	1504.0	1494.4	1512.3	1519.6	1511.2
155°	1535.0	1524.4	1538.7	1545.8	1536.3
157.5°	1560.2	1550.6	1561.4	1569.8	1560.2
160°	1581.7	1574.4	1581.7	1588.8	1580.5
162.5°	1600.7	1593.6	1599.5	1607.9	1597.2
165°	1617.5	1610.4	1613.9	1622.3	1613.9
167.5°	1630.6	1623.4	1627.1	1635.5	1624.6
170°	1641.4	1634.2	1636.6	1644.9	1634.2
172.5°	1648.5	1641.4	1643.8	1652.2	1641.4
175°	1654.5	1646.1	1648.5	1656.8	1644.9
177.5°	1656.8	1648.5	1649.8	1658.2	1647.4
180°	1650.9	1650.9	1650.9	1650.9	1650.9



TEST NUMBER: P916171  
 CATALOG NUMBER: DFN2DIP-HX3F0-030D060US930-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.79	6.52	6.88	7.61	9.10	5.36	6.09	6.45	7.18	8.67
	3H	7.44	8.09	8.53	9.19	10.69	6.97	7.62	8.06	8.72	10.22
	4H	8.01	8.63	9.12	9.73	11.24	7.54	8.16	8.65	9.26	10.77
	6H	8.40	8.97	9.52	10.07	11.60	7.93	8.50	9.05	9.60	11.13
	8H	8.50	9.04	9.62	10.16	11.67	8.03	8.57	9.15	9.69	11.21
	12H	8.54	9.05	9.66	10.16	11.71	8.06	8.58	9.19	9.69	11.23
4H	2H	6.24	6.86	7.35	7.95	9.47	5.89	6.51	7.01	7.61	9.12
	3H	8.08	8.60	9.20	9.72	11.25	7.69	8.21	8.81	9.33	10.86
	4H	8.78	9.26	9.91	10.37	11.92	8.38	8.86	9.51	9.97	11.52
	6H	9.28	9.69	10.42	10.83	12.37	8.88	9.29	10.01	10.42	11.96
	8H	9.43	9.81	10.56	10.94	12.49	9.02	9.40	10.15	10.53	12.08
	12H	9.49	9.84	10.64	10.97	12.53	9.07	9.42	10.22	10.56	12.12
8H	4H	8.97	9.35	10.10	10.48	12.03	8.61	8.99	9.74	10.12	11.67
	6H	9.58	9.90	10.74	11.07	12.62	9.22	9.54	10.38	10.71	12.26
	8H	9.80	10.07	10.96	11.22	12.79	9.43	9.71	10.59	10.86	12.43
	12H	9.92	10.16	11.08	11.31	12.91	9.54	9.78	10.70	10.93	12.53
12H	4H	8.95	9.29	10.09	10.43	11.99	8.60	8.94	9.74	10.08	11.64
	6H	9.61	9.89	10.77	11.04	12.61	9.26	9.54	10.42	10.69	12.26
	8H	9.84	10.08	11.00	11.23	12.83	9.49	9.73	10.65	10.87	12.48