

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927602

Luminaire Tested: DFN2DIP-HX4F0-060D060US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927602
REPORT IS A COMBINATION OF REPORTS P900860 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D060US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11148.2 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 98.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927602

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927602

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53			46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45			40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39			34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34			29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29			26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26			23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23			20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21			18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19			16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17			15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1862	1862	1862
5°	1865	1833	1844
10°	1847	1797	1784
15°	1821	1738	1692
20°	1788	1656	1578
25°	1754	1564	1468
30°	1708	1470	1329
35°	1663	1369	1206
40°	1617	1265	1066
45°	1563	1149	939
50°	1508	1032	814
55°	1450	906	695
60°	1384	776	572
65°	1307	642	515
70°	1214	518	466
75°	1098	457	424
80°	928	384	368
85°	649	257	277

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1563 cd/sqm

TEST NUMBER: P927602

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	234.7	2.1
10°-20°	644.3	5.8
20°-30°	904.5	8.1
30°-40°	986.0	8.8
40°-50°	906.2	8.1
50°-60°	711.7	6.4
60°-70°	463.3	4.2
70°-80°	238.5	2.1
80°-90°	64.5	0.6
90°-100°	67.4	0.6
100°-110°	251.3	2.3
110°-120°	666.6	6.0
120°-130°	1105.6	9.9
130°-140°	1174.4	10.5
140°-150°	1091.5	9.8
150°-160°	877.5	7.9
160°-170°	565.5	5.1
170°-180°	194.6	1.7
0°-30°	1783.5	16.0
0°-40°	2769.5	24.8
0°-60°	4387.4	39.4
0°-90°	5153.6	46.2
90°-120°	985.4	8.8
90°-150°	4357.0	39.1
90°-180°	5995.0	53.8
0°-180°	11148.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2504	2504	2504	2504	2504	
5°	2504	2493	2463	2484	2477	237
15°	2382	2357	2280	2237	2214	671
25°	2162	2089	1940	1847	1813	994
35°	1863	1747	1548	1405	1355	1166
45°	1523	1371	1133	972	918	1176
55°	1158	981	736	601	558	1035
65°	782	598	394	317	310	775
75°	417	258	181	165	163	441
85°	97	50	43	43	43	112
90°	1	18	30	37	40	10
95°	96	47	58	65	64	114
105°	450	494	90	106	112	481
115°	851	876	913	228	121	838
125°	1203	1222	1250	1261	1265	1073
135°	1488	1512	1525	1540	1537	1150
145°	1727	1725	1750	1761	1753	1080
155°	1901	1888	1906	1915	1903	876
165°	2003	1995	1999	2009	1999	566
175°	2049	2039	2042	2052	2037	195
180°	2045	2045	2045	2045	2045	

TEST NUMBER: P927602

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2504.1	2504.1	2504.1	2504.1	2504.1
2.5°	2515.4	2504.1	2479.1	2501.9	2497.3
5°	2504.1	2492.8	2463.2	2483.7	2476.9
7.5°	2483.7	2470.2	2438.5	2447.4	2436.0
10°	2456.4	2440.6	2395.4	2388.5	2374.9
12.5°	2422.6	2402.1	2340.8	2327.4	2302.3
15°	2381.7	2356.7	2279.7	2236.7	2214.1
17.5°	2334.2	2297.8	2202.6	2152.8	2116.5
20°	2279.7	2234.3	2121.1	2064.5	2014.6
22.5°	2220.9	2168.6	2037.2	1960.2	1926.3
25°	2162.0	2089.4	1939.8	1847.0	1812.9
27.5°	2091.8	2014.6	1849.1	1742.6	1690.5
30°	2017.0	1930.6	1749.4	1634.0	1572.7
32.5°	1944.4	1840.1	1654.5	1518.3	1461.6
35°	1862.9	1747.3	1547.9	1405.0	1355.1
37.5°	1783.5	1658.7	1448.2	1291.6	1235.1
40°	1699.6	1563.8	1343.7	1182.9	1124.0
42.5°	1613.6	1468.6	1239.6	1071.8	1015.4
45°	1522.9	1370.9	1133.2	972.0	917.7
47.5°	1436.8	1276.0	1031.2	870.1	820.4
50°	1341.6	1180.8	931.4	774.9	727.6
52.5°	1248.5	1078.6	836.2	686.7	643.6
55°	1157.9	981.2	736.4	600.6	557.5
57.5°	1065.1	883.8	648.2	521.3	484.9
60°	969.9	788.7	555.2	439.8	403.4
62.5°	877.1	695.9	475.8	367.2	349.1
65°	781.9	598.2	394.3	317.4	310.4
67.5°	691.2	507.5	317.4	278.7	271.9
70°	596.0	419.3	262.7	240.2	231.0
72.5°	505.4	337.6	219.7	201.8	197.1
75°	416.9	258.2	181.3	165.4	163.3
77.5°	328.7	183.5	142.8	133.7	129.2
80°	246.9	131.5	108.7	99.8	99.8
82.5°	172.2	88.5	74.7	70.2	70.2
85°	97.3	49.8	43.0	43.0	43.0
87.5°	36.4	18.1	18.1	15.9	15.9
90°	1.4	17.8	29.5	37.1	39.9
92.5°	37.1	31.1	35.4	38.5	39.9
95°	96.1	47.3	57.7	65.2	63.6
97.5°	173.1	51.8	75.3	80.0	81.4
100°	261.9	59.2	84.3	96.1	99.1
102.5°	359.5	356.7	87.3	103.5	108.0
105°	449.8	494.2	90.3	106.4	112.5
107.5°	554.9	591.7	93.3	109.5	115.4
110°	655.6	686.5	259.0	111.1	116.8

TEST NUMBER: P927602

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	750.2	776.7	751.6	113.8	118.4
115°	850.8	875.9	913.0	227.9	121.4
117.5°	938.0	967.6	992.8	781.2	393.5
120°	1035.8	1057.9	1084.6	1102.3	902.6
122.5°	1118.5	1142.2	1171.9	1180.7	1182.3
125°	1202.9	1222.2	1250.2	1260.6	1265.0
127.5°	1279.8	1300.5	1322.8	1337.6	1339.0
130°	1352.3	1376.1	1392.2	1408.6	1407.2
132.5°	1426.3	1445.6	1461.8	1475.1	1473.7
135°	1488.5	1512.3	1525.4	1540.3	1537.3
137.5°	1553.5	1571.2	1586.2	1600.9	1596.6
140°	1617.1	1629.1	1645.3	1658.6	1651.2
142.5°	1670.5	1680.9	1700.1	1711.8	1704.4
145°	1726.8	1725.1	1750.3	1760.7	1753.3
147.5°	1775.4	1771.0	1796.1	1803.5	1797.7
150°	1822.9	1812.5	1836.2	1845.0	1837.6
152.5°	1862.8	1851.0	1873.1	1882.1	1871.7
155°	1901.3	1888.0	1905.8	1914.6	1902.8
157.5°	1932.4	1920.5	1933.9	1944.3	1932.4
160°	1959.0	1950.0	1959.0	1967.8	1957.5
162.5°	1982.5	1973.8	1981.1	1991.5	1978.2
165°	2003.3	1994.6	1998.9	2009.3	1998.9
167.5°	2019.6	2010.7	2015.3	2025.7	2012.2
170°	2033.0	2024.0	2027.1	2037.4	2024.0
172.5°	2041.8	2033.0	2036.0	2046.4	2033.0
175°	2049.2	2038.8	2041.8	2052.1	2037.4
177.5°	2052.1	2041.8	2043.3	2053.7	2040.4
180°	2044.7	2044.7	2044.7	2044.7	2044.7

TEST NUMBER: P927602

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.94	9.74	9.94	10.75	12.07	4.92	5.72	5.91	6.72	8.05
	3H	10.62	11.34	11.63	12.35	13.70	6.11	6.82	7.11	7.83	9.18
	4H	11.23	11.91	12.25	12.92	14.28	6.56	7.23	7.58	8.25	9.60
	6H	11.65	12.27	12.68	13.29	14.66	6.88	7.50	7.91	8.52	9.89
	8H	11.78	12.37	12.81	13.40	14.77	6.97	7.56	8.00	8.60	9.96
	12H	11.84	12.40	12.88	13.43	14.82	7.01	7.57	8.05	8.60	9.99
4H	2H	8.96	9.64	9.98	10.65	12.01	5.51	6.19	6.54	7.20	8.56
	3H	10.79	11.35	11.82	12.39	13.76	6.86	7.42	7.89	8.47	9.83
	4H	11.48	11.99	12.52	13.03	14.42	7.41	7.92	8.45	8.96	10.35
	6H	11.99	12.44	13.04	13.49	14.88	7.83	8.27	8.88	9.33	10.72
	8H	12.17	12.58	13.22	13.63	15.03	7.96	8.37	9.01	9.42	10.82
	12H	12.26	12.64	13.33	13.70	15.11	8.02	8.39	9.09	9.46	10.87
8H	4H	11.44	11.86	12.50	12.91	14.31	7.69	8.10	8.74	9.15	10.55
	6H	12.01	12.35	13.09	13.44	14.84	8.21	8.55	9.28	9.64	11.04
	8H	12.23	12.53	13.31	13.60	15.02	8.40	8.70	9.48	9.77	11.19
	12H	12.37	12.63	13.45	13.70	15.16	8.52	8.78	9.60	9.85	11.31
12H	4H	11.40	11.77	12.46	12.83	14.24	7.69	8.06	8.76	9.13	10.54
	6H	11.99	12.29	13.07	13.36	14.78	8.26	8.55	9.34	9.63	11.05
	8H	12.21	12.47	13.29	13.54	15.00	8.47	8.73	9.55	9.80	11.26

END OF REPORT