

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P916207

Luminaire Tested: DFN2DIP-HX3F0-050D030US930-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P916207
REPORT IS A COMBINATION OF REPORTS P900725 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-050D030US930-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6457.2 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 67.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P916207

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US930-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P916207

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US930-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	62	61	58	55	53	50	48
3	84	74	66	60	78	70	63	57	61	56	52	54	50	46	47	44	41
4	77	65	57	51	71	62	54	49	55	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	53	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	38	32	40	34	30	35	31	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	33	28	24	29	25	22
9	52	40	32	27	49	37	30	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1839	1810	1823
10°	1824	1785	1797
15°	1796	1754	1758
20°	1759	1712	1717
25°	1722	1662	1670
30°	1676	1615	1612
35°	1632	1560	1549
40°	1579	1505	1490
45°	1525	1449	1429
50°	1467	1391	1358
55°	1405	1323	1293
60°	1336	1243	1219
65°	1260	1159	1131
70°	1163	1058	1037
75°	1029	936	947
80°	868	781	780
85°	616	516	506

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1525 cd/sqm

TEST NUMBER: P916207

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US930-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.3	2.3
10°-20°	420.0	6.5
20°-30°	617.3	9.6
30°-40°	717.0	11.1
40°-50°	716.1	11.1
50°-60°	624.4	9.7
60°-70°	461.6	7.1
70°-80°	261.1	4.0
80°-90°	70.4	1.1
90°-100°	27.2	0.4
100°-110°	101.5	1.6
110°-120°	269.1	4.2
120°-130°	446.3	6.9
130°-140°	474.1	7.3
140°-150°	440.6	6.8
150°-160°	354.3	5.5
160°-170°	228.3	3.5
170°-180°	78.6	1.2
0°-30°	1186.6	18.4
0°-40°	1903.6	29.5
0°-60°	3244.1	50.2
0°-90°	4037.2	62.5
90°-120°	397.8	6.2
90°-150°	1758.9	27.2
90°-180°	2420.0	37.5
0°-180°	6457.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1586	1586	1586	1586	1586	
5°	1586	1580	1563	1576	1573	151
15°	1510	1501	1481	1487	1480	425
25°	1367	1354	1328	1332	1328	629
35°	1179	1164	1139	1130	1123	736
45°	959	949	926	909	903	740
55°	726	717	698	680	673	649
65°	490	480	465	452	444	484
75°	256	253	246	236	240	273
85°	62	61	60	55	53	70
90°	1	7	12	15	16	6
95°	39	19	23	26	26	46
105°	182	200	36	43	45	194
115°	343	354	368	92	49	338
125°	486	493	505	509	511	433
135°	601	610	616	622	621	464
145°	697	696	707	711	708	436
155°	768	762	769	773	768	354
165°	809	805	807	811	807	228
175°	827	823	824	828	822	79
180°	826	826	826	826	826	

TEST NUMBER: P916207

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US930-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1586.2	1586.2	1586.2	1586.2	1586.2
2.5°	1595.4	1587.8	1571.0	1586.2	1583.3
5°	1586.2	1580.2	1563.3	1575.5	1572.6
7.5°	1575.5	1566.4	1549.6	1561.9	1558.9
10°	1558.9	1548.2	1529.9	1542.0	1537.5
12.5°	1535.9	1526.8	1508.5	1516.1	1513.0
15°	1509.9	1500.9	1481.0	1487.2	1479.5
17.5°	1477.9	1468.8	1448.9	1456.5	1448.9
20°	1442.8	1433.8	1412.4	1416.9	1411.0
22.5°	1407.9	1394.1	1374.2	1374.2	1371.1
25°	1366.6	1354.5	1328.5	1331.5	1328.5
27.5°	1320.8	1310.1	1290.4	1285.8	1278.2
30°	1275.1	1262.9	1240.1	1235.5	1229.4
32.5°	1226.3	1217.2	1192.8	1183.6	1177.5
35°	1179.0	1163.8	1139.4	1130.2	1122.6
37.5°	1125.6	1111.9	1087.4	1076.8	1069.2
40°	1070.8	1058.5	1034.0	1020.4	1014.3
42.5°	1017.4	1005.1	980.8	965.4	956.3
45°	959.4	948.8	925.8	909.1	902.9
47.5°	902.9	892.3	867.9	851.0	842.0
50°	843.4	835.8	814.5	793.1	785.5
52.5°	785.5	774.8	755.0	738.3	727.6
55°	726.1	716.9	698.5	680.3	672.7
57.5°	666.5	658.9	639.0	620.8	614.6
60°	607.0	601.0	579.7	562.8	558.3
62.5°	549.1	538.4	523.2	507.9	501.8
65°	489.7	480.5	465.2	451.5	443.8
67.5°	428.7	420.9	407.3	396.6	390.4
70°	372.2	366.1	352.3	341.6	335.7
72.5°	314.3	308.1	300.5	289.8	285.3
75°	256.2	253.2	245.5	236.4	239.5
77.5°	204.4	198.2	195.2	190.6	186.1
80°	152.6	151.0	147.9	143.4	140.3
82.5°	103.7	103.7	102.2	96.1	96.1
85°	62.5	61.0	59.5	54.9	53.4
87.5°	27.5	24.5	21.4	16.8	15.2
90°	0.6	7.2	11.9	15.0	16.1
92.5°	15.0	12.6	14.3	15.6	16.1
95°	38.8	19.1	23.2	26.3	25.7
97.5°	69.9	21.0	30.4	32.3	32.9
100°	105.7	23.9	34.1	38.8	40.0
102.5°	145.1	144.0	35.2	41.7	43.6
105°	181.6	199.5	36.4	43.0	45.4
107.5°	224.0	238.9	37.7	44.2	46.6
110°	264.6	277.1	104.5	44.8	47.2

TEST NUMBER: P916207

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US930-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	302.9	313.6	303.5	46.0	47.8
115°	343.4	353.6	368.5	92.0	49.0
117.5°	378.7	390.6	400.8	315.4	158.9
120°	418.1	427.1	437.8	445.0	364.4
122.5°	451.5	461.1	473.1	476.6	477.3
125°	485.6	493.3	504.8	508.9	510.7
127.5°	516.7	525.0	534.0	540.0	540.5
130°	545.9	555.5	562.1	568.6	568.1
132.5°	575.8	583.6	590.1	595.5	594.9
135°	600.9	610.5	615.8	621.8	620.6
137.5°	627.1	634.3	640.3	646.3	644.5
140°	652.8	657.6	664.1	669.5	666.6
142.5°	674.4	678.6	686.3	691.0	688.1
145°	697.1	696.4	706.6	710.8	707.8
147.5°	716.7	714.9	725.1	728.1	725.7
150°	735.9	731.7	741.3	744.8	741.8
152.5°	751.9	747.2	756.2	759.8	755.6
155°	767.5	762.2	769.3	772.9	768.2
157.5°	780.1	775.3	780.7	784.9	780.1
160°	790.8	787.3	790.8	794.4	790.2
162.5°	800.4	796.8	799.8	804.0	798.6
165°	808.7	805.2	807.0	811.1	807.0
167.5°	815.3	811.7	813.5	817.7	812.4
170°	820.7	817.1	818.3	822.5	817.1
172.5°	824.3	820.7	821.9	826.1	820.7
175°	827.2	823.0	824.3	828.4	822.5
177.5°	828.4	824.3	824.9	829.1	823.7
180°	825.5	825.5	825.5	825.5	825.5

TEST NUMBER: P916207

CATALOG NUMBER: DFN2DIP-HX3F0-050D030US930-FLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.42	11.41	11.26	12.27	13.35	9.99	10.98	10.84	11.85	12.93
	3H	12.09	12.97	12.94	13.84	14.95	11.62	12.50	12.47	13.38	14.48
	4H	12.67	13.51	13.54	14.39	15.51	12.20	13.04	13.08	13.92	15.04
	6H	13.07	13.85	13.96	14.73	15.86	12.60	13.38	13.49	14.26	15.39
	8H	13.18	13.91	14.07	14.82	15.95	12.71	13.44	13.60	14.35	15.48
	12H	13.23	13.93	14.13	14.83	15.98	12.75	13.45	13.65	14.35	15.51
4H	2H	10.90	11.73	11.77	12.61	13.73	10.55	11.39	11.43	12.27	13.39
	3H	12.77	13.46	13.65	14.38	15.51	12.38	13.07	13.26	13.99	15.12
	4H	13.48	14.12	14.38	15.02	16.18	13.08	13.71	13.98	14.62	15.78
	6H	13.99	14.54	14.91	15.48	16.64	13.59	14.14	14.50	15.07	16.23
	8H	14.14	14.66	15.06	15.58	16.76	13.74	14.25	14.65	15.18	16.35
	12H	14.22	14.68	15.15	15.63	16.81	13.80	14.27	14.74	15.21	16.39
8H	4H	13.68	14.20	14.60	15.12	16.30	13.32	13.84	14.24	14.77	15.94
	6H	14.31	14.74	15.25	15.70	16.88	13.95	14.38	14.89	15.34	16.52
	8H	14.53	14.90	15.48	15.86	17.05	14.16	14.54	15.11	15.50	16.69
	12H	14.66	14.99	15.61	15.94	17.18	14.28	14.61	15.23	15.56	16.80
12H	4H	13.67	14.14	14.61	15.08	16.26	13.32	13.79	14.26	14.73	15.91
	6H	14.34	14.72	15.29	15.68	16.87	13.99	14.37	14.94	15.33	16.52
	8H	14.58	14.91	15.54	15.86	17.11	14.23	14.56	15.18	15.51	16.75

END OF REPORT