

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927628

Luminaire Tested: DFN2DIP-HX4F0-070D040US840-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927628
REPORT IS A COMBINATION OF REPORTS P900825 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D040US840-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10996.7 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 96.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927628

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US840-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927628

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US840-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	42
4	77	66	58	51	72	62	55	49	55	49	45	48	44	40	42	39	36
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	34	31
6	65	53	44	38	61	50	42	37	44	38	34	39	34	31	35	31	28
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25
8	56	43	35	30	52	41	34	29	37	31	27	33	28	24	29	25	22
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2045	2045	2045
5°	2049	2017	2030
10°	2032	1990	2003
15°	2002	1957	1960
20°	1962	1912	1916
25°	1922	1858	1866
30°	1872	1807	1801
35°	1825	1748	1733
40°	1766	1688	1668
45°	1708	1627	1601
50°	1644	1564	1524
55°	1577	1491	1453
60°	1502	1404	1373
65°	1419	1314	1277
70°	1315	1205	1174
75°	1169	1073	1079
80°	995	907	898
85°	723	618	597

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1708 cd/sqm

TEST NUMBER: P927628

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US840-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	258.9	2.4
10°-20°	728.4	6.6
20°-30°	1070.4	9.7
30°-40°	1243.2	11.3
40°-50°	1241.7	11.3
50°-60°	1082.7	9.8
60°-70°	800.4	7.3
70°-80°	452.8	4.1
80°-90°	121.9	1.1
90°-100°	44.9	0.4
100°-110°	167.6	1.5
110°-120°	444.4	4.0
120°-130°	737.1	6.7
130°-140°	783.0	7.1
140°-150°	727.7	6.6
150°-160°	585.0	5.3
160°-170°	377.0	3.4
170°-180°	129.8	1.2
0°-30°	2057.6	18.7
0°-40°	3300.9	30.0
0°-60°	5625.2	51.2
0°-90°	7000.3	63.7
90°-120°	656.9	6.0
90°-150°	2904.6	26.4
90°-180°	3996.0	36.3
0°-180°	10996.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2740	2711	2732	2727	261
15°	2618	2603	2568	2579	2566	737
25°	2370	2349	2304	2309	2304	1090
35°	2044	2018	1976	1960	1946	1277
45°	1664	1645	1605	1576	1566	1284
55°	1259	1243	1211	1180	1166	1126
65°	849	833	807	783	770	839
75°	444	439	426	410	415	474
85°	108	106	103	95	93	121
90°	1	12	20	25	27	10
95°	64	32	38	43	42	76
105°	300	330	60	71	75	320
115°	567	584	609	152	81	558
125°	802	815	834	840	843	715
135°	992	1008	1017	1027	1025	767
145°	1151	1150	1167	1174	1169	720
155°	1268	1259	1270	1276	1268	584
165°	1336	1330	1333	1340	1333	377
175°	1366	1359	1361	1368	1358	130
180°	1363	1363	1363	1363	1363	

TEST NUMBER: P927628

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US840-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.4	2750.4	2750.4	2750.4	2750.4
2.5°	2766.4	2753.2	2724.0	2750.4	2745.3
5°	2750.4	2740.1	2710.9	2731.9	2726.9
7.5°	2731.9	2716.2	2687.0	2708.4	2703.0
10°	2703.0	2684.5	2652.7	2673.8	2666.0
12.5°	2663.1	2647.5	2615.8	2628.9	2623.6
15°	2618.3	2602.6	2568.0	2578.7	2565.5
17.5°	2562.7	2547.0	2512.5	2525.7	2512.5
20°	2501.8	2486.1	2449.1	2456.9	2446.5
22.5°	2441.2	2417.4	2382.8	2382.8	2377.5
25°	2369.7	2348.6	2303.8	2308.8	2303.8
27.5°	2290.2	2271.7	2237.5	2229.6	2216.4
30°	2211.2	2189.8	2150.3	2142.4	2131.7
32.5°	2126.3	2110.7	2068.3	2052.3	2041.6
35°	2044.4	2018.1	1975.7	1959.7	1946.5
37.5°	1951.8	1928.0	1885.6	1867.1	1853.9
40°	1856.7	1835.4	1793.0	1769.5	1758.8
42.5°	1764.1	1742.8	1700.7	1674.0	1658.3
45°	1663.6	1645.2	1605.3	1576.4	1565.7
47.5°	1565.7	1547.2	1504.8	1475.6	1460.0
50°	1462.5	1449.3	1412.2	1375.2	1362.0
52.5°	1362.0	1343.5	1309.3	1280.1	1261.5
55°	1259.0	1243.1	1211.4	1179.6	1166.4
57.5°	1155.8	1142.6	1108.1	1076.3	1065.7
60°	1052.5	1042.1	1005.2	976.0	968.1
62.5°	952.0	933.6	907.2	880.8	870.1
65°	849.1	833.1	806.7	782.9	769.7
67.5°	743.3	729.9	706.3	687.8	677.1
70°	645.4	634.8	610.8	592.3	581.9
72.5°	544.9	534.3	521.1	502.6	494.7
75°	444.2	439.2	425.6	410.0	415.3
77.5°	354.4	343.7	338.4	330.5	322.7
80°	264.6	261.8	256.5	248.6	243.3
82.5°	179.8	179.8	177.3	166.7	166.7
85°	108.4	105.8	103.3	95.1	92.6
87.5°	47.7	42.4	37.1	29.2	26.4
90°	0.9	11.8	19.7	24.7	26.6
92.5°	24.7	20.7	23.6	25.6	26.6
95°	64.0	31.5	38.4	43.4	42.4
97.5°	115.4	34.5	50.3	53.3	54.2
100°	174.6	39.5	56.2	64.0	66.0
102.5°	239.6	237.8	58.2	69.0	72.0
105°	299.8	329.5	60.2	71.0	74.9
107.5°	369.9	394.5	62.2	73.0	76.9
110°	437.0	457.6	172.7	74.0	77.9

TEST NUMBER: P927628

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US840-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	500.2	517.8	501.1	75.9	79.0
115°	567.1	583.9	608.6	151.9	81.0
117.5°	625.4	645.1	661.9	520.8	262.3
120°	690.5	705.2	723.0	734.9	601.7
122.5°	745.6	761.5	781.3	787.1	788.1
125°	801.9	814.8	833.5	840.5	843.4
127.5°	853.2	867.0	881.9	891.8	892.7
130°	901.5	917.4	928.1	939.0	938.1
132.5°	950.8	963.8	974.6	983.4	982.5
135°	992.3	1008.2	1017.0	1026.9	1024.9
137.5°	1035.7	1047.5	1057.5	1067.3	1064.3
140°	1078.1	1086.0	1096.8	1105.7	1100.8
142.5°	1113.7	1120.6	1133.4	1141.2	1136.3
145°	1151.2	1150.2	1166.8	1173.8	1168.8
147.5°	1183.6	1180.7	1197.4	1202.4	1198.5
150°	1215.2	1208.3	1224.2	1230.0	1225.1
152.5°	1241.9	1234.0	1248.7	1254.7	1247.8
155°	1267.5	1258.7	1270.5	1276.4	1268.5
157.5°	1288.2	1280.3	1289.3	1296.2	1288.2
160°	1306.0	1300.0	1306.0	1311.8	1305.0
162.5°	1321.7	1315.9	1320.8	1327.7	1318.8
165°	1335.6	1329.7	1332.6	1339.5	1332.6
167.5°	1346.5	1340.4	1343.5	1350.4	1341.5
170°	1355.4	1349.4	1351.3	1358.3	1349.4
172.5°	1361.2	1355.4	1357.4	1364.2	1355.4
175°	1366.1	1359.2	1361.2	1368.1	1358.3
177.5°	1368.1	1361.2	1362.2	1369.2	1360.3
180°	1363.2	1363.2	1363.2	1363.2	1363.2

TEST NUMBER: P927628

CATALOG NUMBER: DFN2DIP-HX4F0-070D040US840-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.93	11.93	11.76	12.78	13.85	10.50	11.50	11.33	12.35	13.41
	3H	12.60	13.50	13.45	14.36	15.45	12.13	13.03	12.97	13.89	14.98
	4H	13.20	14.05	14.06	14.91	16.01	12.72	13.57	13.58	14.44	15.54
	6H	13.61	14.39	14.48	15.26	16.38	13.13	13.91	14.00	14.79	15.90
	8H	13.71	14.46	14.59	15.35	16.47	13.24	13.98	14.12	14.88	15.99
	12H	13.77	14.48	14.65	15.37	16.50	13.29	14.00	14.17	14.88	16.02
4H	2H	11.41	12.26	12.27	13.13	14.23	11.07	11.91	11.93	12.78	13.88
	3H	13.29	14.00	14.17	14.90	16.01	12.90	13.60	13.77	14.51	15.62
	4H	14.01	14.66	14.90	15.55	16.70	13.60	14.25	14.49	15.15	16.29
	6H	14.53	15.09	15.44	16.01	17.16	14.12	14.68	15.03	15.60	16.75
	8H	14.69	15.21	15.59	16.13	17.28	14.28	14.80	15.18	15.71	16.87
	12H	14.77	15.24	15.69	16.17	17.34	14.35	14.82	15.27	15.75	16.91
8H	4H	14.22	14.74	15.12	15.66	16.81	13.86	14.38	14.76	15.30	16.45
	6H	14.86	15.29	15.79	16.25	17.40	14.49	14.93	15.43	15.88	17.04
	8H	15.08	15.46	16.02	16.41	17.59	14.71	15.09	15.65	16.04	17.22
	12H	15.22	15.56	16.16	16.50	17.72	14.83	15.17	15.78	16.11	17.34
12H	4H	14.21	14.68	15.14	15.62	16.78	13.86	14.33	14.78	15.26	16.43
	6H	14.89	15.27	15.83	16.22	17.39	14.54	14.92	15.48	15.87	17.04
	8H	15.14	15.47	16.08	16.42	17.64	14.78	15.12	15.73	16.06	17.28

END OF REPORT