

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927668

Luminaire Tested: DFN2DIP-HX4F0-080D050US840-FLLONL

Issue Date: 12/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P927668  
REPORT IS A COMBINATION OF REPORTS P900845 AND P896187  
Test Lab: INNOVATION CENTER  
Issue Date: 12/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-080D050US840-FLONL  
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12996.1 lumens  
Efficiency: N/A  
Efficacy: 113.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 114.3  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9613  
Total Harmonic Distortion (THDi): 0.083  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P927668  
CATALOG NUMBER: DFN2DIP-HX4F0-080D050US840-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P927668

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US840-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56	59	58	56	52
2	91	84	78	72	85	79	73	69	69	65	61	60	57	54	52	50	48	52	50	48	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	46	43	40	37
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35	41	38	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	31	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	28	24	21	19
9	52	39	32	27	49	37	30	26	33	28	23	30	25	21	26	22	19	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	24	20	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2337	2337	2337
5°	2341	2305	2320
10°	2322	2274	2289
15°	2288	2237	2240
20°	2242	2185	2190
25°	2197	2123	2132
30°	2139	2065	2058
35°	2085	1997	1980
40°	2018	1929	1906
45°	1952	1860	1830
50°	1879	1788	1742
55°	1802	1704	1661
60°	1716	1605	1568
65°	1622	1502	1459
70°	1503	1377	1342
75°	1336	1227	1233
80°	1137	1036	1026
85°	825	706	682

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1952 cd/sqm



TEST NUMBER: P927668

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US840-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	295.9	2.3
10°-20°	832.4	6.4
20°-30°	1223.3	9.4
30°-40°	1420.8	10.9
40°-50°	1419.1	10.9
50°-60°	1237.4	9.5
60°-70°	914.7	7.0
70°-80°	517.5	4.0
80°-90°	139.6	1.1
90°-100°	56.2	0.4
100°-110°	209.5	1.6
110°-120°	555.5	4.3
120°-130°	921.4	7.1
130°-140°	978.7	7.5
140°-150°	909.6	7.0
150°-160°	731.3	5.6
160°-170°	471.2	3.6
170°-180°	162.2	1.2
0°-30°	2351.6	18.1
0°-40°	3772.4	29.0
0°-60°	6428.8	49.5
0°-90°	8000.6	61.6
90°-120°	821.2	6.3
90°-150°	3630.8	27.9
90°-180°	4996.0	38.4
0°-180°	12996.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3143	3143	3143	3143	3143	
5°	3143	3132	3098	3122	3116	298
15°	2992	2974	2935	2947	2932	843
25°	2708	2684	2633	2639	2633	1246
35°	2336	2306	2258	2240	2225	1459
45°	1901	1880	1835	1802	1790	1467
55°	1439	1421	1384	1348	1333	1286
65°	970	952	922	895	880	959
75°	508	502	486	468	475	542
85°	124	121	118	109	106	138
90°	1	15	25	31	33	12
95°	80	39	48	54	53	95
105°	375	412	75	89	94	401
115°	709	730	761	190	101	698
125°	1002	1018	1042	1050	1054	894
135°	1240	1260	1271	1284	1281	958
145°	1439	1438	1459	1467	1461	900
155°	1584	1573	1588	1596	1586	730
165°	1669	1662	1666	1674	1666	472
175°	1708	1699	1702	1710	1698	163
180°	1704	1704	1704	1704	1704	



TEST NUMBER: P927668

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US840-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3143.3	3143.3	3143.3	3143.3	3143.3
2.5°	3161.6	3146.5	3113.2	3143.3	3137.5
5°	3143.3	3131.5	3098.2	3122.2	3116.4
7.5°	3122.2	3104.2	3070.9	3095.2	3089.2
10°	3089.2	3068.0	3031.7	3055.8	3046.9
12.5°	3043.6	3025.7	2989.4	3004.5	2998.4
15°	2992.3	2974.4	2934.9	2947.1	2932.1
17.5°	2928.8	2910.8	2871.4	2886.5	2871.4
20°	2859.2	2841.3	2799.0	2808.0	2796.0
22.5°	2790.0	2762.7	2723.2	2723.2	2717.2
25°	2708.2	2684.1	2632.9	2638.6	2632.9
27.5°	2617.4	2596.3	2557.1	2548.1	2533.1
30°	2527.0	2502.6	2457.4	2448.5	2436.2
32.5°	2430.2	2412.2	2363.7	2345.5	2333.3
35°	2336.5	2306.4	2257.9	2239.6	2224.6
37.5°	2230.6	2203.4	2155.0	2133.8	2118.8
40°	2122.0	2097.6	2049.2	2022.2	2010.0
42.5°	2016.2	1991.7	1943.7	1913.2	1895.3
45°	1901.4	1880.1	1834.6	1801.6	1789.5
47.5°	1789.5	1768.3	1719.8	1686.5	1668.5
50°	1671.4	1656.4	1614.0	1571.7	1556.6
52.5°	1556.6	1535.4	1496.3	1463.0	1441.8
55°	1438.9	1420.6	1384.4	1348.2	1333.0
57.5°	1320.9	1305.9	1266.4	1230.1	1217.9
60°	1202.9	1191.1	1148.6	1115.3	1106.3
62.5°	1088.1	1067.0	1036.8	1006.7	994.5
65°	970.4	952.1	921.9	894.7	879.6
67.5°	849.4	834.1	807.1	786.0	773.8
70°	737.6	725.3	698.2	677.0	665.1
72.5°	622.7	610.6	595.5	574.4	565.4
75°	507.6	501.9	486.5	468.5	474.6
77.5°	405.0	392.8	386.8	377.8	368.8
80°	302.4	299.2	293.1	284.2	278.0
82.5°	205.6	205.6	202.7	190.4	190.4
85°	123.8	120.9	118.0	108.8	105.8
87.5°	54.5	48.5	42.3	33.3	30.2
90°	1.2	14.7	24.6	30.9	33.2
92.5°	30.9	26.0	29.6	32.1	33.2
95°	80.1	39.4	48.1	54.3	53.0
97.5°	144.2	43.2	62.8	66.6	67.8
100°	218.3	49.4	70.3	80.1	82.6
102.5°	299.6	297.2	72.8	86.2	90.1
105°	374.8	411.9	75.2	88.8	93.7
107.5°	462.4	493.1	77.8	91.2	96.2
110°	546.3	572.1	215.8	92.5	97.3



TEST NUMBER: P927668

CATALOG NUMBER: DFN2DIP-HX4F0-080D050US840-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	625.2	647.3	626.4	94.9	98.7
115°	709.0	729.9	760.8	189.9	101.2
117.5°	781.7	806.3	827.4	650.9	328.0
120°	863.1	881.6	903.8	918.6	752.1
122.5°	932.0	951.8	976.6	983.9	985.3
125°	1002.3	1018.5	1041.9	1050.5	1054.2
127.5°	1066.4	1083.7	1102.4	1114.6	1115.8
130°	1126.9	1146.7	1160.2	1173.8	1172.7
132.5°	1188.6	1204.7	1218.1	1229.3	1228.1
135°	1240.4	1260.2	1271.1	1283.7	1281.1
137.5°	1294.6	1309.4	1321.8	1334.1	1330.5
140°	1347.6	1357.6	1371.0	1382.1	1376.1
142.5°	1392.1	1400.8	1416.7	1426.5	1420.4
145°	1439.0	1437.7	1458.6	1467.2	1461.1
147.5°	1479.6	1475.8	1496.8	1503.0	1498.1
150°	1519.0	1510.5	1530.1	1537.5	1531.4
152.5°	1552.3	1542.5	1560.9	1568.4	1559.7
155°	1584.4	1573.4	1588.1	1595.5	1585.7
157.5°	1610.2	1600.4	1611.5	1620.2	1610.2
160°	1632.5	1625.1	1632.5	1639.8	1631.2
162.5°	1652.1	1644.9	1650.9	1659.6	1648.5
165°	1669.4	1662.1	1665.8	1674.3	1665.8
167.5°	1683.0	1675.6	1679.4	1688.0	1676.9
170°	1694.1	1686.7	1689.2	1697.8	1686.7
172.5°	1701.5	1694.1	1696.7	1705.2	1694.1
175°	1707.7	1699.0	1701.5	1710.1	1697.8
177.5°	1710.1	1701.5	1702.8	1711.4	1700.3
180°	1703.9	1703.9	1703.9	1703.9	1703.9



TEST NUMBER: P927668  
 CATALOG NUMBER: DFN2DIP-HX4F0-080D050US840-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.23	12.20	12.08	13.07	14.17	10.79	11.77	11.64	12.64	13.74
	3H	12.90	13.77	13.76	14.65	15.78	12.42	13.30	13.29	14.18	15.30
	4H	13.49	14.32	14.37	15.21	16.34	13.02	13.84	13.89	14.73	15.86
	6H	13.90	14.66	14.79	15.55	16.70	13.42	14.18	14.31	15.08	16.22
	8H	14.00	14.73	14.90	15.64	16.79	13.53	14.26	14.43	15.17	16.31
	12H	14.06	14.75	14.96	15.66	16.83	13.57	14.27	14.48	15.18	16.35
4H	2H	11.70	12.53	12.59	13.42	14.55	11.36	12.18	12.24	13.07	14.21
	3H	13.58	14.27	14.47	15.19	16.34	13.19	13.88	14.08	14.80	15.95
	4H	14.30	14.93	15.21	15.85	17.02	13.89	14.52	14.80	15.44	16.61
	6H	14.82	15.37	15.74	16.31	17.48	14.41	14.96	15.33	15.90	17.07
	8H	14.97	15.48	15.90	16.42	17.61	14.56	15.07	15.49	16.01	17.19
	12H	15.05	15.51	16.00	16.47	17.66	14.63	15.09	15.57	16.04	17.24
8H	4H	14.51	15.01	15.43	15.95	17.14	14.14	14.65	15.07	15.59	16.78
	6H	15.14	15.56	16.09	16.54	17.73	14.78	15.20	15.73	16.18	17.37
	8H	15.37	15.74	16.33	16.71	17.91	15.00	15.37	15.96	16.34	17.54
	12H	15.50	15.83	16.47	16.79	18.05	15.12	15.45	16.08	16.41	17.66
12H	4H	14.50	14.96	15.44	15.91	17.10	14.14	14.60	15.09	15.56	16.75
	6H	15.17	15.55	16.13	16.51	17.72	14.82	15.20	15.78	16.16	17.37
	8H	15.42	15.75	16.39	16.71	17.97	15.06	15.39	16.03	16.35	17.61