

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927718

Luminaire Tested: DFN2DIP-HX4F0-090D080US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927718
REPORT IS A COMBINATION OF REPORTS P900902 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D080US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15722.6 lumens
Efficiency: N/A
Efficacy: 107.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 147
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927718

CATALOG NUMBER: DFN2DIP-HX4F0-090D080US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927718

CATALOG NUMBER: DFN2DIP-HX4F0-090D080US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	52	49	44	42	41
3	82	73	66	60	75	68	62	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	37	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	30	27
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2793	2793	2793
5°	2798	2749	2766
10°	2770	2695	2676
15°	2732	2606	2537
20°	2682	2484	2367
25°	2631	2346	2202
30°	2562	2206	1993
35°	2494	2054	1809
40°	2425	1897	1599
45°	2345	1723	1408
50°	2262	1548	1221
55°	2176	1360	1042
60°	2076	1163	858
65°	1961	964	772
70°	1821	777	699
75°	1646	686	636
80°	1393	576	553
85°	973	386	416

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2345 cd/sqm

TEST NUMBER: P927718

CATALOG NUMBER: DFN2DIP-HX4F0-090D080US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	352.0	2.2
10°-20°	966.4	6.1
20°-30°	1356.8	8.6
30°-40°	1479.0	9.4
40°-50°	1359.4	8.6
50°-60°	1067.6	6.8
60°-70°	694.9	4.4
70°-80°	357.7	2.3
80°-90°	96.1	0.6
90°-100°	89.9	0.6
100°-110°	335.1	2.1
110°-120°	888.8	5.7
120°-130°	1474.2	9.4
130°-140°	1565.9	10.0
140°-150°	1455.3	9.3
150°-160°	1170.1	7.4
160°-170°	754.0	4.8
170°-180°	259.5	1.7
0°-30°	2675.2	17.0
0°-40°	4154.2	26.4
0°-60°	6581.1	41.9
0°-90°	7729.8	49.2
90°-120°	1313.9	8.4
90°-150°	5809.3	36.9
90°-180°	7993.0	50.8
0°-180°	15722.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3756	3756	3756	3756	3756	
5°	3756	3739	3695	3726	3715	356
15°	3573	3535	3420	3355	3321	1007
25°	3243	3134	2910	2770	2719	1491
35°	2794	2621	2322	2108	2033	1749
45°	2284	2056	1700	1458	1377	1764
55°	1737	1472	1105	901	836	1552
65°	1173	897	591	476	466	1163
75°	625	387	272	248	245	661
85°	146	75	64	64	64	168
90°	2	24	39	49	53	15
95°	128	63	77	87	85	152
105°	600	659	120	142	150	641
115°	1134	1168	1217	304	162	1117
125°	1604	1630	1667	1681	1687	1430
135°	1985	2016	2034	2054	2050	1533
145°	2302	2300	2334	2348	2338	1440
155°	2535	2517	2541	2553	2537	1168
165°	2671	2659	2665	2679	2665	755
175°	2732	2718	2722	2736	2717	260
180°	2726	2726	2726	2726	2726	

TEST NUMBER: P927718

CATALOG NUMBER: DFN2DIP-HX4F0-090D080US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3756.2	3756.2	3756.2	3756.2	3756.2
2.5°	3773.1	3756.2	3718.6	3752.9	3746.1
5°	3756.2	3739.2	3694.9	3725.5	3715.4
7.5°	3725.5	3705.3	3657.7	3671.0	3654.1
10°	3684.8	3660.9	3593.2	3582.7	3562.5
12.5°	3633.9	3603.3	3511.3	3491.1	3453.5
15°	3572.6	3535.1	3419.7	3355.1	3321.2
17.5°	3501.2	3446.8	3303.9	3229.2	3174.8
20°	3419.7	3351.5	3181.6	3096.9	3021.8
22.5°	3331.3	3253.1	3055.8	2940.3	2889.5
25°	3243.0	3134.0	2909.7	2770.5	2719.3
27.5°	3137.7	3021.8	2773.7	2614.0	2535.7
30°	3025.5	2896.0	2624.1	2451.0	2359.0
32.5°	2916.5	2760.0	2481.6	2277.5	2192.4
35°	2794.3	2620.8	2321.8	2107.7	2032.6
37.5°	2675.3	2488.1	2172.2	1937.4	1852.7
40°	2549.4	2345.7	2015.7	1774.4	1686.1
42.5°	2420.3	2202.9	1859.4	1607.8	1523.0
45°	2284.4	2056.5	1699.7	1458.1	1376.6
47.5°	2155.2	1914.0	1546.8	1305.2	1230.5
50°	2012.4	1771.1	1397.2	1162.4	1091.3
52.5°	1872.9	1617.9	1254.4	1030.0	965.5
55°	1736.9	1471.8	1104.6	900.9	836.3
57.5°	1597.7	1325.8	972.3	781.9	727.5
60°	1454.8	1182.9	832.8	659.6	605.2
62.5°	1315.7	1043.7	713.7	550.7	523.7
65°	1172.8	897.3	591.4	476.0	465.6
67.5°	1036.9	761.3	476.0	418.0	407.9
70°	894.1	629.0	394.2	360.3	346.6
72.5°	758.1	506.3	329.6	302.5	295.8
75°	625.4	387.4	271.9	248.1	244.9
77.5°	493.0	275.2	214.2	200.5	193.7
80°	370.4	197.3	163.0	149.7	149.7
82.5°	258.2	132.7	112.2	105.3	105.3
85°	146.0	74.6	64.5	64.5	64.5
87.5°	54.4	27.1	27.1	23.8	23.8
90°	1.9	23.6	39.4	49.4	53.2
92.5°	49.4	41.5	47.4	51.3	53.2
95°	128.1	63.0	76.8	86.9	84.8
97.5°	230.7	69.1	100.5	106.6	108.5
100°	349.3	79.0	112.5	128.1	132.1
102.5°	479.4	475.5	116.4	137.9	144.1
105°	599.7	659.0	120.4	142.0	150.0
107.5°	739.8	789.0	124.4	145.9	153.9
110°	874.1	915.3	345.4	148.0	155.8

TEST NUMBER: P927718

CATALOG NUMBER: DFN2DIP-HX4F0-090D080US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1000.3	1035.7	1002.2	151.8	157.9
115°	1134.3	1167.8	1217.2	303.8	161.9
117.5°	1250.7	1290.1	1323.8	1041.5	524.8
120°	1381.0	1410.5	1446.1	1469.8	1203.4
122.5°	1491.3	1523.0	1562.6	1574.3	1576.4
125°	1603.8	1629.5	1667.0	1680.8	1686.7
127.5°	1706.4	1734.0	1763.8	1783.4	1785.3
130°	1803.1	1834.7	1856.3	1878.1	1876.2
132.5°	1901.8	1927.5	1949.1	1966.9	1965.0
135°	1984.7	2016.3	2033.8	2053.8	2049.8
137.5°	2071.4	2095.0	2114.9	2134.6	2128.8
140°	2156.1	2172.1	2193.7	2211.5	2201.6
142.5°	2227.4	2241.2	2266.7	2282.5	2272.6
145°	2302.3	2300.2	2333.7	2347.6	2337.7
147.5°	2367.3	2361.4	2394.8	2404.7	2397.0
150°	2430.5	2416.7	2448.3	2460.0	2450.2
152.5°	2483.7	2468.0	2497.4	2509.5	2495.6
155°	2535.0	2517.4	2541.1	2552.8	2537.1
157.5°	2576.4	2560.8	2578.5	2592.4	2576.4
160°	2612.0	2600.1	2612.0	2623.8	2609.9
162.5°	2643.5	2631.7	2641.5	2655.4	2637.6
165°	2671.1	2659.4	2665.3	2679.0	2665.3
167.5°	2692.8	2680.9	2687.0	2700.8	2683.0
170°	2710.7	2698.7	2702.7	2716.6	2698.7
172.5°	2722.4	2710.7	2714.6	2728.5	2710.7
175°	2732.2	2718.4	2722.4	2736.2	2716.6
177.5°	2736.2	2722.4	2724.4	2738.3	2720.5
180°	2726.4	2726.4	2726.4	2726.4	2726.4

TEST NUMBER: P927718

CATALOG NUMBER: DFN2DIP-HX4F0-090D080US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.64	11.46	11.61	12.44	13.73	6.61	7.43	7.58	8.41	9.70
	3H	12.32	13.05	13.30	14.04	15.35	7.80	8.54	8.78	9.53	10.83
	4H	12.92	13.62	13.92	14.61	15.93	8.25	8.95	9.25	9.94	11.26
	6H	13.35	13.99	14.35	14.99	16.31	8.57	9.22	9.58	10.21	11.54
	8H	13.47	14.08	14.49	15.10	16.42	8.67	9.28	9.68	10.29	11.61
	12H	13.54	14.11	14.55	15.12	16.47	8.71	9.29	9.73	10.30	11.65
4H	2H	10.66	11.35	11.66	12.34	13.66	7.21	7.90	8.21	8.90	10.21
	3H	12.49	13.06	13.50	14.09	15.42	8.56	9.14	9.57	10.16	11.49
	4H	13.18	13.71	14.20	14.72	16.07	9.11	9.64	10.12	10.65	12.00
	6H	13.69	14.15	14.72	15.19	16.54	9.53	9.98	10.56	11.02	12.37
	8H	13.87	14.29	14.90	15.32	16.69	9.66	10.08	10.69	11.11	12.48
	12H	13.96	14.35	15.01	15.39	16.76	9.72	10.11	10.77	11.15	12.52
8H	4H	13.15	13.57	14.18	14.60	15.97	9.39	9.81	10.42	10.84	12.21
	6H	13.71	14.06	14.77	15.14	16.50	9.91	10.26	10.96	11.33	12.69
	8H	13.93	14.24	14.99	15.30	16.68	10.10	10.41	11.16	11.47	12.85
	12H	14.07	14.34	15.13	15.39	16.82	10.22	10.49	11.28	11.54	12.97
12H	4H	13.10	13.48	14.14	14.53	15.90	9.39	9.77	10.44	10.82	12.19
	6H	13.69	14.00	14.75	15.05	16.44	9.96	10.26	11.02	11.32	12.70
	8H	13.91	14.18	14.97	15.23	16.66	10.17	10.44	11.23	11.49	12.92