

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927770

Luminaire Tested: DFN2DIP-HX4F0-100D120US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927770
REPORT IS A COMBINATION OF REPORTS P900976 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D120US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20579.7 lumens
Efficiency: N/A
Efficacy: 105.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 195.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927770

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927770

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	43	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	46	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3103	3103	3103
5°	3108	3054	3074
10°	3078	2995	2974
15°	3036	2896	2819
20°	2980	2760	2630
25°	2923	2607	2447
30°	2846	2451	2214
35°	2771	2282	2010
40°	2694	2108	1776
45°	2605	1915	1564
50°	2513	1719	1357
55°	2417	1511	1158
60°	2306	1293	953
65°	2178	1071	858
70°	2023	864	777
75°	1829	762	707
80°	1547	641	614
85°	1082	429	462

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2605 cd/sqm

TEST NUMBER: P927770

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	391.1	1.9
10°-20°	1073.8	5.2
20°-30°	1507.5	7.3
30°-40°	1643.3	8.0
40°-50°	1510.4	7.3
50°-60°	1186.2	5.8
60°-70°	772.1	3.8
70°-80°	397.4	1.9
80°-90°	108.7	0.5
90°-100°	134.8	0.7
100°-110°	502.7	2.4
110°-120°	1333.2	6.5
120°-130°	2211.3	10.7
130°-140°	2348.9	11.4
140°-150°	2183.0	10.6
150°-160°	1755.1	8.5
160°-170°	1130.9	5.5
170°-180°	389.2	1.9
0°-30°	2972.4	14.4
0°-40°	4615.8	22.4
0°-60°	7312.3	35.5
0°-90°	8590.5	41.7
90°-120°	1970.8	9.6
90°-150°	8714.0	42.3
90°-180°	11989.0	58.3
0°-180°	20579.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4174	4174	4174	4174	4174	
5°	4174	4155	4105	4140	4128	396
15°	3970	3928	3800	3728	3690	1119
25°	3603	3482	3233	3078	3021	1657
35°	3105	2912	2580	2342	2258	1943
45°	2538	2285	1889	1620	1530	1960
55°	1930	1635	1227	1001	929	1724
65°	1303	997	657	529	517	1292
75°	695	430	302	276	272	735
85°	162	83	72	72	72	186
90°	3	35	59	74	80	19
95°	192	94	115	130	127	228
105°	900	988	181	213	225	961
115°	1701	1752	1826	456	243	1675
125°	2406	2444	2501	2521	2530	2146
135°	2977	3024	3051	3081	3075	2300
145°	3454	3450	3501	3521	3506	2160
155°	3802	3776	3812	3829	3806	1752
165°	4007	3989	3998	4019	3998	1132
175°	4098	4078	4084	4104	4075	390
180°	4090	4090	4090	4090	4090	

TEST NUMBER: P927770

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4173.5	4173.5	4173.5	4173.5	4173.5
2.5°	4192.3	4173.5	4131.8	4169.9	4162.3
5°	4173.5	4154.6	4105.3	4139.5	4128.2
7.5°	4139.5	4117.0	4064.0	4078.9	4060.1
10°	4094.1	4067.7	3992.3	3980.7	3958.3
12.5°	4037.7	4003.6	3901.4	3878.9	3837.2
15°	3969.5	3927.8	3799.6	3727.9	3690.2
17.5°	3890.2	3829.7	3671.0	3588.0	3527.5
20°	3799.6	3723.8	3535.1	3441.0	3357.6
22.5°	3701.4	3614.5	3395.3	3267.1	3210.6
25°	3603.3	3482.3	3233.0	3078.3	3021.4
27.5°	3486.2	3357.6	3081.9	2904.4	2817.4
30°	3361.6	3217.7	2915.6	2723.3	2621.1
32.5°	3240.7	3066.7	2757.4	2530.6	2435.9
35°	3104.7	2912.1	2579.8	2341.8	2258.4
37.5°	2972.5	2764.5	2413.5	2152.7	2058.5
40°	2832.7	2606.3	2239.6	1971.5	1873.4
42.5°	2689.2	2447.6	2066.2	1786.4	1692.2
45°	2538.1	2284.9	1888.6	1620.1	1529.5
47.5°	2394.7	2126.6	1718.7	1450.2	1367.3
50°	2236.0	1967.9	1552.4	1291.5	1212.6
52.5°	2080.9	1797.6	1393.7	1144.4	1072.7
55°	1929.8	1635.4	1227.4	1001.0	929.2
57.5°	1775.2	1473.0	1080.4	868.7	808.2
60°	1616.5	1314.4	925.3	732.9	672.4
62.5°	1461.8	1159.7	793.0	611.9	581.8
65°	1303.1	997.0	657.2	528.9	517.3
67.5°	1152.1	845.9	528.9	464.4	453.2
70°	993.3	698.9	438.0	400.3	385.1
72.5°	842.3	562.6	366.3	336.2	328.6
75°	694.8	430.4	302.1	275.7	272.0
77.5°	547.8	305.8	238.0	222.8	215.2
80°	411.5	219.2	181.2	166.3	166.3
82.5°	286.9	147.4	124.6	117.0	117.0
85°	162.3	82.9	71.7	71.7	71.7
87.5°	60.5	30.1	30.1	26.5	26.5
90°	2.8	35.4	59.1	74.1	79.8
92.5°	74.1	62.2	71.0	76.9	79.8
95°	192.2	94.5	115.2	130.4	127.2
97.5°	346.2	103.7	150.8	159.9	162.7
100°	523.9	118.4	168.6	192.2	198.2
102.5°	719.0	713.3	174.6	207.0	216.1
105°	899.5	988.5	180.7	213.0	224.9
107.5°	1109.7	1183.5	186.6	218.9	230.8
110°	1311.0	1372.9	517.9	222.1	233.7

TEST NUMBER: P927770

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1500.5	1553.5	1503.3	227.7	236.8
115°	1701.4	1751.7	1825.8	455.7	242.9
117.5°	1876.1	1935.2	1985.8	1562.3	787.1
120°	2071.5	2115.7	2169.2	2204.7	1805.1
122.5°	2237.0	2284.5	2343.8	2361.4	2364.5
125°	2405.6	2444.3	2500.6	2521.3	2530.1
127.5°	2559.5	2601.0	2645.7	2675.2	2678.0
130°	2704.6	2752.1	2784.4	2817.1	2814.3
132.5°	2852.6	2891.3	2923.6	2950.3	2947.5
135°	2977.0	3024.5	3050.8	3080.7	3074.7
137.5°	3107.1	3142.5	3172.4	3201.9	3193.1
140°	3234.3	3258.1	3290.4	3317.2	3302.4
142.5°	3341.0	3361.8	3400.1	3423.6	3408.9
145°	3453.5	3450.4	3500.6	3521.4	3506.5
147.5°	3550.9	3542.1	3592.4	3607.1	3595.5
150°	3645.7	3625.0	3672.4	3690.0	3675.3
152.5°	3725.5	3701.9	3746.3	3764.1	3743.4
155°	3802.4	3776.0	3811.6	3829.2	3805.6
157.5°	3864.6	3841.1	3867.8	3888.5	3864.6
160°	3918.0	3900.2	3918.0	3935.6	3914.9
162.5°	3965.2	3947.6	3962.4	3983.1	3956.4
165°	4006.6	3989.0	3997.8	4018.6	3997.8
167.5°	4039.3	4021.3	4030.5	4051.2	4024.6
170°	4066.0	4048.1	4054.0	4074.7	4048.1
172.5°	4083.5	4066.0	4072.0	4092.7	4066.0
175°	4098.3	4077.6	4083.5	4104.3	4074.7
177.5°	4104.3	4083.5	4086.8	4107.5	4080.8
180°	4089.6	4089.6	4089.6	4089.6	4089.6

TEST NUMBER: P927770

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.26	11.03	11.29	12.06	13.45	6.23	7.00	7.26	8.03	9.42
	3H	11.93	12.62	12.97	13.66	15.07	7.42	8.10	8.46	9.15	10.55
	4H	12.54	13.19	13.59	14.23	15.65	7.87	8.52	8.92	9.56	10.98
	6H	12.96	13.56	14.02	14.61	16.03	8.19	8.78	9.25	9.83	11.26
	8H	13.08	13.65	14.15	14.72	16.14	8.28	8.84	9.34	9.91	11.33
	12H	13.14	13.68	14.22	14.74	16.19	8.32	8.86	9.39	9.92	11.36
4H	2H	10.27	10.92	11.33	11.97	13.38	6.82	7.47	7.88	8.52	9.93
	3H	12.10	12.64	13.16	13.71	15.13	8.17	8.71	9.23	9.78	11.21
	4H	12.79	13.28	13.86	14.34	15.79	8.71	9.21	9.79	10.27	11.72
	6H	13.30	13.72	14.38	14.81	16.25	9.13	9.56	10.21	10.64	12.09
	8H	13.47	13.87	14.55	14.95	16.41	9.26	9.66	10.34	10.74	12.19
	12H	13.57	13.92	14.66	15.02	16.48	9.32	9.68	10.42	10.77	12.24
8H	4H	12.75	13.14	13.83	14.22	15.68	8.99	9.39	10.07	10.47	11.92
	6H	13.31	13.64	14.42	14.76	16.22	9.51	9.84	10.61	10.96	12.41
	8H	13.53	13.82	14.64	14.92	16.40	9.70	9.99	10.81	11.09	12.57
	12H	13.67	13.92	14.78	15.02	16.53	9.82	10.07	10.93	11.17	12.68
12H	4H	12.70	13.06	13.80	14.15	15.61	8.99	9.35	10.09	10.44	11.91
	6H	13.29	13.58	14.40	14.68	16.15	9.56	9.84	10.67	10.95	12.42
	8H	13.51	13.76	14.62	14.86	16.37	9.77	10.02	10.88	11.12	12.63

END OF REPORT