

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927798

Luminaire Tested: DFN2DIP-HX4F0-110D100US840-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927798
REPORT IS A COMBINATION OF REPORTS P900942 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D100US840-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19438.7 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 188.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927798

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927798

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	40
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	35	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	36	42	36	32	35	31	28	29	26	24
7	59	47	39	34	55	44	37	32	38	33	29	32	28	25	27	24	21
8	55	43	35	30	51	40	33	29	35	29	26	30	25	22	25	22	19
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3414	3414	3414
5°	3419	3360	3381
10°	3386	3294	3271
15°	3339	3186	3101
20°	3278	3036	2893
25°	3215	2868	2691
30°	3131	2696	2436
35°	3048	2510	2211
40°	2964	2319	1954
45°	2866	2106	1721
50°	2765	1891	1493
55°	2659	1662	1274
60°	2537	1422	1049
65°	2396	1178	944
70°	2226	950	855
75°	2012	838	778
80°	1702	704	675
85°	1190	472	509

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2866 cd/sqm

TEST NUMBER: P927798

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	430.3	2.2
10°-20°	1181.1	6.1
20°-30°	1658.3	8.5
30°-40°	1807.6	9.3
40°-50°	1661.4	8.5
50°-60°	1304.8	6.7
60°-70°	849.3	4.4
70°-80°	437.2	2.2
80°-90°	117.6	0.6
90°-100°	112.4	0.6
100°-110°	418.9	2.2
110°-120°	1111.0	5.7
120°-130°	1842.7	9.5
130°-140°	1957.4	10.1
140°-150°	1819.2	9.4
150°-160°	1462.6	7.5
160°-170°	942.4	4.8
170°-180°	324.4	1.7
0°-30°	3269.7	16.8
0°-40°	5077.3	26.1
0°-60°	8043.5	41.4
0°-90°	9447.6	48.6
90°-120°	1642.3	8.4
90°-150°	7261.7	37.4
90°-180°	9991.0	51.4
0°-180°	19438.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4591	4591	4591	4591	4591	
5°	4591	4570	4516	4553	4541	435
15°	4366	4321	4180	4101	4059	1230
25°	3964	3830	3556	3386	3324	1823
35°	3415	3203	2838	2576	2484	2138
45°	2792	2513	2078	1782	1682	2156
55°	2123	1799	1350	1101	1022	1897
65°	1433	1097	723	582	569	1421
75°	764	473	332	303	299	808
85°	178	91	79	79	79	205
90°	2	30	49	62	66	18
95°	160	79	96	109	106	190
105°	750	824	151	177	187	801
115°	1418	1460	1522	380	202	1396
125°	2005	2037	2084	2101	2108	1788
135°	2481	2520	2542	2567	2562	1916
145°	2878	2875	2917	2934	2922	1800
155°	3169	3147	3176	3191	3171	1460
165°	3339	3324	3332	3349	3332	943
175°	3415	3398	3403	3420	3396	325
180°	3408	3408	3408	3408	3408	

TEST NUMBER: P927798

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4590.9	4590.9	4590.9	4590.9	4590.9
2.5°	4611.6	4590.9	4545.0	4586.9	4578.5
5°	4590.9	4570.2	4515.9	4553.4	4541.1
7.5°	4553.4	4528.7	4470.5	4486.8	4466.0
10°	4503.6	4474.4	4391.6	4378.8	4354.2
12.5°	4441.4	4403.9	4291.5	4266.8	4221.0
15°	4366.5	4320.6	4179.6	4100.7	4059.2
17.5°	4279.2	4212.7	4038.1	3946.8	3880.3
20°	4179.6	4096.3	3888.6	3785.0	3693.3
22.5°	4071.6	3975.9	3734.8	3593.8	3531.6
25°	3963.6	3830.5	3556.3	3386.2	3323.6
27.5°	3834.9	3693.3	3390.1	3194.8	3099.2
30°	3697.8	3539.6	3207.2	2995.6	2883.2
32.5°	3564.7	3373.3	3033.0	2783.6	2679.6
35°	3415.2	3203.2	2837.8	2576.0	2484.3
37.5°	3269.8	3041.0	2654.9	2367.9	2264.4
40°	3115.9	2866.9	2463.6	2168.6	2060.7
42.5°	2958.1	2692.3	2272.8	1965.1	1861.5
45°	2792.0	2513.4	2077.5	1782.1	1682.5
47.5°	2634.2	2339.3	1890.5	1595.2	1504.0
50°	2459.6	2164.7	1707.7	1420.7	1333.8
52.5°	2289.0	1977.4	1533.1	1258.9	1180.0
55°	2122.8	1798.9	1350.1	1101.1	1022.2
57.5°	1952.8	1620.3	1188.3	955.7	889.0
60°	1778.2	1445.8	1017.8	806.2	739.7
62.5°	1608.0	1275.7	872.4	673.1	640.0
65°	1433.4	1096.6	722.9	581.8	569.0
67.5°	1267.3	930.5	581.8	510.9	498.5
70°	1092.7	768.8	481.8	440.4	423.6
72.5°	926.5	618.9	402.9	369.8	361.4
75°	764.3	473.4	332.3	303.2	299.3
77.5°	602.5	336.4	261.8	245.1	236.7
80°	452.7	241.1	199.2	183.0	183.0
82.5°	315.6	162.2	137.1	128.7	128.7
85°	178.5	91.3	78.9	78.9	78.9
87.5°	66.5	33.0	33.0	29.1	29.1
90°	2.3	29.6	49.2	61.8	66.4
92.5°	61.8	51.8	59.2	64.1	66.4
95°	160.2	78.8	96.0	108.7	106.0
97.5°	288.4	86.3	125.6	133.2	135.6
100°	436.6	98.7	140.6	160.2	165.2
102.5°	599.1	594.5	145.5	172.5	180.0
105°	749.7	823.7	150.6	177.4	187.4
107.5°	924.8	986.3	155.5	182.5	192.4
110°	1092.5	1144.1	431.6	185.1	194.7

TEST NUMBER: P927798

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1250.3	1294.6	1252.8	189.7	197.4
115°	1417.9	1459.8	1521.6	379.8	202.4
117.5°	1563.4	1612.7	1654.8	1301.9	656.0
120°	1726.3	1763.1	1807.6	1837.2	1504.3
122.5°	1864.2	1903.7	1953.2	1967.8	1970.4
125°	2004.8	2037.0	2083.8	2101.1	2108.4
127.5°	2133.0	2167.5	2204.7	2229.3	2231.7
130°	2253.9	2293.5	2320.4	2347.6	2345.3
132.5°	2377.2	2409.4	2436.3	2458.6	2456.2
135°	2480.9	2520.4	2542.4	2567.2	2562.3
137.5°	2589.2	2618.8	2643.7	2668.3	2660.9
140°	2695.2	2715.2	2742.0	2764.3	2752.0
142.5°	2784.2	2801.5	2833.4	2853.0	2840.8
145°	2877.9	2875.3	2917.2	2934.5	2922.2
147.5°	2959.0	2951.7	2993.6	3005.9	2996.3
150°	3038.1	3020.8	3060.4	3075.0	3062.7
152.5°	3104.5	3084.9	3121.9	3136.7	3119.5
155°	3168.8	3146.7	3176.3	3191.0	3171.4
157.5°	3220.6	3201.0	3223.2	3240.4	3220.6
160°	3265.1	3250.1	3265.1	3279.7	3262.5
162.5°	3304.3	3289.6	3301.9	3319.2	3297.0
165°	3338.8	3324.2	3331.5	3348.8	3331.5
167.5°	3366.1	3351.1	3358.8	3376.1	3353.7
170°	3388.3	3373.4	3378.4	3395.7	3373.4
172.5°	3402.9	3388.3	3393.3	3410.6	3388.3
175°	3415.2	3398.0	3402.9	3420.3	3395.7
177.5°	3420.3	3402.9	3405.7	3422.9	3400.6
180°	3408.0	3408.0	3408.0	3408.0	3408.0

TEST NUMBER: P927798

CATALOG NUMBER: DFN2DIP-HX4F0-110D100US840-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.28	12.10	12.26	13.08	14.38	7.25	8.07	8.23	9.06	10.35
	3H	12.96	13.69	13.95	14.68	16.00	8.44	9.18	9.43	10.17	11.49
	4H	13.57	14.26	14.57	15.26	16.58	8.90	9.59	9.90	10.58	11.91
	6H	13.99	14.63	15.00	15.63	16.96	9.22	9.85	10.23	10.86	12.19
	8H	14.12	14.72	15.13	15.74	17.07	9.31	9.91	10.32	10.93	12.27
	12H	14.18	14.75	15.20	15.77	17.12	9.35	9.93	10.37	10.94	12.30
4H	2H	11.30	11.99	12.30	12.99	14.31	7.85	8.54	8.86	9.54	10.86
	3H	13.13	13.70	14.14	14.73	16.07	9.20	9.78	10.22	10.80	12.14
	4H	13.82	14.35	14.84	15.37	16.73	9.75	10.28	10.77	11.29	12.65
	6H	14.34	14.79	15.37	15.83	17.19	10.17	10.62	11.20	11.66	13.02
	8H	14.51	14.93	15.55	15.97	17.34	10.30	10.72	11.33	11.76	13.13
	12H	14.61	14.99	15.66	16.04	17.41	10.37	10.75	11.42	11.80	13.17
8H	4H	13.79	14.21	14.82	15.24	16.62	10.03	10.45	11.06	11.49	12.86
	6H	14.35	14.70	15.41	15.78	17.15	10.55	10.90	11.61	11.97	13.34
	8H	14.57	14.88	15.64	15.94	17.33	10.74	11.05	11.81	12.11	13.50
	12H	14.71	14.98	15.78	16.04	17.47	10.86	11.13	11.93	12.19	13.62
12H	4H	13.74	14.12	14.79	15.17	16.55	10.03	10.41	11.09	11.46	12.84
	6H	14.33	14.64	15.40	15.70	17.09	10.60	10.91	11.66	11.97	13.36
	8H	14.55	14.82	15.62	15.88	17.31	10.81	11.08	11.88	12.14	13.57

END OF REPORT