

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918983

Luminaire Tested: DFN2DIP-HX3F0-070D030US935-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918983
REPORT IS A COMBINATION OF REPORTS P900729 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-070D030US935-FLLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8523.9 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 92.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918983
CATALOG NUMBER: DFN2DIP-HX3F0-070D030US935-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P918983

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	75	75	75	75	75	75	70
1	102	98	94	90	97	93	89	86	83	80	78	74	72	70	66	64	63	63	63	63	59
2	93	85	79	74	88	81	75	71	73	68	64	65	62	59	58	55	53	53	53	53	49
3	85	75	68	62	80	71	65	59	64	59	54	58	53	50	51	48	45	45	45	45	42
4	78	67	58	52	73	63	56	50	57	51	46	51	47	43	46	42	39	39	39	39	36
5	72	60	51	45	67	57	49	43	51	45	40	46	41	37	41	37	34	34	34	34	31
6	66	54	45	39	62	51	43	38	46	40	35	42	37	33	38	33	30	30	30	30	27
7	61	48	40	34	58	46	39	33	42	36	31	38	33	29	34	30	27	27	27	27	24
8	57	44	36	31	54	42	35	30	38	32	28	35	30	26	32	27	24	24	24	24	22
9	53	40	33	27	50	39	32	27	35	29	25	32	27	23	29	25	22	22	22	22	20
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	20	20	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2716	2716	2716
5°	2720	2677	2695
10°	2696	2639	2657
15°	2656	2593	2599
20°	2601	2531	2539
25°	2546	2457	2470
30°	2478	2388	2383
35°	2413	2307	2290
40°	2334	2225	2202
45°	2255	2142	2112
50°	2168	2056	2008
55°	2077	1956	1912
60°	1975	1837	1802
65°	1862	1714	1672
70°	1720	1564	1532
75°	1522	1384	1401
80°	1283	1154	1153
85°	910	764	748

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2255 cd/sqm



TEST NUMBER: P918983

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	220.7	2.6
10°-20°	621.0	7.3
20°-30°	912.7	10.7
30°-40°	1060.0	12.4
40°-50°	1058.7	12.4
50°-60°	923.2	10.8
60°-70°	682.4	8.0
70°-80°	386.1	4.5
80°-90°	103.5	1.2
90°-100°	28.7	0.3
100°-110°	107.2	1.3
110°-120°	284.2	3.3
120°-130°	471.3	5.5
130°-140°	500.7	5.9
140°-150°	465.3	5.5
150°-160°	374.1	4.4
160°-170°	241.1	2.8
170°-180°	83.0	1.0
0°-30°	1754.4	20.6
0°-40°	2814.4	33.0
0°-60°	4796.3	56.3
0°-90°	5968.3	70.0
90°-120°	420.1	4.9
90°-150°	1857.5	21.8
90°-180°	2556.0	30.0
0°-180°	8523.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2345	2345	2345	2345	2345	
5°	2345	2336	2311	2329	2325	223
15°	2232	2219	2190	2199	2188	629
25°	2020	2002	1964	1969	1964	930
35°	1743	1721	1684	1671	1660	1089
45°	1418	1403	1369	1344	1335	1095
55°	1074	1060	1033	1006	994	960
65°	724	710	688	668	656	716
75°	379	374	363	350	354	404
85°	92	90	88	81	79	103
90°	1	8	13	16	17	8
95°	41	20	24	28	27	49
105°	192	211	38	45	48	205
115°	363	373	389	97	52	357
125°	513	521	533	537	539	457
135°	635	645	650	657	655	490
145°	736	736	746	751	747	460
155°	810	805	812	816	811	373
165°	854	850	852	857	852	241
175°	874	869	870	875	869	83
180°	872	872	872	872	872	



TEST NUMBER: P918983

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2345.1	2345.1	2345.1	2345.1	2345.1
2.5°	2358.8	2347.5	2322.6	2345.1	2340.8
5°	2345.1	2336.3	2311.4	2329.3	2325.0
7.5°	2329.3	2315.9	2291.0	2309.3	2304.7
10°	2304.7	2288.9	2261.8	2279.8	2273.1
12.5°	2270.7	2257.4	2230.3	2241.5	2237.0
15°	2232.5	2219.0	2189.6	2198.7	2187.5
17.5°	2185.0	2171.7	2142.2	2153.5	2142.2
20°	2133.1	2119.8	2088.2	2094.9	2086.0
22.5°	2081.5	2061.1	2031.7	2031.7	2027.1
25°	2020.5	2002.5	1964.3	1968.6	1964.3
27.5°	1952.7	1937.0	1907.8	1901.1	1889.8
30°	1885.3	1867.1	1833.4	1826.7	1817.6
32.5°	1813.0	1799.7	1763.5	1749.9	1740.8
35°	1743.2	1720.7	1684.5	1670.9	1659.7
37.5°	1664.2	1643.9	1607.7	1592.0	1580.7
40°	1583.1	1564.9	1528.8	1508.7	1499.6
42.5°	1504.2	1486.0	1450.1	1427.4	1413.9
45°	1418.5	1402.7	1368.7	1344.1	1335.0
47.5°	1335.0	1319.2	1283.1	1258.2	1244.8
50°	1247.0	1235.7	1204.1	1172.6	1161.3
52.5°	1161.3	1145.6	1116.4	1091.5	1075.6
55°	1073.5	1059.9	1032.9	1005.8	994.5
57.5°	985.5	974.2	944.8	917.7	908.7
60°	897.4	888.5	857.0	832.2	825.4
62.5°	811.7	796.0	773.5	751.0	741.9
65°	724.0	710.3	687.9	667.5	656.3
67.5°	633.8	622.3	602.2	586.4	577.3
70°	550.3	541.2	520.8	505.1	496.2
72.5°	464.6	455.6	444.3	428.5	421.8
75°	378.8	374.4	362.9	349.6	354.1
77.5°	302.2	293.1	288.5	281.8	275.2
80°	225.6	223.3	218.7	212.0	207.4
82.5°	153.3	153.3	151.2	142.2	142.2
85°	92.4	90.2	88.1	81.1	79.0
87.5°	40.6	36.2	31.6	24.9	22.5
90°	0.6	7.6	12.6	15.8	17.0
92.5°	15.8	13.3	15.2	16.4	17.0
95°	41.0	20.1	24.5	27.8	27.1
97.5°	73.8	22.1	32.1	34.1	34.7
100°	111.7	25.2	36.0	41.0	42.3
102.5°	153.3	152.1	37.2	44.1	46.1
105°	191.7	210.7	38.5	45.4	48.0
107.5°	236.5	252.3	39.8	46.7	49.2
110°	279.5	292.7	110.4	47.4	49.9



TEST NUMBER: P918983

CATALOG NUMBER: DFN2DIP-HX3F0-070D030US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	319.9	331.1	320.5	48.6	50.5
115°	362.7	373.4	389.2	97.1	51.7
117.5°	399.9	412.5	423.3	333.0	167.8
120°	441.5	451.0	462.4	469.9	384.8
122.5°	476.8	487.0	499.6	503.3	504.0
125°	512.8	521.0	533.0	537.4	539.3
127.5°	545.6	554.4	564.0	570.2	570.8
130°	576.5	586.7	593.6	600.5	599.9
132.5°	608.0	616.3	623.2	628.9	628.3
135°	634.6	644.7	650.3	656.7	655.4
137.5°	662.3	669.9	676.2	682.5	680.6
140°	689.4	694.5	701.4	707.1	704.0
142.5°	712.2	716.6	724.8	729.8	726.7
145°	736.2	735.5	746.2	750.6	747.4
147.5°	756.9	755.0	765.8	768.9	766.4
150°	777.1	772.7	782.8	786.5	783.4
152.5°	794.1	789.1	798.6	802.4	798.0
155°	810.5	804.9	812.4	816.2	811.2
157.5°	823.8	818.8	824.5	828.9	823.8
160°	835.2	831.4	835.2	839.0	834.5
162.5°	845.2	841.5	844.6	849.0	843.3
165°	854.0	850.3	852.2	856.6	852.2
167.5°	861.0	857.2	859.1	863.6	857.9
170°	866.7	862.9	864.2	868.6	862.9
172.5°	870.5	866.7	868.0	872.4	866.7
175°	873.6	869.2	870.5	874.9	868.6
177.5°	874.9	870.5	871.2	875.5	869.9
180°	871.8	871.8	871.8	871.8	871.8



TEST NUMBER: P918983
 CATALOG NUMBER: DFN2DIP-HX3F0-070D030US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.37	13.45	13.13	14.23	15.19	11.94	13.02	12.71	13.80	14.76
	3H	14.04	15.01	14.82	15.80	16.79	13.57	14.54	14.35	15.33	16.32
	4H	14.63	15.54	15.43	16.35	17.34	14.16	15.07	14.96	15.88	16.87
	6H	15.04	15.88	15.84	16.69	17.70	14.57	15.41	15.37	16.22	17.23
	8H	15.14	15.95	15.96	16.78	17.79	14.67	15.48	15.49	16.31	17.32
	12H	15.20	15.96	16.02	16.79	17.82	14.72	15.49	15.54	16.31	17.35
4H	2H	12.86	13.77	13.65	14.57	15.57	12.51	13.42	13.31	14.23	15.22
	3H	14.73	15.49	15.54	16.33	17.34	14.34	15.10	15.15	15.94	16.95
	4H	15.45	16.14	16.27	16.98	18.02	15.05	15.74	15.87	16.58	17.62
	6H	15.97	16.57	16.81	17.43	18.47	15.56	16.16	16.40	17.03	18.07
	8H	16.12	16.68	16.96	17.54	18.59	15.71	16.27	16.56	17.13	18.19
	12H	16.20	16.70	17.06	17.58	18.64	15.78	16.29	16.65	17.17	18.23
8H	4H	15.66	16.22	16.50	17.08	18.13	15.30	15.86	16.15	16.72	17.78
	6H	16.29	16.75	17.16	17.65	18.71	15.93	16.40	16.80	17.29	18.35
	8H	16.51	16.92	17.39	17.81	18.89	16.14	16.56	17.03	17.45	18.52
	12H	16.64	17.01	17.53	17.89	19.02	16.26	16.63	17.15	17.51	18.64
12H	4H	15.65	16.16	16.52	17.04	18.10	15.30	15.81	16.17	16.69	17.75
	6H	16.32	16.73	17.20	17.63	18.70	15.97	16.39	16.86	17.28	18.35
	8H	16.57	16.93	17.45	17.82	18.94	16.21	16.58	17.10	17.46	18.59