

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921640

Luminaire Tested: DFN2DIP-HX3F0-040D030US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921640
REPORT IS A COMBINATION OF REPORTS P899204 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-040D030US940-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5399.3 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921640

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921640

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1708	1708	1708
5°	1710	1679	1690
10°	1692	1645	1634
15°	1668	1590	1549
20°	1636	1514	1443
25°	1604	1428	1342
30°	1561	1341	1214
35°	1518	1248	1101
40°	1475	1151	972
45°	1425	1044	855
50°	1373	936	741
55°	1319	821	631
60°	1256	701	519
65°	1184	578	466
70°	1096	465	420
75°	986	407	380
80°	826	337	327
85°	565	220	240

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1425 cd/sqm

TEST NUMBER: P921640

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	2.6
10°-20°	379.3	7.0
20°-30°	532.5	9.9
30°-40°	580.5	10.8
40°-50°	533.5	9.9
50°-60°	419.0	7.8
60°-70°	272.7	5.1
70°-80°	140.4	2.6
80°-90°	38.2	0.7
90°-100°	52.3	1.0
100°-110°	166.3	3.1
110°-120°	284.7	5.3
120°-130°	374.4	6.9
130°-140°	420.2	7.8
140°-150°	412.1	7.6
150°-160°	345.7	6.4
160°-170°	229.2	4.2
170°-180°	80.1	1.5
0°-30°	1049.9	19.4
0°-40°	1630.4	30.2
0°-60°	2582.9	47.8
0°-90°	3034.2	56.2
90°-120°	503.4	9.3
90°-150°	1710.0	31.7
90°-180°	2365.0	43.8
0°-180°	5399.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	9	25	24	24	5
95°	37	44	46	46	44	41
105°	154	156	157	158	158	162
115°	286	290	288	288	286	283
125°	416	422	420	418	417	371
135°	537	545	547	546	544	415
145°	652	658	662	662	660	408
155°	746	748	750	754	752	343
165°	812	811	811	816	812	229
175°	844	842	841	846	842	80
180°	846	846	846	846	846	

TEST NUMBER: P921640

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	0.8	9.2	25.0	23.5	24.3
92.5°	15.8	21.4	22.2	22.9	22.9
95°	37.3	44.4	45.7	45.7	44.4
97.5°	62.0	68.6	71.4	71.4	71.4
100°	90.5	96.4	98.4	98.4	97.7
102.5°	120.6	125.0	127.8	128.6	127.8
105°	153.6	155.6	157.1	158.4	158.4
107.5°	186.2	189.2	189.2	189.8	186.2
110°	217.8	221.9	221.9	221.9	219.9

TEST NUMBER: P921640

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	252.0	256.4	255.6	253.5	252.0
115°	285.7	289.7	288.5	287.8	285.7
117.5°	319.1	324.7	321.1	319.1	317.0
120°	352.8	358.4	352.8	352.8	350.4
122.5°	383.3	390.5	386.9	384.9	383.3
125°	415.5	421.9	419.8	417.5	416.8
127.5°	446.8	454.8	452.0	448.9	446.8
130°	476.2	485.4	484.1	482.6	479.7
132.5°	509.1	516.2	516.7	513.2	511.1
135°	537.4	545.3	546.9	546.1	544.0
137.5°	569.0	575.4	576.7	576.2	573.1
140°	596.8	603.2	606.8	606.8	604.0
142.5°	625.4	631.8	633.8	634.6	631.8
145°	652.5	657.5	661.6	662.4	659.6
147.5°	676.7	683.1	686.1	687.4	684.6
150°	701.7	706.1	708.8	711.1	708.8
152.5°	723.9	728.2	731.7	734.6	731.7
155°	746.1	748.1	750.4	753.9	751.7
157.5°	765.2	766.7	768.0	773.1	769.5
160°	782.3	783.8	784.6	788.9	785.9
162.5°	798.1	798.1	798.9	803.7	800.1
165°	811.6	810.8	810.8	815.9	812.3
167.5°	823.9	821.5	821.5	826.6	823.0
170°	833.0	831.0	830.3	835.4	831.0
172.5°	839.4	837.4	836.6	841.7	837.4
175°	844.5	842.5	841.0	846.1	841.7
177.5°	847.3	845.3	843.7	848.1	843.7
180°	846.1	846.1	846.1	846.1	846.1

TEST NUMBER: P921640

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.52	10.41	10.43	11.33	12.51	5.50	6.38	6.41	7.30	8.49
	3H	11.20	11.99	12.12	12.92	14.13	6.69	7.48	7.61	8.41	9.62
	4H	11.80	12.55	12.74	13.49	14.70	7.14	7.88	8.07	8.82	10.04
	6H	12.22	12.91	13.17	13.85	15.08	7.46	8.14	8.40	9.09	10.32
	8H	12.34	13.00	13.30	13.96	15.18	7.55	8.20	8.50	9.16	10.39
	12H	12.40	13.03	13.36	13.98	15.23	7.59	8.21	8.55	9.16	10.42
4H	2H	9.54	10.29	10.49	11.23	12.45	6.09	6.84	7.04	7.78	9.00
	3H	11.37	11.99	12.32	12.96	14.19	7.44	8.06	8.40	9.03	10.26
	4H	12.06	12.62	13.02	13.59	14.84	7.99	8.56	8.95	9.52	10.77
	6H	12.57	13.06	13.54	14.04	15.30	8.41	8.90	9.38	9.88	11.14
	8H	12.74	13.20	13.72	14.17	15.44	8.54	8.99	9.51	9.97	11.24
	12H	12.83	13.24	13.83	14.24	15.51	8.60	9.01	9.59	10.01	11.28
8H	4H	12.03	12.48	13.00	13.46	14.73	8.27	8.72	9.25	9.70	10.97
	6H	12.59	12.96	13.59	13.99	15.25	8.78	9.16	9.79	10.18	11.45
	8H	12.80	13.13	13.81	14.14	15.43	8.97	9.30	9.98	10.31	11.60
	12H	12.94	13.23	13.95	14.23	15.56	9.09	9.38	10.10	10.38	11.72
12H	4H	11.98	12.39	12.98	13.39	14.66	8.28	8.69	9.27	9.68	10.96
	6H	12.56	12.89	13.57	13.90	15.19	8.83	9.16	9.84	10.17	11.46
	8H	12.78	13.07	13.79	14.08	15.41	9.04	9.33	10.05	10.33	11.67

END OF REPORT