

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921680

Luminaire Tested: DFN2DIP-HX3F0-050D070US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921680
REPORT IS A COMBINATION OF REPORTS P899262 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-050D070US940-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9314.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 98.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921680

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P921680

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US940-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	27	23	19	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2134	2134	2134
5°	2137	2099	2113
10°	2115	2056	2043
15°	2085	1987	1936
20°	2045	1892	1804
25°	2005	1786	1677
30°	1951	1677	1517
35°	1898	1560	1376
40°	1844	1439	1215
45°	1781	1305	1069
50°	1717	1170	926
55°	1649	1026	789
60°	1570	876	648
65°	1480	723	582
70°	1371	581	525
75°	1233	509	475
80°	1033	422	408
85°	706	275	300

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1857 cd/sqm

TEST NUMBER: P921680

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US940-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	1.9
10°-20°	474.1	5.1
20°-30°	665.6	7.1
30°-40°	725.6	7.8
40°-50°	666.9	7.2
50°-60°	523.7	5.6
60°-70°	340.9	3.7
70°-80°	175.5	1.9
80°-90°	50.4	0.5
90°-100°	122.2	1.3
100°-110°	388.1	4.2
110°-120°	664.2	7.1
120°-130°	873.6	9.4
130°-140°	980.5	10.5
140°-150°	961.5	10.3
150°-160°	806.6	8.7
160°-170°	534.9	5.7
170°-180°	187.0	2.0
0°-30°	1312.4	14.1
0°-40°	2038.0	21.9
0°-60°	3228.6	34.7
0°-90°	3795.4	40.7
90°-120°	1174.5	12.6
90°-150°	3990.1	42.8
90°-180°	5519.0	59.3
0°-180°	9314.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1843	1843	1843	1843	1843	
5°	1843	1834	1813	1828	1823	175
15°	1753	1734	1678	1646	1629	494
25°	1591	1538	1427	1359	1334	732
35°	1371	1286	1139	1034	997	858
45°	1121	1009	834	715	675	865
55°	852	722	542	442	410	761
65°	575	440	290	234	228	570
75°	307	190	133	122	120	324
85°	72	37	32	32	32	82
90°	2	21	58	55	56	9
95°	87	104	107	107	104	97
105°	358	363	367	370	370	378
115°	667	676	673	671	667	659
125°	970	984	980	974	972	866
135°	1254	1272	1276	1274	1269	969
145°	1522	1534	1544	1546	1539	951
155°	1741	1746	1751	1759	1754	801
165°	1894	1892	1892	1904	1896	534
175°	1970	1966	1962	1974	1964	187
180°	1974	1974	1974	1974	1974	

TEST NUMBER: P921680

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US940-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1842.7	1842.7	1842.7	1842.7	1842.7
2.5°	1851.0	1842.7	1824.4	1841.1	1837.7
5°	1842.7	1834.4	1812.7	1827.6	1822.7
7.5°	1827.6	1817.8	1794.4	1801.0	1792.6
10°	1807.7	1796.0	1762.7	1757.7	1747.7
12.5°	1782.7	1767.7	1722.6	1712.7	1694.2
15°	1752.7	1734.3	1677.7	1646.0	1629.3
17.5°	1717.6	1691.0	1620.9	1584.2	1557.5
20°	1677.7	1644.2	1560.8	1519.3	1482.5
22.5°	1634.3	1595.9	1499.1	1442.5	1417.6
25°	1590.9	1537.5	1427.4	1359.1	1334.0
27.5°	1539.3	1482.5	1360.8	1282.4	1244.0
30°	1484.3	1420.8	1287.4	1202.4	1157.3
32.5°	1430.8	1354.1	1217.5	1117.3	1075.6
35°	1370.8	1285.8	1139.1	1033.9	997.2
37.5°	1312.4	1220.7	1065.7	950.5	908.9
40°	1250.7	1150.8	988.8	870.5	827.2
42.5°	1187.4	1080.7	912.2	788.7	747.2
45°	1120.7	1008.9	833.8	715.3	675.3
47.5°	1057.3	939.0	758.8	640.3	603.7
50°	987.3	868.9	685.5	570.2	535.4
52.5°	918.8	793.7	615.4	505.3	473.7
55°	852.1	722.0	541.9	441.9	410.3
57.5°	783.8	650.4	477.0	383.6	356.9
60°	713.7	580.3	408.5	323.6	296.9
62.5°	645.4	512.0	350.2	270.2	256.9
65°	575.3	440.2	290.2	233.5	228.5
67.5°	508.6	373.5	233.5	205.1	200.1
70°	438.6	308.5	193.4	176.7	170.0
72.5°	371.9	248.4	161.8	148.5	145.1
75°	306.8	190.0	133.4	121.7	120.1
77.5°	241.8	135.0	105.1	98.4	95.0
80°	181.7	96.8	80.0	73.4	73.4
82.5°	126.7	65.1	55.0	51.6	51.6
85°	71.7	36.6	31.7	31.7	31.7
87.5°	26.8	13.3	13.3	11.7	11.7
90°	1.8	21.4	58.3	54.8	56.5
92.5°	36.9	50.0	51.8	53.6	53.6
95°	86.9	103.5	106.6	106.6	103.5
97.5°	144.6	160.1	166.7	166.7	166.7
100°	211.2	225.0	229.7	229.7	227.9
102.5°	281.5	291.6	298.2	300.0	298.2
105°	358.3	363.0	366.6	369.6	369.6
107.5°	434.4	441.6	441.6	442.8	434.4
110°	508.3	517.8	517.8	517.8	513.0

TEST NUMBER: P921680

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US940-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.0	598.2	596.4	591.6	588.0
115°	666.6	676.1	673.2	671.4	666.6
117.5°	744.5	757.6	749.3	744.5	739.8
120°	823.0	836.2	823.0	823.0	817.7
122.5°	894.5	911.1	902.9	898.0	894.5
125°	969.5	984.4	979.6	974.3	972.5
127.5°	1042.7	1061.1	1054.6	1047.5	1042.7
130°	1111.2	1132.6	1129.6	1126.1	1119.5
132.5°	1187.9	1204.6	1205.8	1197.5	1192.7
135°	1254.0	1272.4	1276.0	1274.2	1269.4
137.5°	1327.8	1342.6	1345.6	1344.4	1337.3
140°	1392.7	1407.6	1415.9	1415.9	1409.3
142.5°	1459.3	1474.2	1478.9	1480.7	1474.2
145°	1522.4	1534.3	1543.8	1545.6	1539.1
147.5°	1579.0	1593.8	1601.0	1603.9	1597.4
150°	1637.3	1647.3	1653.9	1659.3	1653.9
152.5°	1689.0	1699.2	1707.4	1714.0	1707.4
155°	1740.8	1745.5	1751.0	1759.3	1753.9
157.5°	1785.5	1789.0	1792.0	1803.9	1795.5
160°	1825.3	1828.9	1830.7	1840.8	1833.6
162.5°	1862.2	1862.2	1864.0	1875.3	1867.0
165°	1893.7	1891.9	1891.9	1903.9	1895.5
167.5°	1922.3	1917.0	1917.0	1928.9	1920.6
170°	1943.8	1939.0	1937.2	1949.1	1939.0
172.5°	1958.6	1953.8	1952.0	1964.0	1953.8
175°	1970.5	1965.8	1962.2	1974.1	1964.0
177.5°	1977.1	1972.3	1968.7	1978.9	1968.7
180°	1974.1	1974.1	1974.1	1974.1	1974.1

TEST NUMBER: P921680

CATALOG NUMBER: DFN2DIP-HX3F0-050D070US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.81	9.57	9.85	10.61	12.01	4.78	5.54	5.82	6.58	7.98
	3H	10.47	11.15	11.52	12.20	13.62	5.96	6.64	7.01	7.69	9.11
	4H	11.07	11.71	12.13	12.77	14.19	6.41	7.05	7.47	8.10	9.53
	6H	11.48	12.07	12.55	13.13	14.57	6.72	7.31	7.79	8.37	9.80
	8H	11.60	12.17	12.68	13.24	14.67	6.81	7.37	7.88	8.44	9.87
	12H	11.66	12.19	12.74	13.26	14.72	6.84	7.38	7.92	8.44	9.90
4H	2H	8.81	9.46	9.88	10.51	11.94	5.37	6.01	6.43	7.06	8.49
	3H	10.63	11.16	11.70	12.24	13.68	6.70	7.24	7.78	8.32	9.76
	4H	11.31	11.80	12.39	12.87	14.33	7.24	7.74	8.32	8.81	10.27
	6H	11.82	12.24	12.90	13.33	14.78	7.66	8.08	8.74	9.17	10.62
	8H	11.99	12.38	13.07	13.46	14.93	7.78	8.17	8.87	9.26	10.73
	12H	12.07	12.43	13.18	13.53	15.00	7.84	8.19	8.94	9.29	10.77
8H	4H	11.27	11.67	12.36	12.75	14.22	7.52	7.91	8.60	8.99	10.46
	6H	11.83	12.15	12.94	13.28	14.75	8.02	8.35	9.14	9.48	10.94
	8H	12.04	12.32	13.16	13.43	14.92	8.21	8.50	9.33	9.60	11.09
	12H	12.17	12.42	13.29	13.52	15.05	8.32	8.57	9.44	9.68	11.20
12H	4H	11.22	11.58	12.33	12.68	14.15	7.52	7.87	8.62	8.97	10.44
	6H	11.80	12.09	12.92	13.20	14.68	8.07	8.36	9.19	9.47	10.95
	8H	12.02	12.27	13.14	13.37	14.90	8.27	8.52	9.39	9.63	11.15

END OF REPORT

FIELD PERFORMANCE MAY DIFFER FROM LABORATORY PERFORMANCE

8 of 8