

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910961

Luminaire Tested: DFN2DIP-HX4F0-090D040US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910961
REPORT IS A COMBINATION OF REPORTS P899310 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D040US850-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12409.7 lumens
Efficiency: N/A
Efficacy: 110.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 112.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910961
CATALOG NUMBER: DFN2DIP-HX4F0-090D040US850-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P910961

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US850-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68				68
1	103	98	95	91	97	93	90	87	83	81	78	74	72	70	66	64	63	59				59
2	94	87	81	76	89	82	77	72	74	70	66	66	63	60	59	56	54	50				50
3	86	77	70	64	81	73	67	61	66	61	56	59	55	51	52	49	47	44				44
4	79	69	61	55	75	65	58	53	59	53	49	53	48	45	47	44	41	38				38
5	73	62	53	48	69	59	51	46	53	47	43	48	43	39	43	39	36	33				33
6	68	56	48	42	64	53	46	40	48	42	38	44	39	35	39	35	32	30				30
7	63	51	43	37	59	48	41	36	44	38	33	40	35	31	36	32	29	27				27
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26	24				24
9	55	42	35	30	52	41	34	29	37	31	27	34	29	25	31	27	24	22				22
10	51	39	32	27	48	37	31	26	34	29	25	32	27	23	29	25	22	20				20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3067	3067	3067
5°	3072	3019	3038
10°	3042	2960	2939
15°	3001	2862	2787
20°	2946	2728	2599
25°	2889	2577	2418
30°	2813	2422	2189
35°	2739	2256	1987
40°	2663	2084	1756
45°	2575	1892	1546
50°	2484	1699	1341
55°	2389	1493	1145
60°	2279	1278	942
65°	2153	1058	848
70°	2000	854	768
75°	1808	753	699
80°	1530	633	607
85°	1069	424	457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2575 cd/sqm



TEST NUMBER: P910961

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US850-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	386.6	3.1
10°-20°	1061.3	8.6
20°-30°	1490.1	12.0
30°-40°	1624.3	13.1
40°-50°	1492.9	12.0
50°-60°	1172.4	9.4
60°-70°	763.1	6.1
70°-80°	392.8	3.2
80°-90°	104.3	0.8
90°-100°	86.8	0.7
100°-110°	275.8	2.2
110°-120°	472.0	3.8
120°-130°	620.8	5.0
130°-140°	696.8	5.6
140°-150°	683.3	5.5
150°-160°	573.2	4.6
160°-170°	380.1	3.1
170°-180°	132.9	1.1
0°-30°	2938.0	23.7
0°-40°	4562.3	36.8
0°-60°	7227.6	58.2
0°-90°	8487.9	68.4
90°-120°	834.7	6.7
90°-150°	2835.6	22.8
90°-180°	3922.0	31.6
0°-180°	12409.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4125	4125	4125	4125	4125	
5°	4125	4106	4058	4091	4080	391
15°	3924	3882	3756	3685	3648	1106
25°	3562	3442	3196	3043	2986	1638
35°	3069	2878	2550	2315	2232	1921
45°	2509	2258	1867	1601	1512	1937
55°	1908	1616	1213	989	918	1705
65°	1288	986	650	523	511	1277
75°	687	425	299	272	269	726
85°	160	82	71	71	71	184
90°	1	15	42	39	40	12
95°	62	74	76	76	74	69
105°	255	258	260	263	263	269
115°	474	480	478	477	474	469
125°	689	700	696	692	691	616
135°	891	904	907	906	902	689
145°	1082	1090	1097	1098	1094	676
155°	1237	1240	1244	1250	1246	569
165°	1346	1345	1345	1353	1347	380
175°	1400	1397	1394	1403	1396	133
180°	1403	1403	1403	1403	1403	



TEST NUMBER: P910961

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US850-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4125.1	4125.1	4125.1	4125.1	4125.1
2.5°	4143.8	4125.1	4083.9	4121.6	4114.1
5°	4125.1	4106.5	4057.8	4091.4	4080.3
7.5°	4091.4	4069.3	4017.0	4031.7	4013.0
10°	4046.7	4020.6	3946.2	3934.6	3912.4
12.5°	3990.8	3957.2	3856.2	3834.0	3792.8
15°	3923.5	3882.4	3755.6	3684.7	3647.5
17.5°	3845.1	3785.3	3628.4	3546.5	3486.7
20°	3755.6	3680.8	3494.1	3401.1	3318.7
22.5°	3658.6	3572.6	3355.9	3229.2	3173.4
25°	3561.6	3441.9	3195.6	3042.7	2986.4
27.5°	3445.9	3318.7	3046.2	2870.8	2784.8
30°	3322.7	3180.5	2881.8	2691.8	2590.7
32.5°	3203.0	3031.1	2725.4	2501.2	2407.7
35°	3068.8	2878.3	2549.9	2314.7	2232.3
37.5°	2938.1	2732.6	2385.6	2127.7	2034.7
40°	2799.9	2576.1	2213.7	1948.7	1851.7
42.5°	2658.1	2419.3	2042.1	1765.7	1672.6
45°	2508.8	2258.5	1866.7	1601.3	1511.8
47.5°	2366.9	2102.0	1698.8	1433.4	1351.4
50°	2210.1	1945.1	1534.4	1276.6	1198.5
52.5°	2056.9	1776.8	1377.6	1131.2	1060.3
55°	1907.5	1616.4	1213.1	989.4	918.5
57.5°	1754.7	1456.0	1067.9	858.7	798.9
60°	1597.7	1299.1	914.6	724.4	664.6
62.5°	1444.9	1146.3	783.8	604.8	575.1
65°	1288.0	985.5	649.5	522.8	511.4
67.5°	1138.7	836.1	522.8	459.0	447.9
70°	981.9	690.8	433.0	395.7	380.6
72.5°	832.5	556.1	362.0	332.3	324.8
75°	686.8	425.4	298.7	272.5	268.9
77.5°	541.4	302.2	235.2	220.2	212.7
80°	406.8	216.7	179.0	164.4	164.4
82.5°	283.6	145.7	123.2	115.7	115.7
85°	160.4	82.0	70.9	70.9	70.9
87.5°	59.8	29.7	29.7	26.2	26.2
90°	1.2	15.2	41.5	38.9	40.1
92.5°	26.2	35.5	36.8	38.0	38.0
95°	61.8	73.6	75.7	75.7	73.6
97.5°	102.8	113.8	118.4	118.4	118.4
100°	150.2	159.9	163.2	163.2	162.0
102.5°	200.1	207.3	211.9	213.1	211.9
105°	254.6	258.0	260.5	262.6	262.6
107.5°	308.7	313.8	313.8	314.6	308.7
110°	361.2	368.0	368.0	368.0	364.6



TEST NUMBER: P910961

CATALOG NUMBER: DFN2DIP-HX4F0-090D040US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	417.9	425.1	423.7	420.4	417.9
115°	473.7	480.5	478.3	477.1	473.7
117.5°	529.1	538.4	532.5	529.1	525.8
120°	585.0	594.2	585.0	585.0	581.1
122.5°	635.7	647.5	641.7	638.2	635.7
125°	689.0	699.6	696.2	692.3	691.1
127.5°	741.0	754.1	749.5	744.4	741.0
130°	789.6	804.9	802.8	800.3	795.6
132.5°	844.2	856.0	856.9	850.9	847.6
135°	891.2	904.3	906.8	905.5	902.2
137.5°	943.6	954.2	956.3	955.4	950.4
140°	989.7	1000.3	1006.2	1006.2	1001.5
142.5°	1037.1	1047.7	1051.0	1052.3	1047.7
145°	1081.9	1090.4	1097.1	1098.5	1093.8
147.5°	1122.1	1132.6	1137.7	1139.8	1135.2
150°	1163.6	1170.8	1175.4	1179.2	1175.4
152.5°	1200.4	1207.5	1213.5	1218.1	1213.5
155°	1237.1	1240.5	1244.3	1250.3	1246.4
157.5°	1268.9	1271.4	1273.5	1282.0	1276.0
160°	1297.2	1299.7	1301.0	1308.2	1303.1
162.5°	1323.4	1323.4	1324.7	1332.7	1326.8
165°	1345.9	1344.6	1344.6	1353.0	1347.1
167.5°	1366.2	1362.3	1362.3	1370.8	1364.8
170°	1381.4	1377.9	1376.7	1385.1	1377.9
172.5°	1391.9	1388.6	1387.2	1395.8	1388.6
175°	1400.4	1397.0	1394.5	1402.9	1395.8
177.5°	1405.1	1401.7	1399.1	1406.3	1399.1
180°	1402.9	1402.9	1402.9	1402.9	1402.9



TEST NUMBER: P910961
 CATALOG NUMBER: DFN2DIP-HX4F0-090D040US850-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.61	13.62	13.40	14.42	15.41	8.58	9.59	9.37	10.39	11.38
	3H	14.30	15.20	15.10	16.02	17.03	9.79	10.69	10.59	11.50	12.52
	4H	14.92	15.77	15.74	16.59	17.62	10.24	11.09	11.06	11.92	12.94
	6H	15.35	16.13	16.18	16.96	18.00	10.58	11.36	11.41	12.19	13.23
	8H	15.48	16.22	16.32	17.07	18.11	10.67	11.42	11.51	12.27	13.31
	12H	15.55	16.26	16.39	17.10	18.17	10.72	11.43	11.57	12.28	13.34
4H	2H	12.65	13.50	13.47	14.32	15.35	9.20	10.05	10.02	10.87	11.90
	3H	14.49	15.20	15.33	16.06	17.10	10.57	11.27	11.40	12.13	13.17
	4H	15.19	15.84	16.04	16.69	17.76	11.12	11.76	11.97	12.62	13.69
	6H	15.72	16.27	16.58	17.15	18.23	11.55	12.11	12.42	12.99	14.06
	8H	15.90	16.42	16.77	17.29	18.38	11.69	12.20	12.55	13.08	14.16
	12H	16.00	16.47	16.89	17.36	18.45	11.76	12.23	12.65	13.12	14.21
8H	4H	15.18	15.69	16.04	16.57	17.65	11.42	11.93	12.28	12.81	13.89
	6H	15.75	16.18	16.64	17.09	18.18	11.94	12.37	12.84	13.29	14.37
	8H	15.97	16.35	16.87	17.26	18.36	12.14	12.52	13.04	13.43	14.53
	12H	16.11	16.45	17.02	17.35	18.51	12.27	12.60	13.17	13.50	14.66
12H	4H	15.14	15.60	16.02	16.49	17.58	11.43	11.89	12.32	12.79	13.88
	6H	15.73	16.10	16.63	17.01	18.12	11.99	12.37	12.90	13.28	14.39
	8H	15.95	16.29	16.86	17.19	18.35	12.21	12.55	13.12	13.45	14.60