

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921715

Luminaire Tested: DFN2DIP-HX3F0-070D040US940-FLLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P921715  
REPORT IS A COMBINATION OF REPORTS P900743 AND P897645  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-070D040US940-FLONL  
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9710.8 lumens  
Efficiency: N/A  
Efficacy: 98.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 98.9  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9789  
Total Harmonic Distortion (THDi): 0.074  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P921715  
CATALOG NUMBER: DFN2DIP-HX3F0-070D040US940-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P921715

CATALOG NUMBER: DFN2DIP-HX3F0-070D040US940-FLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	69	69	69	69	69	69	64
1	101	96	92	89	94	91	87	84	80	77	75	70	68	66	61	59	58	61	59	58	54
2	92	84	78	73	86	79	74	69	70	66	62	61	58	55	53	51	49	53	51	49	45
3	84	74	67	61	78	70	63	58	62	57	52	54	50	47	47	44	42	47	44	42	38
4	77	66	58	51	72	62	55	49	55	49	45	48	44	40	42	39	36	42	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39	44	39	35	38	34	31	38	34	31	28
6	65	53	44	38	61	50	42	37	44	38	34	39	34	31	35	31	28	35	31	28	25
7	60	48	39	34	56	45	38	32	40	34	30	36	31	27	32	28	25	32	28	25	22
8	56	43	35	30	52	41	34	29	37	31	27	33	28	24	29	25	22	29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24	30	25	22	27	23	20	27	23	20	18
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	25	21	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2813	2813	2813
5°	2817	2772	2791
10°	2792	2733	2752
15°	2750	2686	2691
20°	2693	2622	2629
25°	2637	2545	2558
30°	2566	2473	2468
35°	2500	2389	2372
40°	2417	2304	2281
45°	2335	2219	2188
50°	2246	2129	2080
55°	2152	2026	1980
60°	2045	1903	1867
65°	1929	1776	1732
70°	1781	1620	1587
75°	1576	1434	1451
80°	1328	1196	1194
85°	943	791	775

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2335 cd/sqm



TEST NUMBER: P921715  
 CATALOG NUMBER: DFN2DIP-HX3F0-070D040US940-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	228.6	2.4
10°-20°	643.2	6.6
20°-30°	945.2	9.7
30°-40°	1097.8	11.3
40°-50°	1096.5	11.3
50°-60°	956.1	9.8
60°-70°	706.8	7.3
70°-80°	399.9	4.1
80°-90°	107.7	1.1
90°-100°	39.7	0.4
100°-110°	148.0	1.5
110°-120°	392.4	4.0
120°-130°	650.9	6.7
130°-140°	691.4	7.1
140°-150°	642.6	6.6
150°-160°	516.6	5.3
160°-170°	332.9	3.4
170°-180°	114.6	1.2
0°-30°	1817.0	18.7
0°-40°	2914.9	30.0
0°-60°	4967.4	51.2
0°-90°	6181.7	63.7
90°-120°	580.1	6.0
90°-150°	2565.0	26.4
90°-180°	3529.0	36.3
0°-180°	9710.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2429	2429	2429	2429	2429	
5°	2429	2420	2394	2412	2408	231
15°	2312	2298	2268	2277	2266	651
25°	2093	2074	2034	2039	2034	963
35°	1805	1782	1745	1730	1719	1127
45°	1469	1453	1418	1392	1383	1134
55°	1112	1098	1070	1042	1030	994
65°	750	736	712	691	680	741
75°	392	388	376	362	367	419
85°	96	94	91	84	82	107
90°	1	10	17	22	24	9
95°	56	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	537	134	72	493
125°	708	720	736	742	745	632
135°	876	890	898	907	905	677
145°	1016	1016	1030	1036	1032	636
155°	1119	1112	1122	1127	1120	516
165°	1179	1174	1177	1183	1177	333
175°	1206	1200	1202	1208	1199	115
180°	1204	1204	1204	1204	1204	



TEST NUMBER: P921715

CATALOG NUMBER: DFN2DIP-HX3F0-070D040US940-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2428.8	2428.8	2428.8	2428.8	2428.8
2.5°	2442.9	2431.2	2405.5	2428.8	2424.3
5°	2428.8	2419.7	2393.9	2412.4	2408.0
7.5°	2412.4	2398.5	2372.8	2391.7	2386.9
10°	2386.9	2370.5	2342.5	2361.2	2354.2
12.5°	2351.7	2337.9	2309.9	2321.5	2316.8
15°	2312.1	2298.2	2267.7	2277.2	2265.5
17.5°	2263.0	2249.2	2218.7	2230.3	2218.7
20°	2209.2	2195.4	2162.7	2169.6	2160.4
22.5°	2155.7	2134.7	2104.2	2104.2	2099.4
25°	2092.6	2073.9	2034.3	2038.8	2034.3
27.5°	2022.4	2006.1	1975.9	1968.9	1957.2
30°	1952.6	1933.7	1898.8	1891.9	1882.4
32.5°	1877.7	1863.9	1826.4	1812.3	1802.9
35°	1805.4	1782.1	1744.6	1730.5	1718.9
37.5°	1723.6	1702.5	1665.1	1648.8	1637.1
40°	1639.6	1620.8	1583.3	1562.5	1553.1
42.5°	1557.8	1539.0	1501.8	1478.3	1464.4
45°	1469.1	1452.8	1417.6	1392.0	1382.6
47.5°	1382.6	1366.3	1328.8	1303.1	1289.2
50°	1291.5	1279.8	1247.1	1214.4	1202.7
52.5°	1202.7	1186.4	1156.2	1130.4	1114.0
55°	1111.8	1097.7	1069.7	1041.7	1030.0
57.5°	1020.7	1009.0	978.5	950.5	941.1
60°	929.4	920.2	887.6	861.8	854.9
62.5°	840.7	824.4	801.1	777.8	768.4
65°	749.8	735.7	712.4	691.3	679.7
67.5°	656.4	644.5	623.7	607.3	597.9
70°	569.9	560.5	539.4	523.1	513.9
72.5°	481.2	471.8	460.1	443.8	436.8
75°	392.3	387.8	375.9	362.0	366.8
77.5°	313.0	303.5	298.8	291.9	285.0
80°	233.6	231.2	226.5	219.5	214.8
82.5°	158.8	158.8	156.6	147.2	147.2
85°	95.7	93.5	91.2	84.0	81.8
87.5°	42.1	37.5	32.7	25.8	23.3
90°	0.8	10.4	17.4	21.8	23.5
92.5°	21.8	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.3	37.5
97.5°	101.9	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.5	58.3
102.5°	211.6	210.0	51.4	60.9	63.6
105°	264.7	291.0	53.1	62.7	66.2
107.5°	326.6	348.4	54.9	64.5	67.9
110°	385.9	404.1	152.5	65.4	68.8



TEST NUMBER: P921715

CATALOG NUMBER: DFN2DIP-HX3F0-070D040US940-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	441.7	457.3	442.5	67.1	69.7
115°	500.8	515.6	537.4	134.1	71.5
117.5°	552.2	569.6	584.5	459.9	231.7
120°	609.8	622.8	638.5	649.0	531.4
122.5°	658.4	672.4	689.9	695.1	696.0
125°	708.1	719.5	736.0	742.2	744.8
127.5°	753.4	765.6	778.7	787.5	788.3
130°	796.1	810.1	819.6	829.2	828.4
132.5°	839.6	851.0	860.6	868.4	867.6
135°	876.3	890.3	898.0	906.8	905.1
137.5°	914.5	925.0	933.8	942.4	939.9
140°	952.0	959.0	968.6	976.4	972.1
142.5°	983.5	989.5	1000.9	1007.7	1003.4
145°	1016.5	1015.7	1030.4	1036.5	1032.2
147.5°	1045.2	1042.6	1057.4	1061.8	1058.4
150°	1073.1	1067.0	1081.0	1086.2	1081.8
152.5°	1096.6	1089.7	1102.7	1108.0	1101.9
155°	1119.3	1111.5	1121.9	1127.1	1120.2
157.5°	1137.6	1130.6	1138.5	1144.6	1137.6
160°	1153.2	1148.0	1153.2	1158.4	1152.4
162.5°	1167.2	1162.0	1166.4	1172.4	1164.6
165°	1179.4	1174.2	1176.8	1182.9	1176.8
167.5°	1189.0	1183.7	1186.4	1192.5	1184.6
170°	1196.9	1191.6	1193.3	1199.4	1191.6
172.5°	1202.0	1196.9	1198.6	1204.7	1196.9
175°	1206.3	1200.2	1202.0	1208.1	1199.4
177.5°	1208.1	1202.0	1202.9	1209.1	1201.2
180°	1203.8	1203.8	1203.8	1203.8	1203.8



TEST NUMBER: P921715  
 CATALOG NUMBER: DFN2DIP-HX3F0-070D040US940-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.00	12.99	12.83	13.85	14.91	11.57	12.57	12.40	13.42	14.48
	3H	13.66	14.56	14.50	15.42	16.51	13.19	14.09	14.03	14.95	16.04
	4H	14.25	15.09	15.11	15.96	17.06	13.78	14.63	14.64	15.49	16.59
	6H	14.65	15.43	15.52	16.31	17.42	14.18	14.96	15.05	15.84	16.95
	8H	14.75	15.50	15.63	16.39	17.51	14.28	15.03	15.16	15.92	17.04
	12H	14.80	15.51	15.69	16.40	17.54	14.33	15.04	15.21	15.93	17.07
4H	2H	12.47	13.32	13.33	14.19	15.29	12.13	12.98	12.99	13.84	14.94
	3H	14.34	15.05	15.22	15.95	17.06	13.95	14.66	14.83	15.56	16.67
	4H	15.05	15.70	15.94	16.60	17.74	14.65	15.30	15.54	16.19	17.34
	6H	15.57	16.13	16.47	17.05	18.19	15.16	15.72	16.07	16.64	17.79
	8H	15.72	16.24	16.62	17.16	18.31	15.31	15.83	16.22	16.75	17.91
	12H	15.79	16.26	16.72	17.20	18.36	15.38	15.85	16.30	16.78	17.95
8H	4H	15.26	15.78	16.16	16.70	17.85	14.90	15.42	15.81	16.34	17.50
	6H	15.89	16.32	16.82	17.28	18.43	15.53	15.96	16.46	16.92	18.07
	8H	16.10	16.48	17.05	17.43	18.61	15.74	16.12	16.68	17.07	18.24
	12H	16.24	16.57	17.18	17.51	18.74	15.86	16.19	16.80	17.14	18.36
12H	4H	15.25	15.72	16.17	16.65	17.82	14.90	15.37	15.83	16.30	17.47
	6H	15.92	16.30	16.86	17.25	18.42	15.57	15.95	16.51	16.90	18.07
	8H	16.16	16.49	17.10	17.44	18.66	15.81	16.14	16.75	17.08	18.31