

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P921751

Luminaire Tested: DFN2DIP-HX3F0-080D070US940-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P921751
REPORT IS A COMBINATION OF REPORTS P900787 AND P897645
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-080D070US940-FLONL
Description: 3 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13241.9 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 133.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P921751
CATALOG NUMBER: DFN2DIP-HX3F0-080D070US940-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P921751

CATALOG NUMBER: DFN2DIP-HX3F0-080D070US940-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	53				53
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45				45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	38				38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32				32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31	27				27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27	24				24
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24	21				21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19				19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	17				17
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	15				15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3215	3215	3215
5°	3219	3168	3190
10°	3191	3123	3145
15°	3143	3070	3076
20°	3078	2996	3005
25°	3014	2908	2924
30°	2933	2827	2820
35°	2856	2731	2711
40°	2763	2633	2607
45°	2669	2536	2500
50°	2566	2433	2377
55°	2459	2315	2263
60°	2337	2175	2133
65°	2204	2029	1979
70°	2035	1851	1813
75°	1801	1638	1658
80°	1519	1367	1365
85°	1077	904	886

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2669 cd/sqm



TEST NUMBER: P921751

CATALOG NUMBER: DFN2DIP-HX3F0-080D070US940-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	261.3	2.0
10°-20°	735.1	5.6
20°-30°	1080.3	8.2
30°-40°	1254.7	9.5
40°-50°	1253.1	9.5
50°-60°	1092.7	8.3
60°-70°	807.7	6.1
70°-80°	457.0	3.5
80°-90°	124.3	0.9
90°-100°	69.5	0.5
100°-110°	259.0	2.0
110°-120°	686.8	5.2
120°-130°	1139.1	8.6
130°-140°	1209.9	9.1
140°-150°	1124.5	8.5
150°-160°	904.1	6.8
160°-170°	582.6	4.4
170°-180°	200.5	1.5
<hr/>		
0°-30°	2076.6	15.7
0°-40°	3331.3	25.2
0°-60°	5677.0	42.9
0°-90°	7066.1	53.4
90°-120°	1015.2	7.7
90°-150°	4488.7	33.9
90°-180°	6176.0	46.6
0°-180°	13241.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2776	2776	2776	2776	2776	
5°	2776	2765	2736	2757	2752	263
15°	2642	2626	2592	2602	2589	744
25°	2392	2370	2325	2330	2325	1100
35°	2063	2037	1994	1978	1964	1288
45°	1679	1660	1620	1591	1580	1296
55°	1271	1254	1222	1190	1177	1136
65°	857	841	814	790	777	847
75°	448	443	430	414	419	479
85°	109	107	104	96	94	122
90°	1	18	30	38	41	12
95°	99	49	59	67	66	117
105°	463	509	93	110	116	495
115°	876	902	940	235	125	863
125°	1239	1259	1288	1299	1303	1105
135°	1534	1558	1572	1587	1584	1185
145°	1779	1777	1803	1814	1806	1113
155°	1959	1945	1963	1972	1960	903
165°	2064	2055	2059	2070	2059	583
175°	2111	2100	2104	2114	2099	201
180°	2107	2107	2107	2107	2107	



TEST NUMBER: P921751

CATALOG NUMBER: DFN2DIP-HX3F0-080D070US940-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2775.7	2775.7	2775.7	2775.7	2775.7
2.5°	2791.9	2778.6	2749.1	2775.7	2770.6
5°	2775.7	2765.3	2735.9	2757.1	2752.0
7.5°	2757.1	2741.2	2711.8	2733.3	2727.9
10°	2727.9	2709.2	2677.2	2698.4	2690.6
12.5°	2687.7	2671.8	2639.8	2653.1	2647.8
15°	2642.4	2626.5	2591.7	2602.5	2589.2
17.5°	2586.3	2570.4	2535.6	2549.0	2535.6
20°	2524.9	2509.0	2471.6	2479.6	2469.1
22.5°	2463.7	2439.6	2404.8	2404.8	2399.4
25°	2391.5	2370.3	2325.0	2330.0	2325.0
27.5°	2311.3	2292.7	2258.1	2250.1	2236.9
30°	2231.5	2209.9	2170.1	2162.1	2151.3
32.5°	2146.0	2130.1	2087.3	2071.2	2060.5
35°	2063.2	2036.7	1993.9	1977.7	1964.4
37.5°	1969.8	1945.7	1903.0	1884.3	1871.0
40°	1873.8	1852.3	1809.5	1785.7	1774.9
42.5°	1780.4	1758.8	1716.4	1689.4	1673.7
45°	1679.0	1660.3	1620.1	1590.9	1580.2
47.5°	1580.2	1561.5	1518.7	1489.2	1473.4
50°	1476.0	1462.7	1425.2	1387.9	1374.6
52.5°	1374.6	1355.8	1321.3	1291.9	1273.2
55°	1270.6	1254.5	1222.5	1190.5	1177.1
57.5°	1166.4	1153.2	1118.3	1086.3	1075.5
60°	1062.2	1051.8	1014.3	984.9	977.0
62.5°	960.8	942.2	915.5	888.9	878.2
65°	856.9	840.8	814.1	790.1	776.8
67.5°	750.1	736.6	712.7	694.1	683.3
70°	651.3	640.5	616.5	597.8	587.3
72.5°	549.9	539.2	525.8	507.2	499.3
75°	448.3	443.2	429.6	413.8	419.1
77.5°	357.7	346.9	341.5	333.6	325.7
80°	267.1	264.2	258.9	250.9	245.5
82.5°	181.6	181.6	179.0	168.2	168.2
85°	109.3	106.7	104.2	96.0	93.5
87.5°	48.2	42.8	37.4	29.4	26.7
90°	1.4	18.3	30.4	38.2	41.1
92.5°	38.2	32.0	36.6	39.7	41.1
95°	99.0	48.7	59.4	67.1	65.5
97.5°	178.3	53.4	77.7	82.4	83.8
100°	269.9	61.0	86.9	99.0	102.1
102.5°	370.3	367.5	90.0	106.6	111.3
105°	463.4	509.2	93.0	109.7	115.8
107.5°	571.6	609.7	96.1	112.8	119.0
110°	675.4	707.2	266.8	114.4	120.4



TEST NUMBER: P921751

CATALOG NUMBER: DFN2DIP-HX3F0-080D070US940-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	772.9	800.2	774.4	117.3	122.0
115°	876.5	902.3	940.5	234.8	125.1
117.5°	966.4	996.8	1022.9	804.8	405.5
120°	1067.0	1089.8	1117.4	1135.7	929.9
122.5°	1152.3	1176.7	1207.4	1216.4	1218.0
125°	1239.2	1259.1	1288.1	1298.8	1303.2
127.5°	1318.5	1339.8	1362.8	1378.0	1379.5
130°	1393.2	1417.6	1434.3	1451.2	1449.7
132.5°	1469.4	1489.3	1506.0	1519.7	1518.3
135°	1533.5	1557.9	1571.6	1586.9	1583.9
137.5°	1600.4	1618.8	1634.1	1649.4	1644.8
140°	1666.0	1678.3	1695.0	1708.7	1701.1
142.5°	1721.0	1731.7	1751.4	1763.5	1756.0
145°	1779.0	1777.4	1803.2	1813.9	1806.3
147.5°	1829.1	1824.6	1850.5	1858.1	1852.1
150°	1877.9	1867.3	1891.8	1900.8	1893.2
152.5°	1919.0	1906.9	1929.8	1938.9	1928.3
155°	1958.7	1945.1	1963.4	1972.5	1960.3
157.5°	1990.7	1978.6	1992.3	2003.0	1990.7
160°	2018.3	2009.0	2018.3	2027.3	2016.6
162.5°	2042.6	2033.5	2041.0	2051.7	2038.0
165°	2063.9	2054.9	2059.3	2070.0	2059.3
167.5°	2080.7	2071.4	2076.2	2086.9	2073.1
170°	2094.4	2085.3	2088.3	2099.0	2085.3
172.5°	2103.5	2094.4	2097.6	2108.2	2094.4
175°	2111.1	2100.4	2103.5	2114.2	2099.0
177.5°	2114.2	2103.5	2105.1	2115.9	2102.0
180°	2106.6	2106.6	2106.6	2106.6	2106.6



TEST NUMBER: P921751
 CATALOG NUMBER: DFN2DIP-HX3F0-080D070US940-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.59	12.48	12.52	13.43	14.65	11.16	12.05	12.09	13.00	14.22
	3H	13.25	14.05	14.19	15.00	16.25	12.78	13.58	13.72	14.53	15.78
	4H	13.83	14.59	14.78	15.55	16.80	13.36	14.12	14.32	15.08	16.33
	6H	14.23	14.92	15.19	15.89	17.16	13.76	14.45	14.72	15.42	16.69
	8H	14.33	14.99	15.30	15.98	17.24	13.86	14.52	14.83	15.51	16.77
	12H	14.38	15.01	15.35	15.98	17.27	13.90	14.53	14.88	15.51	16.80
4H	2H	12.05	12.81	13.01	13.77	15.03	11.71	12.47	12.67	13.43	14.68
	3H	13.91	14.55	14.88	15.54	16.80	13.52	14.16	14.49	15.15	16.41
	4H	14.62	15.20	15.60	16.18	17.48	14.22	14.80	15.20	15.78	17.08
	6H	15.13	15.63	16.12	16.64	17.93	14.73	15.23	15.72	16.23	17.52
	8H	15.28	15.75	16.27	16.74	18.05	14.87	15.34	15.86	16.34	17.64
	12H	15.35	15.77	16.36	16.79	18.10	14.93	15.35	15.95	16.37	17.68
8H	4H	14.82	15.28	15.81	16.28	17.59	14.46	14.93	15.45	15.93	17.23
	6H	15.44	15.83	16.46	16.87	18.17	15.08	15.47	16.10	16.51	17.81
	8H	15.66	16.00	16.68	17.03	18.35	15.29	15.63	16.32	16.66	17.98
	12H	15.79	16.09	16.82	17.11	18.48	15.41	15.71	16.44	16.73	18.10
12H	4H	14.81	15.23	15.82	16.24	17.55	14.46	14.88	15.47	15.89	17.20
	6H	15.47	15.81	16.50	16.84	18.16	15.12	15.46	16.15	16.49	17.81
	8H	15.71	16.01	16.74	17.03	18.40	15.36	15.65	16.39	16.68	18.04