

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924368

Luminaire Tested: DFN2DIP-HX3F0-040D030US950-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P924368  
REPORT IS A COMBINATION OF REPORTS P899204 AND P896089  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX3F0-040D030US950-RLLFLL  
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5776.4 lumens  
Efficiency: N/A  
Efficacy: 100.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 57.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P924368  
CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P924368

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56	56	56	56
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	55	54	53	48	48	48	48
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	49	47	46	41	41	41	41
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40	36	36	36	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31	31	31	31
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	30	27	27	27	27
6	65	53	46	40	61	50	43	38	44	38	34	38	34	31	33	30	27	24	24	24	24
7	61	48	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24	22	22	22	22
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22	20	20	20	20
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20	18	18	18	18
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18	16	16	16	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1827	1827	1827
5°	1829	1797	1808
10°	1810	1760	1749
15°	1784	1701	1657
20°	1751	1619	1544
25°	1716	1528	1436
30°	1670	1435	1298
35°	1624	1335	1178
40°	1578	1232	1040
45°	1525	1117	915
50°	1469	1002	792
55°	1411	878	675
60°	1344	750	555
65°	1267	619	498
70°	1173	497	449
75°	1055	436	407
80°	884	361	350
85°	604	235	257

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1525 cd/sqm



TEST NUMBER: P924368

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-RLFL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	147.8	2.6
10°-20°	405.8	7.0
20°-30°	569.7	9.9
30°-40°	621.0	10.8
40°-50°	570.8	9.9
50°-60°	448.2	7.8
60°-70°	291.8	5.1
70°-80°	150.2	2.6
80°-90°	40.9	0.7
90°-100°	56.0	1.0
100°-110°	178.0	3.1
110°-120°	304.6	5.3
120°-130°	400.5	6.9
130°-140°	449.6	7.8
140°-150°	440.9	7.6
150°-160°	369.8	6.4
160°-170°	245.3	4.2
170°-180°	85.7	1.5
0°-30°	1123.3	19.4
0°-40°	1744.3	30.2
0°-60°	2763.3	47.8
0°-90°	3246.2	56.2
90°-120°	538.5	9.3
90°-150°	1829.5	31.7
90°-180°	2530.0	43.8
0°-180°	5776.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1577	1577	1577	1577	1577	
5°	1577	1570	1551	1564	1560	150
15°	1500	1484	1436	1409	1395	423
25°	1362	1316	1222	1163	1142	626
35°	1173	1100	975	885	853	734
45°	959	864	714	612	578	741
55°	729	618	464	378	351	652
65°	492	377	248	200	196	488
75°	262	163	114	104	103	278
85°	61	31	27	27	27	70
90°	1	10	27	25	26	6
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	



TEST NUMBER: P924368

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-RLFL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1577.2	1577.2	1577.2	1577.2	1577.2
2.5°	1584.3	1577.2	1561.4	1575.8	1572.9
5°	1577.2	1570.0	1551.4	1564.3	1560.1
7.5°	1564.3	1555.8	1535.8	1541.4	1534.3
10°	1547.2	1537.2	1508.7	1504.3	1495.9
12.5°	1525.8	1512.9	1474.3	1465.8	1450.1
15°	1500.1	1484.3	1435.9	1408.8	1394.6
17.5°	1470.1	1447.2	1387.2	1355.9	1333.0
20°	1435.9	1407.2	1335.9	1300.3	1268.8
22.5°	1398.8	1365.9	1283.0	1234.6	1213.3
25°	1361.6	1315.9	1221.7	1163.3	1141.7
27.5°	1317.5	1268.8	1164.6	1097.6	1064.7
30°	1270.3	1216.0	1101.8	1029.1	990.5
32.5°	1224.6	1158.9	1042.0	956.3	920.5
35°	1173.3	1100.4	974.9	884.9	853.4
37.5°	1123.3	1044.7	912.0	813.5	777.9
40°	1070.5	984.9	846.4	745.1	708.0
42.5°	1016.2	924.9	780.8	675.1	639.5
45°	959.2	863.5	713.7	612.3	578.0
47.5°	905.0	803.6	649.5	548.1	516.7
50°	845.0	743.6	586.6	488.1	458.2
52.5°	786.4	679.3	526.7	432.4	405.4
55°	729.3	618.0	463.8	378.3	351.2
57.5°	670.9	556.7	408.2	328.3	305.5
60°	610.8	496.7	349.6	276.9	254.1
62.5°	552.5	438.3	299.7	231.2	219.9
65°	492.5	376.7	248.3	199.9	195.5
67.5°	435.4	319.7	199.9	175.5	171.2
70°	375.4	264.1	165.5	151.3	145.5
72.5°	318.3	212.6	138.4	127.1	124.2
75°	262.5	162.7	114.2	104.2	102.8
77.5°	207.0	115.5	90.0	84.2	81.3
80°	155.5	82.8	68.4	62.9	62.9
82.5°	108.5	55.7	47.1	44.2	44.2
85°	61.3	31.4	27.1	27.1	27.1
87.5°	22.9	11.4	11.4	10.0	10.0
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3



TEST NUMBER: P924368

CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-RLFL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2



TEST NUMBER: P924368  
 CATALOG NUMBER: DFN2DIP-HX3F0-040D030US950-RLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.76	10.64	10.67	11.56	12.75	5.73	6.62	6.64	7.54	8.72
	3H	11.43	12.22	12.35	13.15	14.36	6.92	7.71	7.84	8.64	9.85
	4H	12.04	12.78	12.97	13.72	14.94	7.37	8.12	8.31	9.05	10.27
	6H	12.45	13.14	13.40	14.08	15.31	7.69	8.38	8.64	9.32	10.55
	8H	12.58	13.23	13.53	14.19	15.42	7.78	8.43	8.73	9.39	10.62
	12H	12.64	13.26	13.60	14.21	15.47	7.82	8.45	8.78	9.40	10.65
4H	2H	9.78	10.53	10.72	11.46	12.68	6.33	7.08	7.27	8.01	9.23
	3H	11.61	12.23	12.56	13.19	14.42	7.68	8.30	8.63	9.27	10.50
	4H	12.29	12.86	13.25	13.82	15.08	8.23	8.79	9.19	9.75	11.01
	6H	12.80	13.29	13.78	14.28	15.53	8.64	9.13	9.62	10.12	11.37
	8H	12.98	13.43	13.95	14.41	15.68	8.77	9.22	9.75	10.20	11.47
	12H	13.07	13.48	14.06	14.47	15.75	8.84	9.24	9.83	10.24	11.51
8H	4H	12.26	12.72	13.24	13.70	14.97	8.51	8.96	9.48	9.94	11.21
	6H	12.82	13.20	13.82	14.22	15.49	9.02	9.39	10.02	10.42	11.68
	8H	13.04	13.37	14.04	14.38	15.66	9.21	9.54	10.22	10.55	11.83
	12H	13.17	13.46	14.18	14.46	15.80	9.32	9.62	10.34	10.62	11.95
12H	4H	12.22	12.63	13.21	13.62	14.90	8.51	8.92	9.51	9.92	11.19
	6H	12.80	13.13	13.81	14.14	15.42	9.07	9.40	10.08	10.41	11.69
	8H	13.02	13.31	14.03	14.31	15.64	9.28	9.57	10.29	10.57	11.90