

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P924483

Luminaire Tested: DFN2DIP-HX3F0-080D080US950-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P924483
REPORT IS A COMBINATION OF REPORTS P899282 AND P896089
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX3F0-080D080US950-RLLFLL
Description: 3 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13241.5 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.84' x L: 3.28' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 141.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P924483

CATALOG NUMBER: DFN2DIP-HX3F0-080D080US950-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P924483

CATALOG NUMBER: DFN2DIP-HX3F0-080D080US950-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3654	3654	3654
5°	3658	3593	3617
10°	3620	3520	3497
15°	3569	3401	3313
20°	3501	3239	3088
25°	3432	3057	2871
30°	3339	2870	2597
35°	3249	2670	2356
40°	3157	2463	2079
45°	3049	2234	1829
50°	2938	2003	1585
55°	2823	1757	1350
60°	2688	1499	1110
65°	2534	1238	996
70°	2346	994	899
75°	2110	871	814
80°	1768	723	698
85°	1209	470	513

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3049 cd/sqm

TEST NUMBER: P924483

CATALOG NUMBER: DFN2DIP-HX3F0-080D080US950-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	2.2
10°-20°	811.5	6.1
20°-30°	1139.4	8.6
30°-40°	1242.0	9.4
40°-50°	1141.5	8.6
50°-60°	896.5	6.8
60°-70°	583.5	4.4
70°-80°	300.4	2.3
80°-90°	83.5	0.6
90°-100°	149.4	1.1
100°-110°	474.6	3.6
110°-120°	812.1	6.1
120°-130°	1068.1	8.1
130°-140°	1198.9	9.1
140°-150°	1175.6	8.9
150°-160°	986.2	7.4
160°-170°	654.0	4.9
170°-180°	228.6	1.7
0°-30°	2246.6	17.0
0°-40°	3488.6	26.3
0°-60°	5526.6	41.7
0°-90°	6494.1	49.0
90°-120°	1436.1	10.8
90°-150°	4878.6	36.8
90°-180°	6747.0	51.0
0°-180°	13241.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3154	3154	3154	3154	3154	
5°	3154	3140	3103	3128	3120	299
15°	3000	2969	2872	2818	2789	845
25°	2723	2632	2444	2327	2284	1252
35°	2347	2201	1950	1770	1707	1469
45°	1918	1727	1427	1224	1156	1481
55°	1459	1236	928	756	702	1303
65°	985	754	497	400	391	976
75°	525	325	228	208	206	555
85°	123	63	54	54	54	141
90°	2	26	71	67	69	13
95°	106	127	130	130	127	118
105°	438	444	448	452	452	462
115°	815	827	823	821	815	806
125°	1185	1204	1198	1191	1189	1059
135°	1533	1556	1560	1558	1552	1185
145°	1861	1876	1888	1890	1882	1163
155°	2128	2134	2141	2151	2144	980
165°	2316	2313	2313	2328	2318	653
175°	2409	2404	2399	2414	2401	229
180°	2414	2414	2414	2414	2414	



TEST NUMBER: P924483

CATALOG NUMBER: DFN2DIP-HX3F0-080D080US950-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3154.3	3154.3	3154.3	3154.3	3154.3
2.5°	3168.5	3154.3	3122.8	3151.5	3145.8
5°	3154.3	3140.1	3102.8	3128.5	3120.1
7.5°	3128.5	3111.6	3071.6	3082.9	3068.5
10°	3094.3	3074.4	3017.4	3008.6	2991.6
12.5°	3051.7	3025.9	2948.6	2931.6	2900.2
15°	3000.1	2968.7	2871.7	2817.5	2789.0
17.5°	2940.1	2894.4	2774.5	2711.8	2666.0
20°	2871.7	2814.5	2671.9	2600.7	2537.6
22.5°	2797.5	2731.8	2566.2	2469.2	2426.5
25°	2723.3	2631.9	2443.5	2326.6	2283.6
27.5°	2634.9	2537.6	2329.3	2195.2	2129.4
30°	2540.7	2431.9	2203.6	2058.3	1981.0
32.5°	2449.2	2317.8	2084.0	1912.6	1841.1
35°	2346.6	2200.9	1949.8	1770.0	1706.9
37.5°	2246.6	2089.5	1824.1	1627.0	1555.8
40°	2141.0	1969.8	1692.7	1490.1	1415.8
42.5°	2032.5	1849.9	1561.5	1350.2	1278.9
45°	1918.3	1726.9	1427.4	1224.5	1156.1
47.5°	1809.9	1607.3	1299.0	1096.1	1033.4
50°	1689.9	1487.4	1173.3	976.1	916.4
52.5°	1572.8	1358.6	1053.3	865.0	810.8
55°	1458.6	1236.0	927.7	756.5	702.3
57.5°	1341.7	1113.3	816.5	656.6	610.8
60°	1221.7	993.4	699.3	553.9	508.2
62.5°	1104.8	876.4	599.4	462.5	439.8
65°	984.9	753.5	496.7	399.8	390.9
67.5°	870.7	639.4	399.8	351.0	342.6
70°	750.8	528.2	331.0	302.5	291.1
72.5°	636.6	425.2	276.9	254.1	248.3
75°	525.2	325.3	228.4	208.4	205.7
77.5°	414.0	231.1	179.9	168.4	162.7
80°	311.0	165.7	136.9	125.6	125.6
82.5°	216.8	111.4	94.2	88.4	88.4
85°	122.7	62.7	54.2	54.2	54.2
87.5°	45.7	22.7	22.7	20.0	20.0
90°	2.2	26.2	71.4	67.0	69.2
92.5°	45.1	61.2	63.3	65.4	65.4
95°	106.3	126.6	130.2	130.2	126.6
97.5°	176.9	195.8	203.8	203.8	203.8
100°	258.3	275.0	280.9	280.9	278.7
102.5°	344.2	356.6	364.5	366.7	364.5
105°	438.1	443.9	448.3	451.9	451.9
107.5°	531.2	540.0	540.0	541.4	531.2
110°	621.4	633.1	633.1	633.1	627.3

TEST NUMBER: P924483

CATALOG NUMBER: DFN2DIP-HX3F0-080D080US950-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	718.9	731.3	729.1	723.3	718.9
115°	815.0	826.6	823.0	820.8	815.0
117.5°	910.3	926.3	916.1	910.3	904.5
120°	1006.4	1022.4	1006.4	1006.4	999.8
122.5°	1093.7	1114.1	1103.9	1098.1	1093.7
125°	1185.3	1203.6	1197.7	1191.2	1189.1
127.5°	1274.9	1297.4	1289.4	1280.7	1274.9
130°	1358.6	1384.7	1381.1	1376.8	1368.8
132.5°	1452.5	1472.8	1474.3	1464.1	1458.3
135°	1533.2	1555.8	1560.2	1558.0	1552.2
137.5°	1623.4	1641.6	1645.3	1643.8	1635.1
140°	1702.8	1720.9	1731.1	1731.1	1723.1
142.5°	1784.3	1802.5	1808.3	1810.5	1802.5
145°	1861.4	1875.9	1887.6	1889.8	1881.8
147.5°	1930.5	1948.7	1957.4	1961.1	1953.1
150°	2001.9	2014.2	2022.2	2028.8	2022.2
152.5°	2065.1	2077.5	2087.7	2095.7	2087.7
155°	2128.5	2134.3	2140.9	2151.0	2144.5
157.5°	2183.0	2187.4	2191.1	2205.6	2195.4
160°	2231.8	2236.2	2238.4	2250.7	2242.0
162.5°	2276.9	2276.9	2279.1	2292.9	2282.7
165°	2315.5	2313.3	2313.3	2327.9	2317.6
167.5°	2350.4	2343.9	2343.9	2358.4	2348.2
170°	2376.6	2370.8	2368.6	2383.2	2370.8
172.5°	2394.8	2389.0	2386.8	2401.3	2389.0
175°	2409.3	2403.5	2399.1	2413.7	2401.3
177.5°	2417.3	2411.5	2407.1	2419.5	2407.1
180°	2413.7	2413.7	2413.7	2413.7	2413.7

TEST NUMBER: P924483

CATALOG NUMBER: DFN2DIP-HX3F0-080D080US950-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.51	12.34	12.49	13.32	14.60	7.49	8.31	8.46	9.29	10.58
	3H	13.18	13.92	14.17	14.91	16.22	8.67	9.41	9.66	10.40	11.71
	4H	13.79	14.48	14.78	15.48	16.79	9.12	9.82	10.12	10.81	12.13
	6H	14.20	14.84	15.21	15.84	17.17	9.44	10.08	10.44	11.08	12.41
	8H	14.32	14.93	15.34	15.95	17.27	9.53	10.13	10.54	11.15	12.48
	12H	14.38	14.96	15.40	15.97	17.32	9.57	10.15	10.58	11.15	12.50
4H	2H	11.53	12.23	12.53	13.22	14.54	8.08	8.78	9.08	9.77	11.09
	3H	13.35	13.93	14.36	14.95	16.28	9.42	10.00	10.44	11.03	12.36
	4H	14.04	14.56	15.05	15.58	16.93	9.97	10.50	10.99	11.51	12.87
	6H	14.54	15.00	15.57	16.04	17.39	10.38	10.84	11.41	11.87	13.23
	8H	14.71	15.14	15.74	16.17	17.53	10.51	10.93	11.54	11.96	13.33
	12H	14.80	15.19	15.85	16.23	17.60	10.57	10.95	11.62	12.00	13.37
8H	4H	14.00	14.43	15.03	15.46	16.82	10.24	10.67	11.27	11.70	13.06
	6H	14.56	14.91	15.61	15.98	17.35	10.75	11.10	11.81	12.18	13.54
	8H	14.77	15.08	15.83	16.14	17.52	10.94	11.25	12.00	12.31	13.69
	12H	14.90	15.17	15.97	16.23	17.65	11.06	11.33	12.12	12.38	13.81
12H	4H	13.95	14.34	15.00	15.38	16.75	10.25	10.63	11.29	11.68	13.05
	6H	14.53	14.84	15.60	15.90	17.28	10.80	11.11	11.86	12.17	13.55
	8H	14.75	15.02	15.81	16.07	17.50	11.01	11.28	12.07	12.33	13.76

END OF REPORT