

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928212

Luminaire Tested: DFN2DIP-HX4F0-050D060US927-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928212
REPORT IS A COMBINATION OF REPORTS P900857 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D060US927-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8624.9 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 87.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928212

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928212

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27
5	67	56	48	42	62	52	45	39	43	38	34	36	32	29	29	26	24
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	18
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1146	1146	1146
5°	1148	1130	1137
10°	1138	1115	1122
15°	1122	1097	1098
20°	1099	1071	1073
25°	1077	1041	1045
30°	1049	1012	1009
35°	1022	979	971
40°	989	945	934
45°	957	912	897
50°	921	876	854
55°	884	835	814
60°	841	787	769
65°	795	736	715
70°	736	675	658
75°	655	602	605
80°	558	508	503
85°	405	346	335

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 957 cd/sqm

TEST NUMBER: P928212

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.0	1.7
10°-20°	408.0	4.7
20°-30°	599.7	7.0
30°-40°	696.5	8.1
40°-50°	695.6	8.1
50°-60°	606.6	7.0
60°-70°	448.4	5.2
70°-80°	253.7	2.9
80°-90°	69.8	0.8
90°-100°	52.9	0.6
100°-110°	197.1	2.3
110°-120°	522.8	6.1
120°-130°	867.2	10.1
130°-140°	921.1	10.7
140°-150°	856.1	9.9
150°-160°	688.3	8.0
160°-170°	443.5	5.1
170°-180°	152.6	1.8
0°-30°	1152.7	13.4
0°-40°	1849.2	21.4
0°-60°	3151.4	36.5
0°-90°	3923.2	45.5
90°-120°	772.9	9.0
90°-150°	3417.2	39.6
90°-180°	4702.0	54.5
0°-180°	8624.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1541	1541	1541	1541	1541	
5°	1541	1535	1519	1530	1528	146
15°	1467	1458	1439	1445	1437	413
25°	1328	1316	1291	1293	1291	611
35°	1145	1131	1107	1098	1090	715
45°	932	922	899	883	877	719
55°	705	696	679	661	654	631
65°	476	467	452	439	431	470
75°	249	246	238	230	233	266
85°	61	59	58	53	52	68
90°	1	14	23	29	31	8
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	943	959	981	989	992	841
135°	1168	1186	1196	1208	1206	902
145°	1354	1353	1373	1381	1375	847
155°	1491	1481	1495	1502	1492	687
165°	1571	1564	1568	1576	1568	444
175°	1607	1599	1601	1610	1598	153
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P928212

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1540.8	1540.8	1540.8	1540.8	1540.8
2.5°	1549.8	1542.4	1526.1	1540.8	1538.1
5°	1540.8	1535.1	1518.7	1530.5	1527.7
7.5°	1530.5	1521.7	1505.4	1517.3	1514.3
10°	1514.3	1503.9	1486.2	1497.9	1493.6
12.5°	1492.0	1483.2	1465.4	1472.8	1469.8
15°	1466.8	1458.0	1438.7	1444.7	1437.2
17.5°	1435.7	1426.9	1407.5	1414.9	1407.5
20°	1401.6	1392.8	1372.1	1376.4	1370.6
22.5°	1367.6	1354.2	1334.9	1334.9	1331.9
25°	1327.6	1315.7	1290.6	1293.4	1290.6
27.5°	1283.0	1272.7	1253.5	1249.1	1241.7
30°	1238.7	1226.8	1204.6	1200.2	1194.3
32.5°	1191.2	1182.5	1158.7	1149.7	1143.8
35°	1145.3	1130.6	1106.8	1097.9	1090.5
37.5°	1093.4	1080.1	1056.4	1046.0	1038.6
40°	1040.2	1028.3	1004.5	991.3	985.3
42.5°	988.3	976.4	952.8	937.8	929.0
45°	932.0	921.7	899.3	883.2	877.1
47.5°	877.1	866.8	843.1	826.7	817.9
50°	819.3	812.0	791.2	770.5	763.0
52.5°	763.0	752.6	733.5	717.2	706.8
55°	705.4	696.4	678.6	660.8	653.5
57.5°	647.5	640.1	620.8	603.0	597.0
60°	589.6	583.9	563.1	546.7	542.4
62.5°	533.4	523.0	508.2	493.4	487.5
65°	475.7	466.7	451.9	438.6	431.2
67.5°	416.4	408.9	395.7	385.3	379.3
70°	361.5	355.6	342.2	331.8	326.1
72.5°	305.3	299.3	291.9	281.6	277.1
75°	248.8	246.0	238.5	229.7	232.7
77.5°	198.6	192.5	189.6	185.2	180.8
80°	148.3	146.7	143.7	139.3	136.3
82.5°	100.7	100.7	99.3	93.4	93.4
85°	60.7	59.2	57.8	53.3	51.9
87.5°	26.7	23.8	20.8	16.3	14.8
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.7	40.6	59.1	62.7	63.8
100°	205.4	46.4	66.1	75.4	77.7
102.5°	282.0	279.7	68.5	81.2	84.7
105°	352.8	387.6	70.8	83.5	88.2
107.5°	435.2	464.1	73.2	85.9	90.5
110°	514.2	538.4	203.1	87.1	91.6

TEST NUMBER: P928212

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.4	609.2	589.5	89.3	92.9
115°	667.3	687.0	716.0	178.8	95.2
117.5°	735.7	758.9	778.7	612.7	308.6
120°	812.4	829.7	850.7	864.5	707.9
122.5°	877.2	895.8	919.1	926.0	927.3
125°	943.4	958.6	980.6	988.7	992.1
127.5°	1003.8	1020.0	1037.5	1049.1	1050.2
130°	1060.6	1079.3	1091.9	1104.8	1103.7
132.5°	1118.7	1133.8	1146.5	1157.0	1155.8
135°	1167.5	1186.1	1196.4	1208.1	1205.7
137.5°	1218.4	1232.4	1244.1	1255.6	1252.2
140°	1268.3	1277.7	1290.4	1300.9	1295.1
142.5°	1310.2	1318.4	1333.4	1342.6	1336.8
145°	1354.3	1353.1	1372.8	1380.9	1375.1
147.5°	1392.5	1389.0	1408.7	1414.5	1410.0
150°	1429.7	1421.6	1440.2	1447.1	1441.3
152.5°	1461.0	1451.7	1469.1	1476.1	1468.0
155°	1491.2	1480.8	1494.7	1501.6	1492.4
157.5°	1515.6	1506.3	1516.8	1524.9	1515.6
160°	1536.5	1529.4	1536.5	1543.4	1535.3
162.5°	1554.9	1548.0	1553.8	1562.0	1551.5
165°	1571.2	1564.4	1567.8	1575.9	1567.8
167.5°	1584.0	1577.0	1580.6	1588.8	1578.2
170°	1594.5	1587.5	1589.9	1597.9	1587.5
172.5°	1601.4	1594.5	1596.8	1605.0	1594.5
175°	1607.2	1599.0	1601.4	1609.5	1597.9
177.5°	1609.5	1601.4	1602.6	1610.8	1600.3
180°	1603.7	1603.7	1603.7	1603.7	1603.7

TEST NUMBER: P928212

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.31	8.14	8.31	9.14	10.48	6.88	7.70	7.88	8.71	10.04
	3H	8.97	9.71	9.98	10.72	12.08	8.50	9.24	9.50	10.25	11.61
	4H	9.56	10.26	10.58	11.27	12.64	9.08	9.78	10.10	10.80	12.16
	6H	9.96	10.60	10.99	11.62	13.00	9.48	10.12	10.51	11.15	12.52
	8H	10.06	10.67	11.09	11.71	13.08	9.59	10.20	10.62	11.24	12.61
	12H	10.11	10.69	11.15	11.72	13.12	9.63	10.21	10.67	11.24	12.64
4H	2H	7.77	8.47	8.80	9.49	10.85	7.43	8.12	8.45	9.14	10.51
	3H	9.63	10.22	10.67	11.26	12.64	9.24	9.82	10.27	10.87	12.25
	4H	10.35	10.88	11.39	11.92	13.32	9.94	10.48	10.98	11.51	12.91
	6H	10.86	11.32	11.91	12.38	13.78	10.45	10.91	11.50	11.97	13.37
	8H	11.01	11.44	12.06	12.49	13.90	10.60	11.03	11.65	12.08	13.49
	12H	11.08	11.47	12.15	12.54	13.95	10.66	11.05	11.73	12.12	13.53
8H	4H	10.54	10.97	11.59	12.03	13.43	10.18	10.61	11.23	11.66	13.07
	6H	11.17	11.53	12.25	12.62	14.03	10.81	11.16	11.88	12.26	13.67
	8H	11.39	11.71	12.48	12.79	14.21	11.03	11.34	12.11	12.42	13.84
	12H	11.52	11.80	12.61	12.87	14.34	11.14	11.41	12.23	12.49	13.96
12H	4H	10.53	10.91	11.60	11.98	13.40	10.17	10.56	11.24	11.63	13.05
	6H	11.20	11.51	12.28	12.59	14.02	10.85	11.16	11.93	12.24	13.67
	8H	11.44	11.72	12.53	12.79	14.26	11.09	11.36	12.17	12.44	13.90