

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928214

Luminaire Tested: DFN2DIP-HX4F0-050D060US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928214
REPORT IS A COMBINATION OF REPORTS P900858 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D060US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8070.5 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 87.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928214

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928214

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	43	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	46	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	39	34	30	32	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	25	30	25	22	25	21	18	20	17	15
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1217	1217	1217
5°	1219	1198	1205
10°	1207	1174	1166
15°	1191	1136	1106
20°	1169	1082	1031
25°	1146	1022	959
30°	1116	961	868
35°	1087	895	788
40°	1057	827	697
45°	1022	751	613
50°	986	674	532
55°	948	592	454
60°	904	507	374
65°	854	420	337
70°	794	339	305
75°	717	299	277
80°	607	251	241
85°	425	168	181

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1022 cd/sqm

TEST NUMBER: P928214

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	1.9
10°-20°	421.1	5.2
20°-30°	591.2	7.3
30°-40°	644.4	8.0
40°-50°	592.3	7.3
50°-60°	465.2	5.8
60°-70°	302.8	3.8
70°-80°	155.9	1.9
80°-90°	42.6	0.5
90°-100°	52.9	0.7
100°-110°	197.1	2.4
110°-120°	522.8	6.5
120°-130°	867.2	10.7
130°-140°	921.1	11.4
140°-150°	856.1	10.6
150°-160°	688.3	8.5
160°-170°	443.5	5.5
170°-180°	152.6	1.9
0°-30°	1165.7	14.4
0°-40°	1810.1	22.4
0°-60°	2867.6	35.5
0°-90°	3368.9	41.7
90°-120°	772.9	9.6
90°-150°	3417.2	42.3
90°-180°	4702.0	58.3
0°-180°	8070.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1629	1610	1623	1619	155
15°	1557	1540	1490	1462	1447	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	995	896	741	635	600	769
55°	757	641	481	392	364	676
65°	511	391	258	207	203	507
75°	272	169	118	108	107	288
85°	64	33	28	28	28	73
90°	1	14	23	29	31	8
95°	75	37	45	51	50	89
105°	353	388	71	84	88	377
115°	667	687	716	179	95	657
125°	943	959	981	989	992	841
135°	1168	1186	1196	1208	1206	902
145°	1354	1353	1373	1381	1375	847
155°	1491	1481	1495	1502	1492	687
165°	1571	1564	1568	1576	1568	444
175°	1607	1599	1601	1610	1598	153
180°	1604	1604	1604	1604	1604	

TEST NUMBER: P928214

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1636.7	1636.7	1636.7	1636.7	1636.7
2.5°	1644.0	1636.7	1620.4	1635.2	1632.2
5°	1636.7	1629.3	1610.0	1623.3	1618.9
7.5°	1623.3	1614.5	1593.7	1599.6	1592.2
10°	1605.5	1595.2	1565.6	1561.1	1552.2
12.5°	1583.4	1570.1	1530.0	1521.2	1504.8
15°	1556.7	1540.4	1490.1	1462.0	1447.1
17.5°	1525.6	1501.9	1439.6	1407.1	1383.3
20°	1490.1	1460.4	1386.3	1349.4	1316.7
22.5°	1451.6	1417.4	1331.5	1281.2	1259.0
25°	1413.0	1365.6	1267.8	1207.2	1184.8
27.5°	1367.2	1316.7	1208.6	1139.0	1104.9
30°	1318.3	1261.9	1143.4	1067.9	1027.9
32.5°	1270.8	1202.7	1081.3	992.4	955.3
35°	1217.5	1142.0	1011.7	918.3	885.7
37.5°	1165.7	1084.2	946.5	844.2	807.3
40°	1110.9	1022.1	878.2	773.2	734.7
42.5°	1054.6	959.8	810.2	700.5	663.6
45°	995.4	896.1	740.6	635.3	599.8
47.5°	939.1	834.0	674.0	568.7	536.2
50°	876.9	771.7	608.8	506.5	475.5
52.5°	816.1	705.0	546.6	448.8	420.7
55°	756.8	641.3	481.3	392.5	364.4
57.5°	696.2	577.7	423.6	340.7	317.0
60°	633.9	515.4	362.8	287.4	263.7
62.5°	573.2	454.8	311.0	240.0	228.2
65°	511.0	391.0	257.7	207.4	202.9
67.5°	451.8	331.8	207.4	182.2	177.7
70°	389.6	274.0	171.8	157.0	151.0
72.5°	330.3	220.7	143.7	131.9	128.9
75°	272.5	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.3
80°	161.4	85.9	71.0	65.2	65.2
82.5°	112.5	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	1.1	13.9	23.1	29.1	31.3
92.5°	29.1	24.4	27.8	30.2	31.3
95°	75.4	37.1	45.2	51.2	49.9
97.5°	135.7	40.6	59.1	62.7	63.8
100°	205.4	46.4	66.1	75.4	77.7
102.5°	282.0	279.7	68.5	81.2	84.7
105°	352.8	387.6	70.8	83.5	88.2
107.5°	435.2	464.1	73.2	85.9	90.5
110°	514.2	538.4	203.1	87.1	91.6



TEST NUMBER: P928214

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	588.4	609.2	589.5	89.3	92.9
115°	667.3	687.0	716.0	178.8	95.2
117.5°	735.7	758.9	778.7	612.7	308.6
120°	812.4	829.7	850.7	864.5	707.9
122.5°	877.2	895.8	919.1	926.0	927.3
125°	943.4	958.6	980.6	988.7	992.1
127.5°	1003.8	1020.0	1037.5	1049.1	1050.2
130°	1060.6	1079.3	1091.9	1104.8	1103.7
132.5°	1118.7	1133.8	1146.5	1157.0	1155.8
135°	1167.5	1186.1	1196.4	1208.1	1205.7
137.5°	1218.4	1232.4	1244.1	1255.6	1252.2
140°	1268.3	1277.7	1290.4	1300.9	1295.1
142.5°	1310.2	1318.4	1333.4	1342.6	1336.8
145°	1354.3	1353.1	1372.8	1380.9	1375.1
147.5°	1392.5	1389.0	1408.7	1414.5	1410.0
150°	1429.7	1421.6	1440.2	1447.1	1441.3
152.5°	1461.0	1451.7	1469.1	1476.1	1468.0
155°	1491.2	1480.8	1494.7	1501.6	1492.4
157.5°	1515.6	1506.3	1516.8	1524.9	1515.6
160°	1536.5	1529.4	1536.5	1543.4	1535.3
162.5°	1554.9	1548.0	1553.8	1562.0	1551.5
165°	1571.2	1564.4	1567.8	1575.9	1567.8
167.5°	1584.0	1577.0	1580.6	1588.8	1578.2
170°	1594.5	1587.5	1589.9	1597.9	1587.5
172.5°	1601.4	1594.5	1596.8	1605.0	1594.5
175°	1607.2	1599.0	1601.4	1609.5	1597.9
177.5°	1609.5	1601.4	1602.6	1610.8	1600.3
180°	1603.7	1603.7	1603.7	1603.7	1603.7

TEST NUMBER: P928214

CATALOG NUMBER: DFN2DIP-HX4F0-050D060US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.01	7.78	8.04	8.81	10.20	2.98	3.75	4.01	4.78	6.17
	3H	8.68	9.37	9.72	10.41	11.82	4.17	4.85	5.21	5.90	7.30
	4H	9.29	9.94	10.34	10.98	12.40	4.62	5.26	5.67	6.31	7.72
	6H	9.71	10.30	10.77	11.35	12.78	4.93	5.53	6.00	6.58	8.01
	8H	9.83	10.40	10.90	11.46	12.89	5.02	5.59	6.09	6.66	8.08
	12H	9.89	10.43	10.96	11.49	12.93	5.07	5.61	6.14	6.66	8.11
4H	2H	7.02	7.67	8.08	8.71	10.13	3.57	4.22	4.63	5.26	6.68
	3H	8.84	9.38	9.91	10.46	11.88	4.92	5.46	5.98	6.53	7.95
	4H	9.53	10.03	10.61	11.09	12.54	5.46	5.96	6.54	7.02	8.47
	6H	10.05	10.47	11.13	11.56	13.00	5.88	6.30	6.96	7.39	8.83
	8H	10.22	10.62	11.30	11.70	13.15	6.01	6.40	7.09	7.48	8.94
	12H	10.31	10.67	11.41	11.76	13.23	6.07	6.43	7.17	7.52	8.99
8H	4H	9.50	9.89	10.58	10.97	12.43	5.74	6.13	6.82	7.21	8.67
	6H	10.06	10.39	11.17	11.51	12.97	6.26	6.58	7.36	7.70	9.16
	8H	10.28	10.57	11.39	11.67	13.14	6.45	6.74	7.56	7.84	9.31
	12H	10.42	10.67	11.53	11.77	13.28	6.57	6.82	7.68	7.92	9.43
12H	4H	9.45	9.80	10.55	10.90	12.36	5.74	6.10	6.84	7.19	8.65
	6H	10.04	10.32	11.15	11.43	12.90	6.31	6.59	7.42	7.70	9.17
	8H	10.26	10.51	11.37	11.61	13.12	6.52	6.77	7.63	7.87	9.38

END OF REPORT