

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928218

Luminaire Tested: DFN2DIP-HX4F0-050D070US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928218
REPORT IS A COMBINATION OF REPORTS P900876 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D070US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8854.6 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 95.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928218

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928218

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	88	84	87	83	80	77	68	66	64	54	52	51	40	40	39
2	87	80	74	69	79	73	68	64	60	56	53	47	45	43	36	35	33
3	80	71	64	58	72	65	59	54	53	49	45	42	39	37	32	30	29
4	73	63	55	50	66	57	51	46	47	42	39	38	34	32	29	27	25
5	67	56	48	43	61	51	45	40	42	37	34	34	31	28	26	24	22
6	62	50	43	37	56	46	39	34	38	33	29	31	27	24	24	22	20
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	18
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	18	16
9	50	38	31	26	45	35	28	24	29	24	21	24	20	18	19	16	14
10	46	35	28	23	42	32	26	22	27	22	19	22	18	16	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1217	1217	1217
5°	1219	1198	1205
10°	1207	1174	1166
15°	1191	1136	1106
20°	1169	1082	1031
25°	1146	1022	959
30°	1116	961	868
35°	1087	895	788
40°	1057	827	697
45°	1022	751	613
50°	986	674	532
55°	948	592	454
60°	904	507	374
65°	854	420	337
70°	794	339	305
75°	717	299	277
80°	607	251	241
85°	425	168	181

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1022 cd/sqm

TEST NUMBER: P928218

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.4	1.7
10°-20°	421.1	4.8
20°-30°	591.2	6.7
30°-40°	644.4	7.3
40°-50°	592.3	6.7
50°-60°	465.2	5.3
60°-70°	302.8	3.4
70°-80°	155.9	1.8
80°-90°	43.1	0.5
90°-100°	61.7	0.7
100°-110°	230.0	2.6
110°-120°	610.0	6.9
120°-130°	1011.7	11.4
130°-140°	1074.6	12.1
140°-150°	998.8	11.3
150°-160°	803.0	9.1
160°-170°	517.4	5.8
170°-180°	178.1	2.0
0°-30°	1165.7	13.2
0°-40°	1810.1	20.4
0°-60°	2867.6	32.4
0°-90°	3369.3	38.1
90°-120°	901.6	10.2
90°-150°	3986.8	45.0
90°-180°	5485.0	61.9
0°-180°	8854.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1637	1637	1637	1637	1637	
5°	1637	1629	1610	1623	1619	155
15°	1557	1540	1490	1462	1447	439
25°	1413	1366	1268	1207	1185	650
35°	1218	1142	1012	918	886	762
45°	995	896	741	635	600	769
55°	757	641	481	392	364	676
65°	511	391	258	207	203	507
75°	272	169	118	108	107	288
85°	64	33	28	28	28	73
90°	1	16	27	34	36	8
95°	88	43	53	60	58	104
105°	412	452	83	97	103	440
115°	778	801	835	208	111	766
125°	1101	1118	1144	1154	1158	982
135°	1362	1384	1396	1409	1407	1052
145°	1580	1579	1602	1611	1604	988
155°	1740	1728	1744	1752	1741	802
165°	1833	1825	1829	1838	1829	518
175°	1875	1866	1868	1878	1864	178
180°	1871	1871	1871	1871	1871	

TEST NUMBER: P928218

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1636.7	1636.7	1636.7	1636.7	1636.7
2.5°	1644.0	1636.7	1620.4	1635.2	1632.2
5°	1636.7	1629.3	1610.0	1623.3	1618.9
7.5°	1623.3	1614.5	1593.7	1599.6	1592.2
10°	1605.5	1595.2	1565.6	1561.1	1552.2
12.5°	1583.4	1570.1	1530.0	1521.2	1504.8
15°	1556.7	1540.4	1490.1	1462.0	1447.1
17.5°	1525.6	1501.9	1439.6	1407.1	1383.3
20°	1490.1	1460.4	1386.3	1349.4	1316.7
22.5°	1451.6	1417.4	1331.5	1281.2	1259.0
25°	1413.0	1365.6	1267.8	1207.2	1184.8
27.5°	1367.2	1316.7	1208.6	1139.0	1104.9
30°	1318.3	1261.9	1143.4	1067.9	1027.9
32.5°	1270.8	1202.7	1081.3	992.4	955.3
35°	1217.5	1142.0	1011.7	918.3	885.7
37.5°	1165.7	1084.2	946.5	844.2	807.3
40°	1110.9	1022.1	878.2	773.2	734.7
42.5°	1054.6	959.8	810.2	700.5	663.6
45°	995.4	896.1	740.6	635.3	599.8
47.5°	939.1	834.0	674.0	568.7	536.2
50°	876.9	771.7	608.8	506.5	475.5
52.5°	816.1	705.0	546.6	448.8	420.7
55°	756.8	641.3	481.3	392.5	364.4
57.5°	696.2	577.7	423.6	340.7	317.0
60°	633.9	515.4	362.8	287.4	263.7
62.5°	573.2	454.8	311.0	240.0	228.2
65°	511.0	391.0	257.7	207.4	202.9
67.5°	451.8	331.8	207.4	182.2	177.7
70°	389.6	274.0	171.8	157.0	151.0
72.5°	330.3	220.7	143.7	131.9	128.9
75°	272.5	168.8	118.5	108.1	106.7
77.5°	214.8	119.9	93.4	87.4	84.3
80°	161.4	85.9	71.0	65.2	65.2
82.5°	112.5	57.8	48.9	45.9	45.9
85°	63.7	32.6	28.1	28.1	28.1
87.5°	23.8	11.8	11.8	10.4	10.4
90°	1.3	16.2	27.0	33.9	36.5
92.5°	33.9	28.4	32.5	35.2	36.5
95°	87.9	43.2	52.7	59.6	58.2
97.5°	158.3	47.4	69.0	73.2	74.4
100°	239.7	54.2	77.1	87.9	90.7
102.5°	328.9	326.4	79.9	94.7	98.8
105°	411.6	452.2	82.6	97.4	102.9
107.5°	507.7	541.5	85.4	100.2	105.7
110°	599.9	628.1	237.0	101.6	106.9

TEST NUMBER: P928218

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	686.5	710.7	687.8	104.1	108.3
115°	778.5	801.4	835.3	208.5	111.1
117.5°	858.4	885.4	908.5	714.8	360.1
120°	947.7	968.0	992.5	1008.7	825.9
122.5°	1023.4	1045.1	1072.4	1080.4	1081.8
125°	1100.6	1118.3	1144.0	1153.5	1157.5
127.5°	1171.1	1190.0	1210.4	1224.0	1225.2
130°	1237.4	1259.1	1273.9	1288.9	1287.6
132.5°	1305.1	1322.8	1337.6	1349.8	1348.5
135°	1362.0	1383.7	1395.8	1409.4	1406.8
137.5°	1421.5	1437.8	1451.4	1465.0	1460.9
140°	1479.7	1490.6	1505.4	1517.6	1510.9
142.5°	1528.6	1538.1	1555.6	1566.3	1559.6
145°	1580.0	1578.6	1601.6	1611.1	1604.4
147.5°	1624.6	1620.6	1643.6	1650.3	1645.0
150°	1668.0	1658.5	1680.2	1688.2	1681.5
152.5°	1704.5	1693.7	1714.0	1722.1	1712.7
155°	1739.7	1727.6	1743.8	1751.9	1741.1
157.5°	1768.1	1757.4	1769.6	1779.1	1768.1
160°	1792.6	1784.4	1792.6	1800.6	1791.1
162.5°	1814.2	1806.1	1812.8	1822.3	1810.1
165°	1833.1	1825.1	1829.0	1838.5	1829.0
167.5°	1848.1	1839.8	1844.0	1853.5	1841.3
170°	1860.2	1852.1	1854.8	1864.3	1852.1
172.5°	1868.3	1860.2	1863.0	1872.4	1860.2
175°	1875.1	1865.6	1868.3	1877.8	1864.3
177.5°	1877.8	1868.3	1869.8	1879.3	1867.0
180°	1871.0	1871.0	1871.0	1871.0	1871.0

TEST NUMBER: P928218

CATALOG NUMBER: DFN2DIP-HX4F0-050D070US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.60	7.34	7.66	8.40	9.84	2.58	3.32	3.63	4.37	5.81
	3H	8.27	8.94	9.34	10.00	11.46	3.76	4.42	4.83	5.49	6.94
	4H	8.88	9.51	9.96	10.58	12.04	4.21	4.83	5.29	5.90	7.36
	6H	9.30	9.87	10.39	10.95	12.42	4.52	5.10	5.61	6.17	7.65
	8H	9.42	9.97	10.51	11.06	12.52	4.61	5.16	5.71	6.25	7.72
	12H	9.48	10.00	10.58	11.08	12.57	4.65	5.18	5.75	6.26	7.75
4H	2H	6.61	7.24	7.70	8.31	9.77	3.16	3.79	4.25	4.86	6.32
	3H	8.43	8.95	9.53	10.05	11.52	4.50	5.03	5.60	6.12	7.59
	4H	9.12	9.60	10.22	10.69	12.18	5.05	5.53	6.15	6.62	8.11
	6H	9.63	10.04	10.74	11.15	12.64	5.47	5.88	6.57	6.99	8.47
	8H	9.81	10.19	10.91	11.29	12.79	5.59	5.98	6.70	7.08	8.58
	12H	9.90	10.24	11.02	11.36	12.87	5.66	6.00	6.78	7.12	8.62
8H	4H	9.08	9.47	10.19	10.57	12.07	5.32	5.71	6.43	6.81	8.31
	6H	9.65	9.96	10.77	11.11	12.61	5.84	6.16	6.97	7.30	8.80
	8H	9.86	10.14	11.00	11.27	12.78	6.03	6.31	7.17	7.44	8.95
	12H	10.00	10.24	11.14	11.36	12.92	6.15	6.39	7.29	7.51	9.07
12H	4H	9.03	9.38	10.15	10.49	12.00	5.33	5.67	6.45	6.79	8.29
	6H	9.62	9.90	10.76	11.02	12.54	5.89	6.17	7.02	7.29	8.81
	8H	9.84	10.08	10.98	11.20	12.76	6.10	6.34	7.24	7.46	9.02

END OF REPORT