

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926887

Luminaire Tested: DFN2DIP-HX4F0-040D080US830-FLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926887
REPORT IS A COMBINATION OF REPORTS P899371 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D080US830-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10405.2 lumens
Efficiency: N/A
Efficacy: 113.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 91.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926887

CATALOG NUMBER: DFN2DIP-HX4F0-040D080US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926887

CATALOG NUMBER: DFN2DIP-HX4F0-040D080US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43
1	95	90	87	83	85	82	79	76	66	64	62	52	50	49	38	37	36
2	86	79	73	68	78	72	66	62	58	54	51	45	43	41	34	32	31
3	79	69	62	56	71	63	57	52	51	47	43	40	37	34	30	28	26
4	72	61	54	48	65	56	49	44	45	40	37	36	32	29	27	24	22
5	66	54	47	41	59	50	43	38	40	35	31	32	28	25	24	22	20
6	61	49	41	35	55	45	38	33	36	31	27	29	25	22	22	19	17
7	56	44	36	31	50	40	33	28	33	28	24	26	22	20	20	17	15
8	52	40	32	27	47	36	30	25	30	25	21	24	20	17	18	16	14
9	48	36	29	24	44	33	27	22	27	22	19	22	18	16	17	14	12
10	45	33	26	21	41	30	24	20	25	20	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1091	1091	1091
5°	1093	1076	1083
10°	1084	1061	1068
15°	1068	1044	1045
20°	1046	1020	1022
25°	1025	991	995
30°	998	964	960
35°	973	932	924
40°	942	900	889
45°	911	868	854
50°	877	834	813
55°	841	795	775
60°	801	749	732
65°	757	701	681
70°	701	643	626
75°	624	573	576
80°	531	484	479
85°	385	329	319

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1798 cd/sqm

TEST NUMBER: P926887

CATALOG NUMBER: DFN2DIP-HX4F0-040D080US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	1.3
10°-20°	388.5	3.7
20°-30°	570.9	5.5
30°-40°	663.1	6.4
40°-50°	662.2	6.4
50°-60°	577.4	5.5
60°-70°	426.9	4.1
70°-80°	241.5	2.3
80°-90°	70.5	0.7
90°-100°	147.6	1.4
100°-110°	468.9	4.5
110°-120°	802.3	7.7
120°-130°	1055.2	10.1
130°-140°	1184.4	11.4
140°-150°	1161.5	11.2
150°-160°	974.3	9.4
160°-170°	646.1	6.2
170°-180°	225.8	2.2
0°-30°	1097.4	10.5
0°-40°	1760.5	16.9
0°-60°	3000.2	28.8
0°-90°	3739.1	35.9
90°-120°	1418.8	13.6
90°-150°	4819.9	46.3
90°-180°	6666.0	64.1
0°-180°	10405.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	2	26	70	66	68	10
95°	105	125	129	129	125	117
105°	433	438	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1533	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2285	2285	2300	2290	645
175°	2380	2374	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	

TEST NUMBER: P926887

CATALOG NUMBER: DFN2DIP-HX4F0-040D080US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1466.9	1466.9	1466.9	1466.9	1466.9
2.5°	1475.5	1468.4	1452.9	1466.9	1464.3
5°	1466.9	1461.3	1445.8	1457.0	1454.4
7.5°	1457.0	1448.6	1433.1	1444.5	1441.6
10°	1441.6	1431.8	1414.9	1426.1	1421.9
12.5°	1420.3	1412.0	1395.1	1402.2	1399.2
15°	1396.4	1388.0	1369.6	1375.3	1368.3
17.5°	1366.8	1358.4	1340.0	1347.0	1340.0
20°	1334.3	1325.9	1306.2	1310.4	1304.9
22.5°	1302.0	1289.2	1270.9	1270.9	1268.0
25°	1263.8	1252.6	1228.6	1231.4	1228.6
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1167.9	1146.8	1142.6	1136.9
32.5°	1134.1	1125.7	1103.1	1094.6	1088.9
35°	1090.4	1076.3	1053.7	1045.2	1038.2
37.5°	1041.0	1028.3	1005.6	995.8	988.8
40°	990.3	978.9	956.3	943.7	938.1
42.5°	940.9	929.5	907.1	892.8	884.4
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.6	787.1	778.7
50°	780.0	772.9	753.2	733.5	726.4
52.5°	726.4	716.6	698.3	682.7	672.9
55°	671.5	663.0	646.1	629.1	622.1
57.5°	616.4	609.4	590.9	574.1	568.4
60°	561.4	555.8	536.1	520.5	516.3
62.5°	507.8	497.9	483.9	469.7	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.5	325.8	315.9	310.4
72.5°	290.7	284.9	277.9	268.0	263.8
75°	236.9	234.2	227.0	218.7	221.5
77.5°	189.0	183.3	180.5	176.2	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	95.9	95.9	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.5	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	613.9	625.4	625.4	625.4	619.7

TEST NUMBER: P926887

CATALOG NUMBER: DFN2DIP-HX4F0-040D080US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.5	720.4	714.6	710.3
115°	805.2	816.7	813.1	810.9	805.2
117.5°	899.3	915.2	905.1	899.3	893.6
120°	994.2	1010.1	994.2	994.2	987.7
122.5°	1080.5	1100.7	1090.6	1084.8	1080.5
125°	1171.1	1189.1	1183.3	1176.8	1174.7
127.5°	1259.6	1281.8	1273.9	1265.3	1259.6
130°	1342.2	1368.0	1364.5	1360.2	1352.3
132.5°	1435.0	1455.0	1456.5	1446.5	1440.7
135°	1514.7	1537.0	1541.4	1539.2	1533.4
137.5°	1603.9	1621.9	1625.4	1624.0	1615.4
140°	1682.3	1700.2	1710.3	1710.3	1702.3
142.5°	1762.8	1780.8	1786.5	1788.7	1780.8
145°	1839.0	1853.3	1864.8	1867.0	1859.1
147.5°	1907.2	1925.2	1933.8	1937.5	1929.6
150°	1977.7	1989.9	1997.8	2004.3	1997.8
152.5°	2040.2	2052.5	2062.6	2070.5	2062.6
155°	2102.8	2108.6	2115.1	2125.1	2118.6
157.5°	2156.7	2161.1	2164.6	2179.0	2169.0
160°	2204.9	2209.2	2211.4	2223.5	2215.0
162.5°	2249.5	2249.5	2251.6	2265.3	2255.2
165°	2287.5	2285.4	2285.4	2299.8	2289.7
167.5°	2322.0	2315.6	2315.6	2330.0	2319.9
170°	2348.0	2342.2	2340.0	2354.5	2342.2
172.5°	2366.0	2360.2	2358.0	2372.4	2360.2
175°	2380.3	2374.5	2370.2	2384.6	2372.4
177.5°	2388.2	2382.5	2378.1	2390.4	2378.1
180°	2384.6	2384.6	2384.6	2384.6	2384.6

TEST NUMBER: P926887

CATALOG NUMBER: DFN2DIP-HX4F0-040D080US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.11	6.86	7.18	7.93	9.39	5.68	6.43	6.75	7.50	8.96
	3H	7.76	8.43	8.84	9.51	10.99	7.29	7.96	8.37	9.04	10.52
	4H	8.35	8.98	9.44	10.06	11.55	7.87	8.51	8.96	9.59	11.07
	6H	8.74	9.33	9.84	10.41	11.91	8.26	8.85	9.36	9.93	11.43
	8H	8.84	9.40	9.94	10.50	11.99	8.37	8.92	9.47	10.02	11.51
	12H	8.89	9.42	9.99	10.51	12.02	8.41	8.93	9.51	10.03	11.54
4H	2H	6.56	7.19	7.66	8.28	9.76	6.21	6.85	7.31	7.93	9.41
	3H	8.42	8.95	9.52	10.05	11.55	8.02	8.55	9.13	9.66	11.16
	4H	9.13	9.61	10.23	10.71	12.23	8.72	9.21	9.83	10.31	11.82
	6H	9.64	10.05	10.75	11.17	12.68	9.23	9.64	10.34	10.76	12.27
	8H	9.78	10.17	10.90	11.29	12.81	9.37	9.76	10.49	10.87	12.40
	12H	9.85	10.20	10.98	11.33	12.86	9.43	9.78	10.56	10.91	12.44
8H	4H	9.31	9.70	10.43	10.82	12.34	8.95	9.34	10.07	10.46	11.98
	6H	9.94	10.26	11.08	11.42	12.94	9.58	9.90	10.72	11.06	12.58
	8H	10.16	10.44	11.30	11.58	13.12	9.79	10.07	10.94	11.21	12.75
	12H	10.29	10.54	11.44	11.67	13.25	9.90	10.15	11.05	11.28	12.86
12H	4H	9.29	9.65	10.43	10.77	12.30	8.94	9.30	10.07	10.42	11.95
	6H	9.97	10.25	11.11	11.39	12.93	9.62	9.90	10.76	11.04	12.58
	8H	10.21	10.46	11.35	11.59	13.17	9.85	10.10	11.00	11.23	12.81

END OF REPORT