

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926902

Luminaire Tested: DFN2DIP-HX4F0-040D110US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926902
REPORT IS A COMBINATION OF REPORTS P900946 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-040D110US830-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13468.3 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 120.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926902

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926902

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	57	44	43	42	29	28	27
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	25	24	23
3	77	68	61	56	68	61	55	50	47	43	40	34	32	30	23	21	20
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	20	19	18
5	64	53	46	40	57	48	41	37	37	33	29	28	25	22	19	17	15
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	30	26	22	23	20	17	15	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	36	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1159	1159	1159
5°	1160	1140	1148
10°	1149	1118	1110
15°	1133	1081	1053
20°	1113	1030	982
25°	1091	973	913
30°	1063	915	827
35°	1035	852	751
40°	1006	787	663
45°	973	715	584
50°	938	642	507
55°	903	564	432
60°	861	483	356
65°	813	400	320
70°	756	322	290
75°	683	284	264
80°	578	239	229
85°	404	160	173

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1796 cd/sqm

TEST NUMBER: P926902

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	146.0	1.1
10°-20°	400.9	3.0
20°-30°	562.8	4.2
30°-40°	613.5	4.6
40°-50°	563.9	4.2
50°-60°	442.8	3.3
60°-70°	288.3	2.1
70°-80°	148.4	1.1
80°-90°	44.0	0.3
90°-100°	115.4	0.9
100°-110°	430.1	3.2
110°-120°	1140.7	8.5
120°-130°	1891.9	14.0
130°-140°	2009.6	14.9
140°-150°	1867.7	13.9
150°-160°	1501.6	11.1
160°-170°	967.6	7.2
170°-180°	333.0	2.5
0°-30°	1109.7	8.2
0°-40°	1723.2	12.8
0°-60°	2730.0	20.3
0°-90°	3210.7	23.8
90°-120°	1686.2	12.5
90°-150°	7455.4	55.4
90°-180°	10258.0	76.2
0°-180°	13468.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1558	1558	1558	1558	1558	
5°	1558	1551	1533	1545	1541	148
15°	1482	1466	1419	1392	1378	418
25°	1345	1300	1207	1149	1128	619
35°	1159	1087	963	874	843	726
45°	948	853	705	605	571	732
55°	720	611	458	374	347	644
65°	486	372	245	198	193	482
75°	259	161	113	103	102	274
85°	61	31	27	27	27	70
90°	2	30	50	63	68	12
95°	164	81	99	112	109	195
105°	770	846	155	182	192	822
115°	1456	1499	1562	390	208	1433
125°	2058	2091	2139	2157	2165	1836
135°	2547	2588	2610	2636	2631	1968
145°	2955	2952	2995	3013	3000	1848
155°	3253	3231	3261	3276	3256	1499
165°	3428	3413	3420	3438	3420	968
175°	3506	3489	3494	3512	3486	334
180°	3499	3499	3499	3499	3499	

TEST NUMBER: P926902

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1558.1	1558.1	1558.1	1558.1	1558.1
2.5°	1565.2	1558.1	1542.6	1556.8	1553.9
5°	1558.1	1551.1	1532.7	1545.4	1541.3
7.5°	1545.4	1537.0	1517.3	1522.8	1515.8
10°	1528.5	1518.7	1490.5	1486.1	1477.8
12.5°	1507.4	1494.7	1456.5	1448.2	1432.6
15°	1482.0	1466.4	1418.6	1391.8	1377.7
17.5°	1452.4	1429.8	1370.5	1339.6	1317.0
20°	1418.6	1390.3	1319.8	1284.6	1253.5
22.5°	1381.9	1349.5	1267.6	1219.7	1198.7
25°	1345.2	1300.1	1207.0	1149.3	1128.0
27.5°	1301.6	1253.5	1150.6	1084.3	1051.8
30°	1255.0	1201.3	1088.5	1016.7	978.6
32.5°	1209.9	1144.9	1029.4	944.8	909.4
35°	1159.2	1087.2	963.1	874.3	843.2
37.5°	1109.8	1032.1	901.0	803.7	768.5
40°	1057.6	973.0	836.2	736.1	699.4
42.5°	1004.0	913.8	771.3	666.9	631.8
45°	947.6	853.1	705.1	604.9	571.1
47.5°	894.1	794.0	641.7	541.5	510.5
50°	834.8	734.7	579.5	482.2	452.7
52.5°	776.9	671.2	520.4	427.2	400.5
55°	720.5	610.6	458.2	373.7	346.9
57.5°	662.8	549.9	403.3	324.3	301.8
60°	603.5	490.7	345.4	273.6	251.1
62.5°	545.8	433.0	296.0	228.5	217.2
65°	486.5	372.2	245.3	197.5	193.1
67.5°	430.2	315.8	197.5	173.4	169.2
70°	370.9	260.9	163.5	149.5	143.7
72.5°	314.5	210.1	136.8	125.5	122.7
75°	259.4	160.7	112.8	102.9	101.6
77.5°	204.5	114.1	88.9	83.2	80.3
80°	153.6	81.8	67.6	62.1	62.1
82.5°	107.2	55.0	46.6	43.6	43.6
85°	60.6	31.0	26.8	26.8	26.8
87.5°	22.6	11.2	11.2	9.9	9.9
90°	2.5	30.3	50.5	63.4	68.2
92.5°	63.4	53.3	60.7	65.9	68.2
95°	164.5	80.9	98.6	111.5	108.9
97.5°	296.1	88.7	128.9	136.8	139.2
100°	448.3	101.3	144.3	164.5	169.6
102.5°	615.1	610.3	149.4	177.1	184.9
105°	769.6	845.7	154.6	182.2	192.5
107.5°	949.5	1012.5	159.7	187.3	197.5
110°	1121.7	1174.6	443.2	190.0	199.9

TEST NUMBER: P926902

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1283.8	1329.1	1286.1	194.8	202.6
115°	1455.7	1498.7	1562.2	389.9	207.7
117.5°	1605.2	1655.7	1699.0	1336.7	673.4
120°	1772.3	1810.2	1855.9	1886.2	1544.4
122.5°	1913.9	1954.5	2005.3	2020.3	2023.1
125°	2058.2	2091.3	2139.4	2157.1	2164.6
127.5°	2189.9	2225.3	2263.5	2288.8	2291.2
130°	2314.0	2354.6	2382.3	2410.3	2407.9
132.5°	2440.6	2473.7	2501.4	2524.2	2521.8
135°	2547.1	2587.6	2610.2	2635.8	2630.6
137.5°	2658.3	2688.7	2714.2	2739.5	2731.9
140°	2767.2	2787.5	2815.2	2838.1	2825.4
142.5°	2858.5	2876.2	2909.0	2929.2	2916.6
145°	2954.7	2952.0	2995.0	3012.8	3000.2
147.5°	3038.1	3030.5	3073.5	3086.1	3076.2
150°	3119.2	3101.5	3142.0	3157.1	3144.5
152.5°	3187.4	3167.3	3205.2	3220.5	3202.8
155°	3253.3	3230.7	3261.0	3276.1	3256.0
157.5°	3306.5	3286.3	3309.2	3326.9	3306.5
160°	3352.2	3336.8	3352.2	3367.2	3349.5
162.5°	3392.4	3377.4	3390.1	3407.8	3385.0
165°	3428.0	3412.9	3420.4	3438.1	3420.4
167.5°	3455.9	3440.6	3448.4	3466.1	3443.3
170°	3478.8	3463.4	3468.5	3486.3	3463.4
172.5°	3493.8	3478.8	3483.9	3501.6	3478.8
175°	3506.4	3488.7	3493.8	3511.6	3486.3
177.5°	3511.6	3493.8	3496.5	3514.2	3491.4
180°	3498.9	3498.9	3498.9	3498.9	3498.9

TEST NUMBER: P926902

CATALOG NUMBER: DFN2DIP-HX4F0-040D110US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.50	5.15	5.66	6.29	7.90	0.47	1.13	1.63	2.27	3.87
	3H	6.16	6.75	7.33	7.90	9.52	1.65	2.23	2.81	3.38	5.00
	4H	6.76	7.32	7.94	8.47	10.09	2.09	2.65	3.26	3.80	5.42
	6H	7.18	7.69	8.36	8.84	10.47	2.40	2.92	3.59	4.07	5.70
	8H	7.30	7.78	8.48	8.95	10.58	2.49	2.98	3.67	4.14	5.77
	12H	7.36	7.82	8.54	8.98	10.62	2.53	2.99	3.72	4.15	5.80
4H	2H	4.49	5.05	5.68	6.20	7.82	1.04	1.60	2.23	2.75	4.37
	3H	6.31	6.77	7.49	7.95	9.58	2.38	2.84	3.57	4.02	5.65
	4H	6.99	7.42	8.18	8.58	10.24	2.92	3.35	4.11	4.51	6.17
	6H	7.50	7.87	8.69	9.05	10.69	3.33	3.70	4.53	4.88	6.53
	8H	7.67	8.01	8.86	9.19	10.85	3.46	3.80	4.65	4.98	6.64
	12H	7.76	8.07	8.97	9.26	10.92	3.52	3.83	4.72	5.01	6.68
8H	4H	6.95	7.29	8.14	8.47	10.13	3.19	3.53	4.38	4.71	6.37
	6H	7.51	7.79	8.72	9.01	10.67	3.71	3.99	4.91	5.20	6.86
	8H	7.73	7.97	8.94	9.17	10.84	3.90	4.14	5.11	5.34	7.01
	12H	7.86	8.07	9.08	9.27	10.97	4.01	4.22	5.23	5.42	7.12
12H	4H	6.89	7.20	8.10	8.39	10.05	3.19	3.50	4.39	4.68	6.35
	6H	7.49	7.73	8.70	8.93	10.60	3.75	4.00	4.97	5.19	6.87
	8H	7.70	7.91	8.92	9.11	10.81	3.96	4.17	5.17	5.37	7.07

END OF REPORT