

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928242

Luminaire Tested: DFN2DIP-HX4F0-060D040US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928242
REPORT IS A COMBINATION OF REPORTS P900824 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D040US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7175.5 lumens
Efficiency: N/A
Efficacy: 85.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 84.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928242

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928242

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	100	96	92	88	93	89	86	83	77	75	72	66	64	63	56	54	53
2	91	84	78	73	85	79	73	69	68	64	61	58	56	53	50	48	46
3	84	74	67	62	78	70	63	58	61	56	52	52	49	46	44	42	40
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35
5	71	59	51	46	66	56	49	43	49	43	39	42	38	35	36	33	31
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27
7	61	49	41	35	56	46	39	34	40	35	30	35	31	27	30	27	24
8	56	44	37	31	52	42	35	30	37	31	27	32	28	25	28	25	22
9	53	41	33	28	49	38	32	27	34	28	25	30	25	22	26	23	20
10	49	37	30	25	46	35	29	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1460	1460	1460
5°	1463	1437	1446
10°	1448	1409	1399
15°	1429	1363	1327
20°	1402	1299	1238
25°	1376	1227	1151
30°	1339	1153	1042
35°	1304	1074	946
40°	1268	992	836
45°	1226	901	736
50°	1183	809	639
55°	1138	711	545
60°	1085	608	449
65°	1025	504	404
70°	952	406	366
75°	861	359	333
80°	728	301	289
85°	509	202	217

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1226 cd/sqm

TEST NUMBER: P928242

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	184.1	2.6
10°-20°	505.3	7.0
20°-30°	709.4	9.9
30°-40°	773.3	10.8
40°-50°	710.8	9.9
50°-60°	558.2	7.8
60°-70°	363.3	5.1
70°-80°	187.0	2.6
80°-90°	49.6	0.7
90°-100°	35.2	0.5
100°-110°	131.4	1.8
110°-120°	348.6	4.9
120°-130°	578.1	8.1
130°-140°	614.1	8.6
140°-150°	570.7	8.0
150°-160°	458.8	6.4
160°-170°	295.7	4.1
170°-180°	101.8	1.4
0°-30°	1398.8	19.5
0°-40°	2172.1	30.3
0°-60°	3441.1	48.0
0°-90°	4041.1	56.3
90°-120°	515.2	7.2
90°-150°	2278.1	31.7
90°-180°	3134.0	43.7
0°-180°	7175.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1964	1964	1964	1964	1964	
5°	1964	1955	1932	1948	1943	186
15°	1868	1848	1788	1754	1736	526
25°	1696	1639	1521	1449	1422	780
35°	1461	1370	1214	1102	1063	914
45°	1194	1075	889	762	720	922
55°	908	770	578	471	437	812
65°	613	469	309	249	244	608
75°	327	202	142	130	128	346
85°	76	39	34	34	34	88
90°	1	9	15	19	21	7
95°	50	25	30	34	33	59
105°	235	258	47	56	59	251
115°	445	458	477	119	64	438
125°	629	639	654	659	662	561
135°	778	791	798	805	804	601
145°	903	902	915	921	917	565
155°	994	987	996	1001	995	458
165°	1048	1043	1045	1051	1045	296
175°	1071	1066	1068	1073	1065	102
180°	1069	1069	1069	1069	1069	

TEST NUMBER: P928242

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1964.0	1964.0	1964.0	1964.0	1964.0
2.5°	1972.9	1964.0	1944.4	1962.3	1958.7
5°	1964.0	1955.1	1931.9	1948.0	1942.7
7.5°	1948.0	1937.4	1912.5	1919.5	1910.6
10°	1926.6	1914.2	1878.8	1873.3	1862.7
12.5°	1900.1	1884.0	1835.9	1825.4	1805.8
15°	1868.0	1848.4	1788.0	1754.3	1736.5
17.5°	1830.7	1802.2	1727.5	1688.5	1660.0
20°	1788.0	1752.4	1663.6	1619.2	1580.0
22.5°	1741.8	1700.9	1597.8	1537.4	1510.8
25°	1695.7	1638.7	1521.4	1448.6	1421.9
27.5°	1640.6	1580.0	1450.3	1366.8	1325.9
30°	1581.9	1514.2	1372.1	1281.5	1233.5
32.5°	1525.0	1443.2	1297.6	1190.9	1146.3
35°	1461.1	1370.4	1214.1	1102.0	1062.8
37.5°	1398.8	1300.9	1135.8	1013.0	968.7
40°	1333.0	1226.5	1053.9	927.7	881.6
42.5°	1265.5	1151.8	972.3	840.6	796.4
45°	1194.4	1075.2	888.8	762.4	719.8
47.5°	1126.9	1000.8	808.8	682.5	643.4
50°	1052.3	926.1	730.5	607.8	570.6
52.5°	979.2	845.9	655.9	538.6	504.8
55°	908.2	769.6	577.6	471.1	437.3
57.5°	835.4	693.2	508.4	408.8	380.3
60°	760.7	618.6	435.4	344.9	316.4
62.5°	687.9	545.8	373.2	288.0	273.8
65°	613.2	469.2	309.3	248.9	243.5
67.5°	542.1	398.1	248.9	218.6	213.3
70°	467.4	328.8	206.1	188.4	181.2
72.5°	396.4	264.8	172.3	158.2	154.6
75°	327.0	202.5	142.2	129.7	128.1
77.5°	257.8	143.9	112.0	104.9	101.3
80°	193.6	103.1	85.2	78.2	78.2
82.5°	135.0	69.4	58.6	55.0	55.0
85°	76.3	39.0	33.7	33.7	33.7
87.5°	28.5	14.2	14.2	12.4	12.4
90°	0.7	9.3	15.4	19.4	20.8
92.5°	19.4	16.2	18.5	20.1	20.8
95°	50.2	24.7	30.1	34.1	33.3
97.5°	90.5	27.1	39.4	41.8	42.5
100°	136.9	31.0	44.1	50.2	51.8
102.5°	187.9	186.5	45.6	54.1	56.5
105°	235.1	258.4	47.2	55.7	58.8
107.5°	290.1	309.4	48.8	57.3	60.4
110°	342.8	358.9	135.4	58.1	61.1



TEST NUMBER: P928242

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.3	406.1	393.0	59.6	61.9
115°	444.8	457.9	477.3	119.1	63.5
117.5°	490.5	505.9	519.2	408.4	205.8
120°	541.6	553.1	567.1	576.4	472.0
122.5°	584.8	597.2	612.8	617.4	618.2
125°	628.9	639.1	653.7	659.2	661.5
127.5°	669.2	680.0	691.7	699.4	700.1
130°	707.1	719.5	727.9	736.5	735.8
132.5°	745.7	755.9	764.4	771.3	770.6
135°	778.3	790.7	797.6	805.4	803.9
137.5°	812.3	821.5	829.4	837.1	834.8
140°	845.5	851.8	860.3	867.2	863.4
142.5°	873.5	878.9	888.9	895.0	891.2
145°	902.9	902.1	915.2	920.6	916.7
147.5°	928.3	926.0	939.2	943.0	940.0
150°	953.1	947.7	960.1	964.7	960.9
152.5°	974.0	967.8	979.4	984.1	978.7
155°	994.1	987.2	996.5	1001.1	994.9
157.5°	1010.4	1004.2	1011.2	1016.6	1010.4
160°	1024.3	1019.6	1024.3	1028.9	1023.5
162.5°	1036.6	1032.1	1035.9	1041.3	1034.4
165°	1047.5	1042.9	1045.2	1050.6	1045.2
167.5°	1056.1	1051.3	1053.8	1059.1	1052.2
170°	1063.0	1058.3	1059.9	1065.3	1058.3
172.5°	1067.6	1063.0	1064.6	1070.0	1063.0
175°	1071.4	1066.0	1067.6	1073.0	1065.3
177.5°	1073.0	1067.6	1068.4	1073.9	1066.9
180°	1069.2	1069.2	1069.2	1069.2	1069.2

TEST NUMBER: P928242

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.03	9.92	9.94	10.84	12.02	5.01	5.89	5.92	6.81	7.99
	3H	10.72	11.51	11.64	12.44	13.65	6.20	6.99	7.12	7.92	9.13
	4H	11.33	12.08	12.26	13.01	14.23	6.66	7.40	7.59	8.34	9.55
	6H	11.75	12.44	12.70	13.38	14.61	6.98	7.67	7.93	8.61	9.84
	8H	11.88	12.54	12.84	13.50	14.72	7.07	7.73	8.03	8.69	9.91
	12H	11.95	12.57	12.90	13.52	14.77	7.12	7.74	8.08	8.70	9.95
4H	2H	9.06	9.81	10.00	10.74	11.96	5.61	6.36	6.55	7.29	8.51
	3H	10.89	11.52	11.85	12.48	13.71	6.97	7.59	7.92	8.55	9.78
	4H	11.59	12.16	12.55	13.12	14.37	7.52	8.08	8.48	9.05	10.30
	6H	12.11	12.60	13.08	13.58	14.83	7.94	8.43	8.92	9.41	10.67
	8H	12.29	12.74	13.26	13.72	14.99	8.07	8.53	9.05	9.51	10.77
	12H	12.38	12.79	13.38	13.79	15.06	8.14	8.55	9.13	9.55	10.82
8H	4H	11.56	12.02	12.54	13.00	14.26	7.80	8.26	8.78	9.24	10.50
	6H	12.13	12.51	13.13	13.53	14.79	8.33	8.70	9.33	9.72	10.99
	8H	12.35	12.68	13.36	13.69	14.97	8.52	8.85	9.53	9.86	11.14
	12H	12.49	12.78	13.50	13.78	15.11	8.64	8.93	9.65	9.93	11.26
12H	4H	11.52	11.93	12.51	12.92	14.19	7.81	8.22	8.80	9.22	10.49
	6H	12.11	12.44	13.11	13.45	14.73	8.38	8.71	9.38	9.72	11.00
	8H	12.33	12.62	13.34	13.62	14.95	8.59	8.88	9.60	9.88	11.21