

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926930

Luminaire Tested: DFN2DIP-HX4F0-050D090US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926930
REPORT IS A COMBINATION OF REPORTS P900912 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-050D090US830-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12403.3 lumens
Efficiency: N/A
Efficacy: 111.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 111.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9957
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926930

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926930

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	48	47	36	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	30	29
3	79	70	63	57	71	63	57	52	51	46	43	39	36	34	28	27	25
4	72	62	54	49	65	56	50	45	45	40	37	35	32	29	26	24	22
5	66	55	47	42	59	50	43	38	40	36	32	32	28	26	23	21	19
6	61	49	42	36	55	45	38	33	36	32	28	29	25	22	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	18	16	16	14	13
10	45	34	27	22	41	31	25	21	25	21	18	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1448	1448	1448
5°	1451	1425	1434
10°	1436	1398	1388
15°	1417	1352	1316
20°	1391	1288	1227
25°	1364	1217	1142
30°	1328	1144	1033
35°	1293	1065	938
40°	1257	984	829
45°	1216	893	730
50°	1173	802	633
55°	1128	705	540
60°	1076	603	445
65°	1017	500	401
70°	944	403	363
75°	854	356	330
80°	722	299	286
85°	505	200	216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1469 cd/sqm

TEST NUMBER: P926930

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.5	1.5
10°-20°	501.1	4.0
20°-30°	703.5	5.7
30°-40°	766.9	6.2
40°-50°	704.9	5.7
50°-60°	553.6	4.5
60°-70°	360.3	2.9
70°-80°	185.5	1.5
80°-90°	52.4	0.4
90°-100°	94.4	0.8
100°-110°	351.9	2.8
110°-120°	933.3	7.5
120°-130°	1547.9	12.5
130°-140°	1644.2	13.3
140°-150°	1528.2	12.3
150°-160°	1228.6	9.9
160°-170°	791.7	6.4
170°-180°	272.5	2.2
0°-30°	1387.2	11.2
0°-40°	2154.1	17.4
0°-60°	3412.5	27.5
0°-90°	4010.7	32.3
90°-120°	1379.6	11.1
90°-150°	6099.9	49.2
90°-180°	8393.0	67.7
0°-180°	12403.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1948	1948	1948	1948	1948	
5°	1948	1939	1916	1932	1927	185
15°	1852	1833	1773	1740	1722	522
25°	1682	1625	1509	1437	1410	773
35°	1449	1359	1204	1093	1054	907
45°	1184	1066	881	756	714	915
55°	901	763	573	467	434	805
65°	608	465	307	247	242	603
75°	324	201	141	129	127	343
85°	76	39	34	34	34	87
90°	2	25	41	52	56	12
95°	135	66	81	91	89	159
105°	630	692	126	149	157	673
115°	1191	1226	1278	319	170	1173
125°	1684	1711	1750	1765	1771	1502
135°	2084	2117	2136	2156	2152	1610
145°	2418	2415	2450	2465	2455	1512
155°	2662	2643	2668	2680	2664	1227
165°	2805	2792	2799	2813	2799	792
175°	2869	2854	2859	2873	2852	273
180°	2863	2863	2863	2863	2863	

TEST NUMBER: P926930

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1947.7	1947.7	1947.7	1947.7	1947.7
2.5°	1956.4	1947.7	1928.3	1946.0	1942.4
5°	1947.7	1938.9	1915.9	1931.7	1926.6
7.5°	1931.7	1921.3	1896.6	1903.6	1894.7
10°	1910.6	1898.3	1863.1	1857.8	1847.2
12.5°	1884.2	1868.4	1820.7	1810.3	1790.8
15°	1852.5	1833.1	1773.2	1739.8	1722.1
17.5°	1815.4	1787.3	1713.2	1674.4	1646.2
20°	1773.2	1737.9	1649.8	1605.8	1566.9
22.5°	1727.4	1686.8	1584.5	1524.7	1498.3
25°	1681.5	1625.1	1508.8	1436.6	1410.0
27.5°	1626.9	1566.9	1438.3	1355.4	1314.9
30°	1568.8	1501.7	1360.7	1270.9	1223.2
32.5°	1512.3	1431.2	1286.8	1181.0	1136.8
35°	1448.9	1359.0	1203.9	1092.8	1054.0
37.5°	1387.2	1290.2	1126.4	1004.6	960.7
40°	1322.0	1216.3	1045.1	920.1	874.3
42.5°	1255.0	1142.2	964.2	833.6	789.7
45°	1184.5	1066.3	881.3	756.1	713.8
47.5°	1117.5	992.5	802.1	676.8	638.1
50°	1043.5	918.4	724.5	602.7	565.9
52.5°	971.2	838.9	650.4	534.1	500.7
55°	900.7	763.1	572.8	467.1	433.6
57.5°	828.5	687.5	504.1	405.5	377.2
60°	754.4	613.4	431.8	342.0	313.8
62.5°	682.2	541.2	370.1	285.6	271.5
65°	608.1	465.3	306.7	246.8	241.5
67.5°	537.6	394.8	246.8	216.8	211.5
70°	463.6	326.1	204.4	186.8	179.7
72.5°	393.1	262.6	171.0	156.9	153.3
75°	324.3	200.8	141.0	128.7	127.0
77.5°	255.6	142.7	111.1	104.0	100.4
80°	192.1	102.3	84.5	77.6	77.6
82.5°	133.9	68.8	58.2	54.6	54.6
85°	75.8	38.7	33.5	33.5	33.5
87.5°	28.3	14.0	14.0	12.3	12.3
90°	2.0	24.9	41.3	51.9	55.8
92.5°	51.9	43.5	49.7	53.9	55.8
95°	134.6	66.2	80.7	91.2	89.1
97.5°	242.3	72.6	105.6	111.9	113.9
100°	366.7	82.9	118.1	134.6	138.7
102.5°	503.3	499.3	122.2	144.9	151.3
105°	629.7	692.0	126.4	149.1	157.4
107.5°	776.8	828.5	130.6	153.3	161.6
110°	917.7	961.1	362.6	155.4	163.6

TEST NUMBER: P926930

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1050.3	1087.5	1052.3	159.4	165.8
115°	1191.0	1226.2	1278.1	319.0	169.9
117.5°	1313.3	1354.7	1390.0	1093.7	551.0
120°	1450.0	1481.0	1518.5	1543.2	1263.6
122.5°	1566.0	1599.1	1640.7	1653.0	1655.2
125°	1684.0	1711.0	1750.4	1764.9	1771.1
127.5°	1791.7	1820.7	1852.0	1872.7	1874.6
130°	1893.3	1926.6	1949.2	1972.0	1970.1
132.5°	1996.9	2023.9	2046.5	2065.3	2063.3
135°	2084.0	2117.1	2135.6	2156.5	2152.4
137.5°	2175.0	2199.8	2220.7	2241.4	2235.2
140°	2264.0	2280.8	2303.4	2322.0	2311.8
142.5°	2338.8	2353.3	2380.1	2396.6	2386.3
145°	2417.5	2415.3	2450.5	2465.0	2454.6
147.5°	2485.7	2479.5	2514.7	2525.1	2516.9
150°	2552.1	2537.6	2570.8	2583.0	2572.7
152.5°	2607.9	2591.4	2622.4	2634.9	2620.4
155°	2661.8	2643.3	2668.1	2680.5	2664.0
157.5°	2705.4	2688.9	2707.5	2722.0	2705.4
160°	2742.7	2730.1	2742.7	2755.0	2740.5
162.5°	2775.7	2763.3	2773.7	2788.2	2769.5
165°	2804.7	2792.3	2798.6	2813.1	2798.6
167.5°	2827.6	2815.1	2821.4	2835.9	2817.2
170°	2846.3	2833.7	2837.9	2852.4	2833.7
172.5°	2858.6	2846.3	2850.4	2864.9	2846.3
175°	2868.9	2854.4	2858.6	2873.0	2852.4
177.5°	2873.0	2858.6	2860.8	2875.3	2856.6
180°	2862.7	2862.7	2862.7	2862.7	2862.7

TEST NUMBER: P926930

CATALOG NUMBER: DFN2DIP-HX4F0-050D090US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.51	7.22	7.62	8.31	9.82	2.49	3.19	3.59	4.29	5.79
	3H	8.18	8.81	9.29	9.91	11.44	3.67	4.30	4.78	5.40	6.92
	4H	8.79	9.38	9.91	10.49	12.01	4.11	4.71	5.23	5.81	7.34
	6H	9.20	9.75	10.33	10.86	12.40	4.43	4.98	5.56	6.09	7.62
	8H	9.33	9.85	10.46	10.97	12.50	4.52	5.04	5.65	6.16	7.69
	12H	9.38	9.88	10.52	10.99	12.55	4.56	5.05	5.69	6.17	7.72
4H	2H	6.52	7.11	7.64	8.22	9.75	3.07	3.67	4.19	4.77	6.30
	3H	8.34	8.83	9.47	9.96	11.50	4.41	4.91	5.54	6.04	7.58
	4H	9.02	9.48	10.16	10.60	12.16	4.95	5.41	6.09	6.53	8.09
	6H	9.53	9.92	10.68	11.07	12.62	5.37	5.76	6.51	6.90	8.45
	8H	9.71	10.07	10.85	11.20	12.77	5.49	5.86	6.64	6.99	8.56
	12H	9.80	10.13	10.95	11.27	12.84	5.56	5.89	6.71	7.03	8.60
8H	4H	8.98	9.35	10.12	10.48	12.05	5.22	5.59	6.37	6.72	8.29
	6H	9.55	9.85	10.71	11.02	12.59	5.74	6.04	6.90	7.22	8.78
	8H	9.76	10.02	10.93	11.18	12.76	5.93	6.19	7.10	7.35	8.93
	12H	9.90	10.13	11.07	11.28	12.90	6.05	6.28	7.22	7.43	9.05
12H	4H	8.93	9.26	10.09	10.40	11.98	5.22	5.55	6.38	6.70	8.27
	6H	9.52	9.78	10.69	10.94	12.52	5.79	6.05	6.96	7.21	8.79
	8H	9.74	9.97	10.91	11.12	12.74	6.00	6.23	7.17	7.38	9.00

END OF REPORT