

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926945

Luminaire Tested: DFN2DIP-HX4F0-060D040US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926945
REPORT IS A COMBINATION OF REPORTS P899304 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D040US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8143.2 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 84.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926945

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926945

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88		76	76	76		64
1	100	96	92	89	94	90	87	84	78	76	74		68	66	64		58
2	92	85	79	74	86	79	74	70	69	65	62		60	57	55		52
3	84	75	68	62	78	70	64	59	62	57	53		54	50	47		46
4	77	67	59	53	72	63	56	51	55	50	46		48	44	41		42
5	71	60	52	46	66	56	49	44	50	44	40		44	39	36		38
6	66	54	46	40	61	51	44	39	45	39	35		40	35	32		35
7	61	49	41	36	57	46	39	34	41	35	31		36	32	28		32
8	57	45	37	32	53	42	35	30	38	32	28		33	29	25		29
9	53	41	34	29	50	39	32	27	35	29	25		31	26	23		27
10	50	38	31	26	47	36	29	25	32	27	23		29	24	21		25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1738	1738	1738
5°	1741	1710	1721
10°	1724	1677	1665
15°	1700	1622	1579
20°	1669	1546	1473
25°	1637	1460	1370
30°	1594	1372	1240
35°	1552	1278	1126
40°	1509	1180	995
45°	1459	1072	876
50°	1407	963	760
55°	1354	846	648
60°	1292	724	534
65°	1220	600	481
70°	1133	484	435
75°	1025	427	396
80°	866	358	344
85°	606	241	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1459 cd/sqm

TEST NUMBER: P926945

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.0	2.7
10°-20°	601.3	7.4
20°-30°	844.2	10.4
30°-40°	920.3	11.3
40°-50°	845.8	10.4
50°-60°	664.3	8.2
60°-70°	432.4	5.3
70°-80°	222.6	2.7
80°-90°	60.2	0.7
90°-100°	73.8	0.9
100°-110°	234.4	2.9
110°-120°	401.2	4.9
120°-130°	527.6	6.5
130°-140°	592.2	7.3
140°-150°	580.7	7.1
150°-160°	487.2	6.0
160°-170°	323.1	4.0
170°-180°	112.9	1.4
0°-30°	1664.6	20.4
0°-40°	2584.9	31.7
0°-60°	4095.0	50.3
0°-90°	4810.2	59.1
90°-120°	709.4	8.7
90°-150°	2409.9	29.6
90°-180°	3333.0	40.9
0°-180°	8143.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2066	626
25°	2018	1950	1810	1724	1692	928
35°	1739	1631	1445	1311	1265	1088
45°	1421	1280	1058	907	856	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	1	13	35	33	34	8
95°	52	63	64	64	63	58
105°	216	219	221	223	223	228
115°	402	408	406	406	402	398
125°	586	594	592	588	587	523
135°	757	768	771	770	767	585
145°	920	927	932	934	930	575
155°	1051	1054	1058	1063	1059	484
165°	1144	1143	1143	1150	1145	323
175°	1190	1187	1185	1192	1186	113
180°	1192	1192	1192	1192	1192	

TEST NUMBER: P926945

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.2	2337.2	2337.2	2337.2	2337.2
2.5°	2347.8	2337.2	2313.8	2335.1	2330.9
5°	2337.2	2326.7	2299.0	2318.2	2311.9
7.5°	2318.2	2305.5	2275.9	2284.2	2273.7
10°	2292.7	2277.9	2235.8	2229.3	2216.7
12.5°	2261.2	2242.0	2184.8	2172.3	2148.9
15°	2223.0	2199.6	2127.8	2087.6	2066.5
17.5°	2178.6	2144.7	2055.8	2009.3	1975.5
20°	2127.8	2085.4	1979.7	1926.9	1880.3
22.5°	2072.8	2024.1	1901.4	1829.6	1797.9
25°	2017.9	1950.1	1810.5	1723.9	1692.1
27.5°	1952.4	1880.3	1725.9	1626.5	1577.8
30°	1882.5	1802.0	1632.8	1525.1	1467.8
32.5°	1814.8	1717.4	1544.2	1417.1	1364.2
35°	1738.7	1630.8	1444.8	1311.4	1264.7
37.5°	1664.6	1548.2	1351.6	1205.6	1152.8
40°	1586.3	1459.6	1254.2	1104.0	1049.1
42.5°	1506.0	1370.7	1157.0	1000.4	947.7
45°	1421.4	1279.5	1057.7	907.3	856.5
47.5°	1341.1	1190.9	962.5	812.2	765.7
50°	1252.2	1102.1	869.4	723.3	679.1
52.5°	1165.3	1006.7	780.5	640.9	600.7
55°	1080.8	915.8	687.4	560.6	520.4
57.5°	994.1	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.3	368.0	296.2	289.7
67.5°	645.1	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.6
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.5
80°	230.4	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	1.0	12.9	35.2	33.1	34.1
92.5°	22.2	30.2	31.3	32.3	32.3
95°	52.5	62.6	64.4	64.4	62.6
97.5°	87.4	96.7	100.7	100.7	100.7
100°	127.6	135.9	138.7	138.7	137.7
102.5°	170.0	176.2	180.1	181.1	180.1
105°	216.4	219.2	221.4	223.2	223.2
107.5°	262.4	266.7	266.7	267.4	262.4
110°	307.0	312.7	312.7	312.7	309.9

TEST NUMBER: P926945

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	355.1	361.3	360.1	357.3	355.1
115°	402.5	408.4	406.5	405.5	402.5
117.5°	449.7	457.6	452.6	449.7	446.8
120°	497.2	505.0	497.2	497.2	493.9
122.5°	540.2	550.3	545.3	542.4	540.2
125°	585.6	594.5	591.7	588.4	587.4
127.5°	629.8	640.9	636.9	632.6	629.8
130°	671.1	684.1	682.3	680.1	676.1
132.5°	717.4	727.5	728.3	723.2	720.4
135°	757.4	768.5	770.7	769.6	766.7
137.5°	802.0	810.9	812.7	812.0	807.7
140°	841.1	850.1	855.1	855.1	851.2
142.5°	881.4	890.4	893.2	894.3	890.4
145°	919.5	926.7	932.4	933.5	929.6
147.5°	953.6	962.6	966.9	968.7	964.7
150°	988.9	995.0	999.0	1002.2	999.0
152.5°	1020.2	1026.2	1031.3	1035.2	1031.3
155°	1051.4	1054.3	1057.5	1062.6	1059.3
157.5°	1078.4	1080.5	1082.3	1089.5	1084.4
160°	1102.4	1104.6	1105.6	1111.8	1107.4
162.5°	1124.7	1124.7	1125.8	1132.6	1127.6
165°	1143.8	1142.7	1142.7	1149.8	1144.9
167.5°	1161.1	1157.8	1157.8	1165.0	1159.9
170°	1174.0	1171.1	1170.0	1177.2	1171.1
172.5°	1182.9	1180.1	1179.0	1186.2	1180.1
175°	1190.2	1187.3	1185.1	1192.3	1186.2
177.5°	1194.1	1191.2	1189.1	1195.2	1189.1
180°	1192.3	1192.3	1192.3	1192.3	1192.3

TEST NUMBER: P926945

CATALOG NUMBER: DFN2DIP-HX4F0-060D040US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.87	10.78	10.76	11.68	12.82	5.85	6.76	6.73	7.66	8.79
	3H	11.56	12.37	12.45	13.28	14.44	7.04	7.86	7.94	8.76	9.93
	4H	12.17	12.94	13.08	13.85	15.03	7.50	8.27	8.41	9.18	10.35
	6H	12.60	13.31	13.52	14.22	15.41	7.83	8.53	8.75	9.45	10.64
	8H	12.73	13.40	13.66	14.34	15.52	7.92	8.59	8.85	9.53	10.71
	12H	12.79	13.43	13.73	14.36	15.57	7.97	8.61	8.90	9.54	10.75
4H	2H	9.90	10.67	10.82	11.58	12.76	6.45	7.22	7.37	8.13	9.31
	3H	11.74	12.38	12.67	13.32	14.51	7.81	8.45	8.74	9.39	10.58
	4H	12.44	13.02	13.37	13.96	15.17	8.36	8.95	9.30	9.89	11.10
	6H	12.96	13.46	13.91	14.42	15.63	8.79	9.29	9.74	10.25	11.47
	8H	13.13	13.60	14.09	14.56	15.79	8.92	9.39	9.87	10.35	11.57
	12H	13.23	13.65	14.20	14.63	15.86	8.99	9.41	9.96	10.39	11.62
8H	4H	12.41	12.88	13.36	13.83	15.06	8.65	9.12	9.60	10.08	11.30
	6H	12.98	13.37	13.96	14.36	15.59	9.17	9.56	10.15	10.56	11.79
	8H	13.20	13.54	14.18	14.53	15.77	9.37	9.71	10.35	10.70	11.94
	12H	13.34	13.64	14.33	14.62	15.91	9.49	9.79	10.48	10.77	12.07
12H	4H	12.37	12.79	13.34	13.76	14.99	8.66	9.08	9.63	10.06	11.29
	6H	12.96	13.30	13.94	14.29	15.53	9.22	9.57	10.21	10.55	11.80
	8H	13.18	13.48	14.17	14.46	15.75	9.44	9.74	10.43	10.72	12.01