

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913662

Luminaire Tested: DFN2DIP-HX4F0-070D090US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913662
REPORT IS A COMBINATION OF REPORTS P899395 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D090US927-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11799.6 lumens
Efficiency: N/A
Efficacy: 100.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 117.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913662

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913662

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47		
1	97	93	89	85	89	85	82	79	71	69	67	59	57	55	47	46	45	39		
2	88	81	75	70	81	75	69	65	63	59	55	51	49	46	41	39	38	33		
3	81	71	64	58	74	66	59	54	55	50	47	45	42	39	37	34	32	28		
4	74	63	55	49	67	58	51	46	49	44	40	41	37	34	33	30	28	24		
5	68	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24	21		
6	62	50	42	36	57	47	39	34	39	34	30	33	29	25	27	24	21	18		
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	24	21	19	16		
8	53	41	33	28	49	38	31	27	33	27	23	27	23	20	22	19	17	14		
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15	13		
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1604	1604	1604
5°	1607	1582	1593
10°	1594	1561	1571
15°	1571	1535	1538
20°	1539	1500	1503
25°	1508	1457	1463
30°	1469	1418	1413
35°	1431	1371	1359
40°	1385	1324	1308
45°	1340	1277	1256
50°	1290	1227	1196
55°	1237	1170	1140
60°	1178	1102	1077
65°	1114	1031	1002
70°	1031	945	921
75°	917	842	847
80°	781	711	704
85°	567	485	468

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1701 cd/sqm

TEST NUMBER: P913662

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	203.1	1.7
10°-20°	571.4	4.8
20°-30°	839.7	7.1
30°-40°	975.3	8.3
40°-50°	974.1	8.3
50°-60°	849.4	7.2
60°-70°	627.9	5.3
70°-80°	355.2	3.0
80°-90°	100.2	0.8
90°-100°	139.5	1.2
100°-110°	443.3	3.8
110°-120°	758.7	6.4
120°-130°	997.8	8.5
130°-140°	1120.0	9.5
140°-150°	1098.2	9.3
150°-160°	921.3	7.8
160°-170°	611.0	5.2
170°-180°	213.5	1.8
0°-30°	1614.2	13.7
0°-40°	2589.5	21.9
0°-60°	4412.9	37.4
0°-90°	5496.2	46.6
90°-120°	1341.5	11.4
90°-150°	4557.5	38.6
90°-180°	6303.0	53.4
0°-180°	11799.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2158	2158	2158	2158	2158	
5°	2158	2150	2127	2143	2139	205
15°	2054	2042	2015	2023	2013	578
25°	1859	1842	1807	1811	1807	855
35°	1604	1583	1550	1537	1527	1002
45°	1305	1291	1259	1237	1228	1007
55°	988	975	950	925	915	883
65°	666	654	633	614	604	659
75°	348	344	334	322	326	372
85°	85	83	81	75	73	95
90°	2	24	67	62	65	11
95°	99	118	122	122	118	110
105°	409	415	419	422	422	432
115°	761	772	769	767	761	753
125°	1107	1124	1119	1113	1111	990
135°	1432	1453	1458	1455	1450	1107
145°	1739	1752	1763	1765	1758	1086
155°	1988	1994	2000	2009	2003	915
165°	2163	2161	2161	2175	2165	610
175°	2251	2245	2241	2255	2243	214
180°	2255	2255	2255	2255	2255	

TEST NUMBER: P913662

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2157.7	2157.7	2157.7	2157.7	2157.7
2.5°	2170.3	2159.9	2137.0	2157.7	2153.7
5°	2157.7	2149.6	2126.7	2143.2	2139.2
7.5°	2143.2	2130.8	2107.9	2124.7	2120.5
10°	2120.5	2105.9	2081.1	2097.6	2091.4
12.5°	2089.2	2076.9	2052.1	2062.4	2058.2
15°	2054.0	2041.7	2014.6	2023.0	2012.6
17.5°	2010.4	1998.1	1971.0	1981.4	1971.0
20°	1962.6	1950.4	1921.3	1927.5	1919.3
22.5°	1915.1	1896.4	1869.3	1869.3	1865.1
25°	1859.0	1842.5	1807.3	1811.2	1807.3
27.5°	1796.7	1782.2	1755.3	1749.1	1738.8
30°	1734.6	1717.8	1686.9	1680.7	1672.3
32.5°	1668.1	1655.8	1622.5	1610.0	1601.6
35°	1603.8	1583.2	1549.9	1537.4	1527.0
37.5°	1531.2	1512.5	1479.2	1464.7	1454.4
40°	1456.6	1439.9	1406.6	1388.1	1379.7
42.5°	1383.9	1367.2	1334.2	1313.3	1300.9
45°	1305.1	1290.6	1259.3	1236.7	1228.3
47.5°	1228.3	1213.8	1180.5	1157.6	1145.3
50°	1147.3	1136.9	1107.9	1078.9	1068.5
52.5°	1068.5	1054.0	1027.1	1004.2	989.7
55°	987.7	975.2	950.3	925.4	915.0
57.5°	906.7	896.4	869.3	844.4	836.1
60°	825.7	817.5	788.5	765.6	759.5
62.5°	746.9	732.4	711.7	691.0	682.6
65°	666.1	653.5	632.9	614.2	603.8
67.5°	583.1	572.6	554.1	539.6	531.2
70°	506.3	498.0	479.2	464.7	456.5
72.5°	427.5	419.1	408.8	394.3	388.1
75°	348.5	344.5	333.9	321.6	325.8
77.5°	278.1	269.7	265.5	259.3	253.2
80°	207.6	205.4	201.2	195.0	190.8
82.5°	141.1	141.1	139.1	130.8	130.8
85°	85.0	83.0	81.0	74.6	72.6
87.5°	37.4	33.3	29.1	22.9	20.7
90°	2.1	24.5	66.6	62.5	64.6
92.5°	42.1	57.1	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.2	182.8	190.4	190.4	190.4
100°	241.3	257.0	262.4	262.4	260.4
102.5°	321.5	333.1	340.6	342.6	340.6
105°	409.2	414.6	418.7	422.2	422.2
107.5°	496.2	504.4	504.4	505.7	496.2
110°	580.5	591.4	591.4	591.4	586.0

TEST NUMBER: P913662

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	671.6	683.2	681.1	675.7	671.6
115°	761.4	772.2	768.8	766.8	761.4
117.5°	850.4	865.4	855.9	850.4	844.9
120°	940.2	955.1	940.2	940.2	934.0
122.5°	1021.7	1040.8	1031.3	1025.8	1021.7
125°	1107.4	1124.3	1119.0	1112.8	1110.8
127.5°	1191.0	1212.0	1204.6	1196.4	1191.0
130°	1269.2	1293.6	1290.2	1286.1	1278.7
132.5°	1356.8	1375.9	1377.2	1367.7	1362.3
135°	1432.3	1453.3	1457.5	1455.4	1450.0
137.5°	1516.6	1533.6	1537.0	1535.6	1527.5
140°	1590.7	1607.7	1617.2	1617.2	1609.7
142.5°	1666.8	1683.8	1689.2	1691.3	1683.8
145°	1738.9	1752.5	1763.3	1765.4	1757.9
147.5°	1803.5	1820.4	1828.6	1832.0	1824.6
150°	1870.1	1881.7	1889.1	1895.2	1889.1
152.5°	1929.2	1940.8	1950.3	1957.8	1950.3
155°	1988.4	1993.8	1999.9	2009.4	2003.3
157.5°	2039.3	2043.4	2046.8	2060.4	2050.9
160°	2084.9	2089.0	2091.0	2102.5	2094.4
162.5°	2127.0	2127.0	2129.1	2142.0	2132.5
165°	2163.1	2161.0	2161.0	2174.6	2165.1
167.5°	2195.7	2189.6	2189.6	2203.1	2193.6
170°	2220.2	2214.7	2212.7	2226.3	2214.7
172.5°	2237.1	2231.7	2229.7	2243.3	2231.7
175°	2250.7	2245.3	2241.2	2254.9	2243.3
177.5°	2258.2	2252.8	2248.7	2260.3	2248.7
180°	2254.9	2254.9	2254.9	2254.9	2254.9

TEST NUMBER: P913662

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.59	9.42	9.57	10.42	11.74	8.16	8.99	9.14	9.99	11.31
	3H	10.25	10.99	11.24	12.00	13.34	9.77	10.52	10.77	11.53	12.87
	4H	10.83	11.54	11.84	12.55	13.90	10.36	11.07	11.37	12.08	13.43
	6H	11.23	11.88	12.25	12.90	14.26	10.76	11.41	11.78	12.42	13.78
	8H	11.34	11.96	12.36	12.99	14.35	10.86	11.48	11.89	12.51	13.87
	12H	11.39	11.97	12.42	13.00	14.38	10.90	11.49	11.94	12.52	13.90
4H	2H	9.05	9.75	10.06	10.76	12.11	8.70	9.41	9.72	10.42	11.77
	3H	10.91	11.50	11.94	12.54	13.90	10.52	11.11	11.54	12.15	13.51
	4H	11.63	12.17	12.66	13.20	14.58	11.22	11.76	12.25	12.79	14.18
	6H	12.14	12.60	13.18	13.66	15.04	11.73	12.19	12.77	13.25	14.63
	8H	12.29	12.72	13.33	13.77	15.17	11.88	12.31	12.92	13.36	14.75
	12H	12.36	12.75	13.42	13.82	15.22	11.94	12.33	13.00	13.39	14.79
8H	4H	11.82	12.25	12.86	13.30	14.70	11.46	11.89	12.50	12.94	14.34
	6H	12.45	12.81	13.52	13.90	15.29	12.09	12.45	13.16	13.54	14.93
	8H	12.67	12.99	13.75	14.06	15.47	12.30	12.62	13.38	13.69	15.10
	12H	12.80	13.08	13.88	14.15	15.60	12.42	12.70	13.50	13.77	15.22
12H	4H	11.80	12.20	12.87	13.26	14.66	11.45	11.84	12.51	12.91	14.31
	6H	12.48	12.80	13.56	13.87	15.28	12.13	12.45	13.20	13.52	14.93
	8H	12.72	13.00	13.80	14.07	15.52	12.37	12.64	13.44	13.71	15.17