

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926954

Luminaire Tested: DFN2DIP-HX4F0-060D060US830-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926954
REPORT IS A COMBINATION OF REPORTS P900860 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D060US830-RLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10405.2 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 98.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926954
CATALOG NUMBER: DFN2DIP-HX4F0-060D060US830-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P926954

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53	46				46
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	45	40				40
2	89	82	76	71	82	76	70	66	63	60	57	52	50	48	42	40	39	34				34
3	81	72	65	60	75	67	61	56	56	52	48	47	43	41	38	35	34	29				29
4	75	64	57	51	68	60	53	48	50	45	41	42	38	35	34	31	29	26				26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23				23
6	63	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20				20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16				16
9	51	39	32	27	47	36	30	25	31	26	22	27	23	20	22	19	17	15				15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	20	18	15	13				13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1738	1738	1738
5°	1741	1710	1721
10°	1724	1677	1665
15°	1700	1622	1579
20°	1669	1546	1473
25°	1637	1460	1370
30°	1594	1372	1240
35°	1552	1278	1126
40°	1509	1180	995
45°	1459	1072	876
50°	1407	963	760
55°	1354	846	648
60°	1292	724	534
65°	1220	600	481
70°	1133	484	435
75°	1025	427	396
80°	866	358	344
85°	606	241	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1459 cd/sqm



TEST NUMBER: P926954

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US830-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.0	2.1
10°-20°	601.3	5.8
20°-30°	844.2	8.1
30°-40°	920.3	8.8
40°-50°	845.8	8.1
50°-60°	664.3	6.4
60°-70°	432.4	4.2
70°-80°	222.6	2.1
80°-90°	60.2	0.6
90°-100°	62.9	0.6
100°-110°	234.6	2.3
110°-120°	622.2	6.0
120°-130°	1031.9	9.9
130°-140°	1096.2	10.5
140°-150°	1018.8	9.8
150°-160°	819.1	7.9
160°-170°	527.8	5.1
170°-180°	181.7	1.7
0°-30°	1664.6	16.0
0°-40°	2584.9	24.8
0°-60°	4095.0	39.4
0°-90°	4810.1	46.2
90°-120°	919.7	8.8
90°-150°	4066.6	39.1
90°-180°	5595.0	53.8
0°-180°	10405.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2066	626
25°	2018	1950	1810	1724	1692	928
35°	1739	1631	1445	1311	1265	1088
45°	1421	1280	1058	907	856	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	1	17	28	35	37	10
95°	90	44	54	61	59	106
105°	420	461	84	99	105	449
115°	794	818	852	213	113	782
125°	1123	1141	1167	1177	1181	1001
135°	1389	1412	1424	1438	1435	1073
145°	1612	1610	1634	1643	1636	1008
155°	1774	1762	1779	1787	1776	818
165°	1870	1862	1866	1875	1866	528
175°	1913	1903	1906	1915	1902	182
180°	1908	1908	1908	1908	1908	



TEST NUMBER: P926954

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.2	2337.2	2337.2	2337.2	2337.2
2.5°	2347.8	2337.2	2313.8	2335.1	2330.9
5°	2337.2	2326.7	2299.0	2318.2	2311.9
7.5°	2318.2	2305.5	2275.9	2284.2	2273.7
10°	2292.7	2277.9	2235.8	2229.3	2216.7
12.5°	2261.2	2242.0	2184.8	2172.3	2148.9
15°	2223.0	2199.6	2127.8	2087.6	2066.5
17.5°	2178.6	2144.7	2055.8	2009.3	1975.5
20°	2127.8	2085.4	1979.7	1926.9	1880.3
22.5°	2072.8	2024.1	1901.4	1829.6	1797.9
25°	2017.9	1950.1	1810.5	1723.9	1692.1
27.5°	1952.4	1880.3	1725.9	1626.5	1577.8
30°	1882.5	1802.0	1632.8	1525.1	1467.8
32.5°	1814.8	1717.4	1544.2	1417.1	1364.2
35°	1738.7	1630.8	1444.8	1311.4	1264.7
37.5°	1664.6	1548.2	1351.6	1205.6	1152.8
40°	1586.3	1459.6	1254.2	1104.0	1049.1
42.5°	1506.0	1370.7	1157.0	1000.4	947.7
45°	1421.4	1279.5	1057.7	907.3	856.5
47.5°	1341.1	1190.9	962.5	812.2	765.7
50°	1252.2	1102.1	869.4	723.3	679.1
52.5°	1165.3	1006.7	780.5	640.9	600.7
55°	1080.8	915.8	687.4	560.6	520.4
57.5°	994.1	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.3	368.0	296.2	289.7
67.5°	645.1	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.6
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.5
80°	230.4	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	1.3	16.6	27.5	34.6	37.2
92.5°	34.6	29.0	33.1	35.9	37.2
95°	89.7	44.1	53.8	60.9	59.4
97.5°	161.5	48.4	70.3	74.6	76.0
100°	244.5	55.2	78.7	89.7	92.5
102.5°	335.5	332.9	81.5	96.6	100.8
105°	419.8	461.3	84.3	99.3	105.0
107.5°	517.9	552.3	87.1	102.2	107.7
110°	611.9	640.7	241.8	103.7	109.0



TEST NUMBER: P926954

CATALOG NUMBER: DFN2DIP-HX4F0-060D060US830-RLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	700.2	725.0	701.5	106.2	110.6
115°	794.1	817.5	852.1	212.7	113.3
117.5°	875.5	903.1	926.7	729.1	367.3
120°	966.7	987.4	1012.3	1028.8	842.4
122.5°	1043.9	1066.1	1093.8	1102.0	1103.5
125°	1122.7	1140.7	1166.9	1176.6	1180.7
127.5°	1194.5	1213.8	1234.7	1248.4	1249.8
130°	1262.2	1284.3	1299.4	1314.7	1313.4
132.5°	1331.3	1349.3	1364.4	1376.8	1375.5
135°	1389.3	1411.5	1423.7	1437.7	1434.9
137.5°	1449.9	1466.5	1480.5	1494.2	1490.2
140°	1509.3	1520.5	1535.6	1548.1	1541.2
142.5°	1559.2	1568.9	1586.8	1597.7	1590.8
145°	1611.7	1610.2	1633.6	1643.3	1636.5
147.5°	1657.1	1653.0	1676.4	1683.3	1677.9
150°	1701.4	1691.7	1713.8	1722.0	1715.2
152.5°	1738.6	1727.6	1748.2	1756.6	1746.9
155°	1774.5	1762.2	1778.8	1787.0	1776.0
157.5°	1803.6	1792.5	1805.0	1814.7	1803.6
160°	1828.4	1820.1	1828.4	1836.6	1827.0
162.5°	1850.4	1842.2	1849.1	1858.8	1846.4
165°	1869.8	1861.6	1865.7	1875.4	1865.7
167.5°	1885.0	1876.7	1880.9	1890.7	1878.1
170°	1897.5	1889.1	1892.0	1901.6	1889.1
172.5°	1905.7	1897.5	1900.3	1910.0	1897.5
175°	1912.6	1902.9	1905.7	1915.3	1901.6
177.5°	1915.3	1905.7	1907.1	1916.9	1904.4
180°	1908.5	1908.5	1908.5	1908.5	1908.5



TEST NUMBER: P926954
 CATALOG NUMBER: DFN2DIP-HX4F0-060D060US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.70	9.51	9.70	10.51	11.83	4.68	5.48	5.67	6.48	7.81
	3H	10.38	11.10	11.39	12.11	13.46	5.87	6.58	6.87	7.59	8.94
	4H	10.99	11.67	12.01	12.68	14.04	6.32	6.99	7.34	8.01	9.36
	6H	11.41	12.03	12.44	13.05	14.42	6.64	7.26	7.67	8.28	9.65
	8H	11.54	12.13	12.57	13.16	14.53	6.73	7.32	7.76	8.36	9.72
	12H	11.60	12.16	12.64	13.19	14.58	6.77	7.33	7.81	8.36	9.75
4H	2H	8.72	9.40	9.74	10.41	11.77	5.27	5.95	6.30	6.96	8.32
	3H	10.55	11.11	11.58	12.15	13.52	6.62	7.18	7.65	8.23	9.59
	4H	11.24	11.75	12.28	12.79	14.18	7.17	7.68	8.21	8.72	10.11
	6H	11.75	12.20	12.80	13.25	14.64	7.59	8.03	8.64	9.09	10.48
	8H	11.93	12.34	12.98	13.39	14.79	7.72	8.13	8.77	9.18	10.58
	12H	12.02	12.40	13.09	13.46	14.87	7.78	8.15	8.85	9.22	10.63
8H	4H	11.21	11.62	12.26	12.67	14.07	7.45	7.86	8.50	8.91	10.31
	6H	11.77	12.11	12.85	13.20	14.60	7.97	8.31	9.04	9.40	10.80
	8H	11.99	12.29	13.07	13.36	14.78	8.16	8.46	9.24	9.53	10.95
	12H	12.13	12.39	13.21	13.46	14.92	8.28	8.54	9.36	9.61	11.07
12H	4H	11.16	11.53	12.22	12.59	14.00	7.45	7.82	8.52	8.89	10.30
	6H	11.75	12.05	12.83	13.12	14.54	8.02	8.31	9.10	9.39	10.81
	8H	11.97	12.23	13.05	13.30	14.76	8.23	8.49	9.31	9.56	11.02