

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926969

Luminaire Tested: DFN2DIP-HX4F0-060D100US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926969
REPORT IS A COMBINATION OF REPORTS P899412 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D100US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13147.9 lumens
Efficiency: N/A
Efficacy: 100.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 130.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926969

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926969

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44
1	95	91	87	84	86	83	80	77	67	65	63	53	51	50	39	38	38
2	87	80	74	69	79	73	68	63	59	56	53	47	44	42	35	34	32
3	79	70	64	58	72	64	58	53	52	48	45	41	39	36	31	29	28
4	73	63	55	49	66	57	51	46	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21
6	62	50	42	37	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	38	32	52	41	35	30	34	29	26	28	24	21	21	19	17
8	53	41	34	29	48	38	31	27	31	26	23	25	22	19	20	17	15
9	49	38	30	25	45	34	28	24	29	24	20	23	20	17	18	16	14
10	46	34	27	23	42	32	25	21	26	22	18	22	18	16	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1738	1738	1738
5°	1741	1710	1721
10°	1724	1677	1665
15°	1700	1622	1579
20°	1669	1546	1473
25°	1637	1460	1370
30°	1594	1372	1240
35°	1552	1278	1126
40°	1509	1180	995
45°	1459	1072	876
50°	1407	963	760
55°	1354	846	648
60°	1292	724	534
65°	1220	600	481
70°	1133	484	435
75°	1025	427	396
80°	866	358	344
85°	606	241	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2248 cd/sqm

TEST NUMBER: P926969

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.0	1.7
10°-20°	601.3	4.6
20°-30°	844.2	6.4
30°-40°	920.3	7.0
40°-50°	845.8	6.4
50°-60°	664.3	5.1
60°-70°	432.4	3.3
70°-80°	222.6	1.7
80°-90°	65.3	0.5
90°-100°	184.5	1.4
100°-110°	586.1	4.5
110°-120°	1002.9	7.6
120°-130°	1319.0	10.0
130°-140°	1480.5	11.3
140°-150°	1451.8	11.0
150°-160°	1217.9	9.3
160°-170°	807.7	6.1
170°-180°	282.3	2.1
0°-30°	1664.6	12.7
0°-40°	2584.9	19.7
0°-60°	4095.0	31.1
0°-90°	4815.2	36.6
90°-120°	1773.4	13.5
90°-150°	6024.8	45.8
90°-180°	8333.0	63.4
0°-180°	13147.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2066	626
25°	2018	1950	1810	1724	1692	928
35°	1739	1631	1445	1311	1265	1088
45°	1421	1280	1058	907	856	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	3	32	88	83	85	13
95°	131	156	161	161	156	146
105°	541	548	554	558	558	571
115°	1006	1021	1016	1014	1006	995
125°	1464	1486	1479	1471	1468	1308
135°	1893	1921	1927	1924	1917	1464
145°	2299	2317	2331	2334	2324	1436
155°	2628	2636	2644	2656	2648	1210
165°	2860	2857	2857	2875	2862	807
175°	2975	2968	2963	2981	2966	283
180°	2981	2981	2981	2981	2981	

TEST NUMBER: P926969

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.2	2337.2	2337.2	2337.2	2337.2
2.5°	2347.8	2337.2	2313.8	2335.1	2330.9
5°	2337.2	2326.7	2299.0	2318.2	2311.9
7.5°	2318.2	2305.5	2275.9	2284.2	2273.7
10°	2292.7	2277.9	2235.8	2229.3	2216.7
12.5°	2261.2	2242.0	2184.8	2172.3	2148.9
15°	2223.0	2199.6	2127.8	2087.6	2066.5
17.5°	2178.6	2144.7	2055.8	2009.3	1975.5
20°	2127.8	2085.4	1979.7	1926.9	1880.3
22.5°	2072.8	2024.1	1901.4	1829.6	1797.9
25°	2017.9	1950.1	1810.5	1723.9	1692.1
27.5°	1952.4	1880.3	1725.9	1626.5	1577.8
30°	1882.5	1802.0	1632.8	1525.1	1467.8
32.5°	1814.8	1717.4	1544.2	1417.1	1364.2
35°	1738.7	1630.8	1444.8	1311.4	1264.7
37.5°	1664.6	1548.2	1351.6	1205.6	1152.8
40°	1586.3	1459.6	1254.2	1104.0	1049.1
42.5°	1506.0	1370.7	1157.0	1000.4	947.7
45°	1421.4	1279.5	1057.7	907.3	856.5
47.5°	1341.1	1190.9	962.5	812.2	765.7
50°	1252.2	1102.1	869.4	723.3	679.1
52.5°	1165.3	1006.7	780.5	640.9	600.7
55°	1080.8	915.8	687.4	560.6	520.4
57.5°	994.1	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.3	368.0	296.2	289.7
67.5°	645.1	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.6
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.5
80°	230.4	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	2.7	32.3	88.0	82.7	85.4
92.5°	55.7	75.5	78.2	80.9	80.9
95°	131.2	156.4	160.9	160.9	156.4
97.5°	218.4	241.8	251.6	251.6	251.6
100°	319.0	339.7	346.8	346.8	344.2
102.5°	425.1	440.3	450.2	452.9	450.2
105°	541.0	548.2	553.5	558.1	558.1
107.5°	656.0	666.8	666.8	668.6	656.0
110°	767.5	781.8	781.8	781.8	774.6



TEST NUMBER: P926969

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	887.8	903.1	900.5	893.2	887.8
115°	1006.5	1020.8	1016.4	1013.7	1006.5
117.5°	1124.2	1144.0	1131.4	1124.2	1117.0
120°	1242.8	1262.6	1242.8	1242.8	1234.8
122.5°	1350.6	1375.8	1363.2	1356.1	1350.6
125°	1463.9	1486.3	1479.2	1471.1	1468.4
127.5°	1574.4	1602.2	1592.4	1581.6	1574.4
130°	1677.7	1710.1	1705.6	1700.2	1690.4
132.5°	1793.7	1818.8	1820.6	1808.1	1800.8
135°	1893.4	1921.3	1926.7	1924.0	1916.8
137.5°	2004.9	2027.3	2031.8	2030.1	2019.2
140°	2102.8	2125.2	2137.9	2137.9	2128.0
142.5°	2203.5	2225.9	2233.1	2235.8	2225.9
145°	2298.7	2316.7	2331.1	2333.7	2323.8
147.5°	2384.1	2406.6	2417.3	2421.8	2412.0
150°	2472.2	2487.4	2497.3	2505.4	2497.3
152.5°	2550.3	2565.6	2578.2	2588.1	2578.2
155°	2628.5	2635.7	2643.8	2656.3	2648.2
157.5°	2695.9	2701.3	2705.8	2723.7	2711.2
160°	2756.2	2761.5	2764.2	2779.4	2768.7
162.5°	2811.9	2811.9	2814.5	2831.6	2819.0
165°	2859.5	2856.7	2856.7	2874.7	2862.2
167.5°	2902.6	2894.5	2894.5	2912.5	2899.9
170°	2934.9	2927.8	2925.0	2943.1	2927.8
172.5°	2957.4	2950.2	2947.5	2965.5	2950.2
175°	2975.4	2968.2	2962.8	2980.8	2965.5
177.5°	2985.3	2978.1	2972.6	2987.9	2972.6
180°	2980.8	2980.8	2980.8	2980.8	2980.8

TEST NUMBER: P926969

CATALOG NUMBER: DFN2DIP-HX4F0-060D100US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.67	8.40	8.74	9.47	10.92	3.64	4.38	4.71	5.44	6.90
	3H	9.34	10.00	10.42	11.07	12.54	4.83	5.48	5.91	6.56	8.03
	4H	9.95	10.57	11.04	11.65	13.12	5.27	5.89	6.36	6.97	8.45
	6H	10.36	10.93	11.46	12.02	13.50	5.59	6.16	6.69	7.24	8.73
	8H	10.49	11.03	11.59	12.13	13.61	5.68	6.22	6.78	7.32	8.80
	12H	10.55	11.06	11.65	12.15	13.66	5.72	6.24	6.83	7.33	8.83
4H	2H	7.68	8.30	8.77	9.38	10.85	4.23	4.85	5.33	5.93	7.40
	3H	9.50	10.02	10.60	11.12	12.61	5.57	6.09	6.67	7.19	8.68
	4H	10.19	10.66	11.30	11.76	13.27	6.12	6.59	7.22	7.69	9.20
	6H	10.70	11.10	11.81	12.22	13.73	6.53	6.94	7.65	8.06	9.56
	8H	10.87	11.25	11.99	12.36	13.88	6.66	7.04	7.78	8.15	9.67
	12H	10.96	11.31	12.10	12.43	13.95	6.72	7.07	7.85	8.19	9.71
8H	4H	10.15	10.53	11.26	11.64	13.16	6.39	6.77	7.51	7.88	9.40
	6H	10.71	11.03	11.85	12.18	13.69	6.91	7.22	8.04	8.37	9.89
	8H	10.93	11.20	12.07	12.34	13.87	7.10	7.37	8.24	8.51	10.04
	12H	11.07	11.31	12.21	12.43	14.01	7.22	7.46	8.36	8.59	10.16
12H	4H	10.10	10.44	11.23	11.56	13.09	6.39	6.73	7.52	7.86	9.38
	6H	10.69	10.96	11.83	12.09	13.63	6.96	7.23	8.10	8.36	9.90
	8H	10.91	11.15	12.05	12.27	13.85	7.16	7.40	8.31	8.53	10.11

END OF REPORT