

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926971

Luminaire Tested: DFN2DIP-HX4F0-060D110US830-FLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926971
REPORT IS A COMBINATION OF REPORTS P899429 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-060D110US830-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14773.7 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 141.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926971

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926971

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	79	76	67	65	63	53	51	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	49	44	46	41	37	37	33	30	28	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	41	34	29	33	28	24	27	23	20	21	18	16
8	52	40	32	27	47	37	30	25	30	25	22	25	21	18	19	16	14
9	48	37	29	24	44	34	27	23	28	23	19	23	19	16	17	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1636	1636	1636
5°	1639	1613	1624
10°	1626	1592	1602
15°	1602	1566	1568
20°	1570	1530	1533
25°	1538	1486	1492
30°	1498	1446	1441
35°	1460	1398	1386
40°	1413	1350	1334
45°	1366	1302	1281
50°	1315	1251	1219
55°	1262	1193	1163
60°	1201	1123	1098
65°	1136	1051	1021
70°	1052	964	939
75°	935	859	863
80°	796	725	718
85°	577	494	478

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2472 cd/sqm

TEST NUMBER: P926971

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.1	1.4
10°-20°	582.7	3.9
20°-30°	856.3	5.8
30°-40°	994.6	6.7
40°-50°	993.4	6.7
50°-60°	866.2	5.9
60°-70°	640.3	4.3
70°-80°	362.3	2.5
80°-90°	104.9	0.7
90°-100°	202.9	1.4
100°-110°	644.7	4.4
110°-120°	1103.2	7.5
120°-130°	1450.9	9.8
130°-140°	1628.6	11.0
140°-150°	1597.0	10.8
150°-160°	1339.7	9.1
160°-170°	888.4	6.0
170°-180°	310.5	2.1
0°-30°	1646.2	11.1
0°-40°	2640.7	17.9
0°-60°	4500.3	30.5
0°-90°	5607.8	38.0
90°-120°	1950.8	13.2
90°-150°	6627.3	44.9
90°-180°	9166.0	62.0
0°-180°	14773.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2200	2200	2200	2200	2200	
5°	2200	2192	2169	2186	2182	209
15°	2095	2082	2054	2063	2052	590
25°	1896	1879	1843	1847	1843	872
35°	1636	1614	1581	1568	1557	1021
45°	1331	1316	1284	1261	1253	1027
55°	1007	994	969	944	933	901
65°	679	666	645	626	616	672
75°	355	351	340	328	332	379
85°	87	85	83	76	74	97
90°	3	36	97	91	94	14
95°	144	172	177	177	172	161
105°	595	603	609	614	614	628
115°	1107	1123	1118	1115	1107	1095
125°	1610	1635	1627	1618	1615	1439
135°	2083	2113	2119	2116	2108	1610
145°	2528	2548	2564	2567	2556	1580
155°	2891	2899	2908	2922	2913	1331
165°	3145	3142	3142	3162	3148	887
175°	3273	3265	3259	3279	3262	311
180°	3279	3279	3279	3279	3279	

TEST NUMBER: P926971

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2200.4	2200.4	2200.4	2200.4	2200.4
2.5°	2213.2	2202.6	2179.2	2200.4	2196.3
5°	2200.4	2192.1	2168.7	2185.6	2181.5
7.5°	2185.6	2173.0	2149.7	2166.7	2162.5
10°	2162.5	2147.7	2122.2	2139.1	2132.8
12.5°	2130.6	2118.0	2092.6	2103.2	2098.9
15°	2094.6	2082.1	2054.5	2063.0	2052.5
17.5°	2050.2	2037.7	2010.1	2020.5	2010.1
20°	2001.5	1989.0	1959.3	1965.6	1957.3
22.5°	1953.0	1933.9	1906.3	1906.3	1902.1
25°	1895.7	1879.0	1843.0	1847.0	1843.0
27.5°	1832.2	1817.4	1790.0	1783.8	1773.2
30°	1769.0	1751.8	1720.3	1713.9	1705.4
32.5°	1701.1	1688.6	1654.7	1641.8	1633.4
35°	1635.6	1614.5	1580.6	1567.8	1557.2
37.5°	1561.5	1542.4	1508.6	1493.7	1483.1
40°	1485.4	1468.3	1434.5	1415.6	1407.1
42.5°	1411.3	1394.2	1360.6	1339.3	1326.7
45°	1331.0	1316.1	1284.3	1261.2	1252.6
47.5°	1252.6	1237.8	1203.9	1180.6	1167.9
50°	1170.0	1159.5	1129.9	1100.2	1089.6
52.5°	1089.6	1074.8	1047.4	1024.1	1009.3
55°	1007.2	994.4	969.1	943.7	933.2
57.5°	924.7	914.1	886.5	861.2	852.6
60°	842.0	833.7	804.1	780.8	774.5
62.5°	761.6	746.8	725.7	704.6	696.1
65°	679.3	666.5	645.4	626.3	615.7
67.5°	594.6	583.9	565.0	550.2	541.7
70°	516.3	507.8	488.7	473.9	465.6
72.5°	435.9	427.4	416.9	402.1	395.8
75°	355.3	351.4	340.5	328.0	332.2
77.5°	283.5	275.0	270.7	264.5	258.2
80°	211.7	209.4	205.2	198.9	194.6
82.5°	143.9	143.9	141.8	133.4	133.4
85°	86.6	84.6	82.6	76.1	74.1
87.5°	38.2	33.9	29.6	23.4	21.1
90°	2.9	35.6	96.9	91.0	93.9
92.5°	61.3	83.0	86.0	89.0	89.0
95°	144.3	172.0	176.9	176.9	172.0
97.5°	240.2	265.9	276.8	276.8	276.8
100°	350.9	373.6	381.5	381.5	378.6
102.5°	467.6	484.4	495.3	498.2	495.3
105°	595.1	603.0	608.9	613.9	613.9
107.5°	721.6	733.5	733.5	735.4	721.6
110°	844.2	860.0	860.0	860.0	852.1

TEST NUMBER: P926971

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	976.6	993.4	990.5	982.6	976.6
115°	1107.2	1122.9	1118.0	1115.1	1107.2
117.5°	1236.7	1258.3	1244.5	1236.7	1228.7
120°	1367.1	1388.9	1367.1	1367.1	1358.2
122.5°	1485.8	1513.4	1499.5	1491.6	1485.8
125°	1610.3	1635.0	1627.0	1618.2	1615.2
127.5°	1731.8	1762.5	1751.6	1739.8	1731.8
130°	1845.5	1881.1	1876.1	1870.2	1859.4
132.5°	1973.0	2000.7	2002.7	1988.9	1980.9
135°	2082.7	2113.4	2119.3	2116.4	2108.5
137.5°	2205.4	2230.0	2235.0	2233.0	2221.2
140°	2313.1	2337.8	2351.6	2351.6	2340.8
142.5°	2423.8	2448.5	2456.4	2459.4	2448.5
145°	2528.5	2548.3	2564.2	2567.1	2556.2
147.5°	2622.5	2647.2	2659.1	2664.0	2653.1
150°	2719.4	2736.2	2747.0	2756.0	2747.0
152.5°	2805.4	2822.1	2836.0	2846.9	2836.0
155°	2891.4	2899.2	2908.2	2922.0	2913.1
157.5°	2965.5	2971.4	2976.3	2996.1	2982.3
160°	3031.7	3037.7	3040.6	3057.5	3045.6
162.5°	3093.0	3093.0	3096.0	3114.8	3100.9
165°	3145.4	3142.4	3142.4	3162.2	3148.3
167.5°	3192.8	3184.0	3184.0	3203.7	3189.9
170°	3228.4	3220.5	3217.6	3237.3	3220.5
172.5°	3253.1	3245.2	3242.3	3262.1	3245.2
175°	3272.9	3265.0	3259.1	3278.9	3262.1
177.5°	3283.8	3275.8	3269.9	3286.8	3269.9
180°	3278.9	3278.9	3278.9	3278.9	3278.9

TEST NUMBER: P926971

CATALOG NUMBER: DFN2DIP-HX4F0-060D110US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.75	8.52	8.81	9.57	11.01	7.32	8.08	8.38	9.14	10.58
	3H	9.41	10.09	10.47	11.16	12.61	8.93	9.62	10.00	10.68	12.14
	4H	9.99	10.64	11.07	11.71	13.17	9.52	10.17	10.59	11.23	12.69
	6H	10.39	10.98	11.47	12.05	13.53	9.91	10.51	10.99	11.58	13.05
	8H	10.49	11.06	11.58	12.14	13.61	10.01	10.58	11.10	11.67	13.13
	12H	10.53	11.07	11.63	12.15	13.64	10.05	10.59	11.15	11.67	13.16
4H	2H	8.20	8.85	9.29	9.92	11.38	7.86	8.51	8.94	9.58	11.03
	3H	10.06	10.60	11.15	11.70	13.17	9.67	10.21	10.76	11.31	12.78
	4H	10.77	11.27	11.87	12.35	13.85	10.37	10.86	11.46	11.95	13.44
	6H	11.28	11.71	12.38	12.82	14.30	10.87	11.30	11.98	12.41	13.89
	8H	11.43	11.83	12.53	12.93	14.43	11.02	11.42	12.12	12.52	14.02
	12H	11.50	11.86	12.62	12.97	14.48	11.08	11.44	12.20	12.55	14.06
8H	4H	10.96	11.36	12.06	12.46	13.96	10.60	11.00	11.70	12.10	13.60
	6H	11.59	11.92	12.71	13.06	14.56	11.23	11.56	12.35	12.70	14.20
	8H	11.81	12.10	12.94	13.22	14.74	11.44	11.73	12.57	12.85	14.37
	12H	11.94	12.19	13.07	13.31	14.87	11.55	11.81	12.69	12.93	14.48
12H	4H	10.94	11.30	12.06	12.42	13.92	10.59	10.95	11.71	12.07	13.57
	6H	11.62	11.91	12.75	13.03	14.55	11.27	11.56	12.40	12.68	14.20
	8H	11.86	12.11	12.99	13.23	14.79	11.50	11.75	12.63	12.87	14.43