

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928334

Luminaire Tested: DFN2DIP-HX4F0-080D090US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928334
REPORT IS A COMBINATION OF REPORTS P900918 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D090US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12442.3 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 144.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928334

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928334

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22

TEST NUMBER: P928334

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	245.4	2.0
10°-20°	673.7	5.4
20°-30°	945.9	7.6
30°-40°	1031.1	8.3
40°-50°	947.7	7.6
50°-60°	744.3	6.0
60°-70°	484.4	3.9
70°-80°	249.4	2.0
80°-90°	67.9	0.5
90°-100°	79.3	0.6
100°-110°	295.7	2.4
110°-120°	784.2	6.3
120°-130°	1300.7	10.5
130°-140°	1381.7	11.1
140°-150°	1284.1	10.3
150°-160°	1032.4	8.3
160°-170°	665.2	5.3
170°-180°	229.0	1.8
0°-30°	1865.1	15.0
0°-40°	2896.2	23.3
0°-60°	4588.1	36.9
0°-90°	5389.8	43.3
90°-120°	1159.3	9.3
90°-150°	5125.8	41.2
90°-180°	7052.0	56.7
0°-180°	12442.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2619	2619	2619	2619	2619	
5°	2619	2607	2576	2597	2590	248
15°	2491	2464	2384	2339	2315	7

TEST NUMBER: P928334

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2618.7	2618.7	2618.7	2618.7	2618.7
2.5°	2630.5	2618.7	2592.5	2616.4	2611.6
5°	2618.7	2606.9	2575.9	2597.3	2590.2
7.5°	2597.3	2583.2	2550.0	2559.3	2547.5
10°	2568.9	2552.3	2505.0	2497.7	2483.6
12.5°	2533.4	2512.1	2447.9	2433.8	2407.7
15°	2490.7	2464.5	2384.1	2339.1	2315.4
17.5°	2440.9	2402.9	2303.4	2251.3	2213.3
20°	2384.1	2336.6	2218.2	2159.1	2106.7
22.5°	2322.5	2267.9	2130.4	2049.9	2014.5
25°	2260.8	2185.0	2028.5	1931.5	1895.8
27.5°	2187.4	2106.7	1933.7	1822.4	1767.8
30°	2109.3	2019.0	1829.4	1708.7	1644.6
32.5°	2033.3	1924.2	1730.1	1587.8	1528.5
35°	1948.1	1827.1	1618.7	1469.4	1417.0
37.5°	1865.1	1734.6	1514.4	1350.7	1291.6
40°	1777.4	1635.3	1405.2	1237.0	1175.4
42.5°	1687.4	15			

TEST NUMBER: P928334

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	882.6	913.8	884.3	133.9	139.3
115°	1000.9	1030.4	1074.0	268.1	142.8
117.5°	1103.6	1138.3	1168.0	919.0	463.0
120°	1218.5	1244.5	1276.0	1296.8	1061.8
122.5°	1315.9	1343.8	1378.7	1389.0	1390.9
125°	1415.1	1437.8	1470.9	1483.1	1488.2
127.5°	1505.6	1530.0	1556.3	1573.6	1575.3
130°	1591.0	1618.9	1637.9	1657.1	1655.5
132.5°	1678.0	1700.7	1719.7	1735.5	1733.8
135°	1751.2	1779.1	1794.6	1812.2	1808.7
137.5°	1827.7	1848.5	1866.1	1883.5	1878.3
140°	1902.5	1916.6	1935.6	1951.3	1942.6
142.5°	1965.3	1977.5	2000.0	2013.9	2005.3
145°	2031.5	2029.6	2059.2	2071.4	2062.7
147.5°	2088.7	2083.6	2113.1	2121.8	2115.0
150°	2144.6	2132.4	2160.3	2170.6	2161.9
152.5°	2191.5	2177.6	2203.7	2214.2	2202.0
155°	2236.8	2221.2			

TEST NUMBER: P928334

CATALOG NUMBER: DFN2DIP-HX4F0-080D090US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.81	9.58	9.82	10.61	11.97	4.78	5.56	5.80	6.58	7.95
	3H	10.48	11.18	11.51	12.21	13.59	5.97	6.66	6.99	7.69	9.08
	4H	11.09	11.75	12.13	12.78	14.17	6.41	7.07	7.46	8.11	9.50
	6H	11.51	12.11	12.56	13.15	14.56	6.73	7.34	7.79	8.38	9.79
	8H	11.63	12.21	12.69	13.26	14.66	6.82	7.40	7.88	8.46	9.86
	12H	11.69	12.24	12.75	13.29	14.71	6.87	7.41	7.93	8.46	9.89
4H	2H	8.82	9.48	9.87							