

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926985

Luminaire Tested: DFN2DIP-HX4F0-070D050US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P926985
REPORT IS A COMBINATION OF REPORTS P899324 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D050US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9778.4 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926985

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US830-RLFL

Luminous Intensity Polar Plot



TEST NUMBER: P926985

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63
1	100	96	92	89	93	89	86	83	78	75	73	67	65	63	56	55	54
2	92	84	78	73	85	79	74	69	69	65	61	59	56	54	50	48	47
3	84	75	68	62	78	70	64	59	61	56	52	53	49	46	45	42	40
4	77	66	59	53	72	62	56	50	55	49	45	47	43	40	41	38	35
5	71	60	52	46	66	56	49	44	49	44	39	43	39	35	37	34	31
6	66	54	46	40	61	51	43	38	45	39	35	39	34	31	34	30	28
7	61	49	41	35	57	46	39	34	41	35	31	36	31	28	31	27	25
8	57	44	37	32	53	42	35	30	37	32	28	33	28	25	29	25	22
9	53	41	33	28	49	38	32	27	34	29	25	30	26	23	26	23	20
10	49	37	30	26	46	35	29	25	32	26	23	28	24	21	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2027	2027	2027
5°	2031	1996	2008
10°	2011	1957	1943
15°	1983	1892	1842
20°	1947	1803	1718
25°	1910	1703	1599
30°	1859	1601	1447
35°	1810	1491	1313
40°	1760	1377	1160
45°	1702	1251	1022
50°	1642	1123	887
55°	1579	987	757
60°	1507	844	623
65°	1423	700	561
70°	1322	564	508
75°	1195	498	462
80°	1011	419	401
85°	707	280	302

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1702 cd/sqm

TEST NUMBER: P926985

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.6	2.6
10°-20°	701.5	7.2
20°-30°	984.9	10.1
30°-40°	1073.7	11.0
40°-50°	986.8	10.1
50°-60°	775.0	7.9
60°-70°	504.4	5.2
70°-80°	259.7	2.7
80°-90°	70.5	0.7
90°-100°	92.2	0.9
100°-110°	293.0	3.0
110°-120°	501.5	5.1
120°-130°	659.5	6.7
130°-140°	740.3	7.6
140°-150°	725.9	7.4
150°-160°	608.9	6.2
160°-170°	403.8	4.1
170°-180°	141.2	1.4
0°-30°	1942.0	19.9
0°-40°	3015.7	30.8
0°-60°	4777.5	48.9
0°-90°	5612.0	57.4
90°-120°	886.7	9.1
90°-150°	3012.4	30.8
90°-180°	4166.0	42.6
0°-180°	9778.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2727	2727	2727	2727	2727	
5°	2727	2714	2682	2704	2697	259
15°	2594	2566	2482	2436	2411	731
25°	2354	2275	2112	2011	1974	1083
35°	2028	1902	1686	1530	1476	1270
45°	1658	1493	1234	1058	999	1281
55°	1261	1068	802	654	607	1127
65°	851	651	429	346	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	122
90°	1	16	44	41	43	10
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1437	1431	403
175°	1488	1484	1481	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P926985

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.7	2726.7	2726.7	2726.7	2726.7
2.5°	2739.0	2726.7	2699.5	2724.4	2719.4
5°	2726.7	2714.4	2682.3	2704.5	2697.2
7.5°	2704.5	2689.8	2655.3	2664.9	2652.7
10°	2674.9	2657.7	2608.4	2600.8	2586.1
12.5°	2638.0	2615.7	2549.0	2534.3	2507.0
15°	2593.5	2566.2	2482.5	2435.6	2411.0
17.5°	2541.6	2502.1	2398.5	2344.2	2304.7
20°	2482.5	2433.0	2309.7	2248.1	2193.7
22.5°	2418.4	2361.5	2218.3	2134.5	2097.6
25°	2354.2	2275.1	2112.2	2011.2	1974.1
27.5°	2277.7	2193.7	2013.6	1897.6	1840.8
30°	2196.3	2102.3	1904.9	1779.3	1712.5
32.5°	2117.2	2003.7	1801.5	1653.3	1591.5
35°	2028.4	1902.5	1685.6	1530.1	1475.6
37.5°	1942.1	1806.2	1576.9	1406.4	1344.9
40°	1850.7	1702.8	1463.2	1288.1	1223.9
42.5°	1757.0	1599.1	1349.8	1167.1	1105.6
45°	1658.3	1492.8	1233.9	1058.5	999.3
47.5°	1564.6	1389.4	1122.9	947.5	893.3
50°	1460.9	1285.8	1014.2	843.8	792.3
52.5°	1359.6	1174.4	910.5	747.7	700.8
55°	1260.9	1068.4	801.9	654.0	607.2
57.5°	1159.8	962.4	705.8	567.6	528.1
60°	1056.2	858.7	604.5	478.9	439.3
62.5°	955.0	757.7	518.1	399.8	380.1
65°	851.4	651.4	429.4	345.6	338.0
67.5°	752.7	552.7	345.6	303.4	296.1
70°	649.0	456.5	286.1	261.5	251.6
72.5°	550.3	367.6	239.3	219.7	214.7
75°	454.0	281.1	197.4	180.1	177.8
77.5°	357.9	199.7	155.5	145.5	140.6
80°	268.9	143.2	118.4	108.7	108.7
82.5°	187.5	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	390.9	390.9	390.9	387.3



TEST NUMBER: P926985

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.2	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.5
120°	621.4	631.3	621.4	621.4	617.3
122.5°	675.3	687.9	681.6	678.0	675.3
125°	731.9	743.2	739.6	735.5	734.2
127.5°	787.2	801.1	796.2	790.8	787.2
130°	838.9	855.0	852.8	850.1	845.1
132.5°	896.9	909.4	910.4	904.0	900.5
135°	946.7	960.6	963.3	962.0	958.4
137.5°	1002.4	1013.7	1015.9	1015.0	1009.6
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.3	1165.5	1166.9	1161.9
147.5°	1192.1	1203.3	1208.7	1210.9	1205.9
150°	1236.1	1243.7	1248.6	1252.7	1248.6
152.5°	1275.2	1282.8	1289.1	1294.1	1289.1
155°	1314.2	1317.8	1321.9	1328.2	1324.1
157.5°	1348.0	1350.6	1352.9	1361.9	1355.6
160°	1378.0	1380.8	1382.1	1389.7	1384.3
162.5°	1405.9	1405.9	1407.2	1415.8	1409.5
165°	1429.8	1428.4	1428.4	1437.4	1431.1
167.5°	1451.3	1447.2	1447.2	1456.3	1449.9
170°	1467.5	1463.9	1462.6	1471.5	1463.9
172.5°	1478.7	1475.1	1473.8	1482.7	1475.1
175°	1487.7	1484.1	1481.4	1490.4	1482.7
177.5°	1492.6	1489.1	1486.3	1494.0	1486.3
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P926985

CATALOG NUMBER: DFN2DIP-HX4F0-070D050US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.27	11.16	11.16	12.07	13.24	6.24	7.13	7.14	8.05	9.21
	3H	11.95	12.75	12.86	13.67	14.86	7.43	8.23	8.34	9.16	10.35
	4H	12.56	13.32	13.49	14.24	15.44	7.89	8.64	8.81	9.57	10.77
	6H	12.99	13.68	13.92	14.62	15.83	8.22	8.91	9.15	9.84	11.06
	8H	13.12	13.78	14.06	14.73	15.94	8.31	8.97	9.25	9.92	11.13
	12H	13.18	13.81	14.13	14.75	15.99	8.35	8.98	9.30	9.93	11.16
4H	2H	10.29	11.05	11.22	11.98	13.17	6.84	7.60	7.77	8.53	9.73
	3H	12.13	12.76	13.07	13.71	14.93	8.20	8.83	9.14	9.79	11.00
	4H	12.82	13.40	13.77	14.35	15.59	8.75	9.32	9.70	10.28	11.52
	6H	13.34	13.84	14.31	14.81	16.05	9.18	9.67	10.14	10.65	11.89
	8H	13.52	13.98	14.49	14.95	16.20	9.31	9.77	10.27	10.74	11.99
	12H	13.62	14.03	14.60	15.02	16.28	9.38	9.79	10.36	10.78	12.04
8H	4H	12.80	13.26	13.76	14.23	15.48	9.04	9.50	10.00	10.47	11.72
	6H	13.37	13.75	14.36	14.76	16.01	9.56	9.94	10.55	10.95	12.20
	8H	13.58	13.92	14.58	14.92	16.19	9.75	10.09	10.75	11.09	12.36
	12H	13.73	14.02	14.73	15.02	16.33	9.88	10.17	10.88	11.17	12.48
12H	4H	12.75	13.17	13.74	14.15	15.41	9.05	9.46	10.03	10.45	11.70
	6H	13.34	13.68	14.34	14.68	15.95	9.61	9.95	10.61	10.95	12.22
	8H	13.57	13.86	14.57	14.86	16.17	9.83	10.12	10.83	11.11	12.43

END OF REPORT