

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927001

Luminaire Tested: DFN2DIP-HX4F0-070D090US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927001
REPORT IS A COMBINATION OF REPORTS P899396 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-070D090US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13114.8 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 134.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927001

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927001

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	44	43	43
2	88	81	75	70	80	74	69	65	62	58	55	50	48	46	40	38	36
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	52	46	41	44	39	35	36	32	30	29	26	24
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2027	2027	2027
5°	2031	1996	2008
10°	2011	1957	1943
15°	1983	1892	1842
20°	1947	1803	1718
25°	1910	1703	1599
30°	1859	1601	1447
35°	1810	1491	1313
40°	1760	1377	1160
45°	1702	1251	1022
50°	1642	1123	887
55°	1579	987	757
60°	1507	844	623
65°	1423	700	561
70°	1322	564	508
75°	1195	498	462
80°	1011	419	401
85°	707	280	302

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2022 cd/sqm

TEST NUMBER: P927001

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	255.6	1.9
10°-20°	701.5	5.3
20°-30°	984.9	7.5
30°-40°	1073.7	8.2
40°-50°	986.8	7.5
50°-60°	775.0	5.9
60°-70°	504.4	3.8
70°-80°	259.7	2.0
80°-90°	73.9	0.6
90°-100°	166.0	1.3
100°-110°	527.5	4.0
110°-120°	902.7	6.9
120°-130°	1187.1	9.1
130°-140°	1332.5	10.2
140°-150°	1306.6	10.0
150°-160°	1096.1	8.4
160°-170°	726.9	5.5
170°-180°	254.1	1.9
0°-30°	1942.0	14.8
0°-40°	3015.7	23.0
0°-60°	4777.5	36.4
0°-90°	5615.4	42.8
90°-120°	1596.1	12.2
90°-150°	5422.3	41.3
90°-180°	7499.0	57.2
0°-180°	13114.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2727	2727	2727	2727	2727	
5°	2727	2714	2682	2704	2697	259
15°	2594	2566	2482	2436	2411	731
25°	2354	2275	2112	2011	1974	1083
35°	2028	1902	1686	1530	1476	1270
45°	1658	1493	1234	1058	999	1281
55°	1261	1068	802	654	607	1127
65°	851	651	429	346	338	844
75°	454	281	197	180	178	480
85°	106	54	47	47	47	122
90°	2	29	79	74	77	13
95°	118	141	145	145	141	131
105°	487	493	498	502	502	514
115°	906	919	915	912	906	896
125°	1318	1338	1331	1324	1322	1177
135°	1704	1729	1734	1732	1725	1317
145°	2069	2085	2098	2100	2092	1293
155°	2366	2372	2379	2391	2384	1089
165°	2574	2571	2571	2587	2576	726
175°	2678	2671	2666	2683	2669	254
180°	2683	2683	2683	2683	2683	

TEST NUMBER: P927001

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2726.7	2726.7	2726.7	2726.7	2726.7
2.5°	2739.0	2726.7	2699.5	2724.4	2719.4
5°	2726.7	2714.4	2682.3	2704.5	2697.2
7.5°	2704.5	2689.8	2655.3	2664.9	2652.7
10°	2674.9	2657.7	2608.4	2600.8	2586.1
12.5°	2638.0	2615.7	2549.0	2534.3	2507.0
15°	2593.5	2566.2	2482.5	2435.6	2411.0
17.5°	2541.6	2502.1	2398.5	2344.2	2304.7
20°	2482.5	2433.0	2309.7	2248.1	2193.7
22.5°	2418.4	2361.5	2218.3	2134.5	2097.6
25°	2354.2	2275.1	2112.2	2011.2	1974.1
27.5°	2277.7	2193.7	2013.6	1897.6	1840.8
30°	2196.3	2102.3	1904.9	1779.3	1712.5
32.5°	2117.2	2003.7	1801.5	1653.3	1591.5
35°	2028.4	1902.5	1685.6	1530.1	1475.6
37.5°	1942.1	1806.2	1576.9	1406.4	1344.9
40°	1850.7	1702.8	1463.2	1288.1	1223.9
42.5°	1757.0	1599.1	1349.8	1167.1	1105.6
45°	1658.3	1492.8	1233.9	1058.5	999.3
47.5°	1564.6	1389.4	1122.9	947.5	893.3
50°	1460.9	1285.8	1014.2	843.8	792.3
52.5°	1359.6	1174.4	910.5	747.7	700.8
55°	1260.9	1068.4	801.9	654.0	607.2
57.5°	1159.8	962.4	705.8	567.6	528.1
60°	1056.2	858.7	604.5	478.9	439.3
62.5°	955.0	757.7	518.1	399.8	380.1
65°	851.4	651.4	429.4	345.6	338.0
67.5°	752.7	552.7	345.6	303.4	296.1
70°	649.0	456.5	286.1	261.5	251.6
72.5°	550.3	367.6	239.3	219.7	214.7
75°	454.0	281.1	197.4	180.1	177.8
77.5°	357.9	199.7	155.5	145.5	140.6
80°	268.9	143.2	118.4	108.7	108.7
82.5°	187.5	96.3	81.4	76.4	76.4
85°	106.0	54.2	46.8	46.8	46.8
87.5°	39.5	19.6	19.6	17.2	17.2
90°	2.5	29.1	79.3	74.4	76.8
92.5°	50.1	68.0	70.4	72.8	72.8
95°	118.1	140.7	144.8	144.8	140.7
97.5°	196.5	217.5	226.5	226.5	226.5
100°	287.1	305.7	312.2	312.2	309.8
102.5°	382.6	396.3	405.2	407.6	405.2
105°	486.9	493.3	498.2	502.3	502.3
107.5°	590.4	600.1	600.1	601.7	590.4
110°	690.7	703.7	703.7	703.7	697.2

TEST NUMBER: P927001

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	799.1	812.8	810.4	804.0	799.1
115°	905.8	918.7	914.7	912.3	905.8
117.5°	1011.8	1029.6	1018.3	1011.8	1005.3
120°	1118.6	1136.3	1118.6	1118.6	1111.2
122.5°	1215.5	1238.3	1226.9	1220.4	1215.5
125°	1317.5	1337.7	1331.3	1323.9	1321.6
127.5°	1417.0	1442.0	1433.2	1423.5	1417.0
130°	1510.0	1539.1	1535.0	1530.1	1521.3
132.5°	1614.3	1636.9	1638.5	1627.2	1620.8
135°	1704.0	1729.1	1734.0	1731.6	1725.2
137.5°	1804.3	1824.6	1828.6	1827.0	1817.3
140°	1892.5	1912.7	1924.0	1924.0	1915.2
142.5°	1983.1	2003.3	2009.8	2012.2	2003.3
145°	2068.9	2085.0	2097.9	2100.4	2091.5
147.5°	2145.7	2165.9	2175.6	2179.6	2170.8
150°	2225.0	2238.7	2247.6	2254.8	2247.6
152.5°	2295.3	2309.0	2320.3	2329.3	2320.3
155°	2365.7	2372.1	2379.4	2390.7	2383.5
157.5°	2426.3	2431.2	2435.2	2451.3	2440.0
160°	2480.5	2485.4	2487.8	2501.5	2491.8
162.5°	2530.6	2530.6	2533.1	2548.4	2537.1
165°	2573.5	2571.0	2571.0	2587.3	2575.9
167.5°	2612.3	2605.1	2605.1	2621.2	2609.9
170°	2641.5	2634.9	2632.6	2648.7	2634.9
172.5°	2661.6	2655.2	2652.8	2669.0	2655.2
175°	2677.8	2671.3	2666.5	2682.7	2669.0
177.5°	2686.7	2680.3	2675.4	2689.1	2675.4
180°	2682.7	2682.7	2682.7	2682.7	2682.7



TEST NUMBER: P927001

CATALOG NUMBER: DFN2DIP-HX4F0-070D090US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.89	9.67	9.91	10.69	12.07	4.87	5.64	5.89	6.67	8.04
	3H	10.57	11.26	11.60	12.29	13.69	6.05	6.74	7.08	7.78	9.17
	4H	11.17	11.83	12.22	12.87	14.27	6.50	7.16	7.55	8.19	9.59
	6H	11.59	12.20	12.65	13.24	14.65	6.82	7.42	7.88	8.47	9.88
	8H	11.72	12.29	12.78	13.35	14.76	6.91	7.48	7.97	8.54	9.95
	12H	11.78	12.32	12.84	13.38	14.81	6.95	7.50	8.02	8.55	9.98
4H	2H	8.90	9.56	9.96	10.60	12.00	5.45	6.11	6.51	7.15	8.55
	3H	10.73	11.27	11.79	12.34	13.75	6.80	7.35	7.86	8.41	9.83
	4H	11.42	11.92	12.48	12.98	14.41	7.35	7.85	8.41	8.91	10.34
	6H	11.93	12.36	13.01	13.44	14.87	7.77	8.20	8.84	9.28	10.71
	8H	12.11	12.51	13.18	13.58	15.03	7.90	8.30	8.97	9.37	10.81
	12H	12.20	12.56	13.29	13.65	15.10	7.96	8.32	9.05	9.41	10.86
8H	4H	11.38	11.78	12.46	12.86	14.30	7.63	8.03	8.70	9.10	10.54
	6H	11.95	12.28	13.05	13.39	14.84	8.14	8.47	9.24	9.59	11.03
	8H	12.17	12.46	13.27	13.55	15.01	8.34	8.63	9.44	9.72	11.18
	12H	12.30	12.56	13.41	13.65	15.15	8.45	8.71	9.56	9.80	11.30
12H	4H	11.33	11.69	12.43	12.78	14.23	7.63	7.99	8.72	9.08	10.53
	6H	11.92	12.21	13.03	13.31	14.77	8.19	8.48	9.30	9.58	11.04
	8H	12.14	12.40	13.25	13.49	14.99	8.40	8.66	9.51	9.75	11.25

END OF REPORT