

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927028

Luminaire Tested: DFN2DIP-HX4F0-080D070US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927028
REPORT IS A COMBINATION OF REPORTS P900881 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-080D070US830-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13996.1 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 128.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9613
Total Harmonic Distortion (THDi): 0.083
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927028

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927028

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2181	2181	2181
5°	2185	2151	2166
10°	2168	2123	2137
15°	2136	2088	2091
20°	2093	2039	2044
25°	2050	1982	1990
30°	1997	1928	1921
35°	1946	1864	1848
40°	1884	1800	1779
45°	1822	1736	1708
50°	1753	1668	1626
55°	1682	1591	1550
60°	1602	1498	1464
65°	1514	1402	1362
70°	1402	1285	1252
75°	1247	1145	1151
80°	1062	967	958
85°	771	659	637

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1822 cd/sqm

TEST NUMBER: P927028

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.1	2.0
10°-20°	776.9	5.6
20°-30°	1141.8	8.2
30°-40°	1326.1	9.5
40°-50°	1324.5	9.5
50°-60°	1154.9	8.3
60°-70°	853.7	6.1
70°-80°	483.0	3.5
80°-90°	131.4	0.9
90°-100°	73.4	0.5
100°-110°	273.7	2.0
110°-120°	725.9	5.2
120°-130°	1203.9	8.6
130°-140°	1278.9	9.1
140°-150°	1188.6	8.5
150°-160°	955.6	6.8
160°-170°	615.7	4.4
170°-180°	211.9	1.5
0°-30°	2194.9	15.7
0°-40°	3521.0	25.2
0°-60°	6000.4	42.9
0°-90°	7468.5	53.4
90°-120°	1073.0	7.7
90°-150°	4744.3	33.9
90°-180°	6528.0	46.6
0°-180°	13996.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2934	2934	2934	2934	2934	
5°	2934	2923	2892	2914	2909	278
15°	2793	2776	2739	2751	2737	787
25°	2528	2505	2457	2463	2457	1163
35°	2181	2153	2107	2090	2076	1362
45°	1775	1755	1712	1682	1670	1370
55°	1343	1326	1292	1258	1244	1201
65°	906	889	860	835	821	895
75°	474	468	454	437	443	506
85°	116	113	110	102	99	129
90°	2	19	32	40	43	13
95°	105	52	63	71	69	124
105°	490	538	98	116	122	523
115°	926	954	994	248	132	912
125°	1310	1331	1361	1373	1378	1168
135°	1621	1647	1661	1677	1674	1252
145°	1880	1879	1906	1917	1909	1176
155°	2070	2056	2075	2085	2072	954
165°	2181	2172	2177	2188	2177	616
175°	2231	2220	2223	2235	2219	212
180°	2227	2227	2227	2227	2227	

TEST NUMBER: P927028

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2933.8	2933.8	2933.8	2933.8	2933.8
2.5°	2950.9	2936.8	2905.7	2933.8	2928.4
5°	2933.8	2922.8	2891.7	2914.1	2908.7
7.5°	2914.1	2897.3	2866.2	2889.0	2883.3
10°	2883.3	2863.5	2829.7	2852.1	2843.8
12.5°	2840.8	2824.0	2790.2	2804.2	2798.6
15°	2792.9	2776.1	2739.3	2750.7	2736.6
17.5°	2733.6	2716.9	2680.0	2694.1	2680.0
20°	2668.7	2651.9	2612.4	2620.8	2609.7
22.5°	2604.0	2578.6	2541.7	2541.7	2536.1
25°	2527.7	2505.3	2457.4	2462.8	2457.4
27.5°	2443.0	2423.3	2386.7	2378.3	2364.3
30°	2358.6	2335.8	2293.7	2285.3	2273.9
32.5°	2268.2	2251.4	2206.2	2189.1	2177.8
35°	2180.8	2152.7	2107.4	2090.4	2076.3
37.5°	2082.0	2056.5	2011.4	1991.6	1977.6
40°	1980.6	1957.8	1912.6	1887.5	1876.0
42.5°	1881.8	1859.0	1814.1	1785.7	1769.0
45°	1774.6	1754.8	1712.3	1681.5	1670.2
47.5°	1670.2	1650.4	1605.2	1574.1	1557.3
50°	1560.0	1546.0	1506.4	1466.9	1452.9
52.5°	1452.9	1433.1	1396.6	1365.5	1345.7
55°	1343.0	1325.9	1292.2	1258.3	1244.2
57.5°	1232.9	1218.8	1182.0	1148.2	1136.7
60°	1122.7	1111.7	1072.1	1041.0	1032.6
62.5°	1015.5	995.8	967.7	939.6	928.2
65°	905.7	888.7	860.5	835.1	821.0
67.5°	792.8	778.5	753.3	733.6	722.2
70°	688.4	677.0	651.6	631.9	620.7
72.5°	581.2	569.9	555.8	536.1	527.7
75°	473.8	468.4	454.1	437.3	443.0
77.5°	378.0	366.6	361.0	352.6	344.2
80°	282.3	279.3	273.6	265.2	259.5
82.5°	191.9	191.9	189.2	177.8	177.8
85°	115.6	112.8	110.2	101.5	98.8
87.5°	50.9	45.2	39.5	31.1	28.2
90°	1.5	19.3	32.1	40.3	43.4
92.5°	40.3	33.8	38.6	41.9	43.4
95°	104.6	51.5	62.8	71.0	69.3
97.5°	188.4	56.5	82.1	87.1	88.6
100°	285.3	64.5	91.8	104.6	107.9
102.5°	391.4	388.4	95.1	112.7	117.6
105°	489.8	538.2	98.3	115.9	122.4
107.5°	604.1	644.4	101.6	119.2	125.7
110°	713.8	747.5	282.0	120.9	127.2

TEST NUMBER: P927028

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	817.0	845.8	818.5	123.9	128.9
115°	926.4	953.7	994.1	248.2	132.2
117.5°	1021.5	1053.6	1081.1	850.6	428.6
120°	1127.8	1151.9	1181.0	1200.4	982.8
122.5°	1217.9	1243.7	1276.1	1285.7	1287.4
125°	1309.8	1330.8	1361.4	1372.8	1377.5
127.5°	1393.6	1416.1	1440.4	1456.5	1458.0
130°	1472.6	1498.4	1516.0	1533.8	1532.3
132.5°	1553.1	1574.2	1591.8	1606.3	1604.8
135°	1620.8	1646.6	1661.1	1677.3	1674.1
137.5°	1691.6	1711.0	1727.2	1743.3	1738.5
140°	1760.9	1773.9	1791.5	1806.0	1798.0
142.5°	1819.0	1830.3	1851.2	1864.0	1856.0
145°	1880.3	1878.6	1905.9	1917.2	1909.2
147.5°	1933.3	1928.5	1955.9	1963.9	1957.6
150°	1984.9	1973.7	1999.5	2009.0	2001.0
152.5°	2028.4	2015.5	2039.7	2049.4	2038.2
155°	2070.3	2055.9	2075.2	2084.8	2072.0
157.5°	2104.1	2091.3	2105.8	2117.1	2104.1
160°	2133.3	2123.5	2133.3	2142.8	2131.5
162.5°	2158.9	2149.3	2157.3	2168.6	2154.1
165°	2181.4	2171.9	2176.6	2187.9	2176.6
167.5°	2199.2	2189.4	2194.4	2205.7	2191.2
170°	2213.7	2204.0	2207.2	2218.6	2204.0
172.5°	2223.4	2213.7	2217.0	2228.3	2213.7
175°	2231.4	2220.1	2223.4	2234.6	2218.6
177.5°	2234.6	2223.4	2225.1	2236.4	2221.8
180°	2226.6	2226.6	2226.6	2226.6	2226.6

TEST NUMBER: P927028

CATALOG NUMBER: DFN2DIP-HX4F0-080D070US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.29	11.18	11.22	12.13	13.35	9.86	10.75	10.78	11.69	12.92
	3H	11.95	12.75	12.89	13.71	14.95	11.48	12.28	12.42	13.23	14.48
	4H	12.54	13.30	13.50	14.26	15.51	12.07	12.83	13.02	13.78	15.04
	6H	12.94	13.64	13.91	14.61	15.87	12.47	13.17	13.43	14.13	15.40
	8H	13.05	13.71	14.02	14.70	15.96	12.57	13.24	13.55	14.22	15.49
	12H	13.10	13.73	14.08	14.71	16.00	12.62	13.25	13.60	14.23	15.52
4H	2H	10.75	11.51	11.71	12.47	13.73	10.41	11.17	11.37	12.13	13.38
	3H	12.62	13.26	13.59	14.25	15.51	12.23	12.86	13.20	13.85	15.12
	4H	13.34	13.92	14.32	14.90	16.19	12.93	13.51	13.91	14.50	15.79
	6H	13.86	14.36	14.85	15.36	16.65	13.45	13.95	14.44	14.95	16.24
	8H	14.01	14.47	15.00	15.47	16.78	13.60	14.06	14.59	15.06	16.37
	12H	14.08	14.50	15.10	15.52	16.83	13.66	14.08	14.67	15.10	16.41
8H	4H	13.54	14.01	14.53	15.01	16.31	13.18	13.65	14.17	14.64	15.95
	6H	14.17	14.56	15.19	15.60	16.90	13.81	14.20	14.83	15.24	16.54
	8H	14.40	14.74	15.42	15.76	17.09	14.03	14.37	15.05	15.39	16.72
	12H	14.53	14.83	15.56	15.85	17.22	14.15	14.44	15.17	15.47	16.83
12H	4H	13.53	13.95	14.54	14.96	16.28	13.18	13.60	14.19	14.61	15.92
	6H	14.20	14.54	15.23	15.57	16.90	13.85	14.19	14.88	15.22	16.54
	8H	14.45	14.75	15.48	15.77	17.14	14.09	14.39	15.12	15.41	16.78

END OF REPORT