

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928390

Luminaire Tested: DFN2DIP-HX4F0-100D050US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928390
REPORT IS A COMBINATION OF REPORTS P900850 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D050US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10652.4 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 137
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928390

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928390

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2434	2434	2434
5°	2438	2396	2411
10°	2414	2349	2332
15°	2381	2271	2211
20°	2337	2165	2063
25°	2292	2045	1919
30°	2232	1922	1737
35°	2173	1790	1577
40°	2113	1653	1393
45°	2043	1502	1227
50°	1971	1348	1064
55°	1896	1185	908
60°	1809	1014	748
65°	1709	840	673
70°	1587	677	609
75°	1435	598	555
80°	1213	502	481
85°	849	336	362

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2043 cd/sqm

TEST NUMBER: P928390

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	306.8	2.9
10°-20°	842.2	7.9
20°-30°	1182.4	11.1
30°-40°	1288.9	12.1
40°-50°	1184.6	11.1
50°-60°	930.3	8.7
60°-70°	605.5	5.7
70°-80°	311.7	2.9
80°-90°	81.9	0.8
90°-100°	44.1	0.4
100°-110°	164.3	1.5
110°-120°	435.7	4.1
120°-130°	722.6	6.8
130°-140°	767.6	7.2
140°-150°	713.4	6.7
150°-160°	573.6	5.4
160°-170°	369.6	3.5
170°-180°	127.2	1.2
0°-30°	2331.3	21.9
0°-40°	3620.2	34.0
0°-60°	5735.1	53.8
0°-90°	6734.3	63.2
90°-120°	644.1	6.0
90°-150°	2847.7	26.7
90°-180°	3918.0	36.8
0°-180°	10652.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3273	3273	3273	3273	3273	
5°	3273	3258	3220	3247	3238	310
15°	3113	3081	2980	2924	2894	877
25°	2826	2731	2536	2414	2370	1300
35°	2435	2284	2023	1837	1771	1524
45°	1991	1792	1481	1271	1200	1537
55°	1514	1283	963	785	729	1353
65°	1022	782	515	415	406	1013
75°	545	338	237	216	213	576
85°	127	65	56	56	56	146
90°	1	12	19	24	26	10
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	572	597	149	79	547
125°	786	799	817	824	827	701
135°	973	988	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1251	1244	573
165°	1309	1304	1306	1313	1306	370
175°	1339	1332	1334	1341	1332	127
180°	1336	1336	1336	1336	1336	

TEST NUMBER: P928390

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3273.3	3273.3	3273.3	3273.3	3273.3
2.5°	3288.1	3273.3	3240.6	3270.5	3264.5
5°	3273.3	3258.5	3219.9	3246.6	3237.8
7.5°	3246.6	3229.0	3187.5	3199.1	3184.4
10°	3211.1	3190.3	3131.3	3122.1	3104.6
12.5°	3166.8	3140.0	3059.9	3042.3	3009.6
15°	3113.4	3080.6	2980.1	2923.8	2894.3
17.5°	3051.1	3003.7	2879.2	2814.1	2766.7
20°	2980.1	2920.7	2772.6	2698.8	2633.4
22.5°	2903.1	2834.9	2662.9	2562.4	2518.1
25°	2826.1	2731.2	2535.7	2414.3	2369.7
27.5°	2734.3	2633.4	2417.2	2278.0	2209.8
30°	2636.6	2523.7	2286.7	2135.9	2055.8
32.5°	2541.7	2405.2	2162.6	1984.8	1910.5
35°	2435.1	2284.0	2023.4	1836.7	1771.3
37.5°	2331.4	2168.3	1893.0	1688.4	1614.5
40°	2221.7	2044.2	1756.6	1546.3	1469.3
42.5°	2109.2	1919.6	1620.5	1401.1	1327.2
45°	1990.7	1792.1	1481.3	1270.7	1199.6
47.5°	1878.2	1668.0	1348.0	1137.4	1072.4
50°	1753.7	1543.4	1217.5	1013.0	951.0
52.5°	1632.1	1409.9	1093.1	897.6	841.3
55°	1513.6	1282.6	962.7	785.1	728.8
57.5°	1392.3	1155.3	847.4	681.4	633.9
60°	1267.8	1030.9	725.7	574.8	527.4
62.5°	1146.5	909.5	622.0	480.0	456.4
65°	1022.1	781.9	515.4	414.8	405.7
67.5°	903.6	663.5	414.8	364.2	355.4
70°	779.1	548.1	343.5	313.9	302.1
72.5°	660.6	441.2	287.3	263.7	257.7
75°	545.0	337.6	237.0	216.2	213.4
77.5°	429.7	239.8	186.7	174.7	168.8
80°	322.7	171.9	142.1	130.4	130.4
82.5°	225.0	115.6	97.7	91.8	91.8
85°	127.3	65.0	56.2	56.2	56.2
87.5°	47.4	23.6	23.6	20.8	20.8
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.1
100°	171.2	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.6	70.6
105°	294.0	323.1	59.0	69.6	73.5
107.5°	362.7	386.7	61.0	71.5	75.5
110°	428.5	448.7	169.3	72.5	76.3

TEST NUMBER: P928390

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.3	507.7	491.3	74.4	77.4
115°	556.1	572.5	596.7	149.0	79.4
117.5°	613.1	632.4	649.0	510.5	257.2
120°	676.9	691.4	708.8	720.5	589.9
122.5°	731.0	746.5	765.9	771.7	772.8
125°	786.1	798.8	817.2	823.9	826.8
127.5°	836.4	850.0	864.6	874.2	875.2
130°	883.9	899.4	909.9	920.6	919.7
132.5°	932.3	944.9	955.4	964.2	963.2
135°	972.9	988.4	997.0	1006.8	1004.8
137.5°	1015.3	1027.0	1036.7	1046.4	1043.5
140°	1056.9	1064.8	1075.3	1084.0	1079.3
142.5°	1091.9	1098.7	1111.2	1118.9	1114.0
145°	1128.6	1127.6	1144.0	1150.8	1145.9
147.5°	1160.4	1157.5	1174.0	1178.8	1175.0
150°	1191.4	1184.7	1200.1	1205.9	1201.1
152.5°	1217.5	1209.8	1224.3	1230.1	1223.3
155°	1242.6	1234.0	1245.6	1251.4	1243.7
157.5°	1262.9	1255.2	1264.0	1270.8	1262.9
160°	1280.4	1274.6	1280.4	1286.1	1279.4
162.5°	1295.8	1290.1	1294.8	1301.7	1292.9
165°	1309.3	1303.6	1306.5	1313.2	1306.5
167.5°	1320.0	1314.2	1317.2	1323.9	1315.2
170°	1328.7	1322.9	1324.9	1331.6	1322.9
172.5°	1334.5	1328.7	1330.7	1337.5	1328.7
175°	1339.4	1332.5	1334.5	1341.3	1331.6
177.5°	1341.3	1334.5	1335.5	1342.3	1333.6
180°	1336.4	1336.4	1336.4	1336.4	1336.4

TEST NUMBER: P928390

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.39	12.34	12.23	13.20	14.27	7.36	8.32	8.21	9.17	10.25
	3H	13.08	13.93	13.93	14.80	15.90	8.56	9.41	9.42	10.28	11.38
	4H	13.69	14.50	14.56	15.37	16.48	9.02	9.82	9.89	10.70	11.81
	6H	14.12	14.86	15.00	15.74	16.87	9.35	10.09	10.23	10.97	12.09
	8H	14.25	14.95	15.14	15.85	16.98	9.44	10.15	10.34	11.05	12.17
	12H	14.32	14.99	15.21	15.88	17.03	9.49	10.16	10.39	11.06	12.20
4H	2H	11.42	12.23	12.30	13.10	14.21	7.97	8.78	8.85	9.65	10.76
	3H	13.27	13.93	14.15	14.84	15.96	9.34	10.00	10.22	10.91	12.04
	4H	13.96	14.57	14.86	15.47	16.62	9.89	10.50	10.79	11.40	12.55
	6H	14.49	15.01	15.40	15.94	17.09	10.32	10.84	11.23	11.77	12.92
	8H	14.66	15.15	15.58	16.07	17.24	10.45	10.94	11.37	11.86	13.03
	12H	14.76	15.20	15.70	16.14	17.32	10.52	10.96	11.46	11.90	13.07
8H	4H	13.94	14.43	14.86	15.35	16.52	10.18	10.67	11.10	11.59	12.76
	6H	14.51	14.91	15.45	15.88	17.04	10.71	11.11	11.65	12.07	13.24
	8H	14.73	15.09	15.68	16.04	17.22	10.90	11.26	11.85	12.21	13.39
	12H	14.87	15.19	15.83	16.14	17.37	11.02	11.34	11.98	12.29	13.52
12H	4H	13.90	14.34	14.83	15.28	16.45	10.19	10.63	11.13	11.57	12.74
	6H	14.49	14.84	15.44	15.80	16.98	10.76	11.11	11.71	12.07	13.25
	8H	14.71	15.03	15.67	15.98	17.21	10.97	11.29	11.93	12.23	13.47