

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927083

Luminaire Tested: DFN2DIP-HX4F0-090D120US830-FLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927083
REPORT IS A COMBINATION OF REPORTS P899453 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D120US830-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18407.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 184.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927083

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927083

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-FLLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52			46
1	97	93	89	85	89	85	82	79	71	69	66	58	56	55	46	45	44			38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	41	39	37			32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	34	32			27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27			23
5	67	56	48	42	62	52	45	39	44	38	34	36	32	29	29	26	24			20
6	62	50	42	36	57	46	39	34	39	34	30	33	28	25	26	23	21			18
7	57	45	37	32	53	42	35	30	36	30	26	30	25	22	24	21	19			16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17			14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15			13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2454	2454	2454
5°	2458	2420	2436
10°	2439	2388	2404
15°	2403	2349	2352
20°	2355	2294	2299
25°	2307	2229	2239
30°	2246	2169	2161
35°	2190	2097	2079
40°	2119	2025	2001
45°	2049	1953	1922
50°	1973	1877	1829
55°	1893	1789	1744
60°	1802	1685	1647
65°	1703	1577	1532
70°	1578	1446	1409
75°	1403	1288	1295
80°	1194	1088	1078
85°	867	741	717

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2696 cd/sqm

TEST NUMBER: P927083

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	310.7	1.7
10°-20°	874.1	4.7
20°-30°	1284.5	7.0
30°-40°	1491.9	8.1
40°-50°	1490.0	8.1
50°-60°	1299.3	7.1
60°-70°	960.4	5.2
70°-80°	543.4	3.0
80°-90°	153.6	0.8
90°-100°	221.3	1.2
100°-110°	703.3	3.8
110°-120°	1203.5	6.5
120°-130°	1582.8	8.6
130°-140°	1776.6	9.7
140°-150°	1742.2	9.5
150°-160°	1461.5	7.9
160°-170°	969.2	5.3
170°-180°	338.8	1.8
0°-30°	2469.2	13.4
0°-40°	3961.1	21.5
0°-60°	6750.4	36.7
0°-90°	8407.8	45.7
90°-120°	2128.1	11.6
90°-150°	7229.8	39.3
90°-180°	9999.0	54.3
0°-180°	18407.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3300	3300	3300	3300	3300	
5°	3300	3288	3253	3278	3272	313
15°	3142	3123	3082	3094	3079	885
25°	2844	2818	2764	2771	2764	1308
35°	2453	2422	2371	2352	2336	1532
45°	1996	1974	1926	1892	1879	1541
55°	1511	1492	1454	1416	1400	1351
65°	1019	1000	968	940	924	1007
75°	533	527	511	492	498	569
85°	130	127	124	114	111	145
90°	3	39	106	99	102	18
95°	157	188	193	193	188	175
105°	649	658	664	670	670	685
115°	1208	1225	1220	1216	1208	1195
125°	1757	1784	1775	1765	1762	1570
135°	2272	2306	2312	2309	2300	1756
145°	2758	2780	2797	2800	2789	1724
155°	3154	3163	3172	3188	3178	1452
165°	3431	3428	3428	3450	3435	968
175°	3570	3562	3555	3577	3559	339
180°	3577	3577	3577	3577	3577	

TEST NUMBER: P927083

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3300.5	3300.5	3300.5	3300.5	3300.5
2.5°	3319.8	3303.9	3269.0	3300.5	3294.5
5°	3300.5	3288.1	3253.1	3278.4	3272.3
7.5°	3278.4	3259.5	3224.5	3250.1	3243.7
10°	3243.7	3221.5	3183.4	3208.6	3199.2
12.5°	3195.8	3177.0	3139.0	3154.7	3148.4
15°	3142.0	3123.2	3081.7	3094.5	3078.7
17.5°	3075.3	3056.4	3015.1	3030.9	3015.1
20°	3002.2	2983.4	2938.9	2948.3	2935.9
22.5°	2929.5	2900.9	2859.5	2859.5	2853.0
25°	2843.6	2818.4	2764.5	2770.6	2764.5
27.5°	2748.3	2726.1	2685.1	2675.7	2659.8
30°	2653.4	2627.8	2580.3	2570.9	2558.1
32.5°	2551.7	2532.9	2482.0	2462.8	2450.0
35°	2453.4	2421.8	2370.9	2351.7	2335.9
37.5°	2342.3	2313.6	2262.8	2240.6	2224.8
40°	2228.1	2202.5	2151.6	2123.4	2110.6
42.5°	2116.9	2091.4	2040.9	2008.9	1990.1
45°	1996.4	1974.3	1926.4	1891.7	1879.0
47.5°	1879.0	1856.7	1805.8	1770.9	1752.0
50°	1755.0	1739.2	1694.7	1650.3	1634.5
52.5°	1634.5	1612.2	1571.1	1536.2	1513.9
55°	1510.9	1491.7	1453.6	1415.6	1399.8
57.5°	1387.0	1371.1	1329.8	1291.7	1278.9
60°	1263.0	1250.6	1206.1	1171.2	1161.7
62.5°	1142.5	1120.3	1088.6	1057.0	1044.2
65°	1018.9	999.7	968.0	939.5	923.6
67.5°	892.0	875.9	847.5	825.3	812.5
70°	774.5	761.6	733.1	710.8	698.4
72.5°	653.9	641.1	625.3	603.1	593.7
75°	533.1	527.0	510.8	492.0	498.4
77.5°	425.3	412.5	406.1	396.7	387.3
80°	317.5	314.1	307.7	298.3	292.0
82.5°	215.8	215.8	212.8	200.0	200.0
85°	130.0	127.0	123.9	114.1	111.1
87.5°	57.2	50.8	44.5	35.1	31.7
90°	3.2	38.8	105.7	99.2	102.4
92.5°	66.8	90.6	93.8	97.1	97.1
95°	157.4	187.7	193.0	193.0	187.7
97.5°	262.0	290.1	302.0	302.0	302.0
100°	382.8	407.6	416.2	416.2	413.0
102.5°	510.1	528.4	540.2	543.5	540.2
105°	649.2	657.8	664.3	669.6	669.6
107.5°	787.2	800.2	800.2	802.3	787.2
110°	920.9	938.2	938.2	938.2	929.6

TEST NUMBER: P927083

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1065.4	1083.8	1080.5	1071.9	1065.4
115°	1207.7	1225.1	1219.6	1216.4	1207.7
117.5°	1349.0	1372.8	1357.7	1349.0	1340.4
120°	1491.4	1515.1	1491.4	1491.4	1481.7
122.5°	1620.8	1651.0	1635.9	1627.2	1620.8
125°	1756.6	1783.6	1775.0	1765.3	1762.0
127.5°	1889.3	1922.7	1910.8	1897.9	1889.3
130°	2013.3	2052.1	2046.7	2040.2	2028.4
132.5°	2152.4	2182.6	2184.7	2169.6	2161.1
135°	2272.1	2305.5	2312.0	2308.7	2300.2
137.5°	2405.8	2432.8	2438.2	2436.0	2423.1
140°	2523.4	2550.3	2565.4	2565.4	2553.5
142.5°	2644.2	2671.1	2679.7	2682.9	2671.1
145°	2758.4	2780.0	2797.2	2800.5	2788.7
147.5°	2860.9	2887.8	2900.8	2906.2	2894.3
150°	2966.6	2984.9	2996.8	3006.5	2996.8
152.5°	3060.4	3078.7	3093.9	3105.7	3093.9
155°	3154.2	3162.8	3172.5	3187.6	3177.9
157.5°	3235.1	3241.5	3246.9	3268.5	3253.4
160°	3307.3	3313.8	3317.0	3335.4	3322.4
162.5°	3374.2	3374.2	3377.4	3397.9	3382.8
165°	3431.4	3428.2	3428.2	3449.6	3434.6
167.5°	3483.1	3473.4	3473.4	3495.0	3479.9
170°	3521.9	3513.3	3510.1	3531.6	3513.3
172.5°	3548.9	3540.2	3537.0	3558.6	3540.2
175°	3570.5	3561.8	3555.4	3576.9	3558.6
177.5°	3582.3	3573.7	3567.2	3585.6	3567.2
180°	3576.9	3576.9	3576.9	3576.9	3576.9

TEST NUMBER: P927083

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.98	10.80	10.97	11.81	13.14	9.54	10.37	10.54	11.37	12.71
	3H	11.64	12.37	12.64	13.39	14.74	11.16	11.90	12.17	12.91	14.27
	4H	12.22	12.92	13.24	13.94	15.30	11.75	12.45	12.76	13.47	14.83
	6H	12.62	13.26	13.65	14.29	15.66	12.14	12.79	13.17	13.81	15.18
	8H	12.72	13.34	13.76	14.38	15.74	12.25	12.86	13.28	13.90	15.27
	12H	12.77	13.36	13.81	14.39	15.78	12.29	12.87	13.33	13.91	15.30
4H	2H	10.43	11.13	11.46	12.15	13.51	10.09	10.79	11.11	11.81	13.17
	3H	12.30	12.88	13.33	13.93	15.30	11.91	12.49	12.94	13.53	14.91
	4H	13.01	13.55	14.05	14.58	15.98	12.61	13.14	13.64	14.18	15.57
	6H	13.53	13.99	14.57	15.05	16.44	13.12	13.58	14.16	14.64	16.03
	8H	13.67	14.10	14.72	15.16	16.57	13.26	13.69	14.31	14.75	16.15
	12H	13.75	14.14	14.81	15.20	16.62	13.32	13.71	14.39	14.78	16.19
8H	4H	13.21	13.64	14.26	14.69	16.10	12.85	13.28	13.90	14.33	15.74
	6H	13.84	14.19	14.91	15.29	16.69	13.47	13.83	14.55	14.92	16.33
	8H	14.06	14.37	15.14	15.45	16.87	13.69	14.00	14.77	15.08	16.50
	12H	14.19	14.46	15.27	15.54	17.00	13.80	14.08	14.89	15.15	16.62
12H	4H	13.19	13.58	14.26	14.65	16.06	12.84	13.23	13.91	14.29	15.71
	6H	13.87	14.18	14.95	15.26	16.68	13.51	13.83	14.60	14.91	16.33
	8H	14.11	14.38	15.19	15.46	16.92	13.75	14.03	14.83	15.10	16.56

END OF REPORT