

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P913720

Luminaire Tested: DFN2DIP-HX4F0-100D110US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P913720
REPORT IS A COMBINATION OF REPORTS P899437 AND P896188
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D110US927-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15554.5 lumens
Efficiency: N/A
Efficacy: 94.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 164.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P913720

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P913720

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	57	57	57
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40
3	81	72	64	59	75	67	60	55	57	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30
5	68	57	49	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2292	2292	2292
5°	2296	2260	2275
10°	2277	2230	2245
15°	2244	2194	2197
20°	2199	2143	2147
25°	2154	2082	2091
30°	2098	2025	2018
35°	2045	1959	1942
40°	1979	1891	1869
45°	1914	1824	1795
50°	1842	1753	1708
55°	1767	1671	1629
60°	1683	1574	1538
65°	1591	1473	1431
70°	1473	1350	1316
75°	1311	1203	1210
80°	1115	1016	1006
85°	809	692	669

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2077 cd/sqm

TEST NUMBER: P913720

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	290.1	1.9
10°-20°	816.3	5.2
20°-30°	1199.6	7.7
30°-40°	1393.3	9.0
40°-50°	1391.5	8.9
50°-60°	1213.4	7.8
60°-70°	897.0	5.8
70°-80°	507.5	3.3
80°-90°	141.8	0.9
90°-100°	170.5	1.1
100°-110°	541.8	3.5
110°-120°	927.3	6.0
120°-130°	1219.5	7.8
130°-140°	1368.8	8.8
140°-150°	1342.3	8.6
150°-160°	1126.0	7.2
160°-170°	746.7	4.8
170°-180°	261.0	1.7
0°-30°	2306.0	14.8
0°-40°	3699.3	23.8
0°-60°	6304.2	40.5
0°-90°	7850.4	50.5
90°-120°	1639.7	10.5
90°-150°	5570.3	35.8
90°-180°	7704.0	49.5
0°-180°	15554.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3082	3082	3082	3082	3082	
5°	3082	3071	3038	3062	3056	293
15°	2934	2917	2878	2890	2875	826
25°	2656	2632	2582	2587	2582	1222
35°	2291	2262	2214	2196	2181	1431
45°	1864	1844	1799	1767	1755	1439
55°	1411	1393	1358	1322	1307	1262
65°	952	934	904	877	863	941
75°	498	492	477	460	465	531
85°	121	119	116	107	104	135
90°	2	30	81	76	79	15
95°	121	145	149	149	145	135
105°	500	507	512	516	516	528
115°	931	944	940	937	931	920
125°	1353	1374	1368	1360	1358	1209
135°	1751	1776	1781	1779	1772	1353
145°	2125	2142	2155	2158	2149	1328
155°	2430	2437	2444	2456	2448	1119
165°	2644	2641	2641	2658	2646	746
175°	2751	2744	2739	2756	2742	261
180°	2756	2756	2756	2756	2756	

TEST NUMBER: P913720

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3082.5	3082.5	3082.5	3082.5	3082.5
2.5°	3100.4	3085.5	3052.8	3082.5	3076.8
5°	3082.5	3070.8	3038.1	3061.7	3056.0
7.5°	3061.7	3044.0	3011.3	3035.2	3029.3
10°	3029.3	3008.5	2973.0	2996.6	2987.8
12.5°	2984.6	2967.0	2931.5	2946.3	2940.3
15°	2934.3	2916.7	2878.0	2890.0	2875.2
17.5°	2872.1	2854.5	2815.7	2830.5	2815.7
20°	2803.8	2786.2	2744.7	2753.5	2741.8
22.5°	2735.9	2709.2	2670.4	2670.4	2664.5
25°	2655.7	2632.1	2581.8	2587.4	2581.8
27.5°	2566.7	2545.9	2507.6	2498.8	2484.0
30°	2478.0	2454.1	2409.7	2400.9	2389.0
32.5°	2383.0	2365.5	2317.9	2300.0	2288.1
35°	2291.2	2261.7	2214.1	2196.2	2181.4
37.5°	2187.4	2160.7	2113.2	2092.5	2077.7
40°	2080.8	2056.9	2009.4	1983.1	1971.1
42.5°	1977.0	1953.1	1906.0	1876.1	1858.5
45°	1864.5	1843.7	1799.0	1766.6	1754.8
47.5°	1754.8	1734.0	1686.5	1653.8	1636.2
50°	1639.0	1624.2	1582.7	1541.2	1526.5
52.5°	1526.5	1505.7	1467.3	1434.6	1413.9
55°	1411.0	1393.1	1357.6	1322.0	1307.3
57.5°	1295.3	1280.5	1241.8	1206.3	1194.4
60°	1179.6	1167.9	1126.4	1093.7	1084.9
62.5°	1067.0	1046.2	1016.7	987.1	975.2
65°	951.6	933.7	904.1	877.3	862.6
67.5°	833.1	817.9	791.5	770.8	758.8
70°	723.3	711.3	684.6	663.8	652.2
72.5°	610.7	598.7	584.0	563.2	554.4
75°	497.8	492.2	477.1	459.5	465.4
77.5°	397.2	385.2	379.2	370.4	361.6
80°	296.5	293.4	287.4	278.6	272.7
82.5°	201.6	201.6	198.8	186.8	186.8
85°	121.4	118.6	115.7	106.6	103.8
87.5°	53.5	47.5	41.5	32.7	29.5
90°	2.5	29.9	81.4	76.4	78.9
92.5°	51.5	69.8	72.2	74.8	74.8
95°	121.3	144.6	148.7	148.7	144.6
97.5°	201.9	223.5	232.7	232.7	232.7
100°	294.9	314.0	320.7	320.7	318.2
102.5°	393.0	407.1	416.3	418.7	416.3
105°	500.2	506.8	511.8	515.9	515.9
107.5°	606.5	616.5	616.5	618.1	606.5
110°	709.6	722.9	722.9	722.9	716.2

TEST NUMBER: P913720

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	820.9	835.0	832.5	825.8	820.9
115°	930.6	943.8	939.7	937.2	930.6
117.5°	1039.4	1057.6	1046.0	1039.4	1032.8
120°	1149.1	1167.4	1149.1	1149.1	1141.6
122.5°	1248.8	1272.0	1260.4	1253.7	1248.8
125°	1353.4	1374.2	1367.5	1360.1	1357.6
127.5°	1455.6	1481.4	1472.3	1462.3	1455.6
130°	1551.2	1581.1	1576.9	1571.9	1562.8
132.5°	1658.4	1681.6	1683.3	1671.7	1665.0
135°	1750.6	1776.3	1781.3	1778.8	1772.2
137.5°	1853.6	1874.4	1878.5	1876.8	1866.9
140°	1944.2	1964.9	1976.6	1976.6	1967.5
142.5°	2037.3	2058.0	2064.7	2067.1	2058.0
145°	2125.3	2141.9	2155.2	2157.7	2148.6
147.5°	2204.2	2225.0	2235.0	2239.1	2230.0
150°	2285.7	2299.8	2308.9	2316.4	2308.9
152.5°	2357.9	2372.0	2383.7	2392.9	2383.7
155°	2430.3	2436.8	2444.4	2456.0	2448.5
157.5°	2492.5	2497.5	2501.6	2518.3	2506.6
160°	2548.2	2553.2	2555.7	2569.8	2559.9
162.5°	2599.7	2599.7	2602.2	2618.0	2606.4
165°	2643.7	2641.2	2641.2	2657.8	2646.2
167.5°	2683.6	2676.1	2676.1	2692.8	2681.1
170°	2713.5	2706.9	2704.4	2721.0	2706.9
172.5°	2734.3	2727.6	2725.2	2741.8	2727.6
175°	2750.9	2744.3	2739.3	2755.9	2741.8
177.5°	2760.0	2753.4	2748.4	2762.6	2748.4
180°	2755.9	2755.9	2755.9	2755.9	2755.9

TEST NUMBER: P913720

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.20	11.06	11.15	12.03	13.30	9.76	10.63	10.72	11.60	12.86
	3H	11.86	12.63	12.82	13.61	14.90	11.39	12.16	12.35	13.14	14.43
	4H	12.45	13.18	13.42	14.16	15.46	11.97	12.71	12.95	13.69	14.99
	6H	12.85	13.52	13.84	14.51	15.82	12.37	13.05	13.36	14.04	15.34
	8H	12.95	13.60	13.95	14.60	15.91	12.48	13.12	13.47	14.13	15.43
	12H	13.00	13.61	14.00	14.61	15.94	12.52	13.13	13.52	14.13	15.46
4H	2H	10.66	11.39	11.64	12.38	13.67	10.31	11.05	11.30	12.03	13.33
	3H	12.53	13.14	13.52	14.15	15.46	12.13	12.75	13.13	13.76	15.07
	4H	13.24	13.80	14.24	14.81	16.14	12.84	13.40	13.84	14.40	15.73
	6H	13.76	14.24	14.77	15.27	16.60	13.35	13.83	14.36	14.86	16.19
	8H	13.91	14.36	14.92	15.38	16.73	13.50	13.95	14.51	14.97	16.31
	12H	13.98	14.39	15.02	15.43	16.78	13.56	13.97	14.59	15.00	16.35
8H	4H	13.44	13.89	14.45	14.91	16.26	13.08	13.53	14.09	14.55	15.90
	6H	14.07	14.45	15.11	15.51	16.85	13.71	14.08	14.75	15.15	16.49
	8H	14.29	14.62	15.34	15.67	17.03	13.92	14.25	14.97	15.30	16.66
	12H	14.43	14.72	15.48	15.76	17.16	14.04	14.33	15.09	15.37	16.78
12H	4H	13.43	13.83	14.46	14.87	16.22	13.07	13.48	14.11	14.52	15.87
	6H	14.10	14.43	15.15	15.48	16.84	13.75	14.08	14.80	15.13	16.49
	8H	14.35	14.64	15.40	15.68	17.08	13.99	14.28	15.04	15.32	16.73