

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927085

Luminaire Tested: DFN2DIP-HX4F0-090D120US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927085
REPORT IS A COMBINATION OF REPORTS P899454 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-090D120US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17219.5 lumens
Efficiency: N/A
Efficacy: 93.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 184.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927085

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927085

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2607	2607	2607
5°	2611	2566	2582
10°	2586	2516	2498
15°	2550	2433	2368
20°	2503	2318	2209
25°	2455	2190	2055
30°	2391	2059	1860
35°	2328	1917	1689
40°	2263	1771	1492
45°	2188	1608	1314
50°	2111	1444	1140
55°	2031	1269	973
60°	1937	1086	801
65°	1830	899	721
70°	1700	726	653
75°	1537	640	594
80°	1300	538	516
85°	909	360	388

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2696 cd/sqm

TEST NUMBER: P927085

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	328.6	1.9
10°-20°	902.0	5.2
20°-30°	1266.4	7.4
30°-40°	1380.4	8.0
40°-50°	1268.7	7.4
50°-60°	996.4	5.8
60°-70°	648.6	3.8
70°-80°	333.9	1.9
80°-90°	95.4	0.6
90°-100°	221.3	1.3
100°-110°	703.3	4.1
110°-120°	1203.5	7.0
120°-130°	1582.8	9.2
130°-140°	1776.6	10.3
140°-150°	1742.2	10.1
150°-160°	1461.5	8.5
160°-170°	969.2	5.6
170°-180°	338.8	2.0
0°-30°	2496.9	14.5
0°-40°	3877.3	22.5
0°-60°	6142.5	35.7
0°-90°	7220.3	41.9
90°-120°	2128.1	12.4
90°-150°	7229.8	42.0
90°-180°	9999.0	58.1
0°-180°	17219.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3506	3506	3506	3506	3506	
5°	3506	3490	3449	3477	3468	332
15°	3334	3300	3192	3132	3100	940
25°	3027	2925	2716	2586	2538	1392
35°	2608	2446	2167	1967	1897	1632
45°	2132	1919	1586	1361	1285	1647
55°	1621	1374	1031	841	781	1449
65°	1095	838	552	444	435	1085
75°	584	362	254	232	229	617
85°	136	70	60	60	60	156
90°	3	39	106	99	102	17
95°	157	188	193	193	188	175
105°	649	658	664	670	670	685
115°	1208	1225	1220	1216	1208	1195
125°	1757	1784	1775	1765	1762	1570
135°	2272	2306	2312	2309	2300	1756
145°	2758	2780	2797	2800	2789	1724
155°	3154	3163	3172	3188	3178	1452
165°	3431	3428	3428	3450	3435	968
175°	3570	3562	3555	3577	3559	339
180°	3577	3577	3577	3577	3577	

TEST NUMBER: P927085

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3505.8	3505.8	3505.8	3505.8	3505.8
2.5°	3521.7	3505.8	3470.8	3502.8	3496.4
5°	3505.8	3490.0	3448.6	3477.2	3467.7
7.5°	3477.2	3458.3	3413.9	3426.4	3410.5
10°	3439.2	3416.9	3353.7	3343.9	3325.0
12.5°	3391.7	3363.1	3277.3	3258.4	3223.4
15°	3334.5	3299.5	3191.8	3131.5	3099.9
17.5°	3267.8	3217.0	3083.7	3014.0	2963.2
20°	3191.8	3128.2	2969.5	2890.5	2820.4
22.5°	3109.3	3036.3	2852.1	2744.4	2697.0
25°	3026.8	2925.1	2715.8	2585.8	2538.1
27.5°	2928.5	2820.4	2588.9	2439.8	2366.7
30°	2823.8	2703.0	2449.2	2287.6	2201.8
32.5°	2722.1	2576.0	2316.2	2125.7	2046.3
35°	2608.1	2446.2	2167.1	1967.2	1897.2
37.5°	2497.0	2322.3	2027.4	1808.3	1729.2
40°	2379.5	2189.3	1881.3	1656.2	1573.7
42.5°	2259.0	2056.1	1735.5	1500.6	1421.5
45°	2132.1	1919.4	1586.4	1360.9	1284.8
47.5°	2011.6	1786.4	1443.7	1218.2	1148.5
50°	1878.3	1653.1	1304.0	1084.9	1018.6
52.5°	1748.1	1510.1	1170.8	961.4	901.1
55°	1621.1	1373.7	1031.0	840.9	780.6
57.5°	1491.2	1237.4	907.5	729.8	679.0
60°	1357.9	1104.0	777.3	615.6	564.8
62.5°	1228.0	974.2	666.2	514.0	488.8
65°	1094.6	837.5	552.0	444.3	434.6
67.5°	967.8	710.6	444.3	390.1	380.7
70°	834.5	587.1	368.0	336.3	323.5
72.5°	707.5	472.6	307.6	282.4	276.1
75°	583.7	361.5	253.8	231.6	228.6
77.5°	460.1	256.8	199.9	187.2	180.8
80°	345.7	184.2	152.1	139.7	139.7
82.5°	241.0	123.8	104.7	98.3	98.3
85°	136.3	69.7	60.2	60.2	60.2
87.5°	50.8	25.3	25.3	22.2	22.2
90°	3.2	38.8	105.7	99.2	102.4
92.5°	66.8	90.6	93.8	97.1	97.1
95°	157.4	187.7	193.0	193.0	187.7
97.5°	262.0	290.1	302.0	302.0	302.0
100°	382.8	407.6	416.2	416.2	413.0
102.5°	510.1	528.4	540.2	543.5	540.2
105°	649.2	657.8	664.3	669.6	669.6
107.5°	787.2	800.2	800.2	802.3	787.2
110°	920.9	938.2	938.2	938.2	929.6

TEST NUMBER: P927085

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1065.4	1083.8	1080.5	1071.9	1065.4
115°	1207.7	1225.1	1219.6	1216.4	1207.7
117.5°	1349.0	1372.8	1357.7	1349.0	1340.4
120°	1491.4	1515.1	1491.4	1491.4	1481.7
122.5°	1620.8	1651.0	1635.9	1627.2	1620.8
125°	1756.6	1783.6	1775.0	1765.3	1762.0
127.5°	1889.3	1922.7	1910.8	1897.9	1889.3
130°	2013.3	2052.1	2046.7	2040.2	2028.4
132.5°	2152.4	2182.6	2184.7	2169.6	2161.1
135°	2272.1	2305.5	2312.0	2308.7	2300.2
137.5°	2405.8	2432.8	2438.2	2436.0	2423.1
140°	2523.4	2550.3	2565.4	2565.4	2553.5
142.5°	2644.2	2671.1	2679.7	2682.9	2671.1
145°	2758.4	2780.0	2797.2	2800.5	2788.7
147.5°	2860.9	2887.8	2900.8	2906.2	2894.3
150°	2966.6	2984.9	2996.8	3006.5	2996.8
152.5°	3060.4	3078.7	3093.9	3105.7	3093.9
155°	3154.2	3162.8	3172.5	3187.6	3177.9
157.5°	3235.1	3241.5	3246.9	3268.5	3253.4
160°	3307.3	3313.8	3317.0	3335.4	3322.4
162.5°	3374.2	3374.2	3377.4	3397.9	3382.8
165°	3431.4	3428.2	3428.2	3449.6	3434.6
167.5°	3483.1	3473.4	3473.4	3495.0	3479.9
170°	3521.9	3513.3	3510.1	3531.6	3513.3
172.5°	3548.9	3540.2	3537.0	3558.6	3540.2
175°	3570.5	3561.8	3555.4	3576.9	3558.6
177.5°	3582.3	3573.7	3567.2	3585.6	3567.2
180°	3576.9	3576.9	3576.9	3576.9	3576.9

TEST NUMBER: P927085

CATALOG NUMBER: DFN2DIP-HX4F0-090D120US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.67	10.44	10.70	11.47	12.86	5.65	6.41	6.67	7.45	8.83
	3H	11.35	12.03	12.39	13.07	14.48	6.83	7.52	7.87	8.56	9.96
	4H	11.95	12.60	13.00	13.65	15.06	7.28	7.93	8.33	8.97	10.39
	6H	12.37	12.97	13.43	14.02	15.44	7.60	8.20	8.66	9.25	10.67
	8H	12.50	13.07	13.56	14.13	15.55	7.69	8.26	8.76	9.32	10.74
	12H	12.56	13.10	13.63	14.15	15.60	7.73	8.27	8.80	9.33	10.77
4H	2H	9.68	10.33	10.74	11.38	12.79	6.23	6.88	7.29	7.93	9.34
	3H	11.51	12.05	12.57	13.12	14.54	7.58	8.12	8.65	9.19	10.62
	4H	12.20	12.69	13.27	13.76	15.20	8.13	8.62	9.20	9.69	11.13
	6H	12.71	13.14	13.79	14.22	15.66	8.54	8.97	9.63	10.06	11.50
	8H	12.89	13.28	13.97	14.36	15.82	8.67	9.07	9.75	10.15	11.60
	12H	12.98	13.34	14.08	14.43	15.89	8.74	9.10	9.83	10.19	11.65
8H	4H	12.16	12.56	13.24	13.64	15.09	8.40	8.80	9.48	9.88	11.33
	6H	12.73	13.05	13.83	14.17	15.63	8.92	9.25	10.02	10.37	11.82
	8H	12.94	13.23	14.05	14.33	15.81	9.11	9.40	10.22	10.50	11.98
	12H	13.08	13.33	14.19	14.43	15.94	9.23	9.48	10.34	10.58	12.09
12H	4H	12.11	12.47	13.21	13.56	15.02	8.41	8.76	9.50	9.86	11.32
	6H	12.70	12.99	13.81	14.09	15.56	8.97	9.26	10.08	10.36	11.83
	8H	12.92	13.17	14.03	14.27	15.78	9.18	9.43	10.29	10.53	12.04

END OF REPORT