

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927093

Luminaire Tested: DFN2DIP-HX4F0-100D050US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927093
REPORT IS A COMBINATION OF REPORTS P899330 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D050US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12181.8 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 137
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927093

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927093

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	70	69	63	62	61
2	93	86	80	75	88	81	76	72	72	68	65	64	61	58	57	54	52
3	86	76	69	63	80	72	66	61	65	59	55	57	53	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	42	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	36	31	27	33	28	25	30	26	23
10	51	39	31	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2896	2896	2896
5°	2901	2851	2869
10°	2873	2795	2776
15°	2834	2703	2631
20°	2781	2576	2454
25°	2728	2433	2284
30°	2656	2287	2067
35°	2586	2130	1876
40°	2515	1968	1658
45°	2432	1787	1460
50°	2346	1605	1267
55°	2256	1410	1081
60°	2153	1206	890
65°	2033	999	801
70°	1889	806	725
75°	1707	711	660
80°	1444	598	573
85°	1010	400	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2432 cd/sqm

TEST NUMBER: P927093

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.1	3.0
10°-20°	1002.2	8.2
20°-30°	1407.1	11.6
30°-40°	1533.8	12.6
40°-50°	1409.7	11.6
50°-60°	1107.1	9.1
60°-70°	720.6	5.9
70°-80°	370.9	3.0
80°-90°	98.9	0.8
90°-100°	92.2	0.8
100°-110°	293.0	2.4
110°-120°	501.5	4.1
120°-130°	659.5	5.4
130°-140°	740.3	6.1
140°-150°	725.9	6.0
150°-160°	608.9	5.0
160°-170°	403.8	3.3
170°-180°	141.2	1.2
0°-30°	2774.3	22.8
0°-40°	4308.1	35.4
0°-60°	6825.0	56.0
0°-90°	8015.5	65.8
90°-120°	886.7	7.3
90°-150°	3012.4	24.7
90°-180°	4166.0	34.2
0°-180°	12181.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3895	3895	3895	3895	3895	
5°	3895	3878	3832	3864	3853	369
15°	3705	3666	3546	3479	3444	1044
25°	3363	3250	3018	2873	2820	1547
35°	2898	2718	2408	2186	2108	1814
45°	2369	2133	1763	1512	1428	1829
55°	1801	1526	1146	934	867	1610
65°	1216	930	613	494	483	1206
75°	648	402	282	257	254	686
85°	152	77	67	67	67	174
90°	1	16	44	41	43	12
95°	66	78	80	80	78	73
105°	270	274	277	279	279	285
115°	503	510	508	507	503	498
125°	732	743	740	736	734	654
135°	947	961	963	962	958	732
145°	1149	1158	1166	1167	1162	718
155°	1314	1318	1322	1328	1324	605
165°	1430	1428	1428	1437	1431	403
175°	1488	1484	1481	1490	1483	141
180°	1490	1490	1490	1490	1490	

TEST NUMBER: P927093

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3895.4	3895.4	3895.4	3895.4	3895.4
2.5°	3912.9	3895.4	3856.4	3892.0	3884.9
5°	3895.4	3877.7	3831.7	3863.6	3853.0
7.5°	3863.6	3842.6	3793.2	3807.0	3789.5
10°	3821.3	3796.6	3726.3	3715.4	3694.5
12.5°	3768.6	3736.7	3641.3	3620.4	3581.5
15°	3705.0	3666.0	3546.3	3479.4	3444.3
17.5°	3630.9	3574.4	3426.4	3348.9	3292.4
20°	3546.3	3475.7	3299.5	3211.7	3133.8
22.5°	3454.7	3373.6	3169.0	3049.4	2996.6
25°	3363.1	3250.2	3017.5	2873.1	2820.1
27.5°	3253.9	3133.8	2876.5	2710.8	2629.7
30°	3137.6	3003.3	2721.3	2541.8	2446.4
32.5°	3024.7	2862.3	2573.6	2361.9	2273.6
35°	2897.8	2718.0	2407.9	2185.8	2107.9
37.5°	2774.4	2580.3	2252.7	2009.2	1921.3
40°	2643.9	2432.6	2090.4	1840.1	1748.5
42.5°	2510.0	2284.4	1928.4	1667.4	1579.4
45°	2369.0	2132.6	1762.8	1512.1	1427.6
47.5°	2235.1	1984.9	1604.1	1353.5	1276.1
50°	2087.0	1836.7	1448.9	1205.5	1131.8
52.5°	1942.2	1677.8	1300.8	1068.1	1001.2
55°	1801.2	1526.4	1145.6	934.3	867.3
57.5°	1656.9	1374.8	1008.4	810.8	754.4
60°	1508.8	1226.8	863.6	684.1	627.6
62.5°	1364.4	1082.4	740.1	571.2	543.1
65°	1216.3	930.5	613.4	493.7	482.8
67.5°	1075.3	789.5	493.7	433.5	423.0
70°	927.1	652.3	408.8	373.6	359.5
72.5°	786.1	525.1	341.8	313.8	306.7
75°	648.5	401.7	282.0	257.3	253.9
77.5°	511.3	285.4	222.1	207.9	200.8
80°	384.1	204.6	169.1	155.2	155.2
82.5°	267.8	137.6	116.3	109.2	109.2
85°	151.5	77.4	66.9	66.9	66.9
87.5°	56.5	28.1	28.1	24.7	24.7
90°	1.3	16.2	44.0	41.4	42.7
92.5°	27.9	37.7	39.1	40.4	40.4
95°	65.6	78.2	80.4	80.4	78.2
97.5°	109.1	120.8	125.8	125.8	125.8
100°	159.5	169.8	173.4	173.4	172.1
102.5°	212.5	220.2	225.1	226.5	225.1
105°	270.5	274.1	276.8	279.0	279.0
107.5°	328.0	333.4	333.4	334.3	328.0
110°	383.7	390.9	390.9	390.9	387.3

TEST NUMBER: P927093

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	443.9	451.6	450.2	446.7	443.9
115°	503.2	510.5	508.2	506.9	503.2
117.5°	562.1	572.0	565.7	562.1	558.5
120°	621.4	631.3	621.4	621.4	617.3
122.5°	675.3	687.9	681.6	678.0	675.3
125°	731.9	743.2	739.6	735.5	734.2
127.5°	787.2	801.1	796.2	790.8	787.2
130°	838.9	855.0	852.8	850.1	845.1
132.5°	896.9	909.4	910.4	904.0	900.5
135°	946.7	960.6	963.3	962.0	958.4
137.5°	1002.4	1013.7	1015.9	1015.0	1009.6
140°	1051.4	1062.7	1068.9	1068.9	1064.0
142.5°	1101.7	1113.0	1116.6	1117.9	1113.0
145°	1149.4	1158.3	1165.5	1166.9	1161.9
147.5°	1192.1	1203.3	1208.7	1210.9	1205.9
150°	1236.1	1243.7	1248.6	1252.7	1248.6
152.5°	1275.2	1282.8	1289.1	1294.1	1289.1
155°	1314.2	1317.8	1321.9	1328.2	1324.1
157.5°	1348.0	1350.6	1352.9	1361.9	1355.6
160°	1378.0	1380.8	1382.1	1389.7	1384.3
162.5°	1405.9	1405.9	1407.2	1415.8	1409.5
165°	1429.8	1428.4	1428.4	1437.4	1431.1
167.5°	1451.3	1447.2	1447.2	1456.3	1449.9
170°	1467.5	1463.9	1462.6	1471.5	1463.9
172.5°	1478.7	1475.1	1473.8	1482.7	1475.1
175°	1487.7	1484.1	1481.4	1490.4	1482.7
177.5°	1492.6	1489.1	1486.3	1494.0	1486.3
180°	1490.4	1490.4	1490.4	1490.4	1490.4

TEST NUMBER: P927093

CATALOG NUMBER: DFN2DIP-HX4F0-100D050US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.20	13.18	13.02	14.01	15.04	8.18	9.15	8.99	9.99	11.02
	3H	13.89	14.77	14.72	15.61	16.67	9.38	10.25	10.21	11.10	12.15
	4H	14.51	15.33	15.35	16.18	17.25	9.84	10.66	10.68	11.51	12.58
	6H	14.94	15.70	15.80	16.56	17.64	10.17	10.93	11.02	11.78	12.87
	8H	15.07	15.79	15.94	16.67	17.75	10.26	10.98	11.13	11.86	12.94
	12H	15.14	15.82	16.01	16.69	17.80	10.31	11.00	11.18	11.87	12.98
4H	2H	12.24	13.06	13.09	13.91	14.98	8.79	9.62	9.64	10.47	11.53
	3H	14.08	14.77	14.94	15.65	16.74	10.16	10.84	11.02	11.72	12.81
	4H	14.78	15.40	15.66	16.29	17.40	10.71	11.33	11.58	12.21	13.32
	6H	15.31	15.84	16.20	16.75	17.86	11.14	11.68	12.03	12.58	13.70
	8H	15.48	15.99	16.38	16.89	18.01	11.27	11.77	12.16	12.67	13.80
	12H	15.59	16.04	16.50	16.96	18.09	11.35	11.80	12.26	12.71	13.85
8H	4H	14.76	15.26	15.65	16.16	17.29	11.00	11.50	11.89	12.40	13.53
	6H	15.33	15.75	16.25	16.69	17.82	11.53	11.94	12.45	12.88	14.01
	8H	15.55	15.92	16.48	16.85	18.00	11.72	12.09	12.65	13.02	14.17
	12H	15.70	16.02	16.63	16.95	18.14	11.85	12.17	12.78	13.10	14.29
12H	4H	14.72	15.17	15.63	16.09	17.22	11.01	11.46	11.92	12.38	13.51
	6H	15.31	15.68	16.24	16.61	17.75	11.58	11.95	12.51	12.88	14.02
	8H	15.54	15.86	16.47	16.79	17.98	11.80	12.12	12.73	13.05	14.24

END OF REPORT