

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928422

Luminaire Tested: DFN2DIP-HX4F0-110D040US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928422
REPORT IS A COMBINATION OF REPORTS P900834 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D040US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10541.5 lumens
Efficiency: N/A
Efficacy: 74.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 142.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928422

CATALOG NUMBER: DFN2DIP-HX4F0-110D040US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928422

CATALOG NUMBER: DFN2DIP-HX4F0-110D040US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	112	112	112	112	106	106	106	106	95	95	95	84	84	84	75	75	75
1	103	99	95	92	97	94	90	87	84	82	79	75	73	72	67	66	64
2	94	87	81	76	89	83	77	73	75	70	67	67	64	61	60	58	55
3	87	77	70	64	82	73	67	62	66	61	57	60	56	52	54	51	48
4	80	69	61	55	75	66	59	53	60	54	49	54	49	46	48	45	42
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37
6	68	56	48	42	64	53	46	41	49	43	38	44	39	35	40	36	33
7	63	51	43	37	60	49	41	36	44	38	34	41	36	32	37	33	30
8	59	46	39	33	56	45	37	32	41	35	30	37	32	29	34	30	27
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	27	24
10	52	39	32	27	49	38	31	27	35	29	25	32	27	24	29	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2677	2677	2677
5°	2682	2635	2652
10°	2655	2584	2566
15°	2619	2499	2432
20°	2571	2381	2269
25°	2522	2249	2111
30°	2455	2114	1910
35°	2390	1969	1734
40°	2324	1819	1532
45°	2248	1652	1350
50°	2168	1484	1171
55°	2085	1303	999
60°	1990	1115	822
65°	1879	924	740
70°	1746	745	670
75°	1578	657	610
80°	1335	553	530
85°	933	370	399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2248 cd/sqm

TEST NUMBER: P928422

CATALOG NUMBER: DFN2DIP-HX4F0-110D040US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.5	3.2
10°-20°	926.4	8.8
20°-30°	1300.6	12.3
30°-40°	1417.8	13.4
40°-50°	1303.1	12.4
50°-60°	1023.4	9.7
60°-70°	666.1	6.3
70°-80°	342.9	3.3
80°-90°	89.4	0.8
90°-100°	35.2	0.3
100°-110°	131.4	1.2
110°-120°	348.6	3.3
120°-130°	578.1	5.5
130°-140°	614.1	5.8
140°-150°	570.7	5.4
150°-160°	458.8	4.4
160°-170°	295.7	2.8
170°-180°	101.8	1.0
0°-30°	2564.5	24.3
0°-40°	3982.2	37.8
0°-60°	6308.7	59.8
0°-90°	7407.1	70.3
90°-120°	515.2	4.9
90°-150°	2278.1	21.6
90°-180°	3134.0	29.7
0°-180°	10541.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3601	3601	3601	3601	3601	
5°	3601	3584	3542	3571	3562	341
15°	3425	3389	3278	3216	3184	965
25°	3109	3004	2789	2656	2607	1430
35°	2679	2512	2226	2020	1948	1677
45°	2190	1971	1629	1398	1320	1691
55°	1665	1411	1059	864	802	1488
65°	1124	860	567	456	446	1115
75°	600	371	261	238	235	634
85°	140	72	62	62	62	161
90°	1	9	15	19	21	10
95°	50	25	30	34	33	59
105°	235	258	47	56	59	251
115°	445	458	477	119	64	438
125°	629	639	654	659	662	561
135°	778	791	798	805	804	601
145°	903	902	915	921	917	565
155°	994	987	996	1001	995	458
165°	1048	1043	1045	1051	1045	296
175°	1071	1066	1068	1073	1065	102
180°	1069	1069	1069	1069	1069	

TEST NUMBER: P928422

CATALOG NUMBER: DFN2DIP-HX4F0-110D040US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3600.7	3600.7	3600.7	3600.7	3600.7
2.5°	3616.9	3600.7	3564.7	3597.6	3591.0
5°	3600.7	3584.4	3541.9	3571.3	3561.6
7.5°	3571.3	3551.9	3506.3	3519.1	3502.8
10°	3532.2	3509.4	3444.4	3434.3	3415.0
12.5°	3483.5	3454.1	3365.9	3346.5	3310.6
15°	3424.7	3388.7	3278.1	3216.2	3183.7
17.5°	3356.3	3304.1	3167.1	3095.5	3043.3
20°	3278.1	3212.7	3049.9	2968.7	2896.7
22.5°	3193.4	3118.3	2929.3	2818.6	2769.9
25°	3108.7	3004.3	2789.3	2655.8	2606.7
27.5°	3007.8	2896.7	2658.9	2505.7	2430.7
30°	2900.2	2776.1	2515.5	2349.5	2261.3
32.5°	2795.8	2645.8	2378.9	2183.2	2101.7
35°	2678.6	2512.3	2225.8	2020.4	1948.5
37.5°	2564.6	2385.1	2082.2	1857.2	1776.0
40°	2443.9	2248.6	1932.2	1700.9	1616.2
42.5°	2320.1	2111.6	1782.6	1541.2	1460.0
45°	2189.8	1971.3	1629.4	1397.7	1319.6
47.5°	2066.0	1834.7	1482.8	1251.1	1179.6
50°	1929.1	1697.8	1339.4	1114.3	1046.2
52.5°	1795.3	1550.9	1202.4	987.4	925.5
55°	1664.9	1410.9	1058.9	863.6	801.7
57.5°	1531.6	1270.8	932.0	749.5	697.3
60°	1394.6	1134.0	798.3	632.3	580.1
62.5°	1261.2	1000.5	684.2	527.9	502.0
65°	1124.2	860.1	567.0	456.4	446.3
67.5°	994.0	729.8	456.4	400.7	391.0
70°	857.0	602.9	377.9	345.4	332.2
72.5°	726.7	485.4	316.0	290.0	283.5
75°	599.5	371.3	260.6	237.8	234.7
77.5°	472.6	263.8	205.4	192.2	185.6
80°	355.1	189.1	156.3	143.5	143.5
82.5°	247.5	127.2	107.6	101.0	101.0
85°	140.0	71.6	61.9	61.9	61.9
87.5°	52.2	25.9	25.9	22.8	22.8
90°	0.7	9.3	15.4	19.4	20.8
92.5°	19.4	16.2	18.5	20.1	20.8
95°	50.2	24.7	30.1	34.1	33.3
97.5°	90.5	27.1	39.4	41.8	42.5
100°	136.9	31.0	44.1	50.2	51.8
102.5°	187.9	186.5	45.6	54.1	56.5
105°	235.1	258.4	47.2	55.7	58.8
107.5°	290.1	309.4	48.8	57.3	60.4
110°	342.8	358.9	135.4	58.1	61.1

TEST NUMBER: P928422

CATALOG NUMBER: DFN2DIP-HX4F0-110D040US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	392.3	406.1	393.0	59.6	61.9
115°	444.8	457.9	477.3	119.1	63.5
117.5°	490.5	505.9	519.2	408.4	205.8
120°	541.6	553.1	567.1	576.4	472.0
122.5°	584.8	597.2	612.8	617.4	618.2
125°	628.9	639.1	653.7	659.2	661.5
127.5°	669.2	680.0	691.7	699.4	700.1
130°	707.1	719.5	727.9	736.5	735.8
132.5°	745.7	755.9	764.4	771.3	770.6
135°	778.3	790.7	797.6	805.4	803.9
137.5°	812.3	821.5	829.4	837.1	834.8
140°	845.5	851.8	860.3	867.2	863.4
142.5°	873.5	878.9	888.9	895.0	891.2
145°	902.9	902.1	915.2	920.6	916.7
147.5°	928.3	926.0	939.2	943.0	940.0
150°	953.1	947.7	960.1	964.7	960.9
152.5°	974.0	967.8	979.4	984.1	978.7
155°	994.1	987.2	996.5	1001.1	994.9
157.5°	1010.4	1004.2	1011.2	1016.6	1010.4
160°	1024.3	1019.6	1024.3	1028.9	1023.5
162.5°	1036.6	1032.1	1035.9	1041.3	1034.4
165°	1047.5	1042.9	1045.2	1050.6	1045.2
167.5°	1056.1	1051.3	1053.8	1059.1	1052.2
170°	1063.0	1058.3	1059.9	1065.3	1058.3
172.5°	1067.6	1063.0	1064.6	1070.0	1063.0
175°	1071.4	1066.0	1067.6	1073.0	1065.3
177.5°	1073.0	1067.6	1068.4	1073.9	1066.9
180°	1069.2	1069.2	1069.2	1069.2	1069.2

TEST NUMBER: P928422

CATALOG NUMBER: DFN2DIP-HX4F0-110D040US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.28	13.31	13.05	14.10	15.05	8.26	9.28	9.02	10.07	11.02
	3H	13.98	14.90	14.76	15.69	16.67	9.46	10.38	10.24	11.18	12.16
	4H	14.59	15.46	15.39	16.27	17.26	9.92	10.79	10.72	11.59	12.59
	6H	15.03	15.83	15.84	16.64	17.65	10.25	11.05	11.07	11.87	12.87
	8H	15.16	15.92	15.98	16.75	17.76	10.35	11.11	11.17	11.94	12.95
	12H	15.23	15.95	16.05	16.78	17.81	10.40	11.13	11.23	11.95	12.98
4H	2H	12.33	13.19	13.13	14.00	14.99	8.88	9.74	9.68	10.55	11.54
	3H	14.17	14.89	14.99	15.73	16.74	10.25	10.97	11.06	11.80	12.81
	4H	14.87	15.53	15.70	16.36	17.40	10.80	11.46	11.63	12.29	13.33
	6H	15.40	15.97	16.25	16.83	17.87	11.23	11.80	12.08	12.66	13.70
	8H	15.58	16.11	16.43	16.96	18.02	11.37	11.90	12.22	12.75	13.81
	12H	15.69	16.16	16.55	17.04	18.10	11.44	11.92	12.31	12.79	13.85
8H	4H	14.86	15.38	15.71	16.24	17.29	11.10	11.62	11.95	12.48	13.54
	6H	15.43	15.87	16.31	16.76	17.82	11.63	12.06	12.50	12.96	14.02
	8H	15.65	16.04	16.54	16.93	18.00	11.82	12.21	12.71	13.10	14.17
	12H	15.80	16.14	16.69	17.02	18.15	11.95	12.29	12.84	13.17	14.30
12H	4H	14.82	15.29	15.69	16.17	17.23	11.11	11.59	11.98	12.46	13.52
	6H	15.41	15.79	16.30	16.69	17.76	11.68	12.06	12.56	12.96	14.03
	8H	15.64	15.98	16.53	16.86	17.99	11.90	12.24	12.79	13.12	14.25

END OF REPORT