

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927104

Luminaire Tested: DFN2DIP-HX4F0-100D080US830-FLLONL

Issue Date: 12/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P927104  
REPORT IS A COMBINATION OF REPORTS P900903 AND P896187  
Test Lab: INNOVATION CENTER  
Issue Date: 12/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-100D080US830-FLONL  
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 16795.4 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 157.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.946  
Total Harmonic Distortion (THDi): 0.132  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P927104  
CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P927104  
 CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	56			56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	54	53	52	47			47
2	90	83	76	71	84	77	72	67	66	62	59	57	54	51	48	46	44	39			39
3	82	73	65	59	76	68	61	56	59	54	50	50	46	43	42	39	37	33			33
4	75	64	56	50	70	60	53	48	52	47	42	45	40	37	38	35	32	29			29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25			25
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25	22			22
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19			19
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17			17
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16			16
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14			14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2727	2727	2727
5°	2732	2689	2707
10°	2710	2653	2671
15°	2670	2610	2614
20°	2616	2549	2555
25°	2563	2477	2487
30°	2496	2410	2401
35°	2433	2330	2310
40°	2355	2250	2224
45°	2277	2170	2135
50°	2192	2086	2032
55°	2103	1988	1938
60°	2002	1872	1830
65°	1893	1753	1703
70°	1753	1606	1566
75°	1559	1432	1439
80°	1327	1209	1197
85°	963	824	797

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2277 cd/sqm



TEST NUMBER: P927104

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-FLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	345.2	2.1
10°-20°	971.2	5.8
20°-30°	1427.2	8.5
30°-40°	1657.6	9.9
40°-50°	1655.6	9.9
50°-60°	1443.6	8.6
60°-70°	1067.2	6.4
70°-80°	603.8	3.6
80°-90°	163.9	1.0
90°-100°	83.9	0.5
100°-110°	312.8	1.9
110°-120°	829.6	4.9
120°-130°	1375.9	8.2
130°-140°	1461.6	8.7
140°-150°	1358.3	8.1
150°-160°	1092.1	6.5
160°-170°	703.7	4.2
170°-180°	242.2	1.4
0°-30°	2743.6	16.3
0°-40°	4401.2	26.2
0°-60°	7500.4	44.7
0°-90°	9335.2	55.6
90°-120°	1226.3	7.3
90°-150°	5422.1	32.3
90°-180°	7460.0	44.4
0°-180°	16795.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3654	3615	3643	3636	348
15°	3491	3470	3424	3438	3421	983
25°	3160	3132	3072	3078	3072	1454
35°	2726	2691	2634	2613	2595	1702
45°	2218	2194	2140	2102	2088	1712
55°	1679	1658	1615	1573	1555	1501
65°	1132	1111	1076	1044	1026	1119
75°	592	586	568	547	554	632
85°	144	141	138	127	124	161
90°	2	22	37	46	50	16
95°	120	59	72	81	79	142
105°	560	615	112	132	140	598
115°	1059	1090	1136	284	151	1042
125°	1497	1521	1556	1569	1574	1335
135°	1852	1882	1898	1917	1913	1431
145°	2149	2147	2178	2191	2182	1344
155°	2366	2350	2372	2383	2368	1090
165°	2493	2482	2488	2500	2488	704
175°	2550	2537	2541	2554	2536	243
180°	2545	2545	2545	2545	2545	



TEST NUMBER: P927104

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3667.4	3667.4	3667.4	3667.4	3667.4
2.5°	3688.7	3671.0	3632.1	3667.4	3660.6
5°	3667.4	3653.5	3614.6	3642.7	3635.9
7.5°	3642.7	3621.7	3582.7	3611.2	3604.1
10°	3604.1	3579.4	3537.1	3565.2	3554.7
12.5°	3551.0	3530.0	3487.7	3505.3	3498.2
15°	3491.1	3470.2	3424.1	3438.3	3420.8
17.5°	3417.0	3396.1	3350.0	3367.6	3350.0
20°	3335.8	3314.9	3265.5	3275.9	3262.1
22.5°	3255.0	3223.3	3177.2	3177.2	3170.1
25°	3159.6	3131.6	3071.7	3078.4	3071.7
27.5°	3053.7	3029.0	2983.4	2972.9	2955.3
30°	2948.2	2919.8	2867.0	2856.5	2842.3
32.5°	2835.2	2814.3	2757.8	2736.5	2722.2
35°	2726.0	2690.8	2634.3	2613.0	2595.4
37.5°	2602.5	2570.7	2514.2	2489.5	2471.9
40°	2475.7	2447.2	2390.7	2359.4	2345.1
42.5°	2352.2	2323.7	2267.7	2232.1	2211.2
45°	2218.3	2193.6	2140.4	2101.9	2087.7
47.5°	2087.7	2063.0	2006.5	1967.6	1946.6
50°	1950.0	1932.4	1883.0	1833.6	1816.1
52.5°	1816.1	1791.4	1745.7	1706.9	1682.2
55°	1678.8	1657.5	1615.2	1572.8	1555.3
57.5°	1541.1	1523.5	1477.5	1435.2	1421.0
60°	1403.4	1389.5	1340.1	1301.2	1290.8
62.5°	1269.5	1244.8	1209.6	1174.4	1160.2
65°	1132.1	1110.8	1075.7	1043.8	1026.3
67.5°	991.1	973.1	941.7	917.1	902.8
70°	860.5	846.3	814.5	789.8	776.0
72.5°	726.6	712.3	694.8	670.1	659.6
75°	592.3	585.6	567.6	546.6	553.7
77.5°	472.6	458.3	451.2	440.7	430.3
80°	352.8	349.1	341.9	331.5	324.4
82.5°	239.9	239.9	236.5	222.2	222.2
85°	144.4	141.1	137.7	126.9	123.5
87.5°	63.6	56.5	49.4	38.9	35.2
90°	1.8	22.1	36.8	46.1	49.7
92.5°	46.1	38.7	44.2	47.9	49.7
95°	119.6	58.8	71.7	81.1	79.2
97.5°	215.4	64.5	93.8	99.5	101.2
100°	326.0	73.7	105.0	119.6	123.3
102.5°	447.4	443.8	108.7	128.7	134.5
105°	559.8	615.1	112.3	132.5	140.0
107.5°	690.5	736.4	116.1	136.2	143.6
110°	815.8	854.3	322.3	138.2	145.4



TEST NUMBER: P927104

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	933.6	966.6	935.4	141.7	147.4
115°	1058.7	1090.0	1136.1	283.6	151.1
117.5°	1167.4	1204.1	1235.6	972.1	489.8
120°	1289.0	1316.5	1349.8	1371.8	1123.2
122.5°	1391.9	1421.5	1458.4	1469.4	1471.3
125°	1496.9	1520.9	1555.9	1568.8	1574.3
127.5°	1592.6	1618.5	1646.3	1664.5	1666.3
130°	1682.9	1712.4	1732.6	1753.0	1751.2
132.5°	1775.0	1799.0	1819.2	1835.8	1834.0
135°	1852.4	1881.9	1898.3	1917.0	1913.2
137.5°	1933.4	1955.4	1974.0	1992.4	1986.9
140°	2012.4	2027.3	2047.5	2064.1	2054.8
142.5°	2079.0	2091.8	2115.6	2130.3	2121.1
145°	2148.9	2146.9	2178.2	2191.1	2181.9
147.5°	2209.5	2204.0	2235.2	2244.5	2237.2
150°	2268.5	2255.6	2285.1	2296.0	2286.9
152.5°	2318.2	2303.5	2331.0	2342.2	2329.3
155°	2366.1	2349.7	2371.7	2382.6	2368.0
157.5°	2404.7	2390.1	2406.7	2419.6	2404.7
160°	2438.0	2426.8	2438.0	2448.9	2436.0
162.5°	2467.3	2456.3	2465.5	2478.4	2461.8
165°	2493.1	2482.2	2487.6	2500.5	2487.6
167.5°	2513.4	2502.2	2507.9	2520.8	2504.2
170°	2530.0	2518.8	2522.6	2535.5	2518.8
172.5°	2541.0	2530.0	2533.7	2546.6	2530.0
175°	2550.1	2537.2	2541.0	2553.8	2535.5
177.5°	2553.8	2541.0	2542.9	2555.8	2539.2
180°	2544.7	2544.7	2544.7	2544.7	2544.7



TEST NUMBER: P927104  
 CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.26	12.17	12.17	13.10	14.29	10.83	11.74	11.73	12.67	13.86
	3H	12.92	13.74	13.84	14.68	15.89	12.45	13.27	13.37	14.21	15.42
	4H	13.51	14.29	14.45	15.23	16.45	13.04	13.82	13.98	14.76	15.98
	6H	13.92	14.63	14.86	15.58	16.82	13.44	14.16	14.39	15.10	16.34
	8H	14.02	14.71	14.98	15.67	16.90	13.55	14.23	14.50	15.19	16.43
	12H	14.08	14.72	15.03	15.68	16.94	13.59	14.24	14.55	15.20	16.46
4H	2H	11.73	12.50	12.67	13.44	14.67	11.38	12.16	12.32	13.10	14.32
	3H	13.60	14.25	14.55	15.22	16.46	13.21	13.85	14.16	14.83	16.06
	4H	14.32	14.91	15.28	15.87	17.14	13.91	14.50	14.87	15.47	16.73
	6H	14.84	15.35	15.81	16.34	17.60	14.43	14.94	15.40	15.93	17.19
	8H	14.99	15.46	15.96	16.45	17.72	14.57	15.05	15.55	16.03	17.31
	12H	15.06	15.49	16.06	16.49	17.77	14.64	15.07	15.63	16.07	17.35
8H	4H	14.52	14.99	15.49	15.98	17.25	14.16	14.63	15.13	15.62	16.89
	6H	15.15	15.55	16.15	16.57	17.85	14.79	15.18	15.79	16.21	17.48
	8H	15.38	15.72	16.38	16.74	18.03	15.01	15.35	16.01	16.37	17.66
	12H	15.51	15.82	16.52	16.82	18.16	15.12	15.43	16.14	16.44	17.77
12H	4H	14.51	14.94	15.50	15.94	17.22	14.15	14.58	15.15	15.58	16.86
	6H	15.18	15.53	16.19	16.54	17.84	14.83	15.18	15.84	16.19	17.48
	8H	15.43	15.74	16.44	16.74	18.08	15.07	15.38	16.08	16.38	17.72