

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927105

Luminaire Tested: DFN2DIP-HX4F0-100D080US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927105
REPORT IS A COMBINATION OF REPORTS P899384 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D080US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14684.1 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 157.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927105

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927105

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	95	91	88	92	89	85	82	76	74	72	65	63	62	54	53	52
2	91	84	78	73	84	78	73	69	67	63	60	57	55	52	48	46	45
3	83	74	67	61	77	69	63	58	60	55	51	51	48	45	43	41	39
4	76	66	58	52	71	62	55	50	54	48	44	46	42	39	39	36	34
5	70	59	51	45	65	55	48	43	48	43	38	42	37	34	35	32	30
6	65	53	45	40	60	50	43	38	44	38	34	38	33	30	32	29	26
7	60	48	40	35	56	45	38	33	40	34	30	35	30	27	30	26	24
8	56	44	36	31	52	41	34	30	36	31	27	32	27	24	27	24	21
9	52	40	33	28	49	38	31	27	34	28	24	29	25	22	25	22	19
10	49	37	30	25	46	35	28	24	31	26	22	27	23	20	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2896	2896	2896
5°	2901	2851	2869
10°	2873	2795	2776
15°	2834	2703	2631
20°	2781	2576	2454
25°	2728	2433	2284
30°	2656	2287	2067
35°	2586	2130	1876
40°	2515	1968	1658
45°	2432	1787	1460
50°	2346	1605	1267
55°	2256	1410	1081
60°	2153	1206	890
65°	2033	999	801
70°	1889	806	725
75°	1707	711	660
80°	1444	598	573
85°	1010	400	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2432 cd/sqm

TEST NUMBER: P927105

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.1	2.5
10°-20°	1002.2	6.8
20°-30°	1407.1	9.6
30°-40°	1533.8	10.4
40°-50°	1409.7	9.6
50°-60°	1107.1	7.5
60°-70°	720.6	4.9
70°-80°	370.9	2.5
80°-90°	101.5	0.7
90°-100°	147.6	1.0
100°-110°	468.9	3.2
110°-120°	802.3	5.5
120°-130°	1055.2	7.2
130°-140°	1184.4	8.1
140°-150°	1161.5	7.9
150°-160°	974.3	6.6
160°-170°	646.1	4.4
170°-180°	225.8	1.5
0°-30°	2774.3	18.9
0°-40°	4308.1	29.3
0°-60°	6825.0	46.5
0°-90°	8018.0	54.6
90°-120°	1418.8	9.7
90°-150°	4819.9	32.8
90°-180°	6666.0	45.4
0°-180°	14684.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3895	3895	3895	3895	3895	
5°	3895	3878	3832	3864	3853	369
15°	3705	3666	3546	3479	3444	1044
25°	3363	3250	3018	2873	2820	1547
35°	2898	2718	2408	2186	2108	1814
45°	2369	2133	1763	1512	1428	1829
55°	1801	1526	1146	934	867	1610
65°	1216	930	613	494	483	1206
75°	648	402	282	257	254	686
85°	152	77	67	67	67	174
90°	2	26	70	66	68	14
95°	105	125	129	129	125	117
105°	433	438	443	446	446	457
115°	805	817	813	811	805	796
125°	1171	1189	1183	1177	1175	1047
135°	1515	1537	1541	1539	1533	1171
145°	1839	1853	1865	1867	1859	1149
155°	2103	2109	2115	2125	2119	968
165°	2288	2285	2285	2300	2290	645
175°	2380	2374	2370	2385	2372	226
180°	2385	2385	2385	2385	2385	

TEST NUMBER: P927105

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3895.4	3895.4	3895.4	3895.4	3895.4
2.5°	3912.9	3895.4	3856.4	3892.0	3884.9
5°	3895.4	3877.7	3831.7	3863.6	3853.0
7.5°	3863.6	3842.6	3793.2	3807.0	3789.5
10°	3821.3	3796.6	3726.3	3715.4	3694.5
12.5°	3768.6	3736.7	3641.3	3620.4	3581.5
15°	3705.0	3666.0	3546.3	3479.4	3444.3
17.5°	3630.9	3574.4	3426.4	3348.9	3292.4
20°	3546.3	3475.7	3299.5	3211.7	3133.8
22.5°	3454.7	3373.6	3169.0	3049.4	2996.6
25°	3363.1	3250.2	3017.5	2873.1	2820.1
27.5°	3253.9	3133.8	2876.5	2710.8	2629.7
30°	3137.6	3003.3	2721.3	2541.8	2446.4
32.5°	3024.7	2862.3	2573.6	2361.9	2273.6
35°	2897.8	2718.0	2407.9	2185.8	2107.9
37.5°	2774.4	2580.3	2252.7	2009.2	1921.3
40°	2643.9	2432.6	2090.4	1840.1	1748.5
42.5°	2510.0	2284.4	1928.4	1667.4	1579.4
45°	2369.0	2132.6	1762.8	1512.1	1427.6
47.5°	2235.1	1984.9	1604.1	1353.5	1276.1
50°	2087.0	1836.7	1448.9	1205.5	1131.8
52.5°	1942.2	1677.8	1300.8	1068.1	1001.2
55°	1801.2	1526.4	1145.6	934.3	867.3
57.5°	1656.9	1374.8	1008.4	810.8	754.4
60°	1508.8	1226.8	863.6	684.1	627.6
62.5°	1364.4	1082.4	740.1	571.2	543.1
65°	1216.3	930.5	613.4	493.7	482.8
67.5°	1075.3	789.5	493.7	433.5	423.0
70°	927.1	652.3	408.8	373.6	359.5
72.5°	786.1	525.1	341.8	313.8	306.7
75°	648.5	401.7	282.0	257.3	253.9
77.5°	511.3	285.4	222.1	207.9	200.8
80°	384.1	204.6	169.1	155.2	155.2
82.5°	267.8	137.6	116.3	109.2	109.2
85°	151.5	77.4	66.9	66.9	66.9
87.5°	56.5	28.1	28.1	24.7	24.7
90°	2.2	25.9	70.5	66.2	68.3
92.5°	44.6	60.4	62.6	64.7	64.7
95°	105.0	125.1	128.7	128.7	125.1
97.5°	174.7	193.4	201.3	201.3	201.3
100°	255.2	271.7	277.5	277.5	275.3
102.5°	340.1	352.3	360.1	362.3	360.1
105°	432.8	438.5	442.9	446.5	446.5
107.5°	524.8	533.5	533.5	534.9	524.8
110°	613.9	625.4	625.4	625.4	619.7

TEST NUMBER: P927105

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	710.3	722.5	720.4	714.6	710.3
115°	805.2	816.7	813.1	810.9	805.2
117.5°	899.3	915.2	905.1	899.3	893.6
120°	994.2	1010.1	994.2	994.2	987.7
122.5°	1080.5	1100.7	1090.6	1084.8	1080.5
125°	1171.1	1189.1	1183.3	1176.8	1174.7
127.5°	1259.6	1281.8	1273.9	1265.3	1259.6
130°	1342.2	1368.0	1364.5	1360.2	1352.3
132.5°	1435.0	1455.0	1456.5	1446.5	1440.7
135°	1514.7	1537.0	1541.4	1539.2	1533.4
137.5°	1603.9	1621.9	1625.4	1624.0	1615.4
140°	1682.3	1700.2	1710.3	1710.3	1702.3
142.5°	1762.8	1780.8	1786.5	1788.7	1780.8
145°	1839.0	1853.3	1864.8	1867.0	1859.1
147.5°	1907.2	1925.2	1933.8	1937.5	1929.6
150°	1977.7	1989.9	1997.8	2004.3	1997.8
152.5°	2040.2	2052.5	2062.6	2070.5	2062.6
155°	2102.8	2108.6	2115.1	2125.1	2118.6
157.5°	2156.7	2161.1	2164.6	2179.0	2169.0
160°	2204.9	2209.2	2211.4	2223.5	2215.0
162.5°	2249.5	2249.5	2251.6	2265.3	2255.2
165°	2287.5	2285.4	2285.4	2299.8	2289.7
167.5°	2322.0	2315.6	2315.6	2330.0	2319.9
170°	2348.0	2342.2	2340.0	2354.5	2342.2
172.5°	2366.0	2360.2	2358.0	2372.4	2360.2
175°	2380.3	2374.5	2370.2	2384.6	2372.4
177.5°	2388.2	2382.5	2378.1	2390.4	2378.1
180°	2384.6	2384.6	2384.6	2384.6	2384.6

TEST NUMBER: P927105

CATALOG NUMBER: DFN2DIP-HX4F0-100D080US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.26	12.13	12.18	13.07	14.27	7.23	8.10	8.16	9.04	10.25
	3H	12.94	13.72	13.88	14.67	15.90	8.43	9.21	9.36	10.15	11.38
	4H	13.55	14.29	14.50	15.24	16.48	8.88	9.62	9.83	10.57	11.81
	6H	13.98	14.65	14.94	15.61	16.86	9.21	9.88	10.17	10.84	12.09
	8H	14.11	14.75	15.07	15.72	16.97	9.30	9.94	10.27	10.91	12.16
	12H	14.17	14.78	15.14	15.75	17.02	9.34	9.96	10.32	10.92	12.20
4H	2H	11.28	12.02	12.24	12.97	14.21	7.83	8.57	8.79	9.52	10.76
	3H	13.12	13.73	14.08	14.71	15.96	9.19	9.80	10.16	10.78	12.04
	4H	13.81	14.37	14.79	15.34	16.62	9.74	10.30	10.72	11.27	12.55
	6H	14.33	14.81	15.32	15.81	17.09	10.16	10.64	11.15	11.64	12.92
	8H	14.51	14.96	15.50	15.95	17.24	10.30	10.74	11.28	11.73	13.03
	12H	14.61	15.01	15.61	16.02	17.31	10.36	10.77	11.37	11.77	13.07
8H	4H	13.78	14.23	14.77	15.22	16.51	10.03	10.47	11.01	11.46	12.76
	6H	14.35	14.72	15.37	15.76	17.04	10.55	10.92	11.56	11.95	13.24
	8H	14.57	14.90	15.59	15.92	17.22	10.74	11.07	11.76	12.09	13.39
	12H	14.71	15.00	15.74	16.01	17.37	10.86	11.15	11.89	12.16	13.52
12H	4H	13.74	14.14	14.74	15.15	16.45	10.03	10.44	11.04	11.44	12.74
	6H	14.33	14.65	15.35	15.68	16.98	10.60	10.92	11.62	11.94	13.25
	8H	14.55	14.84	15.58	15.85	17.21	10.81	11.10	11.83	12.11	13.47