

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927113

Luminaire Tested: DFN2DIP-HX4F0-100D100US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927113
REPORT IS A COMBINATION OF REPORTS P899420 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D100US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 16352.4 lumens
Efficiency: N/A
Efficacy: 93.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 175.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927113

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927113

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2896	2896	2896
5°	2901	2851	2869
10°	2873	2795	2776
15°	2834	2703	2631
20°	2781	2576	2454
25°	2728	2433	2284
30°	2656	2287	2067
35°	2586	2130	1876
40°	2515	1968	1658
45°	2432	1787	1460
50°	2346	1605	1267
55°	2256	1410	1081
60°	2153	1206	890
65°	2033	999	801
70°	1889	806	725
75°	1707	711	660
80°	1444	598	573
85°	1010	400	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2432 cd/sqm

TEST NUMBER: P927113

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.1	2.2
10°-20°	1002.2	6.1
20°-30°	1407.1	8.6
30°-40°	1533.8	9.4
40°-50°	1409.7	8.6
50°-60°	1107.1	6.8
60°-70°	720.6	4.4
70°-80°	370.9	2.3
80°-90°	103.2	0.6
90°-100°	184.5	1.1
100°-110°	586.1	3.6
110°-120°	1002.9	6.1
120°-130°	1319.0	8.1
130°-140°	1480.5	9.1
140°-150°	1451.8	8.9
150°-160°	1217.9	7.4
160°-170°	807.7	4.9
170°-180°	282.3	1.7
0°-30°	2774.3	17.0
0°-40°	4308.1	26.3
0°-60°	6825.0	41.7
0°-90°	8019.7	49.0
90°-120°	1773.4	10.8
90°-150°	6024.8	36.8
90°-180°	8333.0	51.0
0°-180°	16352.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3895	3895	3895	3895	3895	
5°	3895	3878	3832	3864	3853	369
15°	3705	3666	3546	3479	3444	1044
25°	3363	3250	3018	2873	2820	1547
35°	2898	2718	2408	2186	2108	1814
45°	2369	2133	1763	1512	1428	1829
55°	1801	1526	1146	934	867	1610
65°	1216	930	613	494	483	1206
75°	648	402	282	257	254	686
85°	152	77	67	67	67	174
90°	3	32	88	83	85	16
95°	131	156	161	161	156	146
105°	541	548	554	558	558	571
115°	1006	1021	1016	1014	1006	995
125°	1464	1486	1479	1471	1468	1308
135°	1893	1921	1927	1924	1917	1464
145°	2299	2317	2331	2334	2324	1436
155°	2628	2636	2644	2656	2648	1210
165°	2860	2857	2857	2875	2862	807
175°	2975	2968	2963	2981	2966	283
180°	2981	2981	2981	2981	2981	

TEST NUMBER: P927113

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3895.4	3895.4	3895.4	3895.4	3895.4
2.5°	3912.9	3895.4	3856.4	3892.0	3884.9
5°	3895.4	3877.7	3831.7	3863.6	3853.0
7.5°	3863.6	3842.6	3793.2	3807.0	3789.5
10°	3821.3	3796.6	3726.3	3715.4	3694.5
12.5°	3768.6	3736.7	3641.3	3620.4	3581.5
15°	3705.0	3666.0	3546.3	3479.4	3444.3
17.5°	3630.9	3574.4	3426.4	3348.9	3292.4
20°	3546.3	3475.7	3299.5	3211.7	3133.8
22.5°	3454.7	3373.6	3169.0	3049.4	2996.6
25°	3363.1	3250.2	3017.5	2873.1	2820.1
27.5°	3253.9	3133.8	2876.5	2710.8	2629.7
30°	3137.6	3003.3	2721.3	2541.8	2446.4
32.5°	3024.7	2862.3	2573.6	2361.9	2273.6
35°	2897.8	2718.0	2407.9	2185.8	2107.9
37.5°	2774.4	2580.3	2252.7	2009.2	1921.3
40°	2643.9	2432.6	2090.4	1840.1	1748.5
42.5°	2510.0	2284.4	1928.4	1667.4	1579.4
45°	2369.0	2132.6	1762.8	1512.1	1427.6
47.5°	2235.1	1984.9	1604.1	1353.5	1276.1
50°	2087.0	1836.7	1448.9	1205.5	1131.8
52.5°	1942.2	1677.8	1300.8	1068.1	1001.2
55°	1801.2	1526.4	1145.6	934.3	867.3
57.5°	1656.9	1374.8	1008.4	810.8	754.4
60°	1508.8	1226.8	863.6	684.1	627.6
62.5°	1364.4	1082.4	740.1	571.2	543.1
65°	1216.3	930.5	613.4	493.7	482.8
67.5°	1075.3	789.5	493.7	433.5	423.0
70°	927.1	652.3	408.8	373.6	359.5
72.5°	786.1	525.1	341.8	313.8	306.7
75°	648.5	401.7	282.0	257.3	253.9
77.5°	511.3	285.4	222.1	207.9	200.8
80°	384.1	204.6	169.1	155.2	155.2
82.5°	267.8	137.6	116.3	109.2	109.2
85°	151.5	77.4	66.9	66.9	66.9
87.5°	56.5	28.1	28.1	24.7	24.7
90°	2.7	32.3	88.0	82.7	85.4
92.5°	55.7	75.5	78.2	80.9	80.9
95°	131.2	156.4	160.9	160.9	156.4
97.5°	218.4	241.8	251.6	251.6	251.6
100°	319.0	339.7	346.8	346.8	344.2
102.5°	425.1	440.3	450.2	452.9	450.2
105°	541.0	548.2	553.5	558.1	558.1
107.5°	656.0	666.8	666.8	668.6	656.0
110°	767.5	781.8	781.8	781.8	774.6



TEST NUMBER: P927113

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	887.8	903.1	900.5	893.2	887.8
115°	1006.5	1020.8	1016.4	1013.7	1006.5
117.5°	1124.2	1144.0	1131.4	1124.2	1117.0
120°	1242.8	1262.6	1242.8	1242.8	1234.8
122.5°	1350.6	1375.8	1363.2	1356.1	1350.6
125°	1463.9	1486.3	1479.2	1471.1	1468.4
127.5°	1574.4	1602.2	1592.4	1581.6	1574.4
130°	1677.7	1710.1	1705.6	1700.2	1690.4
132.5°	1793.7	1818.8	1820.6	1808.1	1800.8
135°	1893.4	1921.3	1926.7	1924.0	1916.8
137.5°	2004.9	2027.3	2031.8	2030.1	2019.2
140°	2102.8	2125.2	2137.9	2137.9	2128.0
142.5°	2203.5	2225.9	2233.1	2235.8	2225.9
145°	2298.7	2316.7	2331.1	2333.7	2323.8
147.5°	2384.1	2406.6	2417.3	2421.8	2412.0
150°	2472.2	2487.4	2497.3	2505.4	2497.3
152.5°	2550.3	2565.6	2578.2	2588.1	2578.2
155°	2628.5	2635.7	2643.8	2656.3	2648.2
157.5°	2695.9	2701.3	2705.8	2723.7	2711.2
160°	2756.2	2761.5	2764.2	2779.4	2768.7
162.5°	2811.9	2811.9	2814.5	2831.6	2819.0
165°	2859.5	2856.7	2856.7	2874.7	2862.2
167.5°	2902.6	2894.5	2894.5	2912.5	2899.9
170°	2934.9	2927.8	2925.0	2943.1	2927.8
172.5°	2957.4	2950.2	2947.5	2965.5	2950.2
175°	2975.4	2968.2	2962.8	2980.8	2965.5
177.5°	2985.3	2978.1	2972.6	2987.9	2972.6
180°	2980.8	2980.8	2980.8	2980.8	2980.8

TEST NUMBER: P927113

CATALOG NUMBER: DFN2DIP-HX4F0-100D100US830-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.75	11.57	11.72	12.55	13.84	6.72	7.55	7.70	8.53	9.82
	3H	12.43	13.16	13.41	14.15	15.46	7.91	8.65	8.90	9.64	10.95
	4H	13.04	13.73	14.03	14.73	16.04	8.36	9.06	9.36	10.05	11.37
	6H	13.46	14.10	14.47	15.10	16.43	8.69	9.33	9.69	10.33	11.66
	8H	13.59	14.19	14.60	15.21	16.54	8.78	9.39	9.79	10.40	11.73
	12H	13.65	14.23	14.67	15.24	16.59	8.82	9.40	9.84	10.41	11.76
4H	2H	10.77	11.46	11.77	12.46	13.78	7.32	8.01	8.32	9.01	10.33
	3H	12.60	13.18	13.61	14.20	15.53	8.67	9.25	9.68	10.27	11.60
	4H	13.29	13.82	14.31	14.83	16.19	9.22	9.75	10.24	10.76	12.12
	6H	13.81	14.26	14.84	15.30	16.65	9.64	10.09	10.67	11.13	12.48
	8H	13.98	14.41	15.01	15.44	16.80	9.77	10.19	10.80	11.23	12.59
	12H	14.08	14.46	15.13	15.51	16.88	9.84	10.22	10.88	11.26	12.64
8H	4H	13.26	13.68	14.29	14.71	16.08	9.50	9.92	10.53	10.95	12.32
	6H	13.83	14.18	14.88	15.25	16.61	10.02	10.37	11.07	11.44	12.81
	8H	14.04	14.35	15.10	15.41	16.79	10.21	10.52	11.27	11.58	12.96
	12H	14.18	14.45	15.25	15.51	16.93	10.33	10.60	11.40	11.66	13.08
12H	4H	13.21	13.59	14.26	14.64	16.01	9.50	9.89	10.55	10.93	12.30
	6H	13.80	14.11	14.86	15.17	16.55	10.07	10.38	11.13	11.44	12.82
	8H	14.02	14.29	15.09	15.35	16.77	10.28	10.55	11.35	11.61	13.03