

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928442

Luminaire Tested: DFN2DIP-HX4F0-110D090US927-RLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P928442
REPORT IS A COMBINATION OF REPORTS P900924 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D090US927-RLLONL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14461.9 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 180.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P928442

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US927-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P928442

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32
5	70	58	51	45	64	54	48	42	47	42	37	40	36	33	34	31	28
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2677	2677	2677
5°	2682	2635	2652
10°	2655	2584	2566
15°	2619	2499	2432
20°	2571	2381	2269
25°	2522	2249	2111
30°	2455	2114	1910
35°	2390	1969	1734
40°	2324	1819	1532
45°	2248	1652	1350
50°	2168	1484	1171
55°	2085	1303	999
60°	1990	1115	822
65°	1879	924	740
70°	1746	745	670
75°	1578	657	610
80°	1335	553	530
85°	933	370	399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2248 cd/sqm

TEST NUMBER: P928442

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US927-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	337.5	2.3
10°-20°	926.4	6.4
20°-30°	1300.6	9.0
30°-40°	1417.8	9.8
40°-50°	1303.1	9.0
50°-60°	1023.4	7.1
60°-70°	666.1	4.6
70°-80°	342.9	2.4
80°-90°	91.8	0.6
90°-100°	79.3	0.5
100°-110°	295.7	2.0
110°-120°	784.2	5.4
120°-130°	1300.7	9.0
130°-140°	1381.7	9.6
140°-150°	1284.1	8.9
150°-160°	1032.4	7.1
160°-170°	665.2	4.6
170°-180°	229.0	1.6
0°-30°	2564.5	17.7
0°-40°	3982.2	27.5
0°-60°	6308.7	43.6
0°-90°	7409.4	51.2
90°-120°	1159.3	8.0
90°-150°	5125.8	35.4
90°-180°	7052.0	48.8
0°-180°	14461.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3601	3601	3601	3601	3601	
5°	3601	3584	3542	3571	3562	341
15°	3425	3389	3278	3216	3184	965
25°	3109	3004	2789	2656	2607	1430
35°	2679	2512	2226	2020	1948	1677
45°	2190	1971	1629	1398	1320	1691
55°	1665	1411	1059	864	802	1488
65°	1124	860	567	456	446	1115
75°	600	371	261	238	235	634
85°	140	72	62	62	62	161
90°	2	21	35	44	47	14
95°	113	56	68	77	75	134
105°	529	582	106	125	132	565
115°	1001	1030	1074	268	143	985
125°	1415	1438	1471	1483	1488	1262
135°	1751	1779	1795	1812	1809	1353
145°	2032	2030	2059	2071	2063	1271
155°	2237	2221	2242	2252	2239	1031
165°	2357	2346	2352	2364	2352	666
175°	2411	2399	2402	2414	2397	229
180°	2406	2406	2406	2406	2406	

TEST NUMBER: P928442

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3600.7	3600.7	3600.7	3600.7	3600.7
2.5°	3616.9	3600.7	3564.7	3597.6	3591.0
5°	3600.7	3584.4	3541.9	3571.3	3561.6
7.5°	3571.3	3551.9	3506.3	3519.1	3502.8
10°	3532.2	3509.4	3444.4	3434.3	3415.0
12.5°	3483.5	3454.1	3365.9	3346.5	3310.6
15°	3424.7	3388.7	3278.1	3216.2	3183.7
17.5°	3356.3	3304.1	3167.1	3095.5	3043.3
20°	3278.1	3212.7	3049.9	2968.7	2896.7
22.5°	3193.4	3118.3	2929.3	2818.6	2769.9
25°	3108.7	3004.3	2789.3	2655.8	2606.7
27.5°	3007.8	2896.7	2658.9	2505.7	2430.7
30°	2900.2	2776.1	2515.5	2349.5	2261.3
32.5°	2795.8	2645.8	2378.9	2183.2	2101.7
35°	2678.6	2512.3	2225.8	2020.4	1948.5
37.5°	2564.6	2385.1	2082.2	1857.2	1776.0
40°	2443.9	2248.6	1932.2	1700.9	1616.2
42.5°	2320.1	2111.6	1782.6	1541.2	1460.0
45°	2189.8	1971.3	1629.4	1397.7	1319.6
47.5°	2066.0	1834.7	1482.8	1251.1	1179.6
50°	1929.1	1697.8	1339.4	1114.3	1046.2
52.5°	1795.3	1550.9	1202.4	987.4	925.5
55°	1664.9	1410.9	1058.9	863.6	801.7
57.5°	1531.6	1270.8	932.0	749.5	697.3
60°	1394.6	1134.0	798.3	632.3	580.1
62.5°	1261.2	1000.5	684.2	527.9	502.0
65°	1124.2	860.1	567.0	456.4	446.3
67.5°	994.0	729.8	456.4	400.7	391.0
70°	857.0	602.9	377.9	345.4	332.2
72.5°	726.7	485.4	316.0	290.0	283.5
75°	599.5	371.3	260.6	237.8	234.7
77.5°	472.6	263.8	205.4	192.2	185.6
80°	355.1	189.1	156.3	143.5	143.5
82.5°	247.5	127.2	107.6	101.0	101.0
85°	140.0	71.6	61.9	61.9	61.9
87.5°	52.2	25.9	25.9	22.8	22.8
90°	1.7	20.9	34.7	43.6	46.9
92.5°	43.6	36.6	41.7	45.3	46.9
95°	113.1	55.6	67.8	76.7	74.8
97.5°	203.6	61.0	88.7	94.0	95.7
100°	308.2	69.7	99.2	113.1	116.6
102.5°	422.9	419.6	102.7	121.7	127.1
105°	529.1	581.5	106.2	125.3	132.3
107.5°	652.8	696.2	109.8	128.8	135.8
110°	771.2	807.6	304.7	130.6	137.5

TEST NUMBER: P928442

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	882.6	913.8	884.3	133.9	139.3
115°	1000.9	1030.4	1074.0	268.1	142.8
117.5°	1103.6	1138.3	1168.0	919.0	463.0
120°	1218.5	1244.5	1276.0	1296.8	1061.8
122.5°	1315.9	1343.8	1378.7	1389.0	1390.9
125°	1415.1	1437.8	1470.9	1483.1	1488.2
127.5°	1505.6	1530.0	1556.3	1573.6	1575.3
130°	1591.0	1618.9	1637.9	1657.1	1655.5
132.5°	1678.0	1700.7	1719.7	1735.5	1733.8
135°	1751.2	1779.1	1794.6	1812.2	1808.7
137.5°	1827.7	1848.5	1866.1	1883.5	1878.3
140°	1902.5	1916.6	1935.6	1951.3	1942.6
142.5°	1965.3	1977.5	2000.0	2013.9	2005.3
145°	2031.5	2029.6	2059.2	2071.4	2062.7
147.5°	2088.7	2083.6	2113.1	2121.8	2115.0
150°	2144.6	2132.4	2160.3	2170.6	2161.9
152.5°	2191.5	2177.6	2203.7	2214.2	2202.0
155°	2236.8	2221.2	2242.1	2252.4	2238.6
157.5°	2273.4	2259.5	2275.2	2287.4	2273.4
160°	2304.7	2294.2	2304.7	2315.1	2302.9
162.5°	2332.4	2322.1	2330.8	2343.0	2327.3
165°	2356.8	2346.5	2351.7	2363.9	2351.7
167.5°	2376.1	2365.5	2370.9	2383.0	2367.4
170°	2391.8	2381.2	2384.7	2396.9	2381.2
172.5°	2402.1	2391.8	2395.2	2407.4	2391.8
175°	2410.8	2398.6	2402.1	2414.3	2396.9
177.5°	2414.3	2402.1	2404.0	2416.2	2400.5
180°	2405.6	2405.6	2405.6	2405.6	2405.6

TEST NUMBER: P928442

CATALOG NUMBER: DFN2DIP-HX4F0-110D090US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.68	11.52	11.64	12.49	13.75	6.66	7.50	7.61	8.46	9.72
	3H	12.36	13.12	13.33	14.09	15.37	7.85	8.60	8.81	9.57	10.85
	4H	12.97	13.68	13.95	14.66	15.95	8.30	9.01	9.28	9.99	11.28
	6H	13.40	14.05	14.39	15.03	16.33	8.62	9.28	9.61	10.26	11.56
	8H	13.52	14.15	14.52	15.14	16.44	8.72	9.34	9.71	10.34	11.63
	12H	13.59	14.18	14.59	15.17	16.49	8.76	9.35	9.76	10.34	11.67
4H	2H	10.70	11.41	11.69	12.39	13.68	7.25	7.96	8.24	8.94	10.23
	3H	12.54	13.13	13.53	14.13	15.43	8.61	9.20	9.60	10.21	11.51
	4H	13.23	13.77	14.23	14.77	16.09	9.16	9.70	10.16	10.70	12.02
	6H	13.75	14.21	14.76	15.23	16.56	9.58	10.04	10.59	11.07	12.39
	8H	13.92	14.35	14.94	15.37	16.71	9.71	10.14	10.72	11.16	12.50
	12H	14.02	14.41	15.05	15.44	16.78	9.78	10.17	10.81	11.20	12.54
8H	4H	13.20	13.63	14.21	14.65	15.98	9.44	9.87	10.45	10.89	12.22
	6H	13.77	14.12	14.80	15.18	16.52	9.96	10.32	11.00	11.38	12.71
	8H	13.98	14.30	15.03	15.34	16.70	10.15	10.47	11.20	11.51	12.87
	12H	14.12	14.40	15.17	15.44	16.84	10.27	10.55	11.32	11.59	12.99
12H	4H	13.15	13.54	14.18	14.57	15.91	9.44	9.83	10.48	10.87	12.21
	6H	13.74	14.06	14.79	15.10	16.45	10.01	10.32	11.06	11.37	12.72
	8H	13.96	14.24	15.01	15.28	16.68	10.22	10.50	11.27	11.54	12.94