

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927115

Luminaire Tested: DFN2DIP-HX4F0-100D110US830-FLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927115
REPORT IS A COMBINATION OF REPORTS P899437 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D110US830-FLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18506.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 186.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927115

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927115

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	57	57	57
1	98	94	90	86	90	86	83	80	73	71	69	61	59	58	50	49	48
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40
3	81	72	64	59	75	67	60	55	57	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	30
5	68	57	49	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	25	46	36	29	24	31	25	22	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2727	2727	2727
5°	2732	2689	2707
10°	2710	2653	2671
15°	2670	2610	2614
20°	2616	2549	2555
25°	2563	2477	2487
30°	2496	2410	2401
35°	2433	2330	2310
40°	2355	2250	2224
45°	2277	2170	2135
50°	2192	2086	2032
55°	2103	1988	1938
60°	2002	1872	1830
65°	1893	1753	1703
70°	1753	1606	1566
75°	1559	1432	1439
80°	1327	1209	1197
85°	963	824	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2472 cd/sqm

TEST NUMBER: P927115

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.2	1.9
10°-20°	971.2	5.2
20°-30°	1427.2	7.7
30°-40°	1657.6	9.0
40°-50°	1655.6	8.9
50°-60°	1443.6	7.8
60°-70°	1067.2	5.8
70°-80°	603.8	3.3
80°-90°	168.7	0.9
90°-100°	202.9	1.1
100°-110°	644.7	3.5
110°-120°	1103.2	6.0
120°-130°	1450.9	7.8
130°-140°	1628.6	8.8
140°-150°	1597.0	8.6
150°-160°	1339.7	7.2
160°-170°	888.4	4.8
170°-180°	310.5	1.7
0°-30°	2743.6	14.8
0°-40°	4401.2	23.8
0°-60°	7500.4	40.5
0°-90°	9340.1	50.5
90°-120°	1950.8	10.5
90°-150°	6627.3	35.8
90°-180°	9166.0	49.5
0°-180°	18506.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3654	3615	3643	3636	348
15°	3491	3470	3424	3438	3421	983
25°	3160	3132	3072	3078	3072	1454
35°	2726	2691	2634	2613	2595	1702
45°	2218	2194	2140	2102	2088	1712
55°	1679	1658	1615	1573	1555	1501
65°	1132	1111	1076	1044	1026	1119
75°	592	586	568	547	554	632
85°	144	141	138	127	124	161
90°	3	36	97	91	94	18
95°	144	172	177	177	172	161
105°	595	603	609	614	614	628
115°	1107	1123	1118	1115	1107	1095
125°	1610	1635	1627	1618	1615	1439
135°	2083	2113	2119	2116	2108	1610
145°	2528	2548	2564	2567	2556	1580
155°	2891	2899	2908	2922	2913	1331
165°	3145	3142	3142	3162	3148	887
175°	3273	3265	3259	3279	3262	311
180°	3279	3279	3279	3279	3279	

TEST NUMBER: P927115

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US830-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3667.4	3667.4	3667.4	3667.4	3667.4
2.5°	3688.7	3671.0	3632.1	3667.4	3660.6
5°	3667.4	3653.5	3614.6	3642.7	3635.9
7.5°	3642.7	3621.7	3582.7	3611.2	3604.1
10°	3604.1	3579.4	3537.1	3565.2	3554.7
12.5°	3551.0	3530.0	3487.7	3505.3	3498.2
15°	3491.1	3470.2	3424.1	3438.3	3420.8
17.5°	3417.0	3396.1	3350.0	3367.6	3350.0
20°	3335.8	3314.9	3265.5	3275.9	3262.1
22.5°	3255.0	3223.3	3177.2	3177.2	3170.1
25°	3159.6	3131.6	3071.7	3078.4	3071.7
27.5°	3053.7	3029.0	2983.4	2972.9	2955.3
30°	2948.2	2919.8	2867.0	2856.5	2842.3
32.5°	2835.2	2814.3	2757.8	2736.5	2722.2
35°	2726.0	2690.8	2634.3	2613.0	2595.4
37.5°	2602.5	2570.7	2514.2	2489.5	2471.9
40°	2475.7	2447.2	2390.7	2359.4	2345.1
42.5°	2352.2	2323.7	2267.7	2232.1	2211.2
45°	2218.3	2193.6	2140.4	2101.9	2087.7
47.5°	2087.7	2063.0	2006.5	1967.6	1946.6
50°	1950.0	1932.4	1883.0	1833.6	1816.1
52.5°	1816.1	1791.4	1745.7	1706.9	1682.2
55°	1678.8	1657.5	1615.2	1572.8	1555.3
57.5°	1541.1	1523.5	1477.5	1435.2	1421.0
60°	1403.4	1389.5	1340.1	1301.2	1290.8
62.5°	1269.5	1244.8	1209.6	1174.4	1160.2
65°	1132.1	1110.8	1075.7	1043.8	1026.3
67.5°	991.1	973.1	941.7	917.1	902.8
70°	860.5	846.3	814.5	789.8	776.0
72.5°	726.6	712.3	694.8	670.1	659.6
75°	592.3	585.6	567.6	546.6	553.7
77.5°	472.6	458.3	451.2	440.7	430.3
80°	352.8	349.1	341.9	331.5	324.4
82.5°	239.9	239.9	236.5	222.2	222.2
85°	144.4	141.1	137.7	126.9	123.5
87.5°	63.6	56.5	49.4	38.9	35.2
90°	2.9	35.6	96.9	91.0	93.9
92.5°	61.3	83.0	86.0	89.0	89.0
95°	144.3	172.0	176.9	176.9	172.0
97.5°	240.2	265.9	276.8	276.8	276.8
100°	350.9	373.6	381.5	381.5	378.6
102.5°	467.6	484.4	495.3	498.2	495.3
105°	595.1	603.0	608.9	613.9	613.9
107.5°	721.6	733.5	733.5	735.4	721.6
110°	844.2	860.0	860.0	860.0	852.1

TEST NUMBER: P927115

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	976.6	993.4	990.5	982.6	976.6
115°	1107.2	1122.9	1118.0	1115.1	1107.2
117.5°	1236.7	1258.3	1244.5	1236.7	1228.7
120°	1367.1	1388.9	1367.1	1367.1	1358.2
122.5°	1485.8	1513.4	1499.5	1491.6	1485.8
125°	1610.3	1635.0	1627.0	1618.2	1615.2
127.5°	1731.8	1762.5	1751.6	1739.8	1731.8
130°	1845.5	1881.1	1876.1	1870.2	1859.4
132.5°	1973.0	2000.7	2002.7	1988.9	1980.9
135°	2082.7	2113.4	2119.3	2116.4	2108.5
137.5°	2205.4	2230.0	2235.0	2233.0	2221.2
140°	2313.1	2337.8	2351.6	2351.6	2340.8
142.5°	2423.8	2448.5	2456.4	2459.4	2448.5
145°	2528.5	2548.3	2564.2	2567.1	2556.2
147.5°	2622.5	2647.2	2659.1	2664.0	2653.1
150°	2719.4	2736.2	2747.0	2756.0	2747.0
152.5°	2805.4	2822.1	2836.0	2846.9	2836.0
155°	2891.4	2899.2	2908.2	2922.0	2913.1
157.5°	2965.5	2971.4	2976.3	2996.1	2982.3
160°	3031.7	3037.7	3040.6	3057.5	3045.6
162.5°	3093.0	3093.0	3096.0	3114.8	3100.9
165°	3145.4	3142.4	3142.4	3162.2	3148.3
167.5°	3192.8	3184.0	3184.0	3203.7	3189.9
170°	3228.4	3220.5	3217.6	3237.3	3220.5
172.5°	3253.1	3245.2	3242.3	3262.1	3245.2
175°	3272.9	3265.0	3259.1	3278.9	3262.1
177.5°	3283.8	3275.8	3269.9	3286.8	3269.9
180°	3278.9	3278.9	3278.9	3278.9	3278.9

TEST NUMBER: P927115

CATALOG NUMBER: DFN2DIP-HX4F0-100D110US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.80	11.67	11.75	12.63	13.90	10.37	11.23	11.32	12.20	13.47
	3H	12.46	13.24	13.43	14.22	15.50	11.99	12.77	12.95	13.74	15.03
	4H	13.05	13.79	14.03	14.77	16.06	12.58	13.31	13.55	14.29	15.59
	6H	13.45	14.13	14.44	15.12	16.42	12.98	13.65	13.96	14.64	15.95
	8H	13.56	14.20	14.55	15.21	16.51	13.08	13.73	14.08	14.73	16.03
	12H	13.61	14.22	14.61	15.22	16.55	13.12	13.74	14.12	14.74	16.07
4H	2H	11.26	12.00	12.25	12.98	14.28	10.92	11.65	11.90	12.64	13.93
	3H	13.13	13.74	14.12	14.76	16.06	12.74	13.35	13.73	14.36	15.67
	4H	13.85	14.41	14.85	15.41	16.74	13.44	14.00	14.44	15.01	16.34
	6H	14.36	14.85	15.38	15.87	17.20	13.95	14.44	14.97	15.46	16.79
	8H	14.51	14.96	15.53	15.98	17.33	14.10	14.55	15.11	15.57	16.92
	12H	14.59	14.99	15.62	16.03	17.38	14.16	14.57	15.20	15.61	16.96
8H	4H	14.04	14.49	15.06	15.52	16.86	13.68	14.13	14.70	15.16	16.50
	6H	14.68	15.05	15.72	16.11	17.46	14.31	14.69	15.35	15.75	17.09
	8H	14.90	15.23	15.95	16.28	17.64	14.53	14.86	15.58	15.91	17.27
	12H	15.03	15.32	16.08	16.36	17.77	14.65	14.93	15.70	15.98	17.38
12H	4H	14.03	14.44	15.06	15.47	16.82	13.68	14.09	14.71	15.12	16.47
	6H	14.71	15.04	15.75	16.08	17.45	14.35	14.68	15.40	15.73	17.09
	8H	14.95	15.24	16.00	16.28	17.69	14.59	14.88	15.64	15.92	17.33

END OF REPORT