

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927120

Luminaire Tested: DFN2DIP-HX4F0-100D120US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927120
REPORT IS A COMBINATION OF REPORTS P900975 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-100D120US830-FLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 20527.7 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 195.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.946
Total Harmonic Distortion (THDi): 0.132
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927120
CATALOG NUMBER: DFN2DIP-HX4F0-100D120US830-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P927120

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45	45	45	45
1	97	92	89	85	89	85	82	79	71	68	66	58	56	55	46	45	44	38	38	38	38
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	39	37	32	32	32	32
3	80	71	64	58	73	65	59	54	55	50	46	45	42	39	36	33	31	27	27	27	27
4	74	63	55	49	67	58	51	46	49	43	39	40	36	33	32	29	27	23	23	23	23
5	67	56	48	42	62	52	45	39	43	38	34	36	32	29	29	26	24	20	20	20	20
6	62	50	42	36	57	46	39	34	39	34	30	32	28	25	26	23	21	18	18	18	18
7	57	45	37	32	53	42	35	30	35	30	26	30	25	22	24	21	18	16	16	16	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	17	14	14	14	14
9	50	37	30	25	45	35	28	24	30	24	21	25	21	18	20	17	15	13	13	13	13
10	46	34	27	22	42	32	25	21	27	22	19	23	19	16	19	16	14	12	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2727	2727	2727
5°	2732	2689	2707
10°	2710	2653	2671
15°	2670	2610	2614
20°	2616	2549	2555
25°	2563	2477	2487
30°	2496	2410	2401
35°	2433	2330	2310
40°	2355	2250	2224
45°	2277	2170	2135
50°	2192	2086	2032
55°	2103	1988	1938
60°	2002	1872	1830
65°	1893	1753	1703
70°	1753	1606	1566
75°	1559	1432	1439
80°	1327	1209	1197
85°	963	824	797

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2277 cd/sqm



TEST NUMBER: P927120

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	345.2	1.7
10°-20°	971.2	4.7
20°-30°	1427.2	7.0
30°-40°	1657.6	8.1
40°-50°	1655.6	8.1
50°-60°	1443.6	7.0
60°-70°	1067.2	5.2
70°-80°	603.8	2.9
80°-90°	166.1	0.8
90°-100°	125.9	0.6
100°-110°	469.2	2.3
110°-120°	1244.4	6.1
120°-130°	2063.9	10.1
130°-140°	2192.3	10.7
140°-150°	2037.5	9.9
150°-160°	1638.1	8.0
160°-170°	1055.6	5.1
170°-180°	363.3	1.8
0°-30°	2743.6	13.4
0°-40°	4401.2	21.4
0°-60°	7500.4	36.5
0°-90°	9337.5	45.5
90°-120°	1839.4	9.0
90°-150°	8133.2	39.6
90°-180°	11190.0	54.5
0°-180°	20527.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3654	3615	3643	3636	348
15°	3491	3470	3424	3438	3421	983
25°	3160	3132	3072	3078	3072	1454
35°	2726	2691	2634	2613	2595	1702
45°	2218	2194	2140	2102	2088	1712
55°	1679	1658	1615	1573	1555	1501
65°	1132	1111	1076	1044	1026	1119
75°	592	586	568	547	554	632
85°	144	141	138	127	124	161
90°	3	33	55	69	74	19
95°	179	88	108	122	119	212
105°	840	923	169	199	210	897
115°	1588	1635	1704	425	227	1563
125°	2245	2281	2334	2353	2361	2003
135°	2779	2823	2848	2875	2870	2146
145°	3223	3220	3267	3287	3273	2016
155°	3549	3524	3558	3574	3552	1635
165°	3740	3723	3731	3751	3731	1057
175°	3825	3806	3811	3831	3803	364
180°	3817	3817	3817	3817	3817	



TEST NUMBER: P927120

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3667.4	3667.4	3667.4	3667.4	3667.4
2.5°	3688.7	3671.0	3632.1	3667.4	3660.6
5°	3667.4	3653.5	3614.6	3642.7	3635.9
7.5°	3642.7	3621.7	3582.7	3611.2	3604.1
10°	3604.1	3579.4	3537.1	3565.2	3554.7
12.5°	3551.0	3530.0	3487.7	3505.3	3498.2
15°	3491.1	3470.2	3424.1	3438.3	3420.8
17.5°	3417.0	3396.1	3350.0	3367.6	3350.0
20°	3335.8	3314.9	3265.5	3275.9	3262.1
22.5°	3255.0	3223.3	3177.2	3177.2	3170.1
25°	3159.6	3131.6	3071.7	3078.4	3071.7
27.5°	3053.7	3029.0	2983.4	2972.9	2955.3
30°	2948.2	2919.8	2867.0	2856.5	2842.3
32.5°	2835.2	2814.3	2757.8	2736.5	2722.2
35°	2726.0	2690.8	2634.3	2613.0	2595.4
37.5°	2602.5	2570.7	2514.2	2489.5	2471.9
40°	2475.7	2447.2	2390.7	2359.4	2345.1
42.5°	2352.2	2323.7	2267.7	2232.1	2211.2
45°	2218.3	2193.6	2140.4	2101.9	2087.7
47.5°	2087.7	2063.0	2006.5	1967.6	1946.6
50°	1950.0	1932.4	1883.0	1833.6	1816.1
52.5°	1816.1	1791.4	1745.7	1706.9	1682.2
55°	1678.8	1657.5	1615.2	1572.8	1555.3
57.5°	1541.1	1523.5	1477.5	1435.2	1421.0
60°	1403.4	1389.5	1340.1	1301.2	1290.8
62.5°	1269.5	1244.8	1209.6	1174.4	1160.2
65°	1132.1	1110.8	1075.7	1043.8	1026.3
67.5°	991.1	973.1	941.7	917.1	902.8
70°	860.5	846.3	814.5	789.8	776.0
72.5°	726.6	712.3	694.8	670.1	659.6
75°	592.3	585.6	567.6	546.6	553.7
77.5°	472.6	458.3	451.2	440.7	430.3
80°	352.8	349.1	341.9	331.5	324.4
82.5°	239.9	239.9	236.5	222.2	222.2
85°	144.4	141.1	137.7	126.9	123.5
87.5°	63.6	56.5	49.4	38.9	35.2
90°	2.6	33.1	55.1	69.2	74.5
92.5°	69.2	58.1	66.3	71.8	74.5
95°	179.4	88.2	107.5	121.7	118.8
97.5°	323.1	96.8	140.7	149.2	151.8
100°	489.0	110.6	157.4	179.4	185.0
102.5°	671.1	665.8	163.0	193.2	201.7
105°	839.6	922.6	168.6	198.8	209.9
107.5°	1035.7	1104.6	174.2	204.3	215.5
110°	1223.6	1281.4	483.4	207.3	218.1



TEST NUMBER: P927120

CATALOG NUMBER: DFN2DIP-HX4F0-100D120US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1400.5	1449.9	1403.1	212.5	221.0
115°	1588.0	1635.0	1704.1	425.4	226.7
117.5°	1751.1	1806.2	1853.4	1458.1	734.7
120°	1933.4	1974.7	2024.6	2057.8	1684.8
122.5°	2087.9	2132.2	2187.6	2204.0	2207.0
125°	2245.3	2281.4	2333.9	2353.2	2361.4
127.5°	2389.0	2427.7	2469.4	2496.9	2499.5
130°	2524.4	2568.7	2598.8	2629.4	2626.7
132.5°	2662.5	2698.6	2728.7	2753.7	2751.1
135°	2778.6	2822.9	2847.5	2875.4	2869.8
137.5°	2900.0	2933.1	2961.0	2988.5	2980.3
140°	3018.7	3041.0	3071.1	3096.1	3082.4
142.5°	3118.4	3137.8	3173.5	3195.5	3181.7
145°	3223.4	3220.4	3267.3	3286.7	3272.8
147.5°	3314.2	3306.0	3352.9	3366.7	3355.9
150°	3402.7	3383.4	3427.7	3444.1	3430.3
152.5°	3477.2	3455.2	3496.6	3513.3	3493.9
155°	3549.0	3524.4	3557.6	3574.0	3552.0
157.5°	3607.0	3585.1	3610.1	3629.4	3607.0
160°	3656.9	3640.2	3656.9	3673.3	3654.0
162.5°	3700.9	3684.5	3698.3	3717.6	3692.7
165°	3739.6	3723.2	3731.4	3750.8	3731.4
167.5°	3770.1	3753.3	3761.9	3781.2	3756.3
170°	3795.0	3778.3	3783.9	3803.2	3778.3
172.5°	3811.4	3795.0	3800.6	3820.0	3795.0
175°	3825.1	3805.8	3811.4	3830.8	3803.2
177.5°	3830.8	3811.4	3814.4	3833.7	3808.8
180°	3817.0	3817.0	3817.0	3817.0	3817.0



TEST NUMBER: P927120
 CATALOG NUMBER: DFN2DIP-HX4F0-100D120US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.33	11.15	11.32	12.15	13.49	9.89	10.72	10.89	11.72	13.06
	3H	11.98	12.72	12.99	13.74	15.09	11.51	12.25	12.52	13.26	14.62
	4H	12.57	13.27	13.59	14.29	15.65	12.10	12.80	13.12	13.81	15.18
	6H	12.97	13.61	14.00	14.64	16.01	12.49	13.14	13.52	14.16	15.53
	8H	13.07	13.69	14.11	14.73	16.10	12.60	13.21	13.63	14.25	15.62
	12H	13.12	13.70	14.16	14.74	16.13	12.64	13.22	13.68	14.25	15.65
4H	2H	10.78	11.48	11.81	12.50	13.86	10.44	11.14	11.46	12.16	13.52
	3H	12.65	13.23	13.68	14.28	15.65	12.25	12.84	13.29	13.88	15.26
	4H	13.36	13.89	14.40	14.93	16.33	12.95	13.49	13.99	14.53	15.93
	6H	13.87	14.33	14.92	15.40	16.79	13.46	13.92	14.51	14.99	16.38
	8H	14.02	14.45	15.08	15.51	16.92	13.61	14.04	14.66	15.09	16.50
	12H	14.10	14.48	15.16	15.55	16.97	13.67	14.06	14.74	15.13	16.54
8H	4H	13.55	13.98	14.61	15.04	16.45	13.19	13.62	14.25	14.68	16.09
	6H	14.19	14.54	15.26	15.64	17.04	13.82	14.18	14.90	15.27	16.68
	8H	14.41	14.72	15.49	15.80	17.23	14.04	14.35	15.12	15.43	16.86
	12H	14.54	14.81	15.62	15.89	17.35	14.15	14.43	15.24	15.50	16.97
12H	4H	13.54	13.93	14.61	15.00	16.41	13.19	13.57	14.26	14.64	16.06
	6H	14.22	14.53	15.30	15.61	17.03	13.86	14.18	14.95	15.26	16.68
	8H	14.46	14.73	15.54	15.81	17.27	14.10	14.37	15.18	15.45	16.92