

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927152

Luminaire Tested: DFN2DIP-HX4F0-110D110US830-FLLONL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927152
REPORT IS A COMBINATION OF REPORTS P900959 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-110D110US830-FLLONL
Description: 4 foot, Hexagon Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 20527.6 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 199.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9967
Total Harmonic Distortion (THDi): 0.063
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927152

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P927152

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US830-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	90	86	90	86	83	80	73	71	68	61	59	58	50	48	47
2	89	82	75	70	82	76	70	66	64	60	57	53	51	48	44	42	40
3	81	72	64	59	75	66	60	55	56	52	48	47	44	41	39	36	34
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	35	32	29
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	31	28	26
6	63	51	43	37	58	47	40	35	40	35	31	34	30	27	28	25	23
7	58	46	38	32	53	43	36	30	37	31	27	31	27	23	26	23	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3000	3000	3000
5°	3005	2958	2978
10°	2980	2919	2938
15°	2937	2871	2875
20°	2878	2804	2811
25°	2819	2725	2736
30°	2746	2651	2641
35°	2676	2563	2541
40°	2590	2475	2446
45°	2505	2387	2349
50°	2411	2294	2236
55°	2313	2187	2132
60°	2202	2059	2013
65°	2082	1928	1873
70°	1928	1767	1722
75°	1715	1575	1583
80°	1459	1330	1317
85°	1059	906	876

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2505 cd/sqm

TEST NUMBER: P927152

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US830-FLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	379.7	1.8
10°-20°	1068.3	5.2
20°-30°	1570.0	7.6
30°-40°	1823.4	8.9
40°-50°	1821.2	8.9
50°-60°	1588.0	7.7
60°-70°	1173.9	5.7
70°-80°	664.1	3.2
80°-90°	181.4	0.9
90°-100°	115.4	0.6
100°-110°	430.1	2.1
110°-120°	1140.7	5.6
120°-130°	1891.9	9.2
130°-140°	2009.6	9.8
140°-150°	1867.7	9.1
150°-160°	1501.6	7.3
160°-170°	967.6	4.7
170°-180°	333.0	1.6
0°-30°	3017.9	14.7
0°-40°	4841.4	23.6
0°-60°	8250.5	40.2
0°-90°	10270.0	50.0
90°-120°	1686.2	8.2
90°-150°	7455.4	36.3
90°-180°	10258.0	50.0
0°-180°	20527.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4034	4034	4034	4034	4034	
5°	4034	4019	3976	4007	4000	383
15°	3840	3817	3766	3782	3763	1082
25°	3476	3445	3379	3386	3379	1599
35°	2999	2960	2898	2874	2855	1872
45°	2440	2413	2354	2312	2296	1883
55°	1847	1823	1777	1730	1711	1651
65°	1245	1222	1183	1148	1129	1231
75°	652	644	624	601	609	695
85°	159	155	152	140	136	177
90°	2	30	50	63	68	19
95°	164	81	99	112	109	195
105°	770	846	155	182	192	822
115°	1456	1499	1562	390	208	1433
125°	2058	2091	2139	2157	2165	1836
135°	2547	2588	2610	2636	2631	1968
145°	2955	2952	2995	3013	3000	1848
155°	3253	3231	3261	3276	3256	1499
165°	3428	3413	3420	3438	3420	968
175°	3506	3489	3494	3512	3486	334
180°	3499	3499	3499	3499	3499	

TEST NUMBER: P927152

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4034.1	4034.1	4034.1	4034.1	4034.1
2.5°	4057.5	4038.1	3995.4	4034.1	4026.6
5°	4034.1	4018.8	3976.0	4006.9	3999.5
7.5°	4006.9	3983.9	3941.1	3972.4	3964.5
10°	3964.5	3937.3	3890.8	3921.6	3910.1
12.5°	3906.1	3883.0	3836.5	3855.9	3848.0
15°	3840.2	3817.1	3766.5	3782.2	3762.8
17.5°	3758.7	3735.7	3685.1	3704.4	3685.1
20°	3669.4	3646.3	3592.1	3603.6	3588.4
22.5°	3580.6	3545.5	3494.9	3494.9	3487.1
25°	3475.6	3444.7	3378.9	3386.3	3378.9
27.5°	3359.1	3331.9	3281.7	3270.2	3250.9
30°	3243.0	3211.8	3153.7	3142.2	3126.6
32.5°	3118.7	3095.7	3033.5	3010.1	2994.4
35°	2998.6	2959.9	2897.7	2874.2	2854.9
37.5°	2862.7	2827.8	2765.7	2738.4	2719.1
40°	2723.3	2692.0	2629.9	2595.3	2579.6
42.5°	2587.4	2556.2	2494.4	2455.3	2432.3
45°	2440.1	2412.9	2354.5	2312.1	2296.5
47.5°	2296.5	2269.4	2207.1	2164.4	2141.3
50°	2145.0	2125.7	2071.3	2017.0	1997.7
52.5°	1997.7	1970.5	1920.3	1877.5	1850.3
55°	1846.6	1823.2	1776.7	1730.1	1710.8
57.5°	1695.2	1675.9	1625.2	1578.7	1563.0
60°	1543.7	1528.5	1474.2	1431.4	1419.9
62.5°	1396.4	1369.3	1330.5	1291.9	1276.2
65°	1245.3	1221.9	1183.2	1148.2	1128.9
67.5°	1090.2	1070.5	1035.9	1008.8	993.1
70°	946.6	930.9	895.9	868.8	853.5
72.5°	799.2	783.6	764.3	737.1	725.5
75°	651.5	644.1	624.3	601.3	609.1
77.5°	519.8	504.1	496.3	484.8	473.3
80°	388.1	384.0	376.2	364.7	356.8
82.5°	263.8	263.8	260.1	244.5	244.5
85°	158.9	155.1	151.5	139.5	135.8
87.5°	69.9	62.1	54.3	42.8	38.6
90°	2.5	30.3	50.5	63.4	68.2
92.5°	63.4	53.3	60.7	65.9	68.2
95°	164.5	80.9	98.6	111.5	108.9
97.5°	296.1	88.7	128.9	136.8	139.2
100°	448.3	101.3	144.3	164.5	169.6
102.5°	615.1	610.3	149.4	177.1	184.9
105°	769.6	845.7	154.6	182.2	192.5
107.5°	949.5	1012.5	159.7	187.3	197.5
110°	1121.7	1174.6	443.2	190.0	199.9

TEST NUMBER: P927152

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1283.8	1329.1	1286.1	194.8	202.6
115°	1455.7	1498.7	1562.2	389.9	207.7
117.5°	1605.2	1655.7	1699.0	1336.7	673.4
120°	1772.3	1810.2	1855.9	1886.2	1544.4
122.5°	1913.9	1954.5	2005.3	2020.3	2023.1
125°	2058.2	2091.3	2139.4	2157.1	2164.6
127.5°	2189.9	2225.3	2263.5	2288.8	2291.2
130°	2314.0	2354.6	2382.3	2410.3	2407.9
132.5°	2440.6	2473.7	2501.4	2524.2	2521.8
135°	2547.1	2587.6	2610.2	2635.8	2630.6
137.5°	2658.3	2688.7	2714.2	2739.5	2731.9
140°	2767.2	2787.5	2815.2	2838.1	2825.4
142.5°	2858.5	2876.2	2909.0	2929.2	2916.6
145°	2954.7	2952.0	2995.0	3012.8	3000.2
147.5°	3038.1	3030.5	3073.5	3086.1	3076.2
150°	3119.2	3101.5	3142.0	3157.1	3144.5
152.5°	3187.4	3167.3	3205.2	3220.5	3202.8
155°	3253.3	3230.7	3261.0	3276.1	3256.0
157.5°	3306.5	3286.3	3309.2	3326.9	3306.5
160°	3352.2	3336.8	3352.2	3367.2	3349.5
162.5°	3392.4	3377.4	3390.1	3407.8	3385.0
165°	3428.0	3412.9	3420.4	3438.1	3420.4
167.5°	3455.9	3440.6	3448.4	3466.1	3443.3
170°	3478.8	3463.4	3468.5	3486.3	3463.4
172.5°	3493.8	3478.8	3483.9	3501.6	3478.8
175°	3506.4	3488.7	3493.8	3511.6	3486.3
177.5°	3511.6	3493.8	3496.5	3514.2	3491.4
180°	3498.9	3498.9	3498.9	3498.9	3498.9

TEST NUMBER: P927152

CATALOG NUMBER: DFN2DIP-HX4F0-110D110US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.09	11.95	12.05	12.93	14.20	10.66	11.52	11.62	12.49	13.76
	3H	12.75	13.53	13.72	14.51	15.80	12.28	13.05	13.25	14.03	15.33
	4H	13.34	14.07	14.32	15.06	16.36	12.87	13.60	13.85	14.58	15.89
	6H	13.74	14.42	14.74	15.41	16.72	13.27	13.94	14.26	14.93	16.25
	8H	13.85	14.49	14.85	15.50	16.81	13.37	14.01	14.37	15.02	16.33
	12H	13.90	14.51	14.90	15.51	16.84	13.41	14.03	14.42	15.03	16.36
4H	2H	11.55	12.29	12.54	13.27	14.57	11.21	11.94	12.20	12.93	14.23
	3H	13.42	14.03	14.42	15.05	16.36	13.03	13.64	14.03	14.65	15.97
	4H	14.14	14.70	15.14	15.70	17.04	13.73	14.29	14.74	15.30	16.64
	6H	14.65	15.13	15.67	16.16	17.50	14.24	14.72	15.26	15.75	17.09
	8H	14.80	15.25	15.82	16.28	17.63	14.39	14.84	15.41	15.86	17.21
	12H	14.88	15.28	15.91	16.32	17.68	14.45	14.86	15.49	15.90	17.26
8H	4H	14.33	14.78	15.35	15.81	17.16	13.97	14.42	14.99	15.45	16.80
	6H	14.97	15.34	16.01	16.40	17.75	14.60	14.98	15.65	16.04	17.39
	8H	15.19	15.52	16.24	16.57	17.93	14.82	15.15	15.87	16.20	17.56
	12H	15.32	15.61	16.37	16.65	18.06	14.94	15.22	15.99	16.27	17.68
12H	4H	14.32	14.73	15.36	15.77	17.12	13.97	14.37	15.00	15.41	16.77
	6H	15.00	15.32	16.05	16.38	17.74	14.65	14.97	15.70	16.02	17.39
	8H	15.24	15.53	16.29	16.57	17.98	14.88	15.17	15.94	16.22	17.63