

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P927189

Luminaire Tested: DFN2DIP-HX4F0-120D110US830-RLLFLL

Issue Date: 12/12/2024

Test Information

Test Method: LM-79-2019
Report Number: P927189
REPORT IS A COMBINATION OF REPORTS P899442 AND P896187
Test Lab: INNOVATION CENTER
Issue Date: 12/12/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-HX4F0-120D110US830-RLLFLL
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 18788.7 lumens
Efficiency: N/A
Efficacy: 88.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 213.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9954
Total Harmonic Distortion (THDi): 0.076
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P927189

CATALOG NUMBER: DFN2DIP-HX4F0-120D110US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P927189

CATALOG NUMBER: DFN2DIP-HX4F0-120D110US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57
1	99	94	91	87	91	87	84	81	74	72	70	62	61	59	51	50	49
2	90	83	77	72	83	77	72	68	66	62	59	55	53	50	46	44	42
3	83	73	66	61	76	68	62	57	58	54	50	49	46	43	41	39	37
4	76	65	58	52	70	61	54	49	52	47	43	44	41	37	37	34	32
5	70	58	51	45	64	54	47	42	47	42	37	40	36	33	34	31	28
6	64	53	45	39	59	49	42	37	43	37	33	36	32	29	31	27	25
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22
8	55	43	36	31	51	41	34	29	35	30	26	31	26	23	26	23	20
9	52	40	32	27	48	37	31	26	33	27	24	28	24	21	24	21	18
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3476	3476	3476
5°	3482	3421	3443
10°	3447	3354	3331
15°	3400	3244	3158
20°	3338	3091	2945
25°	3274	2920	2740
30°	3188	2745	2480
35°	3103	2556	2252
40°	3018	2361	1989
45°	2918	2144	1752
50°	2815	1926	1520
55°	2708	1692	1297
60°	2583	1448	1068
65°	2440	1199	961
70°	2267	968	870
75°	2049	854	792
80°	1734	717	687
85°	1212	480	518

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2918 cd/sqm

TEST NUMBER: P927189

CATALOG NUMBER: DFN2DIP-HX4F0-120D110US830-RLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	2.3
10°-20°	1202.7	6.4
20°-30°	1688.5	9.0
30°-40°	1840.5	9.8
40°-50°	1691.7	9.0
50°-60°	1328.5	7.1
60°-70°	864.8	4.6
70°-80°	445.1	2.4
80°-90°	122.9	0.7
90°-100°	202.9	1.1
100°-110°	644.7	3.4
110°-120°	1103.2	5.9
120°-130°	1450.9	7.7
130°-140°	1628.6	8.7
140°-150°	1597.0	8.5
150°-160°	1339.7	7.1
160°-170°	888.4	4.7
170°-180°	310.5	1.7
0°-30°	3329.2	17.7
0°-40°	5169.8	27.5
0°-60°	8190.0	43.6
0°-90°	9622.8	51.2
90°-120°	1950.8	10.4
90°-150°	6627.3	35.3
90°-180°	9166.0	48.8
0°-180°	18788.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4674	4674	4674	4674	4674	
5°	4674	4653	4598	4636	4624	443
15°	4446	4399	4256	4175	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3477	3262	2889	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1931
65°	1460	1117	736	592	579	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	3	36	97	91	94	18
95°	144	172	177	177	172	161
105°	595	603	609	614	614	628
115°	1107	1123	1118	1115	1107	1095
125°	1610	1635	1627	1618	1615	1439
135°	2083	2113	2119	2116	2108	1610
145°	2528	2548	2564	2567	2556	1580
155°	2891	2899	2908	2922	2913	1331
165°	3145	3142	3142	3162	3148	887
175°	3273	3265	3259	3279	3262	311
180°	3279	3279	3279	3279	3279	

TEST NUMBER: P927189

CATALOG NUMBER: DFN2DIP-HX4F0-120D110US830-RLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4674.4	4674.4	4674.4	4674.4	4674.4
2.5°	4695.5	4674.4	4627.8	4670.4	4661.8
5°	4674.4	4653.3	4598.1	4636.3	4623.7
7.5°	4636.3	4611.1	4551.9	4568.5	4547.4
10°	4585.5	4556.0	4471.5	4458.5	4433.4
12.5°	4522.2	4484.1	4369.6	4344.5	4297.9
15°	4446.0	4399.3	4255.7	4175.3	4133.1
17.5°	4357.1	4289.3	4111.6	4018.7	3951.0
20°	4255.7	4170.8	3959.4	3854.0	3760.6
22.5°	4145.7	4048.3	3802.8	3659.2	3595.9
25°	4035.8	3900.2	3621.0	3447.8	3384.0
27.5°	3904.7	3760.6	3451.8	3253.0	3155.6
30°	3765.1	3604.0	3265.6	3050.1	2935.7
32.5°	3629.6	3434.8	3088.3	2834.3	2728.3
35°	3477.4	3261.5	2889.4	2622.9	2529.5
37.5°	3329.3	3096.4	2703.2	2411.0	2305.5
40°	3172.6	2919.1	2508.5	2208.2	2098.2
42.5°	3011.9	2741.4	2314.1	2000.8	1895.4
45°	2842.8	2559.2	2115.3	1814.6	1713.1
47.5°	2682.1	2381.9	1925.0	1624.3	1531.4
50°	2504.4	2204.1	1738.7	1446.5	1358.1
52.5°	2330.7	2013.4	1561.0	1281.8	1201.5
55°	2161.5	1831.7	1374.7	1121.1	1040.8
57.5°	1988.2	1649.8	1210.0	973.0	905.3
60°	1810.5	1472.1	1036.3	820.9	753.2
62.5°	1637.3	1298.9	888.2	685.4	651.6
65°	1459.6	1116.7	736.1	592.5	579.4
67.5°	1290.4	947.4	592.5	520.2	507.6
70°	1112.6	782.7	490.6	448.3	431.3
72.5°	943.4	630.2	410.2	376.5	368.0
75°	778.2	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	2.9	35.6	96.9	91.0	93.9
92.5°	61.3	83.0	86.0	89.0	89.0
95°	144.3	172.0	176.9	176.9	172.0
97.5°	240.2	265.9	276.8	276.8	276.8
100°	350.9	373.6	381.5	381.5	378.6
102.5°	467.6	484.4	495.3	498.2	495.3
105°	595.1	603.0	608.9	613.9	613.9
107.5°	721.6	733.5	733.5	735.4	721.6
110°	844.2	860.0	860.0	860.0	852.1

TEST NUMBER: P927189

CATALOG NUMBER: DFN2DIP-HX4F0-120D110US830-RLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	976.6	993.4	990.5	982.6	976.6
115°	1107.2	1122.9	1118.0	1115.1	1107.2
117.5°	1236.7	1258.3	1244.5	1236.7	1228.7
120°	1367.1	1388.9	1367.1	1367.1	1358.2
122.5°	1485.8	1513.4	1499.5	1491.6	1485.8
125°	1610.3	1635.0	1627.0	1618.2	1615.2
127.5°	1731.8	1762.5	1751.6	1739.8	1731.8
130°	1845.5	1881.1	1876.1	1870.2	1859.4
132.5°	1973.0	2000.7	2002.7	1988.9	1980.9
135°	2082.7	2113.4	2119.3	2116.4	2108.5
137.5°	2205.4	2230.0	2235.0	2233.0	2221.2
140°	2313.1	2337.8	2351.6	2351.6	2340.8
142.5°	2423.8	2448.5	2456.4	2459.4	2448.5
145°	2528.5	2548.3	2564.2	2567.1	2556.2
147.5°	2622.5	2647.2	2659.1	2664.0	2653.1
150°	2719.4	2736.2	2747.0	2756.0	2747.0
152.5°	2805.4	2822.1	2836.0	2846.9	2836.0
155°	2891.4	2899.2	2908.2	2922.0	2913.1
157.5°	2965.5	2971.4	2976.3	2996.1	2982.3
160°	3031.7	3037.7	3040.6	3057.5	3045.6
162.5°	3093.0	3093.0	3096.0	3114.8	3100.9
165°	3145.4	3142.4	3142.4	3162.2	3148.3
167.5°	3192.8	3184.0	3184.0	3203.7	3189.9
170°	3228.4	3220.5	3217.6	3237.3	3220.5
172.5°	3253.1	3245.2	3242.3	3262.1	3245.2
175°	3272.9	3265.0	3259.1	3278.9	3262.1
177.5°	3283.8	3275.8	3269.9	3286.8	3269.9
180°	3278.9	3278.9	3278.9	3278.9	3278.9

TEST NUMBER: P927189

CATALOG NUMBER: DFN2DIP-HX4F0-120D110US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.59	12.43	12.54	13.39	14.65	7.56	8.40	8.51	9.37	10.62
	3H	13.27	14.02	14.23	14.99	16.27	8.75	9.50	9.72	10.48	11.76
	4H	13.88	14.59	14.86	15.56	16.85	9.20	9.91	10.18	10.89	12.18
	6H	14.30	14.95	15.29	15.94	17.24	9.53	10.18	10.52	11.16	12.46
	8H	14.43	15.05	15.42	16.05	17.35	9.62	10.24	10.61	11.24	12.54
	12H	14.49	15.08	15.49	16.07	17.40	9.66	10.25	10.66	11.25	12.57
4H	2H	11.61	12.32	12.59	13.30	14.58	8.16	8.87	9.14	9.85	11.13
	3H	13.44	14.03	14.43	15.04	16.34	9.51	10.10	10.50	11.11	12.41
	4H	14.13	14.67	15.13	15.67	17.00	10.06	10.60	11.06	11.60	12.93
	6H	14.65	15.11	15.66	16.14	17.46	10.48	10.95	11.50	11.97	13.29
	8H	14.83	15.26	15.84	16.27	17.61	10.61	11.05	11.63	12.06	13.40
	12H	14.92	15.31	15.95	16.34	17.69	10.68	11.07	11.71	12.10	13.44
8H	4H	14.10	14.53	15.12	15.55	16.89	10.34	10.78	11.36	11.79	13.13
	6H	14.67	15.03	15.71	16.08	17.42	10.86	11.22	11.90	12.28	13.61
	8H	14.89	15.20	15.93	16.25	17.60	11.06	11.37	12.10	12.41	13.77
	12H	15.03	15.30	16.08	16.34	17.74	11.18	11.45	12.23	12.49	13.89
12H	4H	14.05	14.44	15.09	15.48	16.82	10.35	10.74	11.38	11.77	13.11
	6H	14.64	14.96	15.69	16.00	17.36	10.91	11.23	11.96	12.27	13.63
	8H	14.87	15.14	15.92	16.18	17.58	11.13	11.40	12.17	12.44	13.84