

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P928514

Luminaire Tested: DFN2DIP-HX4F0-040D090US930-RLLONL

Issue Date: 12/12/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P928514  
REPORT IS A COMBINATION OF REPORTS P900910 AND P896187  
Test Lab: INNOVATION CENTER  
Issue Date: 12/12/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-HX4F0-040D090US930-RLONL  
Description: 4 foot, Hexagon Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10032.7 lumens  
Efficiency: N/A  
Efficacy: 99.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.54' x L: 4.09' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 101.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9977  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P928514  
CATALOG NUMBER: DFN2DIP-HX4F0-040D090US930-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P928514

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US930-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	36	36	36	28
1	93	89	85	82	83	80	77	74	62	60	59	46	45	44	32	31	31	31	31	31	24
2	85	78	72	67	76	70	65	61	55	52	49	41	39	37	28	27	26	26	26	26	20
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	25	24	22	22	22	22	18
4	71	61	53	48	63	55	48	44	43	39	35	33	30	27	23	21	20	20	20	20	15
5	65	54	47	41	58	49	42	37	39	34	30	29	26	24	21	19	17	17	17	17	13
6	60	49	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15	15	15	15	12
7	55	44	36	31	49	40	33	28	32	27	23	24	21	18	17	15	14	14	14	14	11
8	51	40	32	27	46	36	30	25	29	24	21	22	19	16	16	14	12	12	12	12	10
9	48	36	29	24	43	33	27	22	26	22	19	20	17	15	15	13	11	11	11	11	9
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10	10	10	10	8

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1002	1002	1002
5°	1004	986	992
10°	994	967	960
15°	980	935	910
20°	962	891	849
25°	944	842	790
30°	919	791	715
35°	895	737	649
40°	870	681	573
45°	841	618	505
50°	811	555	438
55°	781	488	374
60°	744	417	308
65°	703	346	277
70°	653	279	251
75°	590	246	228
80°	499	206	198
85°	349	138	149

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 90°  
 Luminance: 1269 cd/sqm



TEST NUMBER: P928514

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US930-RLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.3	1.3
10°-20°	346.7	3.5
20°-30°	486.7	4.9
30°-40°	530.5	5.3
40°-50°	487.6	4.9
50°-60°	382.9	3.8
60°-70°	249.3	2.5
70°-80°	128.3	1.3
80°-90°	37.1	0.4
90°-100°	81.6	0.8
100°-110°	304.3	3.0
110°-120°	807.0	8.0
120°-130°	1338.5	13.3
130°-140°	1421.8	14.2
140°-150°	1321.4	13.2
150°-160°	1062.4	10.6
160°-170°	684.6	6.8
170°-180°	235.6	2.3
0°-30°	959.6	9.6
0°-40°	1490.1	14.9
0°-60°	2360.7	23.5
0°-90°	2775.4	27.7
90°-120°	1193.0	11.9
90°-150°	5274.7	52.6
90°-180°	7257.0	72.3
0°-180°	10032.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1347	1347	1347	1347	1347	
5°	1347	1341	1325	1336	1333	128
15°	1282	1268	1227	1204	1191	361
25°	1163	1124	1044	994	975	535
35°	1002	940	833	756	729	627
45°	819	738	610	523	494	633
55°	623	528	396	323	300	557
65°	421	322	212	171	167	417
75°	224	139	98	89	88	237
85°	52	27	23	23	23	60
90°	2	22	36	45	48	9
95°	116	57	70	79	77	138
105°	544	598	109	129	136	582
115°	1030	1060	1105	276	147	1014
125°	1456	1480	1514	1526	1532	1299
135°	1802	1831	1847	1865	1861	1392
145°	2090	2088	2119	2132	2123	1307
155°	2302	2286	2307	2318	2304	1061
165°	2425	2415	2420	2432	2420	685
175°	2481	2468	2472	2484	2466	236
180°	2476	2476	2476	2476	2476	



TEST NUMBER: P928514

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US930-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1347.4	1347.4	1347.4	1347.4	1347.4
2.5°	1353.5	1347.4	1333.9	1346.2	1343.7
5°	1347.4	1341.2	1325.4	1336.4	1332.8
7.5°	1336.4	1329.1	1312.1	1316.8	1310.8
10°	1321.8	1313.2	1288.8	1285.1	1277.9
12.5°	1303.5	1292.5	1259.5	1252.2	1238.8
15°	1281.5	1268.1	1226.7	1203.5	1191.4
17.5°	1255.9	1236.4	1185.1	1158.4	1138.8
20°	1226.7	1202.2	1141.2	1110.8	1083.9
22.5°	1195.0	1166.9	1096.1	1054.7	1036.5
25°	1163.2	1124.2	1043.7	993.8	975.4
27.5°	1125.5	1083.9	995.0	937.7	909.5
30°	1085.3	1038.8	941.2	879.1	846.2
32.5°	1046.2	990.1	890.1	817.0	786.4
35°	1002.4	940.1	832.8	756.0	729.1
37.5°	959.7	892.5	779.1	695.0	664.6
40°	914.5	841.4	723.1	636.5	604.8
42.5°	868.1	790.1	667.0	576.7	546.3
45°	819.4	737.7	609.7	523.1	493.8
47.5°	773.1	686.6	554.9	468.2	441.4
50°	721.8	635.3	501.1	417.0	391.4
52.5°	671.8	580.4	450.0	369.4	346.3
55°	623.1	528.0	396.3	323.1	300.0
57.5°	573.1	475.6	348.7	280.4	261.0
60°	521.8	424.3	298.7	236.6	217.1
62.5°	472.0	374.4	256.0	197.6	187.9
65°	420.7	321.8	212.1	170.7	167.0
67.5°	372.0	273.1	170.7	150.0	146.3
70°	320.7	225.6	141.4	129.3	124.3
72.5°	272.0	181.7	118.3	108.6	106.1
75°	224.3	139.0	97.6	89.0	87.9
77.5°	176.9	98.7	76.9	72.0	69.4
80°	132.8	70.7	58.4	53.7	53.7
82.5°	92.7	47.6	40.3	37.7	37.7
85°	52.4	26.8	23.1	23.1	23.1
87.5°	19.6	9.7	9.7	8.6	8.6
90°	1.7	21.5	35.7	44.9	48.2
92.5°	44.9	37.7	43.0	46.6	48.2
95°	116.4	57.2	69.8	78.9	77.0
97.5°	209.5	62.8	91.3	96.7	98.5
100°	317.1	71.7	102.1	116.4	120.0
102.5°	435.2	431.8	105.7	125.3	130.8
105°	544.5	598.4	109.3	128.9	136.1
107.5°	671.7	716.4	113.0	132.5	139.8
110°	793.6	831.1	313.5	134.4	141.5



TEST NUMBER: P928514

CATALOG NUMBER: DFN2DIP-HX4F0-040D090US930-RLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	908.2	940.3	909.9	137.8	143.4
115°	1029.9	1060.3	1105.2	275.9	146.9
117.5°	1135.6	1171.4	1202.0	945.7	476.4
120°	1253.9	1280.7	1313.0	1334.5	1092.7
122.5°	1354.1	1382.8	1418.8	1429.3	1431.3
125°	1456.2	1479.6	1513.6	1526.2	1531.5
127.5°	1549.3	1574.4	1601.5	1619.3	1621.0
130°	1637.2	1665.9	1685.5	1705.2	1703.6
132.5°	1726.7	1750.1	1769.7	1785.9	1784.2
135°	1802.0	1830.7	1846.7	1864.8	1861.2
137.5°	1880.8	1902.2	1920.3	1938.2	1932.9
140°	1957.7	1972.2	1991.8	2007.9	1999.0
142.5°	2022.4	2035.0	2058.1	2072.4	2063.5
145°	2090.5	2088.5	2119.0	2131.6	2122.6
147.5°	2149.4	2144.1	2174.5	2183.5	2176.4
150°	2206.9	2194.3	2223.0	2233.6	2224.7
152.5°	2255.1	2240.8	2267.7	2278.5	2265.9
155°	2301.7	2285.7	2307.2	2317.9	2303.6
157.5°	2339.4	2325.1	2341.3	2353.8	2339.4
160°	2371.6	2360.8	2371.6	2382.3	2369.8
162.5°	2400.2	2389.5	2398.5	2411.0	2394.9
165°	2425.3	2414.6	2420.0	2432.5	2420.0
167.5°	2445.1	2434.2	2439.7	2452.3	2436.1
170°	2461.2	2450.4	2454.0	2466.5	2450.4
172.5°	2471.9	2461.2	2464.8	2477.4	2461.2
175°	2480.8	2468.2	2471.9	2484.4	2466.5
177.5°	2484.4	2471.9	2473.8	2486.3	2470.2
180°	2475.5	2475.5	2475.5	2475.5	2475.5



TEST NUMBER: P928514  
 CATALOG NUMBER: DFN2DIP-HX4F0-040D090US930-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.59	5.27	5.72	6.39	7.95	0.56	1.24	1.70	2.36	3.92
	3H	6.26	6.86	7.40	7.99	9.57	1.74	2.35	2.88	3.48	5.05
	4H	6.86	7.43	8.01	8.56	10.14	2.19	2.76	3.34	3.89	5.47
	6H	7.27	7.80	8.43	8.93	10.53	2.50	3.03	3.66	4.16	5.75
	8H	7.40	7.90	8.56	9.05	10.63	2.59	3.09	3.75	4.24	5.82
	12H	7.45	7.93	8.62	9.07	10.68	2.63	3.10	3.79	4.24	5.85
4H	2H	4.59	5.16	5.75	6.29	7.87	1.14	1.71	2.30	2.84	4.42
	3H	6.41	6.88	7.57	8.04	9.63	2.48	2.96	3.64	4.11	5.70
	4H	7.09	7.53	8.26	8.68	10.29	3.02	3.46	4.19	4.61	6.22
	6H	7.60	7.98	8.77	9.14	10.75	3.43	3.81	4.60	4.98	6.58
	8H	7.77	8.12	8.94	9.28	10.90	3.56	3.91	4.73	5.07	6.69
	12H	7.86	8.18	9.05	9.35	10.97	3.62	3.94	4.80	5.11	6.73
8H	4H	7.05	7.40	8.22	8.56	10.18	3.29	3.64	4.46	4.80	6.42
	6H	7.61	7.90	8.80	9.10	10.72	3.81	4.10	4.99	5.30	6.91
	8H	7.83	8.08	9.02	9.26	10.89	4.00	4.25	5.19	5.43	7.06
	12H	7.96	8.18	9.16	9.36	11.03	4.11	4.33	5.31	5.51	7.18
12H	4H	7.00	7.31	8.18	8.48	10.11	3.29	3.61	4.47	4.78	6.40
	6H	7.59	7.84	8.78	9.02	10.65	3.86	4.11	5.05	5.29	6.92
	8H	7.80	8.02	9.00	9.20	10.87	4.06	4.28	5.26	5.46	7.13